


Item #	Description	1-9	10-24	25-99	100-249	250-499
RoHS Mounting Brackets for Antennas, Amplifiers and Surge Protectors						
L-com offers an extensive line of mounting bracket options for its antennas, amplifiers, and surge protectors. Options include wall mount, window mount, mast mount and more. Visit us online at L-com.com for complete bracket dimensions and specifications.						
HGX-LPMOUNT01	ALQ2-MNMF Surge Protector Mounting Bracket	4.99	4.49	3.99	3.49	2.99
HGX-PMT02	Indoor Antenna Mounting Kit, Small Metal Tilt & Swivel	9.99	8.99	7.99	6.99	5.99
HGX-PMT03	Indoor Antenna Mounting Kit, Medium Plastic Tilt & Swivel	11.99	10.79	9.59	8.39	7.19
HGX-PMT04	Large Metal Tilt & Swivel Mounting Bracket for Wall or Mast Mounting	19.99	17.99	15.99	13.99	11.99
HGX-PMT06	60° Tilt & Swivel Mounting Kit for Mounting to 1-1/4" (3.2cm) to 2" (5.1cm) Dia. Masts	9.49	8.54	7.59	6.64	5.69
HGX-PMT07	Stationary Mounting Kit for Mounting to 1-1/4" (3.2cm) to 2" (5.1cm) Dia. Masts	5.99	5.39	4.79	4.19	3.59
HGX-PMT08	Suction Cup Window Mounting Kit for Select HyperLink Antennas	9.99	8.99	7.99	6.99	CALL
HGX-PMT11	Heavy Duty Stationary Mast Mounting Kit for Mtg. to 1-1/4" (3.2cm) to 2" (5.1cm) Dia.	10.99	9.89	8.79	7.69	6.59
HGX-PMT14	Mast Mount Kit for Outdoor Filters/Splitters 1-1/4" (3.2cm) to 2" (5.1cm) Dia. Masts	12.99	11.69	10.39	9.09	CALL
HGX-PMT15	Indoor Antenna Mounting Kit- Compact Metal Tilt & Swivel	9.99	8.99	7.99	6.99	5.99
HGX-UMOUNT	Powder Coated Galvanized Steel "DSS-style" Arm-Outdoor Wall Mtg. 21 in.	14.99	14.39	13.79	12.74	11.24
HGX-UMOUNT-10PK	Powder Coated Galvanized Steel "DSS-style" Arm-Outdoor Wall Mtg. 10 Pack	119.99	115.19	110.39	101.99	89.99
HGX-UMOUNT01	Powder Coated Galvanized Steel "DSS-style" Arm-Outdoor Wall Mtg. 26.7 in.	15.99	15.35	14.71	13.59	11.99
HGX-UMOUNT01-10PK	Powder Coated Galvanized Steel "DSS-style" Arm-Outdoor Wall Mtg. 10 Pack	129.99	124.79	119.59	110.49	97.49
HGX-UMOUNT02	Ceiling/Wall Mount for 4.5" (11.4cm) sq. and 8.5" (21.6cm) sq. Patch Antennas	14.99	13.49	11.99	10.49	8.99
HGX-UMOUNT04	Universal Corner Mounting Bracket	24.99	22.49	19.99	17.49	CALL



Directional Antenna Application

The HG913Y-NF is being used in a waste water lift station application. Data is being sent wirelessly to a central control location where water levels and pressure can be monitored.

This particular installation has a series of sensors monitoring the key parameters of the location. The data is logged and formatted for transmission as packet data to the central control facility. The packet data is sent via a wireless link and in this case, a directional, high gain YAGI antenna pointed at the receiving antenna location. The central control station has the capability to send data to this remote installation to deliver commands, if needed, to properly operate the waste water lift station.

RoHS RET/AISG 8-Pin FS1 Type Male or Female Connectors

Remote Electrical Tilt (RET) antenna systems are designed so that wireless providers can make adjustments remotely to their antenna systems. The Antenna Interface Standards Group (AISG) has created specifications for the control interface for these types of systems. L-com now offers these FS1 type connectors for AISG applications as well as industrial control applications.

AISGM-2000	RET/AISG 8-Pin FS1 Type Connector, Male	12.95	12.43	11.91	11.40	10.88
AISGF-2000	RET/AISG 8-Pin FS1 Type Connector, Female	12.95	12.43	11.91	11.40	10.88



RoHS RET/AISG 6-Conductor Control Cable Assemblies

L-com's 6-Conductor Remote Electrical Tilt (RET) / AISG compatible control cable assemblies are terminated with Male and Female FS1 type DIN connectors. The connectors on these cable assemblies are interchangeable with Amphenol C 901 A/B/C and Binder 423 series connectors.

CA-AISG6MFM01	RET/AISG 6-Conductor Control Cable, Male/Female, 1.0m	56.20	54.51	52.83	51.14	49.46
CA-AISG6MFM02	RET/AISG 6-Conductor Control Cable, Male/Female, 2.0m	59.90	58.10	56.31	54.51	52.71
CA-AISG6MFM03	RET/AISG 6-Conductor Control Cable, Male/Female, 3.0m	63.60	61.69	59.78	57.88	55.97
CA-AISG6MFM04	RET/AISG 6-Conductor Control Cable, Male/Female, 4.0m	68.50	66.44	64.39	62.34	60.28
CA-AISG6MFM05	RET/AISG 6-Conductor Control Cable, Male/Female, 5.0m	72.10	69.94	67.77	65.61	63.45
CA-AISG6MFM06	RET/AISG 6-Conductor Control Cable, Male/Female, 6.0m	75.80	73.53	71.25	68.98	66.70
CA-AISG6MFM09	RET/AISG 6-Conductor Control Cable, Male/Female, 9.0m	88.20	85.55	82.91	80.26	77.62
CA-AISG6MFM10	RET/AISG 6-Conductor Control Cable, Male/Female, 10.0m	93.00	90.21	87.42	84.63	81.84
CA-AISG6MFM15	RET/AISG 6-Conductor Control Cable, Male/Female, 15.0m	111.40	108.06	104.72	101.37	98.03
CA-AISG6MFM20	RET/AISG 6-Conductor Control Cable, Male/Female, 20.0m	129.80	125.91	122.01	118.12	114.22
CA-AISG6MFM30	RET/AISG 6-Conductor Control Cable, Male/Female, 30.0m	167.90	162.86	157.83	152.79	147.75
CA-AISG6MFM40	RET/AISG 6-Conductor Control Cable, Male/Female, 40.0m	204.70	198.56	192.42	186.28	180.14
CA-AISG6MFM50	RET/AISG 6-Conductor Control Cable, Male/Female, 50.0m	242.70	235.42	228.14	220.86	213.58
CA-AISG6MFM60	RET/AISG 6-Conductor Control Cable, Male/Female, 60.0m	279.50	271.12	262.73	254.34	245.96

Item #	Description	List Price
--------	-------------	------------

RoHS 6-Conductor RET/AISG Control Cable, by the Meter or in 305 Meter Reel

L-com now offers 6-Conductor Remote Electrical Tilt (RET) control cable, in bulk or by-the-Meter.

CA-AISG6-METER	6-Conductor Control Cable, per Meter	3.95
CA-AISG6-R305M	6-Conductor Control Cable, 305 Meter Reel	934.99

Custom design and manufacturing capabilities

Our product design process takes you from concept to production. L-com.com/Custom

