

Item #	Description	List Price
--------	-------------	------------

EnGenius® Access Points/Routers/Bridges/Clients

L-com now offers a broad line of EnGenius® access points, routers and wireless bridges.

EnGenius® ECB Series Access Points

With the quality and functionality expected of an EnGenius® product, the ECB Series provides up to 400mW of high wireless output power and also adds advanced features such as SNMP management, Wireless Distribution System (WDS), and Power-over-Ethernet (PoE) capability.

EN-ECB-3500	EnGenius Multi Function 802.11b/g AP/Router/Bridge	109.00
EN-ECB-9500	EnGenius Multi Function 802.11n AP/Router/Bridge	109.00

EnGenius® EOC, EOA, EOR and EAG Series Outdoor Access Points

The EOC series brings superior range with its 400mW high wireless output power, and the flexibility you need for adaptable deployments such as industrial grade outdoor enclosures, antenna options, and 802.3af Power-over-Ethernet (PoE) certification.

EN-EOC-1650	EnGenius 802.11g Access Point/Client Bridge/Client Router	61.00
EN-EOA-3630	EnGenius 802.11b/g AP/CB/WDC. 600mW, 5dBi Antenna	149.99
EN-EOA-7530	EnGenius 802.11a/b/g Outdoor Dual Radio Access Point/Repeater Client Bridge	319.00
EN-EOC-2611P	EnGenius 802.11g Outdoor HP 600mW CB/AP Dual Antenna Polarity	87.00
EN-EOC-5611P	EnGenius 802.11a/g Outdoor HP 600mW CB/AP Dual Antenna Polarity	98.00
EN-EOC-MK	EnGenius Mounting Kit, EOC Radio Wall/Pole	39.00
EN-EOR-7550	EnGenius AP/CB/CR, 600/150MmW 6dBi Antenna	159.00

EnGenius® EAP, ERB, ESR, and ETR Series A/P Routers Indoor

This Series of A/P routers include "smoke detector" versions, mini routers and high power A/P routers. Some have integral antennas while others permit external and detachable antennas to be deployed for better coverage.

EN-EAP-3660	EnGenius 802.11b/g "Smoke Detector" Access Point	109.00
EN-EAP-9550	EnGenius Wireless N Router/Repeater "Smoke Detector"	109.00
EN-ERB-9250	EnGenius 802.11b/g/n Wireless N Range Extender-300Mbps	49.99
EN-ESR-1221-EXT	EnGenius 802.11g Mini Router	41.00
EN-ERS-7750	EnGenius 802.11a/b/g/n Dual Band Wireless N Router-300Mbps	159.99
EN-ERS-9752	EnGenius 802.11b/g/n Wireless N Router with Detachable Antenna-300Mbps	49.99
EN-ERS-9850	EnGenius 802.11b/g/n Wireless N Router with 4-Port Gigabit Switch-300Mbps	69.99
EN-ERS-9855G	EnGenius 802.11b/g/n Wireless N Gaming Router with Dual Antenna 4-Port Gigabit Switch	99.99
EN-ERT-9330	EnGenius Wireless N Travel Router-300Mbps	49.99

EnGenius® EUB Series 802.11b/g High Power USB Adapter


The EnGenius® EUB series USB WLAN adapters are designed for users who require maximum range and performance in their wireless networks. The EUB series offers a rich feature set including security features such as WPA and 802.1x.

EN-EUB-9603EXT	EnGenius 802.11b/g/n High Power USB Adapter with External Antenna	29.99
EN-EUB-9603H	EnGenius 802.11b/g/n High Power USB Adapter	44.99
EN-EUB-9706	EnGenius 802.11b/g/n Wireless N USB Adapter-300Mbps	29.99
EN-EUB-9707	EnGenius 802.11b/g/n High Power Dongle USB Adapter	24.99
EN-EUB-9801	EnGenius 802.11b/g/n Wireless N USB Dual Band Adapter-300Mbps	39.99

EnGenius® 802.11a/b/g Mini PCI Type III RF Module

These are EnGenius® high powered embedded radios. They come in various styles, all adaptable to integrated applications. The power output of the transmitter assures strong performance when coupled to PoE power and HyperLink™ antennas.

EN-EMP-3602	EnGenius 802.11g HP 250mW Atheros Mini-PCI IIIB	29.00
EN-EMP-8603	EnGenius 802.11a/b/g Mini PCI Type IIIA RF Module	76.00
EN-EPI-3601-S	EnGenius 802.11b/g HP 600mW PCI Adapter with External Antenna-SuperG 108Mbps	25.00



Detail view of the EN-EAP-3660

RJ45 Port with (802.3af PoE)

DC Power - In

Aesthetic "Smoke Detector" Design

- Minimal footprint and no protruding antennas
- Designed to blend in to various business environments
- Unobtrusive design prevents tampering to protect your investment

High 600mW Wireless Power

- Ensures robust signal to overcome long distances
- Offers superior WiFi coverage than leading brands

Multiple Wireless Names

- Broadcast multiple WiFi networks with one device
- Permits different levels of network access (VLAN Tagging)

Power-over-Ethernet (802.3af Compliant)

- Power and data over one cable to ease deployment

ALCON® 802.11a/b/g/n and Super G Wireless Access Points and MESH Radios

The ALCON® 802.11 Access Point and MESH Radios provide the user and installer with a number of very versatile and powerful radios for installations where performance, range and coverage are challenging. These radios provide coverage for 2.4 GHz and 5.8 GHz frequency ranges in IEEE 802.11a/b/g/n and Super G, as specified by each radio. The power of each radio, when teamed with the correct antennas, provide extend range and wide area coverage. The ALCON® radios below are an excellent selection option for commercial and industrial applications and installation.

ALR-ASU-24005G-N	WiFi AP/Bridge/Repeater 150mW, 801.11b/g	359.00
ALR-ASU-5000-N	WiFi AP/Bridge/Repeater 100mW, 802.11a	575.00
ALR-APRO-2408G-N	WiFi AP/Bridge/Repeater 800mW, 801.11b/g	975.00
ALR-APE-2408G-N	WiFi AP/Bridge/Repeater 800mW, 802.11b/g	875.00
ALR-AMESH-100	WiFi MESH Network 100mW	425.00
ALR-AMESH-500	WiFi MESH Network 500mW	625.00



Same day shipping

Orders placed before 4:00 EST ship the same day.

