

Item #	Pwr. Rating	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-------------	-----	-------	-------	---------	---------

✓RoHS Load Cell/RTD/Strain Gauge Sensor Protectors

The AL-LC series lightning and surge protectors that provide superior protection for devices such as load cells, weighbridges, resistance temperature detectors (RTD) and strain gauge sensors.

AL-LC-30	*****	Weatherproof 3-Stage Load Cell/RTD Lightning Surge Protector	59.99	57.59	55.19	52.79	50.39
AL-LC	*****	Weatherproof Single Stage Load Cell/RTD Lightning Surge Protector	39.99	38.79	37.59	36.39	35.19

✓RoHS Audio System Protectors

L-com's HyperLink™ outdoor speaker and public address system lightning protectors offer protection of valuable PA equipment at an affordable price.

AL-D2-AW	*****	Weatherproof, 4/8 Ohm Audio Systems, Screw Terminal	49.99	48.49	46.99	45.49	CALL
AL-D2-PAW	*****	Weatherproof, 70.7/100V Public Address Systems, Screw Terminals	49.99	48.49	46.99	45.49	CALL

✓RoHS Coaxial Video Protectors

L-com's HyperLink™ Coaxial Video protectors are ideal for protecting surveillance and CCTV cameras, DVRs, surveillance PCs and video monitors

HGLN-VIDEO-1	****	Indoor, 1-Port Video, BNC Connectors	37.99	34.19	30.39	26.59	22.79
HGLN-VIDEO-1I	****	Indoor, 1-Port Video, Isolated BNC Connectors	37.99	34.19	30.39	26.59	22.79
C MSP-VIDEO-4	****	Indoor, 4-Port Video, BNC Connectors	59.99	55.19	50.39	45.59	CALL
C MSP-VIDEO-4I	****	Indoor, 4-Port Video, Isolated BNC Connectors	59.99	55.19	50.39	45.59	CALL
R MSP-VIDEO-4	****	19in (48.3cm) Rack Panel, 4-Port Video, BNC Connectors	69.99	64.39	58.79	53.19	CALL
R MSP-VIDEO-4I	****	19in (48.3cm) Rack Panel, 4-Port Video, Isolated BNC Connectors	69.99	64.39	58.79	53.19	CALL

The lightning bolts next to the part numbers indicate Power Rating. * = Low Power to ***** = High Power

Tripp-Lite In-Line Surge Suppressors

Tripp-Lite's In-Line data and telephone surge suppressors help protect valuable equipment from electrical surge. These low cost suppressors easily connect in-line with existing data and telephone connections.

TL-DNET1	Network Surge Suppressor, RJ45 Jacks	20.95	20.11	19.27	18.44	CALL
TL-DTEL2	2-Line Telephone Suppressor, RJ11/45 Jacks	22.95	22.03	21.11	20.20	CALL

✓RoHS USB Panel Mountable Surge Protector

The L-com AL-ECF504-AB USB surge protector is a commercial quality device designed to protect a computer's sensitive USB ports from surges and spikes from attached devices. This surge protector is ideal for protecting a PC from WiFi client adapters and surveillance cameras used with long USB extender cables.

AL-ECF504-AB	USB Panel Mountable Surge Protector, Type A / Type B	15.95	14.99	14.04	13.08	12.12
--------------	--	-------	-------	-------	-------	-------

HyperLink™ Coaxial Lightning and Surge Protectors

L-com's HyperLink™ coaxial lightning and surge protectors feature replaceable gas tubes (except for 1/4 wave model), multi-strike capability and bi-directional protection.

✓RoHS 0-3 GHz Coaxial Protectors

AL-NFNFB-9	Type N Female to Type N Female Bulkhead, 90V	18.99	17.09	15.19	13.29	11.39
AL-NFNFBHP-9	Type N Female to Type N Female Bulkhead, Indoor, High Power, 90V	24.99	23.99	22.99	21.24	18.74
AL-NMNF-9	Type N Male to Type N Female Bulkhead, 90V	18.99	17.09	15.19	13.29	11.39
AL-BMBFB-9	BNC Male to BNC Female Bulkhead, 90V	14.99	14.39	13.79	12.74	11.24
AL-TMTFB-9	TNC Male to TNC Female Bulkhead, 90V	23.99	23.03	22.07	20.39	17.99
AL-UUFUB-6	UHF Female to UHF Female Bulkhead, 600V	14.99	14.39	13.79	12.74	11.24
AL-RBPRBJB-9	RP-BNC Plug to RP-BNC Jack Bulkhead, 90V	14.99	14.39	13.79	12.74	11.24
AL-RTPRJB-9	RP-TNC Plug to RP-TNC Jack Bulkhead, 90V	23.99	23.03	22.07	20.39	17.99
AL-FFFF-9	Type F Female to Type F Female, 90V	23.99	21.59	19.19	16.79	14.39
AL-F	Type F Male to Type F Female, 50V	7.49	6.89	6.29	5.69	5.09

✓RoHS 0-6 GHz Coaxial Protectors

AL6-NFNFBW-9	Type N Female to Type N Female Bulkhead, 90V	34.00	30.60	27.20	23.80	20.40
AL6-NMNFBW-9	Type N Male to Type N Female Bulkhead, 90V	34.00	30.60	27.20	23.80	20.40
AL6-RSPRSJBW-9	RP-SMA Plug to RP-SMA Jack Bulkhead, 90V	29.99	26.99	23.99	20.99	17.99

✓RoHS 2.4 GHz Quarter Wave Coaxial Protectors

ALQ2-NMNF	Type N Male to Type N Female Bulkhead, 1/4 Wave	34.99	33.59	32.19	29.74	26.24
-----------	---	-------	-------	-------	-------	-------

✓RoHS Replacement Gas Tubes

LPX090G	0-6 GHz, 90V, Replacement Gas Tube	9.99	8.99	7.99	6.99	5.99
LPX090-6	0-6 GHz, 90V, Replacement Gas Tube For AL-NMNFBW-9	5.99	5.39	4.79	4.19	3.59
LPX090	0-3 GHz, 90V, Replacement Gas Tube	4.99	4.49	3.99	3.49	2.99
LPX230	0-3 GHz, 230V, Replacement Gas Tube	4.99	4.49	3.99	3.49	2.99
LPX350	0-3 GHz, 350V, Replacement Gas Tube	4.99	4.49	3.99	3.49	2.99
LPX600	0-3 GHz, 600V, Replacement Gas Tube	4.99	4.49	3.99	3.49	2.99




✓RoHS Accessories

HGX-LPMOUNT01	ALQ2 Mounting Bracket	4.99	4.49	3.99	3.49	2.99
---------------	-----------------------	------	------	------	------	------

✓RoHS Grounding Kits and Clamps

L-com's grounding kits are designed to withstand the damaging effects of lightning currents in excess of 200kA and comply with MIL-STD-188-124A. These grounding kits support LMR400, LMR600 and LMR900 series coaxial cable. Our grounding clamp fits around existing conduit pipe or water pipe for a secure ground.

HT-GK400	Grounding Kit for LMR400 Series Cable	17.99	17.27	16.55	15.29	13.49
HT-GK600	Grounding Kit for LMR600 Series Cable	17.99	17.27	16.55	15.29	13.49
HT-GK900	Grounding Kit for LMR900 Series Cable	17.99	17.27	16.55	15.29	13.49
HT-GCLAMP01	Grounding Pipe Clamp	0.99	0.94	0.89	0.84	CALL



More information on Protectors

May be found at L-com.com/Protectors