




PS4820GB-POE


Best Seller



BT-CAT5-P1



BT-CAT5E-P1-HP



BT-CAT5E-P1-HPW



BT-CAT5-P4J



TRD855SCR-series



PS1240-21R



PS-LIGHTER-06

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

Power-over-Ethernet (PoE) 48 VDC Midspan/Injectors

L-com offers a wide range of PoE Midspan/Injector styles including reverse polarity and 48 VDC models. These PoE midspan/injectors can be used to connect PoE compliant devices such as access points, IP phones or wireless routers and supply data as well as power over a single CAT5 cable. Power-over-Ethernet eliminates the need for an AC outlet at each end device location. Only a single Ethernet cable is run to each device such as an access point instead of separate power and data cables.


RoHS All-In-One Midspan/Injector and Power Supply

PS4820-POE-1	48 VDC, 20W, Dual RJ45	23.25	21.86	20.46	19.07	17.67
PS4820GB-POE	48 VDC, 19W, Gigabit, Dual RJ45, Requires PSCORD3	24.99	23.99	22.99	21.99	CALL
PS4860-POE	48 VDC, 60W, Dual RJ45, Requires PSCORD3	74.99	71.99	68.99	63.74	56.24

RoHS CAT5 Midspan/Injectors

BT-CAT5-P1	5-48 VDC, 1 Port	22.95	21.11	19.28	17.44	15.61
BT-CAT5-P1-4848	48 VDC, 1 Port, Includes 48VDC/48W Supply	49.99	45.99	41.99	37.99	33.99
BT-CAT5-P1R	5-48 VDC, 1 Port, Reverse Polarity	29.99	27.59	25.19	22.79	20.39
BT-CAT5-P1R4848	48 VDC, 1 Port, Reverse Polarity, Includes 48VDC/48W Supply	49.99	45.99	41.99	37.99	33.99

BT-CAT5-P1 Power over Ethernet Injector Application



RoHS CAT5E Midspan/Injectors

BT-CAT5E-P1-HP	5-48 VDC, 1 Port, High Power CAT5E	44.99	41.39	37.79	34.19	30.59
BT-CAT5E-P1-HP-4848	48 VDC, 1 Port, High Power CAT5E w/48VDC/48W Supply	59.99	55.19	50.39	45.59	40.79
BT-CAT5E-P1-HP-4870	48 VDC, 1 Port, High Power CAT5E w/48VDC/70W Supply	79.99	73.59	67.19	60.79	54.39
BT-CAT5E-P1-HPW	5-48 VDC, 1 Port, High Power CAT5E Weather Resistant	44.99	41.39	37.79	34.19	30.59
BT-CAT5E-P1-HPW-4848	48 VDC, 1 Port, High Power CAT5E Weather Resistant, w/48VDC/48W Supply	59.99	55.19	50.39	45.59	40.79
BT-CAT5E-P1-HPW-4870	48 VDC, 1 Port, High Power CAT5E Weather Resistant, w/48VDC/70W Supply	79.99	73.59	67.19	60.79	54.39

RoHS CAT5 Four Port Midspan/Injectors

BT-CAT5-P4	5-48 VDC, 4 Port	49.99	45.99	41.99	37.99	33.99
BT-CAT5-P4-4848	48 VDC, 4 Port, Includes 48VDC/48W Supply	59.99	55.19	50.39	45.59	40.79
BT-CAT5-P4-4870	48 VDC, 4 Port, Includes 48VDC/70W Supply	84.99	78.19	71.39	64.59	57.79
BT-CAT5-P4J	5-48 VDC, 4 Port, CAT5 Surge Protection	54.99	50.59	46.19	41.79	37.39
BT-CAT5-P4J-4848	48 VDC, 4 Port, CAT5 Surge Protection, Includes 48VDC/48W Supply	64.99	59.79	54.59	49.39	44.19
BT-CAT5-P4J-4870	48 VDC, 4 Port, CAT5 Surge Protection, Includes 48VDC/70W Supply	89.99	82.79	75.59	68.39	61.19

RoHS Accessories

TRD855SCR-1	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 1.0ft (0.3m)	7.45	7.30	7.00	6.56	5.59
TRD855SCR-2	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 2.0ft (0.6m)	7.95	7.79	7.47	7.00	5.96
TRD855SCR-3	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 3.0ft (0.9m)	8.45	8.28	7.94	7.44	6.34
TRD855SCR-5	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 5.0ft (1.5m)	9.45	9.26	8.88	8.32	7.09
TRD855SCR-7	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 7.0ft (2.1m)	10.45	10.24	9.82	9.20	7.84
TRD855SCR-10	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 10.0ft (3.0m)	11.95	11.71	11.23	10.52	8.96
TRD855SCR-15	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 15.0ft (4.6m)	14.45	14.16	13.58	12.72	10.84
TRD855SCR-20	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 20.0ft (6.1m)	16.95	16.61	15.93	14.92	12.71
TRD855SCR-25	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 25.0ft (7.6m)	19.45	19.06	18.28	17.12	14.59
TRD855SCR-30	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 30.0ft (9.1m)	21.95	21.51	20.63	19.32	16.46
TRD855SCR-40	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 40.0ft (12.2m)	26.95	26.41	25.33	23.72	20.21
TRD855SCR-50	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 50.0ft (15.2m)	31.95	31.31	30.03	28.12	23.96
TRD855SCR-75	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 75.0ft (22.9m)	44.45	43.56	41.78	39.12	33.34
TRD855SCR-100	Shielded CAT5E EIA568 Patch Cord, RJ45 / RJ45, 100.0ft (30.4m)	56.95	55.81	53.53	50.12	42.71
CA-POE-02	CAT5 PoE Conversion Cable for Cisco APs, 2.0ft (0.6m)	14.99	13.49	11.99	10.49	8.99

RoHS Switching Power Supplies

PS909-21R	9 VDC @ 1A (9W), 2.1mm DC Plug	9.99	9.59	9.19	8.49	7.49
PS1212-21R	12 VDC @ 1A (12W), 2.1mm Right Angle DC Plug	12.99	12.47	11.95	11.04	9.74
PS1224-21R	12 VDC @ 2A (24W), 2.1mm Right Angle DC Plug	14.99	14.39	13.79	12.74	11.24
PS1240-21R	12 VDC @ 3.33A (40W), 2.1mm Right Angle DC Plug	21.99	21.11	20.23	18.69	16.49
PS1566	15 VDC @ 4.4A (66W), 2.1mm DC Plug	89.99	86.39	82.79	76.49	67.49
PS4870-25R	48 VDC @ 1.5A (70W), 2.5mm Right Angle DC Plug	59.00	56.64	54.28	50.15	44.25
PS4848-25R	48 VDC @ 1A (48W) 2.5mm Right Angle DC Plug	24.95	24.45	23.95	23.45	22.95

12 VDC to 48 VDC Converter/Regulator

PS-LIGHTER-06	Cigarette Plug to 2.1mm Right Angle DC Plug, 3A Fuse, 6ft	9.99	9.59	9.19	8.49	7.49
---------------	---	------	------	------	------	------

RoHS Accessories

PSX-EU1	US Flat or Euro Round to Euro 4.8mm Round A/C Adapter	3.99	3.59	3.19	2.79	2.39
PSX-EU2	EU 4/4.8mm Round to US NEMA 6-15R Flat A/C Adapter	3.99	3.59	3.19	2.79	2.39
PSCORD2	2 Conductor Plug, USA/AC Power Cord, 1.0ft (0.3m)	3.99	3.59	3.19	2.79	2.39
PSCORD3	3 Conductor Plug, USA/AC Power Cord, 1.0ft (0.3m)	2.99	2.75	2.51	2.27	2.03

