



**RoHS Premium Category 5E RJ45 Molded Ethernet Patch Cords**

Designed for today's high-density patch panels, these unique Category 5E molded patch cords feature an easy to depress "shark fin" snagless molded boot that makes connecting cables easier. The clear boot also allows the color of each cable to be easily seen on each port for easy cable identification. Each cable is tested for Category 5E performance to ensure maximum network throughput.



**BL BLK GR R Y GRY WHT OR V**


Ordering is easy, add the desired color code to the part number. Ex: TRD815BL-3

Item #	Description	Length	1-9	10-24	25-99	100-249	250-499
TRD815 __-3	Category 5E Patch Cord, RJ45 / RJ45	3.0ft (0.9m)	3.99	3.59	3.19	2.79	2.39
TRD815 __-5	Category 5E Patch Cord, RJ45 / RJ45	5.0ft (1.5m)	4.99	4.49	3.99	3.49	2.99
TRD815 __-7	Category 5E Patch Cord, RJ45 / RJ45	7.0ft (2.1m)	5.99	5.39	4.79	4.19	3.59
TRD815 __-10	Category 5E Patch Cord, RJ45 / RJ45	10.0ft (3.0m)	6.99	6.29	5.59	4.89	4.19
TRD815 __-14	Category 5E Patch Cord, RJ45 / RJ45	14.0ft (4.3m)	8.99	8.09	7.19	6.29	5.39
TRD815 __-25	Category 5E Patch Cord, RJ45 / RJ45	25.0ft (7.6m)	13.99	12.59	11.19	9.79	8.39
TRD815 __-50	Category 5E Patch Cord, RJ45 / RJ45	50.0ft (15.2m)	24.99	22.49	19.99	17.49	14.99
TRD815 __-75	Category 5E Patch Cord, RJ45 / RJ45	75.0ft (22.9m)	35.99	32.39	28.79	25.19	21.59
TRD815 __-100	Category 5E Patch Cord, RJ45 / RJ45	100.0ft (30.4m)	46.99	42.29	37.59	32.89	28.19

**RoHS Premium Category 5E RJ45 Molded Crossover Ethernet Patch Cords**

Also designed for today's high-density patch panels, these unique Category 5E molded patch cords feature an easy to depress "shark fin" snagless molded boot that makes connecting cables effortless. The clear boot also allows the color of each cable to be easily seen up to each port

for easy cable identification. Each cable is crossover wired (EIA568A/B) for usage as either uplink connections or for direct connecting of two computers. Contact us today for all your patch cord needs.





Ordering is easy, add the desired color code to the part number

Item #	Description	Length	3-9	10-24	25-99	100-249	250-499
TRD815CR __-3	10/100Base-T Crossover Patch Cord, RJ45 / RJ45	3.0ft (0.9m)	3.99	3.67	3.35	3.03	2.71
TRD815CR __-7	10/100Base-T Crossover Patch Cord, RJ45 / RJ45	7.0ft (2.1m)	5.99	5.51	5.03	4.55	4.07
TRD815CR __-10	10/100Base-T Crossover Patch Cord, RJ45 / RJ45	10.0ft (3.0m)	6.99	6.43	5.87	5.31	4.75
TRD815CR __-15	10/100Base-T Crossover Patch Cord, RJ45 / RJ45	15.0ft (4.6m)	8.99	8.27	7.55	6.83	6.11

**RoHS Premium Category 6 RJ45 Hi-Speed Network Patch Cords**

Competitive pricing and high quality is what makes L-com's Category 6 patch cords the right choice. Made with high performance 4-pair Category 6 cable and snagless plugs, these cables are ready to be installed in your network. Affordability and peace of mind are assured when choosing

L-com's patch cords. Large volume OEM requests are welcomed with this series. Contact us today for all your patch cord needs.



Ordering is easy, add the desired color code to the part number

Item #	Description	Length	3-9	10-24	25-99	100-249	250-499
TRD695 __-1	Category 6 Patch Cord, RJ45 / RJ45	1.0ft (0.3m)	5.99	5.87	5.63	5.27	4.49
TRD695 __-3	Category 6 Patch Cord, RJ45 / RJ45	3.0ft (0.9m)	6.99	6.85	6.57	6.15	5.24
TRD695 __-5	Category 6 Patch Cord, RJ45 / RJ45	5.0ft (1.5m)	7.99	7.83	7.51	7.03	5.99
TRD695 __-7	Category 6 Patch Cord, RJ45 / RJ45	7.0ft (2.1m)	8.99	8.81	8.45	7.91	6.74
TRD695 __-10	Category 6 Patch Cord, RJ45 / RJ45	10.0ft (3.0m)	10.99	10.77	10.33	9.67	8.24
TRD695 __-14	Category 6 Patch Cord, RJ45 / RJ45	14.0ft (4.3m)	12.99	12.73	12.21	11.43	9.74
TRD695 __-25	Category 6 Patch Cord, RJ45 / RJ45	25.0ft (7.6m)	17.99	17.63	16.91	15.83	13.49
TRD695 __-50	Category 6 Patch Cord, RJ45 / RJ45	50.0ft (15.2m)	29.99	29.39	28.19	26.39	22.49
TRD695 __-75	Category 6 Patch Cord, RJ45 / RJ45	75.0ft (22.9m)	41.99	41.15	39.47	36.95	31.49
TRD695 __-100	Category 6 Patch Cord, RJ45 / RJ45	100.0ft (30.4m)	53.99	52.91	50.75	47.51	40.49