

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

M12 D-Coded 4 Position and 5 Position Panel, PCB and Solder Style Connectors

L-com offers a complete line of D-Coded 4 and 5 Position M12 connectors for enclosure, panel and PCB applications. These quality constructed connectors provide years of trouble free use in the most trying applications. These M12 connectors are offered in both male and female versions and are rated to IP68.

✓RoHS M12 D-Coded Panel Mount Connectors

CON-M124PM	M12 4 Position Male Panel Mount Connector	7.50	7.35	7.20	7.05	6.90
CON-M125PM	M12 5 Position Male Panel Mount Connector	7.95	7.79	7.63	7.47	7.31
CON-M124PF	M12 4 Position Female Panel Mount Connector	8.25	8.08	7.92	7.75	7.59
CON-M125PF	M12 5 Position Female Panel Mount Connector	8.95	8.77	8.59	8.41	8.23

✓RoHS M12 D-Coded PCB Mount Connectors

CON-M124PCBM	M12 4 Position Male PCB Mount Connector	6.95	6.81	6.67	6.53	6.39
CON-M125PCBM	M12 5 Position Male PCB Mount Connector	7.25	7.10	6.96	6.81	6.67
CON-M124PCBF	M12 4 Position Female PCB Mount Connector	9.95	9.75	9.55	9.35	9.15
CON-M125PCBF	M12 5 Position Female PCB Mount Connector	10.95	10.73	10.51	10.29	10.07

✓RoHS M12 D-Coded Solder Style Connectors

CON-M124SLDM	M12 4 Position Male Solder Style Connector	7.95	7.79	7.63	7.47	7.31
CON-M125SLDM	M12 5 Position Male Solder Style Connector	8.50	8.33	8.16	7.99	7.82
CON-M124SLDF	M12 4 Position Female Solder Style Connector	9.95	9.75	9.55	9.35	9.15
CON-M125SLDF	M12 5 Position Female Solder Style Connector	10.25	10.04	9.84	9.63	9.43

✓RoHS M12 D-Coded 4 Position and 5 Position Adapters

L-com stocks a multitude of M12 D-Coded adapters including T style, I style and Y style M12 4 Position and 5 Position adapters. These rugged adapters are designed for use in harsh environments requiring temperature ranges from -25°C to 90°C.

✓RoHS M12 D-Coded 3 Way T Style Adapters

ADPT-M124MT	M12 4 Position 3 Way Male T Adapter	16.95	16.61	16.27	15.93	15.59
ADPT-M125MT	M12 5 Position 3 Way Male T Adapter	18.25	17.88	17.52	17.15	16.79
ADPT-M124FT	M12 4 Position 3 Way Female T Adapter	19.95	19.55	19.15	18.75	18.35
ADPT-M125FT	M12 5 Position 3 Way Female T Adapter	22.25	21.80	21.36	20.91	20.47

✓RoHS M12 D-Coded 2 Way I Style Adapters

ADPT-M124MI	M12 4 Position Inline Male I Adapter	10.59	10.38	10.17	9.95	9.74
ADPT-M125MI	M12 5 Position Inline Male I Adapter	11.59	11.36	11.13	10.89	10.66
ADPT-M124FI	M12 4 Position Inline Female I Adapter	12.95	12.69	12.43	12.17	11.91
ADPT-M125FI	M12 5 Position Inline Female I Adapter	14.50	14.21	13.92	13.63	13.34

✓RoHS M12 D-Coded 3 Way Y Style Adapters

ADPT-M124MY	M12 4 Position 3 Way Male Y Adapter	14.00	13.72	13.44	13.16	12.88
ADPT-M125MY	M12 5 Position 3 Way Male Y Adapter	16.95	16.61	16.27	15.93	15.59
ADPT-M124FY	M12 4 Position 3 Way Female Y Adapter	17.95	17.59	17.23	16.87	16.51
ADPT-M125FY	M12 5 Position 3 Way Female Y Adapter	19.95	19.55	19.15	18.75	18.35

Item #	Description	List Price
--------	-------------	------------

Hirschmann Field Attachable IP67 M12 Connector

This robust field attachable Industrial Ethernet M12 connector from Hirschmann is perfect for repair or installation of new and existing industrial cable plants. This connector is "D"-coded according to IEC 61076-2-101 4 and supports both 10Base-T and 100Base-T Ethernet applications. The EM12S Octopus is IP67 rated and features 4 contacts and IDC style termination.

EM12S OCTOPUS	Hirschmann Field Attachable IP67 M12 Connector	30.00
---------------	------------------------------------------------	-------

Hirschmann Bulkhead M12 to RJ45 IP67/65 Connector

This versatile IP67/65 adapter from Hirschmann provides a bulkhead style M12 connector on one and a shielded RJ45 jack on the other to address specific Industrial Ethernet applications. The M12 connector is "D"-coded according to IEC 61076-2-101 and supports both 10Base-T and 100Base-T Ethernet applications.

EF12RJ45 OCTOPUS	Hirschmann Bulkhead M12 to RJ45 IP67/65 Connector	78.00
------------------	---------------------------------------------------	-------

M12 Adapter Configuration Options



T Style



I Style



Y Style




CON-M125PF
Front View

CON-M125PF
Back View



CON-M124PCBF
Front View

CON-M124PCBF
Back View



CON-M124SLDF
Front View

CON-M124SLDF
Back View



ADPT-M125MT



ADPT-M124MI



ADPT-M124MY



Front View

Back View

EM12S OCTOPUS



EF12RJ45 OCTOPUS



To see our entire product offering
go to... L-com.com