



Item #	Description	1-9	10-24	25-99	100-249	250-499
<b>✓RoHS</b>	<b>Ruggedized IP67 Rated RJ45 Ethernet Plug Kit</b>					
WT6788D	Non-Shielded Dome Style	19.95	19.15	18.35	17.56	16.76
WT6788F	Non-Shielded Flex Style	19.95	19.15	18.35	17.56	16.76
WT6788DS	Shielded Dome Style	22.95	22.03	21.11	20.20	19.28
WT6788FS	Shielded Flex Style	22.95	22.03	21.11	20.20	19.28
TSP4088C5	Replacement RJ45 Non-Shielded Plugs, Pkg/50	29.95	27.55	25.16	22.76	CALL
TSP4088C5S	Replacement RJ45 Shielded Plugs, Pkg/50	49.95	45.95	41.96	37.96	CALL

**Tip** *Easily attach a field installable plug*

**STEP 1**

**STEP 1:** Slide compression nut, coupling and plug housing onto cable.

**STEP 2**

**STEP 2:** Strip and prepare conductors for crimping. Trim to .56" (1.4cm).

**STEP 3**

**STEP 3:** Install plug and crimp.

**STEP 4**

**STEP 4:** Slide crimped connector into place and tighten compression nut.

<b>✓RoHS</b>	<b>Ruggedized IP67 Rated Keystone Flange Adapter Kits</b>					
Pass your Ethernet connections through a panel while still maintaining an IP67 rated seal. These receptacle kits consist of an IP67 rated flange adapter and industry standard keystone jacks and couplers. Don't see the combination you need? Call today and we'll help you find the right connection system for your application.						
WT6700FM	Front Mount Empty	17.95	17.23	16.51	15.80	15.08
WT6700RM	Rear Mount Empty	17.95	17.23	16.51	15.80	15.08
WT67KC5FM	Front Mount C5E Coupler	24.95	23.95	22.95	21.96	20.96
WT67KC5RM	Rear Mount C5E Coupler	24.95	23.95	22.95	21.96	20.96
WT671105FM	Front Mount C5E IDC 110 Jack	19.95	19.15	18.35	17.56	16.76
WT671105RM	Rear Mount C5E IDC 110 Jack	19.95	19.15	18.35	17.56	16.76

<b>✓RoHS</b>	<b>Protective Covers for WT67 Series Plugs and Jacks</b>					
Maintain the IP67 rating for all open plugs and jacks with these covers. These caps are specifically designed to fit the WT67 series jacks and plugs. When a cable is connected, just attach a cap over the expose connection and the seal is maintained.						
WT67RC	IP67 Jack Cover for Female Receptacles	5.95	5.71	5.47	5.24	5.00
WT67RCT	IP67 Jack Cover for Female Receptacles with Tether	12.95	12.69	12.43	12.17	11.91
WT67PC	IP67 Jack Cover for Male Plug Kits	6.95	6.67	6.39	6.12	5.84
WT67PCT	IP67 Jack Cover for Male Plug Kits with Tether	12.95	12.69	12.43	12.17	11.91

<b>✓RoHS</b>	<b>Category 5E Outdoor Cables with Weather Tight Grommet</b>					
Protect Ethernet cable runs outside with L-com's Outdoor Category 5E rated cable. The Gel-filled jacket provides moisture protection when used in an outdoor environment. The built in feed-thru grommet allows the cable to pass through an enclosure while maintaining a watertight seal. With the UV protected jacket, outdoor cable runs are protected from damage caused by sunlight exposure. The cable is EIA568 color-coded for compatibility with standard installations and features solid conductors for termination into standard IDC connectors.						
TRD855WTG-5	Category 5E Outdoor Patch Cable with Weathertight Grommets, 5.0ft (1.5m)	41.75	39.24	36.74	34.23	31.73
TRD855WTG-10	Category 5E Outdoor Patch Cable with Weathertight Grommets, 10.0ft (3.0m)	44.75	42.06	39.38	36.70	34.01
TRD855WTG-25	Category 5E Outdoor Patch Cable with Weathertight Grommets, 25.0ft (7.6m)	53.75	50.52	47.30	44.08	40.85
TRD855WTG-50	Category 5E Outdoor Patch Cable with Weathertight Grommets, 50.0ft (15.2m)	68.75	64.63	60.50	56.38	52.25
TRD855WTG-100	Category 5E Outdoor Patch Cable with Weathertight Grommets, 100.0ft (30.5m)	98.75	92.82	86.90	80.98	75.05

<b>✓RoHS</b>	<b>IP67 RJ45 to RJ45 Cable Assemblies</b>					
L-com's IP67 RJ45 Industrial Ethernet cables are perfect for all your harsh environment networking applications where moisture and dust are prevalent. These IP67 RJ45 cables feature gasketed IP67 plugs and PUR jackets which are UV and chemical resistant. Additionally these cables feature shielded cable to reduce EMI/RFI.						
TRD5WP-1	IP67 RJ45 to IP67 RJ45, PUR Jacket 1.0m	32.00	30.08	28.16	26.24	24.32
TRD5WP-2	IP67 RJ45 to IP67 RJ45, PUR Jacket 2.0m	36.00	33.84	31.68	29.52	27.36
TRD5WP-3	IP67 RJ45 to IP67 RJ45, PUR Jacket 3.0m	40.00	37.60	35.20	32.80	30.40
TRD5WP-5	IP67 RJ45 to IP67 RJ45, PUR Jacket 5.0m	48.00	45.12	42.24	39.36	36.48
TRD5WP-10	IP67 RJ45 to IP67 RJ45, PUR Jacket 10.0m	66.00	62.04	58.08	54.12	50.16

<b>✓RoHS</b>	<b>IP67 Panel Mount RJ45 Couplers</b>					
L-com offers IP67 rated panel mount RJ45 feed-through and 110 punch down couplers for all your demanding Industrial Ethernet applications. These robust IP67 RJ45 panel mount couplers are constructed of ABS 94V-0 plastic and feature gaskets to keep dust and moisture out. These IP67 RJ45 panel mount couplers are designed for a maximum panel thickness of 2.8mm.						
WPRJ-110CAT5E	IP67 Panel Mount RJ45 Coupler, 110 Punch Down, Shielded	19.95	17.95	15.96	13.96	CALL
WPRJ-FTCAT5E	IP67 Panel Mount RJ45 Coupler, Feed-Thru, Shielded	18.95	17.05	15.16	13.26	CALL
WPRJ-FTRACAT5E	IP67 Panel Mount RJ45 Coupler, Feed-Thru Right Angle, Shielded	19.95	17.95	15.96	13.96	CALL

<b>✓RoHS</b>	<b>IP67 Rated RJ45 Cable Glnds</b>					
L-com offers a versatile solution for running RJ45 connections into enclosures and panels. The CG-XX series feature EPDM rubber gaskets to keep moisture and dust out of your critical LAN connections. These cable glands can be used for wired LAN applications as well as WiFi wireless installations.						
CG-CRJ	IP67 RJ45 Feed-Through Cable Gland with 14.5" (36.8cm) Pigtail	8.95	8.77	8.59	8.41	8.23
CG-RJ	IP67 RJ45 Feed-Through Cable Gland, One Way Style	6.95	6.81	6.67	6.53	6.39
CG-DRJ	IP67 RJ45 Feed-Through Cable Gland, Two Way Style	8.95	8.77	8.59	8.41	8.23

"I placed an order today, and it truly was one of the best customer service experiences I have had in years. I dealt with two customer service people and one IT person. They all took the time to find answers to my questions. You are lucky to have people working for you that make customers feel good about your service." - Matthew Scanlon, University of Kansas Medical Center