

Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
--------	-------------	-------	-----	-------	-------	---------	---------

**RoHS Category 3 RJ12 110 Keystone Jacks - Telephone and Data Applications**

L-com's keystone Category 3 110 punch style connectors offer an economical choice with the popular 110-punch style connection system. Each jack is color coded for both the EIA and USOC standards for compatibility with any installation. Jacks are available in two colors to fit individual installations. Large volume quotations are available for installers and contractors looking to save money. Contact us today.

MJS110RJ12-IV	Category 3 RJ12 IDC Keystone Jack	Ivory	1.95	1.75	1.56	1.37	1.17
MJS110RJ12-WT	Category 3 RJ12 IDC Keystone Jack	White	1.95	1.75	1.56	1.37	1.17

**Premium Category 6 RJ45 - 110 Keystone Jack - 90 Degree Style**

Hellermann-Tyton's Gigaband™ Category 6 modular jack is designed to "future proof" installations. Its patented design uses innovative crosstalk cancellation technology. The performance of the Gigaband system exceeds Category 6 and Class E requirements. These jacks will easily support emerging applications such as Gigabit Ethernet and 622 Mbps ATM. The 90° design has the 110 connectors at right angles to the modular plug. Comes in colors of Black, Blue, Office White, Green, Gray, Ivory, Orange, Red, Violet, White and Yellow.

**Category 6 Keystone Jack, 110/RJ45 (8x8), EIA568A/B**

UJ110C6-BLK	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Black	7.95	7.63	7.31	7.00	CALL
UJ110C6-BLU	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Blue	7.95	7.63	7.31	7.00	CALL
UJ110C6-FW	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Office White	7.95	7.63	7.31	7.00	CALL
UJ110C6-GRN	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Green	7.95	7.63	7.31	7.00	CALL
UJ110C6-GRY	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Gray	7.95	7.63	7.31	7.00	CALL
UJ110C6-I	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Ivory	7.95	7.63	7.31	7.00	CALL
UJ110C6-ORN	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Orange	7.95	7.63	7.31	7.00	CALL
UJ110C6-RED	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Red	7.95	7.63	7.31	7.00	CALL
UJ110C6-VIO	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Violet	7.95	7.63	7.31	7.00	CALL
UJ110C6-W	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	White	7.95	7.63	7.31	7.00	CALL
UJ110C6-YEL	Category 6 Keystone Jack, 110 / RJ45 (8x8) 568A/B	Yellow	7.95	7.63	7.31	7.00	CALL

**Premium Category 5E RJ45 - 110 Keystone Jack - 90 Degree Style**

Hellermann-Tyton Megaband™ Category 5E flush modular jacks are designed to meet the needs of end users and installers. These jacks will support Gigabit Ethernet and 622 Mbps ATM applications.

UJ110C5E-BLK	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Black	5.95	5.71	5.47	5.24	CALL
UJ110C5E-BLU	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Blue	5.95	5.71	5.47	5.24	CALL
UJ110C5E-BRN	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Brown	5.95	5.71	5.47	5.24	CALL
UJ110C5E-FW	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Office White	5.95	5.71	5.47	5.24	CALL
UJ110C5E-GRN	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Green	5.95	5.71	5.47	5.24	CALL
UJ110C5E-GRY	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Gray	5.95	5.71	5.47	5.24	CALL
UJ110C5E-I	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Ivory	5.95	5.71	5.47	5.24	CALL
UJ110C5E-ORN	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Orange	5.95	5.71	5.47	5.24	CALL
UJ110C5E-RED	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Red	5.95	5.71	5.47	5.24	CALL
UJ110C5E-W	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	White	5.95	5.71	5.47	5.24	CALL
UJ110C5E-YEL	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Yellow	5.95	5.71	5.47	5.24	CALL

**RoHS Category 6A RJ45 - 110 Keystone Jack - Traditional 180 Degree Style**

L-com now offers the latest in Ethernet technology in the Category 6A standard. With network speeds up to 10 Gigabit, video and large file transfers are a breeze. These IDC 110 jacks are easy to assemble and the popular Keystone mount design is compatible with many different wall plates. Build your network with the fastest network technology available today!

RJ110C6A-90-GRY	Category 6A Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Gray	11.95	10.99	10.04	9.08	8.13
-----------------	---	------	-------	-------	-------	------	------

**Category 5E RJ45 - 110 Keystone Jack - Traditional 180 Degree Style**

The traditional 180° design has the 110 connectors parallel to the modular plug entry. This jack comes in Ivory and is EIA568A/B dual color coded.

RJ110C5B-I	Category 5E Keystone Jack, 110 / RJ45 (8x8) EIA568A/B	Ivory	5.95	5.83	5.71	5.59	5.47
------------	---	-------	------	------	------	------	------

**RoHS 10 Position Category 5 and USOC - 110 IDC Keystone Jacks - Traditional 180 Degree Style**



These 10 position 10 contact keystone style jacks are an ideal solution in applications where additional contacts are required. The traditional 180° design has the 110 connectors parallel to the modular plug entry. Category 5 version is dual color coded, compatible with EIA568A and B wiring with position 1 and 10 populated.

EC1107B-USOC	Keystone IDC - 10P10C Jack, USOC	Black	6.95	6.67	6.39	6.12	CALL
EC1107B-10C5	Keystone IDC - 10P10C Jack, Cat. 5-568A/B	Black	6.95	6.67	6.39	6.12	CALL

**RoHS Miscellaneous Keystone Jacks - Coaxial, Fiber and Audio/Video Couplers**

Add more than just data and telephone connections to workstation outlets. L-com features audio, video, fiber and RF adapters designed to fit our wall plate systems.

MJSCPF-WT	Keystone Coaxial Type F Coupler Insert	White	1.45	1.30	1.16	1.01	0.87
MJSCPRCA-WT	Keystone RCA Coupler Insert	White	2.45	2.21	1.96	1.72	1.47
MJSCPSC-WT	Keystone Fiber SC Coupler Insert	White	5.95	5.36	4.76	4.17	3.57
MJSCPST-WT	Keystone Fiber ST Coupler Insert	White	5.95	5.36	4.76	4.17	3.57
MJSCVR-WT	Keystone Blank Insert	White	0.35	0.34	0.32	0.31	0.29
MJSCPF-IV	Keystone Coaxial Type F Coupler Insert	Ivory	1.45	1.30	1.16	1.01	0.87
MJSCPRCA-IV	Keystone RCA Coupler Insert	Ivory	2.45	2.21	1.96	1.72	1.47
MJSCPBNC-IV	Keystone BNC Coupler Insert	Ivory	3.49	3.21	2.93	2.65	2.37
MJSCPSC-IV	Keystone Fiber SC Coupler Insert	Ivory	5.95	5.36	4.76	4.17	3.57
MJSCPST-IV	Keystone Fiber ST Coupler Insert	Ivory	5.95	5.36	4.76	4.17	3.57
MJSCVR-IV	Keystone Blank Insert	Ivory	0.35	0.34	0.32	0.31	0.29



**Free access to over 3,000 CAD models**  
 Download CAD models and 2D drawings for integrating into your projects. [L-com.com/CadDemo](http://L-com.com/CadDemo)