



Item #	Description	Wiring	1-9	10-24	25-99	100-249
RoHS 25-Pair Telco Cables - Dual Terminated and Breakout (Octopus) Versions						
L-com offers a variety of straight-thru and breakout 25 pair telco trunk cables for voice and data networks. Cables come in Category 3 and 5 grades and utilize PVC jackets. Plenum grade and other configurations available by custom request. Category 5 cables utilize 180° or 90° connector ends.						
TDC350FF-5	Cat. 3, Telco Cable, 90° Female / 90° Female, 5.0ft (1.5m)	A	31.95	29.39	26.84	CALL
TDC350FF-10	Cat. 3, Telco Cable, 90° Female / 90° Female, 10.0ft (3.0m)	A	36.95	33.99	31.04	CALL
TDC350FF-15	Cat. 3, Telco Cable, 90° Female / 90° Female, 15.0ft (4.6m)	A	42.95	39.51	36.08	CALL
TDC350FF-25	Cat. 3, Telco Cable, 90° Female / 90° Female, 25.0ft (7.6m)	A	53.95	49.63	45.32	CALL
TDC350FF-50	Cat. 3, Telco Cable, 90° Female / 90° Female, 50.0ft (15.2m)	A	80.95	74.47	68.00	CALL
TDC350FF-100	Cat. 3, Telco Cable, 90° Female / 90° Female, 100.0ft (30.5m)	A	135.95	125.07	114.20	CALL
TDC350MM-5	Cat. 3, Telco Cable, 90° Male / 90° Male, 5.0ft (1.5m)	A	31.95	29.39	26.84	CALL
TDC350MM-10	Cat. 3, Telco Cable, 90° Male / 90° Male, 10.0ft (3.0m)	A	36.95	33.99	31.04	CALL
TDC350MM-15	Cat. 3, Telco Cable, 90° Male / 90° Male, 15.0ft (4.6m)	A	42.95	39.51	36.08	CALL
TDC350MM-25	Cat. 3, Telco Cable, 90° Male / 90° Male, 25.0ft (7.6m)	A	53.95	49.63	45.32	CALL
TDC350MM-50	Cat. 3, Telco Cable, 90° Male / 90° Male, 50.0ft (15.2m)	A	80.95	74.47	68.00	CALL
TDC350MM-100	Cat. 3, Telco Cable, 90° Male / 90° Male, 100.0ft (30.5m)	A	135.95	125.07	114.20	CALL
TDC550FF-5	Cat. 5, Telco Cable, 90° Female / 90° Female, 5.0ft (1.5m)	A	69.50	65.33	61.16	56.99
TDC550FF-10	Cat. 5, Telco Cable, 90° Female / 90° Female, 10.0ft (3.0m)	A	78.50	73.79	69.08	64.37
TDC550FF-15	Cat. 5, Telco Cable, 90° Female / 90° Female, 15.0ft (4.6m)	A	87.50	82.25	77.00	71.75
TDC550FF-25	Cat. 5, Telco Cable, 90° Female / 90° Female, 25.0ft (7.6m)	A	104.50	98.23	91.96	85.69
TDC550FF-50	Cat. 5, Telco Cable, 90° Female / 90° Female, 50.0ft (15.2m)	A	148.50	139.59	130.68	121.77
TDC550FF-100	Cat. 5, Telco Cable, 90° Female / 90° Female, 100.0ft (30.5m)	A	235.50	221.37	207.24	193.11
TDC550MM-5	Cat. 5, Telco Cable, 180° Male / 180° Male, 5.0ft (1.5m)	A	69.50	65.33	61.16	56.99
TDC550MM-10	Cat. 5, Telco Cable, 180° Male / 180° Male, 10.0ft (3.0m)	A	78.50	73.79	69.08	64.37
TDC550MM-15	Cat. 5, Telco Cable, 180° Male / 180° Male, 15.0ft (4.6m)	A	87.50	82.25	77.00	71.75
TDC550MM-25	Cat. 5, Telco Cable, 180° Male / 180° Male, 25.0ft (7.6m)	A	104.50	98.23	91.96	85.69
TDC550MM-50	Cat. 5, Telco Cable, 180° Male / 180° Male, 50.0ft (15.2m)	A	148.50	139.59	130.68	121.77
TDC550MM-100	Cat. 5, Telco Cable, 180° Male / 180° Male, 100.0ft (30.5m)	A	235.50	221.37	207.24	193.11

RoHS Category 3, Octopus Cables - Convert 25-Pair Telco to a Variety of Modular Cable Breakouts

This is a useful cable arrangement that allows conversion from a 90° 50 pin Telco connector to a variety of modular cables terminated with male RJ plugs having 2, 4, 6 or 8 active pins. All cables are three feet long. Wired per USOC Standard. Category 3 rated.

TDC50M62	Cat. 3 Telco Breakout Cable, Male Telco / 25 (6x2), 3.0ft (0.9m)	B	89.95	84.55	79.16	73.76
TDC50M64	Cat. 3 Telco Breakout Cable, Male Telco / 12 (6x4), 3.0ft (0.9m)	C	64.95	61.05	57.16	53.26
TDC50M66	Cat. 3 Telco Breakout Cable, Male Telco / 8 (6x6), 3.0ft (0.9m)	D	59.95	56.35	52.76	49.16
TDC50M88	Cat. 3 Telco Breakout Cable, Male Telco / 6 (8x8), 3.0ft (0.9m)	E	59.95	56.35	52.76	49.16
TDC50F62	Cat. 3 Telco Breakout Cable, Female Telco / 25 (6x2), 3.0ft (0.9m)	B	89.95	84.55	79.16	73.76
TDC50F64	Cat. 3 Telco Breakout Cable, Female Telco / 12 (6x4), 3.0ft (0.9m)	C	64.95	61.05	57.16	53.26
TDC50F66	Cat. 3 Telco Breakout Cable, Female Telco / 8 (6x6), 3.0ft (0.9m)	D	59.95	56.35	52.76	49.16
TDC50F88	Cat. 3 Telco Breakout Cable, Female Telco / 6 (8x8), 3.0ft (0.9m)	E	59.95	56.35	52.76	49.16


RoHS Category 5, Octopus Cables - Patch to Network Ethernet Equipment, etc.

Category 5 octopus cables break out one 180° telco connector to 12 RJ45 plugs wired for Ethernet 10Base-T.

TRDC500M-3S	Cat. 5 Breakout Cable, Male Telco / 12 10Base-T (8x4), 3.0ft (0.9m)	F	58.60	55.08	51.57	CALL
TRDC500M-6S	Cat. 5 Breakout Cable, Male Telco / 12 10Base-T (8x4), 6.0ft (1.8m)	F	62.20	58.47	54.74	CALL
TRDC500M-10S	Cat. 5 Breakout Cable, Male Telco / 12 10Base-T (8x4), 10.0ft (3.0m)	F	67.00	62.98	58.96	CALL

RoHS 50 Position Slim-Line Gender Changers - Mate with SCSI-1 and 50 Position Telco Connectors

DGC50F	50 Pin SCSI Gender Changer, Female / Female	10.95	9.86	8.76	7.66
DGC50M	50 Pin SCSI Gender Changer, Male / Male	10.95	9.86	8.76	7.66
DGC50MF	50 Pin SCSI Telco Socket Saver, Male / Female	10.95	9.86	8.76	7.66



"Great products...L-com is the only place to shop for quality at a fantastic price from people who really know their products."
- Larry Miller, MIS/IT Manager, Exterior Wood, Inc., Washougal, WA