



Item #	Description	Length	1-9	10-24	25-99	100-249	250-499
--------	-------------	--------	-----	-------	-------	---------	---------

Category 5E and 6 Network Extension Cables

L-com's unique network extension cables offer the perfect solution for extending an Ethernet network cable to the outside of an enclosure or by making a hard to reach port more accessible. Available in either Category 5E or Category 6, shielded or un-shielded, these cables are up to the task for your high demand data tasks. These extensions feature either a panel mountable flange or an inline flange-free design.

- Category 5E or Category 6 Network Extension Cables
- Available either with or without a panel mountable flange
- Choose either un-shielded (UTP) or Shielded (FTP)
- Feature L-com's unique snag-less molded plugs
- Standard lengths up to 25ft or call for custom options

✓RoHS Category 5E Non-Shielded Non-Flanged Extension Cables

TRDC5EXT-3	Category 5E RJ45 Extension Cable	3.0ft (0.9m)	13.52	12.44	11.36	10.28	9.19
TRDC5EXT-5	Category 5E RJ45 Extension Cable	5.0ft (1.5m)	14.40	13.25	12.10	10.94	9.79
TRDC5EXT-7	Category 5E RJ45 Extension Cable	7.0ft (2.1m)	16.40	15.09	13.78	12.46	11.15
TRDC5EXT-10	Category 5E RJ45 Extension Cable	10.0ft (3.0m)	16.68	15.35	14.01	12.68	11.34
TRDC5EXT-15	Category 5E RJ45 Extension Cable	15.0ft (4.6m)	18.84	17.33	15.83	14.32	12.81
TRDC5EXT-25	Category 5E RJ45 Extension Cable	25.0ft (7.6m)	22.88	21.05	19.22	17.39	15.56

✓RoHS Category 5E Shielded Non-Flanged Extension Cables

TRDC5EXTS-3	Category 5E RJ45 Shielded Extension Cable	3.0ft (0.9m)	16.16	14.87	13.57	12.28	10.99
TRDC5EXTS-5	Category 5E RJ45 Shielded Extension Cable	5.0ft (1.5m)	17.20	15.82	14.45	13.07	11.70
TRDC5EXTS-7	Category 5E RJ45 Shielded Extension Cable	7.0ft (2.1m)	19.40	17.85	16.30	14.74	13.19
TRDC5EXTS-10	Category 5E RJ45 Shielded Extension Cable	10.0ft (3.0m)	19.96	18.36	16.77	15.17	13.57
TRDC5EXTS-15	Category 5E RJ45 Shielded Extension Cable	15.0ft (4.6m)	22.60	20.79	18.98	17.18	15.37
TRDC5EXTS-25	Category 5E RJ45 Shielded Extension Cable	25.0ft (7.6m)	27.52	25.32	23.12	20.92	18.71

✓RoHS Category 6 Non-Shielded Non-Flanged Extension Cables

TRDC6EXT-3	Category 6 RJ45 Extension Cable	3.0ft (0.9m)	13.80	12.70	11.59	10.49	9.38
TRDC6EXT-5	Category 6 RJ45 Extension Cable	5.0ft (1.5m)	14.88	13.69	12.50	11.31	10.12
TRDC6EXT-7	Category 6 RJ45 Extension Cable	7.0ft (2.1m)	17.08	15.71	14.35	12.98	11.61
TRDC6EXT-10	Category 6 RJ45 Extension Cable	10.0ft (3.0m)	17.60	16.19	14.78	13.38	11.97
TRDC6EXT-15	Category 6 RJ45 Extension Cable	15.0ft (4.6m)	20.24	18.62	17.00	15.38	13.76
TRDC6EXT-25	Category 6 RJ45 Extension Cable	25.0ft (7.6m)	25.16	23.15	21.13	19.12	17.11

✓RoHS Category 6 Shielded Non-Flanged Extension Cables

TRDC6EXTS-3	Category 6 RJ45 Shielded Extension Cable	3.0ft (0.9m)	15.60	14.35	13.10	11.86	10.61
TRDC6EXTS-5	Category 6 RJ45 Shielded Extension Cable	5.0ft (1.5m)	16.88	15.53	14.18	12.83	11.48
TRDC6EXTS-7	Category 6 RJ45 Shielded Extension Cable	7.0ft (2.1m)	19.36	17.81	16.26	14.71	13.16
TRDC6EXTS-10	Category 6 RJ45 Shielded Extension Cable	10.0ft (3.0m)	20.24	18.62	17.00	15.38	13.76
TRDC6EXTS-15	Category 6 RJ45 Shielded Extension Cable	15.0ft (4.6m)	23.52	21.64	19.76	17.88	15.99
TRDC6EXTS-25	Category 6 RJ45 Shielded Extension Cable	25.0ft (7.6m)	29.60	27.23	24.86	22.50	20.13

✓RoHS Category 5E Non-Shielded Flanged Extension Cables

TRDC5EXTF-3	Category 5E RJ45 Extension Cable	3.0ft (0.9m)	14.84	13.65	12.47	11.28	10.09
TRDC5EXTF-5	Category 5E RJ45 Extension Cable	5.0ft (1.5m)	15.72	14.46	13.20	11.95	10.69
TRDC5EXTF-7	Category 5E RJ45 Extension Cable	7.0ft (2.1m)	17.72	16.30	14.88	13.47	12.05
TRDC5EXTF-10	Category 5E RJ45 Extension Cable	10.0ft (3.0m)	18.00	16.56	15.12	13.68	12.24
TRDC5EXTF-15	Category 5E RJ45 Extension Cable	15.0ft (4.6m)	20.16	18.55	16.93	15.32	13.71
TRDC5EXTF-25	Category 5E RJ45 Extension Cable	25.0ft (7.6m)	24.20	22.26	20.33	18.39	16.46

✓RoHS Category 5E Shielded Flanged Extension Cables

TRDC5EXTSF-3	Category 5E RJ45 Shielded Extension Cable	3.0ft (0.9m)	16.24	14.94	13.64	12.34	11.04
TRDC5EXTSF-5	Category 5E RJ45 Shielded Extension Cable	5.0ft (1.5m)	17.32	15.93	14.55	13.16	11.78
TRDC5EXTSF-7	Category 5E RJ45 Shielded Extension Cable	7.0ft (2.1m)	19.52	17.96	16.40	14.84	13.27
TRDC5EXTSF-10	Category 5E RJ45 Shielded Extension Cable	10.0ft (3.0m)	20.08	18.47	16.87	15.26	13.65
TRDC5EXTSF-15	Category 5E RJ45 Shielded Extension Cable	15.0ft (4.6m)	22.72	20.90	19.08	17.27	15.45
TRDC5EXTSF-25	Category 5E RJ45 Shielded Extension Cable	25.0ft (7.6m)	27.64	25.43	23.22	21.01	18.80

✓RoHS Category 6 Non-Shielded Flanged Extension Cables

TRDC6EXTF-3	Category 6 RJ45 Extension Cable	3.0ft (0.9m)	15.12	13.91	12.70	11.49	10.28
TRDC6EXTF-5	Category 6 RJ45 Extension Cable	5.0ft (1.5m)	16.20	14.90	13.61	12.31	11.02
TRDC6EXTF-7	Category 6 RJ45 Extension Cable	7.0ft (2.1m)	18.40	16.93	15.46	13.98	12.51
TRDC6EXTF-10	Category 6 RJ45 Extension Cable	10.0ft (3.0m)	18.92	17.41	15.89	14.38	12.87
TRDC6EXTF-15	Category 6 RJ45 Extension Cable	15.0ft (4.6m)	21.56	19.84	18.11	16.39	14.66
TRDC6EXTF-25	Category 6 RJ45 Extension Cable	25.0ft (7.6m)	26.48	24.36	22.24	20.12	18.01

✓RoHS Category 6 Shielded Flanged Extension Cables

TRDC6EXTSF-3	Category 6 RJ45 Shielded Extension Cable	3.0ft (0.9m)	16.64	15.31	13.98	12.65	11.32
TRDC6EXTSF-5	Category 6 RJ45 Shielded Extension Cable	5.0ft (1.5m)	17.92	16.49	15.05	13.62	12.19
TRDC6EXTSF-7	Category 6 RJ45 Shielded Extension Cable	7.0ft (2.1m)	20.40	18.77	17.14	15.50	13.87
TRDC6EXTSF-10	Category 6 RJ45 Shielded Extension Cable	10.0ft (3.0m)	21.28	19.58	17.88	16.17	14.47
TRDC6EXTSF-15	Category 6 RJ45 Shielded Extension Cable	15.0ft (4.6m)	24.56	22.60	20.63	18.67	16.70
TRDC6EXTSF-25	Category 6 RJ45 Shielded Extension Cable	25.0ft (7.6m)	30.68	28.23	25.77	23.32	20.86

✓RoHS Category 5 25-Pair Trunk Cables – Male 90-Degree Breakout for Ethernet

Breakout your 25-Pair Trunk lines to RJ45 style plugs for Ethernet. Available in a Category 5 rating, these cables simplify the process of connecting individual lines from or to a 25-pair Telco connection. One end features a standard RJ21 Telco connection and the other has twelve RJ45 style connectors. Custom lengths are available with modest minimums.

TRDC500M-3S	Cat. 5 Breakout Cable, Male Telco / 12 10Base-T (8x4)	3.0ft (0.9m)	58.60	55.08	51.57	CALL	CALL
TRDC500M-6S	Cat. 5 Breakout Cable, Male Telco / 12 10Base-T (8x4)	6.0ft (1.8m)	62.20	58.47	54.74	CALL	CALL
TRDC500M-10S	Cat. 5 Breakout Cable, Male Telco / 12 10Base-T (8x4)	10.0ft (3.0m)	67.00	62.98	58.96	CALL	CALL