




Item #	Description	Wiring	1-9	10-24	25-99	100-249	250-499
✓RoHS Modular TEE Adapters - The Most Practical Way to Tap Into Your Wiring Networks							
All units have either 2, 3 or 4 RJ jacks mating to a male or female. Useful in daisy chain wiring, parallel phones or answering machines. It also is very useful in test environments where access to specific pins is required.							
EC503-4	Modular TEE Adapter (6x4)M / (6x4)F	A	3.95	3.63	3.32	3.00	CALL
EC503-6E	Modular TEE Adapter (6x6)M / (6x6)F / (6x6)F	B	3.95	3.63	3.32	3.00	CALL
EC503-8	Modular TEE Adapter (8x8)M / (8x8)KF / (8x8)KF	C	4.95	4.55	4.16	3.76	CALL
EC503-448	Modular TEE Splitter (8x8)M / (8x4)KF / (8x4)KF	D	4.95	4.55	4.16	3.76	CALL



EC503-1703	Modular TEE Splitter (6x4)M / (6x2)F / (6x2)F	E	4.95	4.55	4.16	3.76	CALL
------------	---	---	------	------	------	------	------


✓RoHS Modular Splitter Adapter - Allows Three RJ11/12 Circuits to be Parallel Connected							
EC503-2134	Modular 1 to 3 Adapter (6x4)M / 3 (6x4)F	F	4.95	4.55	4.16	3.76	CALL
EC503-2136	Modular 1 to 3 Adapter (6x6)M / 3 (6x6)F	F	4.95	4.55	4.16	3.76	CALL



✓RoHS Modular TEE Junction - Three RJ11/12 or RJ45 Receptacles Accept Three Plugs							
TDS1039-4C	Modular TEE Junction (6x4)F / (6x4)F, (6x4)F	A	3.95	3.63	3.32	3.00	CALL
TDS1039-6C	Modular TEE Junction (6x6)F / (6x6)F, (6x6)F	B	4.95	4.55	4.16	3.76	CALL
TDS1039-8C	Modular TEE Junction (8x8)F / (8x8)F, (8x8)F	C	5.29	4.87	4.44	4.02	CALL


✓RoHS Socket Saver Adapters - Extend the Life of Frequently Used Modular Jacks
 Avoid costly repairs trying to replace modular jacks. Particularly useful with cable testers where jacks are in constant use. A small price to pay to assure maximum performance for the life of your equipment. Also available is the EC535D-10X 10Base-T crossover adapter. Attach this in series with any 10Base-T compatible patch cord and the 1-2 pair crosses to the 3-6 pair. This wiring is often necessary for stacking Ethernet hubs.

EC535AD	Modular Conversion Adapter (6x6)M / (8x6)KF	G	3.95	3.63	3.32	3.00	CALL
EC535A	Modular Socket Saver (6x6)M / (6x6)F	H	3.95	3.63	3.32	3.00	CALL
EC535D	Modular Socket Saver (8x8)M / (8x8)KF	J	3.95	3.63	3.32	3.00	CALL
EC535D-10X	Modular 10Base-T Crossover Adapter (8x4)M / (8x4)KF	K	3.95	3.63	3.32	3.00	CALL




✓RoHS Modular Couplers - Allow Mating of Cables Having Same Modular Termination
 We offer a choice of wiring types, straight-thru for use in low speed data communication and crossed wiring for voice applications. This series has gold plated contact surfaces.

TDG1026-4R	Modular Coupler, RJ11 (6x4), Cross Wired	2.15	1.98	1.81	1.63	1.46
TDG1026-6R	Modular Coupler, RJ12 (6x6), Cross Wired	2.35	2.16	1.97	1.79	1.60
TDG1026-8R	Modular Coupler, RJ45 (8x8), Cross Wired	2.95	2.71	2.48	2.24	2.01
TDG1026-4C	Modular Coupler, RJ11 (6x4), Straight Wired	2.15	1.98	1.81	1.63	1.46
TDG1026-6C	Modular Coupler, RJ12 (6x6), Straight Wired	2.35	2.16	1.97	1.79	1.60
TDG1026-8C	Modular Coupler, RJ45 (8x8), Straight Wired	2.95	2.71	2.48	2.24	2.01
TDG1026-8CK	Modular Coupler, RJ45K (8x8), Straight, Keyed	3.15	2.90	2.65	2.39	2.14






✓RoHS Reverse Cable Adapter - A Handy Device To Have To Reverse Polarity (Cross Wiring)							
TDC48R	Reverse Cable Adapter, RJ11 (6x4), Male / Female, 10"	2.65	2.44	2.23	2.01	1.80	
Note: Longer lengths and modular connector types available on special orders							

✓RoHS Telephone and Data 7 Ft Extension Cords - With Male and Female Modular Connectors							
TAC535-4-7	7 ft Modular Extension Cord, Straight Wired, RJ11 (6x4)	4.49	4.13	3.77	3.41	CALL	
TAC535-6-7	7 ft Modular Extension Cord, Straight Wired, RJ12 (6x6)	4.79	4.41	4.02	3.64	CALL	
TAC535-8-7	7 ft Modular Extension Cord, Straight Wired, RJ45K (8x8), Keyed	4.99	4.59	4.19	3.79	CALL	
Note: 8x8 jacks are keyed. This series also available as Cross Wired. Custom wiring schemes considered.							



✓RoHS Modular Insert Adapters
 These adapters provide a simple way to allow smaller modular plugs to fit securely into a larger jack. Two types are available: an RJ11/12 plug into an RJ45 jack or an RJ22 style handset plug into an RJ11/12 size jack.

EC4X4A	Modular Insert Adapter, RJ22 Handset Plug into an RJ11/12 Jack, Pkg/10	2.99	2.81	2.63	2.45	CALL
EC8X8A	Modular Insert Adapter, RJ11/12 Plug into an RJ45 Jack, Pkg/10	2.99	2.75	2.51	2.27	CALL



Helpful videos
 How-to videos help with some of today's popular product applications. L-com.com/Tips