


Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

Deluxe D-Sub Cable Assemblies - Fully Populated with 4-40 Thumbscrews

The CSMN Series of D-Sub cable assemblies is our middle of the line offering excellent performance and lower pricing. All assemblies utilize 26AWG stranded conductors with foil shielding for flexibility and performance. Backshells are fully molded with copper shielding for better immunity to outside noise. Mating hardware is 4-40 thumbscrews which makes securing without tools quick and easy. Hex nuts on female connectors are removable to expose 4-40 thumbscrews. **Note:** 50 pin assemblies use 28AWG twisted pairs due to space constraints in backshell molding. Color: Light Gray.



- See L-com's Master Catalog or website for our Economy Molded D-Sub Cable Assemblies
- More lengths available. Go to L-com.com
- New Female / Female in DB9, DB15 and DB25

RoHS Deluxe 9 Pin D-Sub Molded Cables with Thumbscrews - Shielded and Fully Populated

CSMN9MM-1	Deluxe Molded Cable, DB9 Male / Male, 1.0ft (0.3m)	6.75	6.21	5.67	5.13	4.59
CSMN9MM-2.5	Deluxe Molded Cable, DB9 Male / Male, 2.5ft (0.8m)	7.50	6.90	6.30	5.70	5.10
CSMN9MM-5	Deluxe Molded Cable, DB9 Male / Male, 5.0ft (1.5m)	8.75	8.05	7.35	6.65	5.95
CSMN9MM-10	Deluxe Molded Cable, DB9 Male / Male, 10.0ft (3.0m)	11.25	10.35	9.45	8.55	7.65
CSMN9MM-15	Deluxe Molded Cable, DB9 Male / Male, 15.0ft (4.6m)	13.75	12.65	11.55	10.45	9.35
CSMN9MM-25	Deluxe Molded Cable, DB9 Male / Male, 25.0ft (7.6m)	18.75	17.25	15.75	14.25	12.75
CSMN9MM-125	Deluxe Molded Cable, DB9 Male / Male, 125.0ft (38.1m)	68.75	63.25	57.75	52.25	46.75
CSMN9MF-1	Deluxe Molded Cable, DB9 Male / Female, 1.0ft (0.3m)	6.75	6.21	5.67	5.13	4.59
CSMN9MF-2.5	Deluxe Molded Cable, DB9 Male / Female, 2.5ft (0.8m)	7.50	6.90	6.30	5.70	5.10
CSMN9MF-5	Deluxe Molded Cable, DB9 Male / Female, 5.0ft (1.5m)	8.75	8.05	7.35	6.65	5.95
CSMN9MF-10	Deluxe Molded Cable, DB9 Male / Female, 10.0ft (3.0m)	11.25	10.35	9.45	8.55	7.65
CSMN9MF-15	Deluxe Molded Cable, DB9 Male / Female, 15.0ft (4.6m)	13.75	12.65	11.55	10.45	9.35
CSMN9MF-25	Deluxe Molded Cable, DB9 Male / Female, 25.0ft (7.6m)	18.75	17.25	15.75	14.25	12.75
CSMN9FF-1	Deluxe Molded Cable, DB9 Female / Female, 1.0ft (0.3m)	6.75	6.21	5.67	5.13	4.59
CSMN9FF-2.5	Deluxe Molded Cable, DB9 Female / Female, 2.5ft (0.8m)	7.50	6.90	6.30	5.70	5.10
CSMN9FF-5	Deluxe Molded Cable, DB9 Female / Female, 5.0ft (1.5m)	8.75	8.05	7.35	6.65	5.95
CSMN9FF-10	Deluxe Molded Cable, DB9 Female / Female, 10.0ft (3.0m)	11.25	10.35	9.45	8.55	7.65
CSMN9FF-15	Deluxe Molded Cable, DB9 Female / Female, 15.0ft (4.6m)	13.75	12.65	11.55	10.45	9.35
CSMN9FF-25	Deluxe Molded Cable, DB9 Female / Female, 25.0ft (7.6m)	18.75	17.25	15.75	14.25	12.75
CSMN9FF-50	Deluxe Molded Cable, DB9 Female / Female, 50.0ft (15.2m)	31.25	28.75	26.25	23.75	21.25

RoHS Deluxe 15 Pin D-Sub Molded Cables with Thumbscrews - Shielded and Fully Populated

CSMN15MM-1	Deluxe Molded Cable, DB15 Male / Male, 1.0ft (0.3m)	10.35	9.73	9.11	8.49	7.87
CSMN15MM-2.5	Deluxe Molded Cable, DB15 Male / Male, 2.5ft (0.8m)	11.25	10.57	9.90	9.23	8.55
CSMN15MM-5	Deluxe Molded Cable, DB15 Male / Male, 5.0ft (1.5m)	12.75	11.98	11.22	10.46	9.69
CSMN15MM-10	Deluxe Molded Cable, DB15 Male / Male, 10.0ft (3.0m)	15.75	14.80	13.86	12.92	11.97
CSMN15MM-15	Deluxe Molded Cable, DB15 Male / Male, 15.0ft (4.6m)	18.75	17.63	16.50	15.38	14.25
CSMN15MM-25	Deluxe Molded Cable, DB15 Male / Male, 25.0ft (7.6m)	24.75	23.26	21.78	20.30	18.81
CSMN15MM-50	Deluxe Molded Cable, DB15 Male / Male, 50.0ft (15.2m)	39.75	37.36	34.98	32.60	30.21
CSMN15MF-1	Deluxe Molded Cable, DB15 Male / Female, 1.0ft (0.3m)	10.35	9.73	9.11	8.49	7.87
CSMN15MF-2.5	Deluxe Molded Cable, DB15 Male / Female, 2.5ft (0.8m)	11.25	10.57	9.90	9.23	8.55
CSMN15MF-5	Deluxe Molded Cable, DB15 Male / Female, 5.0ft (1.5m)	12.75	11.98	11.22	10.46	9.69
CSMN15MF-10	Deluxe Molded Cable, DB15 Male / Female, 10.0ft (3.0m)	15.75	14.80	13.86	12.92	11.97
CSMN15MF-15	Deluxe Molded Cable, DB15 Male / Female, 15.0ft (4.6m)	18.75	17.63	16.50	15.38	14.25
CSMN15MF-25	Deluxe Molded Cable, DB15 Male / Female, 25.0ft (7.6m)	24.75	23.26	21.78	20.30	18.81
CSMN15MF-50	Deluxe Molded Cable, DB15 Male / Female, 50.0ft (15.2m)	39.75	37.36	34.98	32.60	30.21
CSMN15FF-1	Deluxe Molded Cable, DB15 Female / Female, 1.0ft (0.3m)	10.35	9.73	9.11	8.49	7.87
CSMN15FF-2.5	Deluxe Molded Cable, DB15 Female / Female, 2.5ft (0.8m)	11.25	10.57	9.90	9.23	8.55
CSMN15FF-5	Deluxe Molded Cable, DB15 Female / Female, 5.0ft (1.5m)	12.75	11.98	11.22	10.46	9.69
CSMN15FF-10	Deluxe Molded Cable, DB15 Female / Female, 10.0ft (3.0m)	15.75	14.80	13.86	12.92	11.97
CSMN15FF-15	Deluxe Molded Cable, DB15 Female / Female, 15.0ft (4.6m)	18.75	17.63	16.50	15.38	14.25
CSMN15FF-25	Deluxe Molded Cable, DB15 Female / Female, 25.0ft (7.6m)	24.75	23.26	21.78	20.30	18.81
CSMN15FF-50	Deluxe Molded Cable, DB15 Female / Female, 50.0ft (15.2m)	39.75	37.36	34.98	32.60	30.21

RoHS Deluxe 25 Pin D-Sub Molded Cables with Thumbscrews - Shielded and Fully Populated

CSMN25MM-1	Deluxe Molded Cable, DB25 Male / Male, 1.0ft (0.3m)	9.15	8.42	7.69	6.95	6.22
CSMN25MM-2.5	Deluxe Molded Cable, DB25 Male / Male, 2.5ft (0.8m)	9.75	8.97	8.19	7.41	6.63
CSMN25MM-5	Deluxe Molded Cable, DB25 Male / Male, 5.0ft (1.5m)	10.75	9.89	9.03	8.17	7.31
CSMN25MM-10	Deluxe Molded Cable, DB25 Male / Male, 10.0ft (3.0m)	12.75	11.73	10.71	9.69	8.67
CSMN25MM-15	Deluxe Molded Cable, DB25 Male / Male, 15.0ft (4.6m)	14.75	13.57	12.39	11.21	10.03
CSMN25MM-25	Deluxe Molded Cable, DB25 Male / Male, 25.0ft (7.6m)	18.75	17.25	15.75	14.25	12.75
CSMN25MM-125	Deluxe Molded Cable, DB25 Male / Male, 125.0ft (38.1m)	58.75	54.05	49.35	44.65	39.95
CSMN25MF-1	Deluxe Molded Cable, DB25 Male / Female, 1.0ft (0.3m)	9.15	8.42	7.69	6.95	6.22
CSMN25MF-2.5	Deluxe Molded Cable, DB25 Male / Female, 2.5ft (0.8m)	9.75	8.97	8.19	7.41	6.63
CSMN25MF-5	Deluxe Molded Cable, DB25 Male / Female, 5.0ft (1.5m)	10.75	9.89	9.03	8.17	7.31
CSMN25MF-10	Deluxe Molded Cable, DB25 Male / Female, 10.0ft (3.0m)	12.75	11.73	10.71	9.69	8.67
CSMN25MF-15	Deluxe Molded Cable, DB25 Male / Female, 15.0ft (4.6m)	14.75	13.57	12.39	11.21	10.03
CSMN25MF-25	Deluxe Molded Cable, DB25 Male / Female, 25.0ft (7.6m)	18.75	17.25	15.75	14.25	12.75
CSMN25MF-50	Deluxe Molded Cable, DB25 Male / Female, 50.0ft (15.2m)	28.75	26.45	24.15	21.85	19.55
CSMN25FF-1	Deluxe Molded Cable, DB25 Female / Female, 1.0ft (0.3m)	9.15	8.42	7.69	6.95	6.22
CSMN25FF-2.5	Deluxe Molded Cable, DB25 Female / Female, 2.5ft (0.8m)	9.75	8.97	8.19	7.41	6.63
CSMN25FF-5	Deluxe Molded Cable, DB25 Female / Female, 5.0ft (1.5m)	10.75	9.89	9.03	8.17	7.31
CSMN25FF-10	Deluxe Molded Cable, DB25 Female / Female, 10.0ft (3.0m)	12.75	11.73	10.71	9.69	8.67
CSMN25FF-15	Deluxe Molded Cable, DB25 Female / Female, 15.0ft (4.6m)	14.75	13.57	12.39	11.21	10.03
CSMN25FF-25	Deluxe Molded Cable, DB25 Female / Female, 25.0ft (7.6m)	18.75	17.25	15.75	14.25	12.75
CSMN25FF-50	Deluxe Molded Cable, DB25 Female / Female, 50.0ft (15.2m)	28.75	26.45	24.15	21.85	19.55

RoHS Replacement 4-40 Screws for CSMN Series Assemblies - Sold in 10/Packs

TS-CSMN	Replacement Screws for CSMN Series Assemblies, Pkg/10	4.10	3.85	3.61	3.36	3.12
---------	---	------	------	------	------	------



Best Seller



CSMN9MF



CSMN15MF



CSMN15FF



CSMN25MF



CSMN25FF

New

New

Assembled vs molded D-Sub connectors
See the difference at L-com.com/BackshellConstruction