




Item #	Description	1-9	10-24	25-99	100-249	250-499
✓RoHS Deluxe 37 Pin D-Sub Molded Cables with Thumbscrews - Shielded and Fully Populated						
CSMN37MM-1	Deluxe Molded Cable, DB37 Male / Male, 1.0ft (0.3m)	26.00	24.44	22.88	21.32	19.76
CSMN37MM-2.5	Deluxe Molded Cable, DB37 Male / Male, 2.5ft (0.8m)	27.50	25.85	24.20	22.55	20.90
CSMN37MM-5	Deluxe Molded Cable, DB37 Male / Male, 5.0ft (1.5m)	30.00	28.20	26.40	24.60	22.80
CSMN37MM-10	Deluxe Molded Cable, DB37 Male / Male, 10.0ft (3.0m)	35.00	32.90	30.80	28.70	26.60
CSMN37MM-25	Deluxe Molded Cable, DB37 Male / Male, 25.0ft (7.6m)	50.00	47.00	44.00	41.00	38.00
CSMN37MM-50	Deluxe Molded Cable, DB37 Male / Male, 50.0ft (15.2m)	75.00	70.50	66.00	61.50	57.00
CSMN37MF-1	Deluxe Molded Cable, DB37 Male / Female, 1.0ft (0.3m)	26.00	24.44	22.88	21.32	19.76
CSMN37MF-2.5	Deluxe Molded Cable, DB37 Male / Female, 2.5ft (0.8m)	27.50	25.85	24.20	22.55	20.90
CSMN37MF-5	Deluxe Molded Cable, DB37 Male / Female, 5.0ft (1.5m)	30.00	28.20	26.40	24.60	22.80
CSMN37MF-10	Deluxe Molded Cable, DB37 Male / Female, 10.0ft (3.0m)	35.00	32.90	30.80	28.70	26.60
CSMN37MF-25	Deluxe Molded Cable, DB37 Male / Female, 25.0ft (7.6m)	50.00	47.00	44.00	41.00	38.00
CSMN37MF-50	Deluxe Molded Cable, DB37 Male / Female, 50.0ft (15.2m)	75.00	70.50	66.00	61.50	57.00
✓RoHS Deluxe 50 Pin D-Sub Molded Cables with Thumbscrews - Shielded and Fully Populated						
CSMN50MM-1	Deluxe Molded Cable, DB50 Male / Male, 1.0ft (0.3m)	47.00	44.18	41.36	38.54	35.72
CSMN50MM-2.5	Deluxe Molded Cable, DB50 Male / Male, 2.5ft (0.8m)	51.50	48.41	45.32	42.23	39.14
CSMN50MM-10	Deluxe Molded Cable, DB50 Male / Male, 10.0ft (3.0m)	74.00	69.56	65.12	60.68	56.24
CSMN50MM-25	Deluxe Molded Cable, DB50 Male / Male, 25.0ft (7.6m)	119.00	111.86	104.72	97.58	90.44
CSMN50MM-50	Deluxe Molded Cable, DB50 Male / Male, 50.0ft (15.2m)	194.00	182.36	170.72	159.08	147.44
CSMN50MF-1	Deluxe Molded Cable, DB50 Male / Female, 1.0ft (0.3m)	47.00	44.18	41.36	38.54	35.72
CSMN50MF-2.5	Deluxe Molded Cable, DB50 Male / Female, 2.5ft (0.8m)	51.50	48.41	45.32	42.23	39.14
CSMN50MF-10	Deluxe Molded Cable, DB50 Male / Female, 10.0ft (3.0m)	74.00	69.56	65.12	60.68	56.24
CSMN50MF-25	Deluxe Molded Cable, DB50 Male / Female, 25.0ft (7.6m)	119.00	111.86	104.72	97.58	90.44
CSMN50MF-50	Deluxe Molded Cable, DB50 Male / Female, 50.0ft (15.2m)	194.00	182.36	170.72	159.08	147.44
✓RoHS Replacement 4-40 Screws for CSMN Series Assemblies - Sold in 10/Packs						
TS-CSMN	Replacement Screws for CSMN Series Assemblies, Pkg/10	4.10	3.85	3.61	3.36	3.12

Heavy Duty D-Sub Cables - 20 AWG Conductors, Double Shielded

L-com's new, ground breaking D-Sub cables use 20 AWG conductors, the largest conductor most D-Sub connectors can accommodate. This allows for maximum current throughput as well as an extremely durable assembly. Other key features include double shielding to prevent against data corrupting EMI/RFI, threaded inserts allowing the cable to be panel mounted directly without use of an adapter, and straight through wiring to accommodate most applications. Standard lengths range from 1 to 50ft (0.3 to 15.2m) and custom lengths/pinouts are available with modest minimum requirements.



✓RoHS Heavy Duty 9 Pin D-Sub Molded Cables with Thumbscrews - 20 AWG Conductors, Double Shielded

CPMS9MM-1	Heavy Duty Molded Cable, DB9 Male / Male, 1.0ft (0.3m)	15.50	14.57	13.64	12.71	11.78
CPMS9MM-2.5	Heavy Duty Molded Cable, DB9 Male / Male, 2.5ft (0.8m)	18.15	17.06	15.97	14.88	13.79
CPMS9MM-5	Heavy Duty Molded Cable, DB9 Male / Male, 5.0ft (1.5m)	22.50	21.15	19.80	18.45	17.10
CPMS9MM-10	Heavy Duty Molded Cable, DB9 Male / Male, 10.0ft (3.0m)	31.25	29.38	27.50	25.63	23.75
CPMS9MM-25	Heavy Duty Molded Cable, DB9 Male / Male, 25.0ft (7.6m)	57.50	54.05	50.60	47.15	43.70
CPMS9MM-50	Heavy Duty Molded Cable, DB9 Male / Male, 50.0ft (15.2m)	101.25	95.17	89.10	83.03	76.95
CPMS9MF-1	Heavy Duty Molded Cable, DB9 Male / Female, 1.0ft (0.3m)	15.50	14.57	13.64	12.71	11.78
CPMS9MF-2.5	Heavy Duty Molded Cable, DB9 Male / Female, 2.5ft (0.8m)	18.15	17.06	15.97	14.88	13.79
CPMS9MF-5	Heavy Duty Molded Cable, DB9 Male / Female, 5.0ft (1.5m)	22.50	21.15	19.80	18.45	17.10
CPMS9MF-10	Heavy Duty Molded Cable, DB9 Male / Female, 10.0ft (3.0m)	31.25	29.38	27.50	25.63	23.75
CPMS9MF-25	Heavy Duty Molded Cable, DB9 Male / Female, 25.0ft (7.6m)	57.50	54.05	50.60	47.15	43.70
CPMS9MF-50	Heavy Duty Molded Cable, DB9 Male / Female, 50.0ft (15.2m)	101.25	95.17	89.10	83.03	76.95

✓RoHS Heavy Duty 15 Pin D-Sub Molded Cables with Thumbscrews - 20 AWG Conductors, Double Shielded

CPMS15MM-1	Heavy Duty Molded Cable, DB15 Male / Male, 1.0ft (0.3m)	21.50	20.21	18.92	17.63	16.34
CPMS15MM-2.5	Heavy Duty Molded Cable, DB15 Male / Male, 2.5ft (0.8m)	25.65	24.11	22.57	21.03	19.49
CPMS15MM-5	Heavy Duty Molded Cable, DB15 Male / Male, 5.0ft (1.5m)	32.50	30.55	28.60	26.65	24.70
CPMS15MM-10	Heavy Duty Molded Cable, DB15 Male / Male, 10.0ft (3.0m)	46.25	43.47	40.70	37.93	35.15
CPMS15MM-25	Heavy Duty Molded Cable, DB15 Male / Male, 25.0ft (7.6m)	87.50	82.25	77.00	71.75	66.50
CPMS15MM-50	Heavy Duty Molded Cable, DB15 Male / Male, 50.0ft (15.2m)	156.25	146.88	137.50	128.13	118.75
CPMS15MF-1	Heavy Duty Molded Cable, DB15 Male / Female, 1.0ft (0.3m)	21.50	20.21	18.92	17.63	16.34
CPMS15MF-2.5	Heavy Duty Molded Cable, DB15 Male / Female, 2.5ft (0.8m)	25.65	24.11	22.57	21.03	19.49
CPMS15MF-5	Heavy Duty Molded Cable, DB15 Male / Female, 5.0ft (1.5m)	32.50	30.55	28.60	26.65	24.70
CPMS15MF-10	Heavy Duty Molded Cable, DB15 Male / Female, 10.0ft (3.0m)	46.25	43.47	40.70	37.93	35.15
CPMS15MF-25	Heavy Duty Molded Cable, DB15 Male / Female, 25.0ft (7.6m)	87.50	82.25	77.00	71.75	66.50
CPMS15MF-50	Heavy Duty Molded Cable, DB15 Male / Female, 50.0ft (15.2m)	156.25	146.88	137.50	128.13	118.75

✓RoHS Heavy Duty 25 Pin D-Sub Molded Cables with Thumbscrews - 20 AWG Conductors, Double Shielded

CPMS25MM-1	Heavy Duty Molded Cable, DB25 Male / Male, 1.0ft (0.3m)	28.50	26.79	25.08	23.37	21.66
CPMS25MM-2.5	Heavy Duty Molded Cable, DB25 Male / Male, 2.5ft (0.8m)	35.65	33.51	31.37	29.23	27.09
CPMS25MM-5	Heavy Duty Molded Cable, DB25 Male / Male, 5.0ft (1.5m)	47.50	44.65	41.80	38.95	36.10
CPMS25MM-10	Heavy Duty Molded Cable, DB25 Male / Male, 10.0ft (3.0m)	71.25	66.97	62.70	58.43	54.15
CPMS25MM-25	Heavy Duty Molded Cable, DB25 Male / Male, 25.0ft (7.6m)	142.50	133.95	125.40	116.85	108.30
CPMS25MM-50	Heavy Duty Molded Cable, DB25 Male / Male, 50.0ft (15.2m)	261.25	245.57	229.90	214.23	198.55
CPMS25MF-1	Heavy Duty Molded Cable, DB25 Male / Female, 1.0ft (0.3m)	28.50	26.79	25.08	23.37	21.66
CPMS25MF-2.5	Heavy Duty Molded Cable, DB25 Male / Female, 2.5ft (0.8m)	35.65	33.51	31.37	29.23	27.09
CPMS25MF-5	Heavy Duty Molded Cable, DB25 Male / Female, 5.0ft (1.5m)	47.50	44.65	41.80	38.95	36.10
CPMS25MF-10	Heavy Duty Molded Cable, DB25 Male / Female, 10.0ft (3.0m)	71.25	66.97	62.70	58.43	54.15
CPMS25MF-25	Heavy Duty Molded Cable, DB25 Male / Female, 25.0ft (7.6m)	142.50	133.95	125.40	116.85	108.30
CPMS25MF-50	Heavy Duty Molded Cable, DB25 Male / Female, 50.0ft (15.2m)	261.25	245.57	229.90	214.23	198.55

✓RoHS Replacement 4-40 Screws for CPMS Series Assemblies - Sold in 10/Packs

TS-CSMN	Replacement Screws for CPMS Series Assemblies, Pkg/10	4.10	3.85	3.61	3.36	3.12
---------	---	------	------	------	------	------

