


Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

Premium D-Sub Cable Assemblies - Fully Populated and Double Shielded

The CS2N Series of D-Sub cable assemblies is our top of the line D-Sub cabling offering. These cables offer the best features for those applications where only the best will do. The bulk cable utilizes 26AWG stranded conductors with double shielding (copper braid plus aluminum mylar foil) and flexible PVC jacket. Fully molded backshells also have a unique stamped steel internal enclosure that provides the ultimate in shielding performance. Mounting is done via rugged 4-40 thumbscrews that are easy to grip without the need for a screwdriver. Hex nuts on female connectors are removable to expose 4-40 thumbscrews. Color: Light Gray.

• More lengths available. Go to L-com.com



No more D-Sub connector gender confusion!

Online Video
L-com.com/Videos/A14

Best Seller



RoHS Premium 9 Pin D-Sub Cables - Molded, Fully Populated and Double Shielded

CS2N9MM-1	Premium Molded Cable, DB9 Male / Male, 1.0ft (0.3m)	14.90	14.01	13.11	12.22	11.32
CS2N9MM-2.5	Premium Molded Cable, DB9 Male / Male, 2.5ft (0.75m)	16.25	15.27	14.30	13.33	12.35
CS2N9MM-6	Premium Molded Cable, DB9 Male / Male, 6.0ft (1.8m)	19.40	18.24	17.07	15.91	14.74
CS2N9MM-10	Premium Molded Cable, DB9 Male / Male, 10.0ft (3.0m)	23.00	21.62	20.24	18.86	17.48
CS2N9MM-15	Premium Molded Cable, DB9 Male / Male, 15.0ft (4.6m)	27.50	25.85	24.20	22.55	20.90
CS2N9MM-25	Premium Molded Cable, DB9 Male / Male, 25.0ft (7.6m)	36.50	34.31	32.12	29.93	27.74
CS2N9MM-50	Premium Molded Cable, DB9 Male / Male, 50.0ft (15.2m)	59.00	55.46	51.92	48.38	44.84
CS2N9MF-1	Premium Molded Cable, DB9 Male / Female, 1.0ft (0.3m)	14.90	14.01	13.11	12.22	11.32
CS2N9MF-2.5	Premium Molded Cable, DB9 Male / Female, 2.5ft (0.75m)	16.25	15.27	14.30	13.33	12.35
CS2N9MF-6	Premium Molded Cable, DB9 Male / Female, 6.0ft (1.8m)	19.40	18.24	17.07	15.91	14.74
CS2N9MF-10	Premium Molded Cable, DB9 Male / Female, 10.0ft (3.0m)	23.00	21.62	20.24	18.86	17.48
CS2N9MF-15	Premium Molded Cable, DB9 Male / Female, 15.0ft (4.6m)	27.50	25.85	24.20	22.55	20.90
CS2N9MF-25	Premium Molded Cable, DB9 Male / Female, 25.0ft (7.6m)	36.50	34.31	32.12	29.93	27.74
CS2N9MF-50	Premium Molded Cable, DB9 Male / Female, 50.0ft (15.2m)	59.00	55.46	51.92	48.38	44.84

RoHS Premium HD15 D-Sub Cables - Molded, Fully Populated and Double Shielded

CS2H15MM-1	Premium Molded Cable, HD15 Male / Male, 1.0ft (0.3m)	19.00	17.86	16.72	15.58	14.44
CS2H15MM-2.5	Premium Molded Cable, HD15 Male / Male, 2.5ft (0.75m)	20.50	19.27	18.04	16.81	15.58
CS2H15MM-5	Premium Molded Cable, HD15 Male / Male, 5.0ft (1.5m)	23.00	21.62	20.24	18.86	17.48
CS2H15MM-10	Premium Molded Cable, HD15 Male / Male, 10.0ft (3.0m)	28.00	26.32	24.64	22.96	21.28
CS2H15MM-25	Premium Molded Cable, HD15 Male / Male, 25.0ft (7.6m)	43.00	40.42	37.84	35.26	32.68
CS2H15MM-50	Premium Molded Cable, HD15 Male / Male, 50.0ft (15.2m)	68.00	63.92	59.84	55.76	51.68
CS2H15MF-1	Premium Molded Cable, HD15 Male / Female, 1.0ft (0.3m)	19.00	17.86	16.72	15.58	14.44
CS2H15MF-2.5	Premium Molded Cable, HD15 Male / Female, 2.5ft (0.75m)	20.50	19.27	18.04	16.81	15.58
CS2H15MF-5	Premium Molded Cable, HD15 Male / Female, 5.0ft (1.5m)	23.00	21.62	20.24	18.86	17.48
CS2H15MF-10	Premium Molded Cable, HD15 Male / Female, 10.0ft (3.0m)	28.00	26.32	24.64	22.96	21.28
CS2H15MF-25	Premium Molded Cable, HD15 Male / Female, 25.0ft (7.6m)	43.00	40.42	37.84	35.26	32.68
CS2H15MF-50	Premium Molded Cable, HD15 Male / Female, 50.0ft (15.2m)	68.00	63.92	59.84	55.76	51.68

RoHS Premium DB15 D-Sub Cables - Molded, Fully Populated and Double Shielded

CS2N15MM-1	Premium Molded Cable, DB15 Male / Male, 1.0ft (0.3m)	19.20	18.05	16.90	15.74	14.59
CS2N15MM-2.5	Premium Molded Cable, DB15 Male / Male, 2.5ft (0.75m)	20.40	19.18	17.95	16.73	15.50
CS2N15MM-5	Premium Molded Cable, DB15 Male / Male, 5.0ft (1.5m)	22.00	20.68	19.36	18.04	16.72
CS2N15MM-10	Premium Molded Cable, DB15 Male / Male, 10.0ft (3.0m)	25.50	23.97	22.44	20.91	19.38
CS2N15MM-25	Premium Molded Cable, DB15 Male / Male, 25.0ft (7.6m)	36.00	33.84	31.68	29.52	27.36
CS2N15MF-1	Premium Molded Cable, DB15 Male / Female, 1.0ft (0.3m)	19.20	18.05	16.90	15.74	14.59
CS2N15MF-2.5	Premium Molded Cable, DB15 Male / Female, 2.5ft (0.75m)	20.40	19.18	17.95	16.73	15.50
CS2N15MF-5	Premium Molded Cable, DB15 Male / Female, 5.0ft (1.5m)	22.00	20.68	19.36	18.04	16.72
CS2N15MF-10	Premium Molded Cable, DB15 Male / Female, 10.0ft (3.0m)	25.50	23.97	22.44	20.91	19.38
CS2N15MF-25	Premium Molded Cable, DB15 Male / Female, 25.0ft (7.6m)	36.00	33.84	31.68	29.52	27.36

RoHS Premium 25 Pin D-Sub Cables - Molded, Fully Populated and Double Shielded

CS2N25MM-1	Premium Molded Cable, DB25 Male / Male, 1.0ft (0.3m)	21.00	19.74	18.48	17.22	15.96
CS2N25MM-2.5	Premium Molded Cable, DB25 Male / Male, 2.5ft (0.75m)	22.50	21.15	19.80	18.45	17.10
CS2N25MM-5	Premium Molded Cable, DB25 Male / Male, 5.0ft (1.5m)	25.00	23.50	22.00	20.50	19.00
CS2N25MM-10	Premium Molded Cable, DB25 Male / Male, 10.0ft (3.0m)	30.00	28.20	26.40	24.60	22.80
CS2N25MM-25	Premium Molded Cable, DB25 Male / Male, 25.0ft (7.6m)	45.00	42.30	39.60	36.90	34.20
CS2N25MM-50	Premium Molded Cable, DB25 Male / Male, 50.0ft (15.2m)	70.00	65.80	61.60	57.40	53.20
CS2N25MF-1	Premium Molded Cable, DB25 Male / Female, 1.0ft (0.3m)	21.00	19.74	18.48	17.22	15.96
CS2N25MF-5	Premium Molded Cable, DB25 Male / Female, 5.0ft (1.5m)	25.00	23.50	22.00	20.50	19.00
CS2N25MF-10	Premium Molded Cable, DB25 Male / Female, 10.0ft (3.0m)	30.00	28.20	26.40	24.60	22.80
CS2N25MF-25	Premium Molded Cable, DB25 Male / Female, 25.0ft (7.6m)	45.00	42.30	39.60	36.90	34.20
CS2N25MF-50	Premium Molded Cable, DB25 Male / Female, 50.0ft (15.2m)	70.00	65.80	61.60	57.40	53.20

RoHS Premium 37 Pin D-Sub Cables - Molded, Fully Populated and Double Shielded

CS2N37MM-1	Premium Molded Cable, DB37 Male / Male, 1.0ft (0.3m)	36.50	34.31	32.12	29.93	27.74
CS2N37MM-2.5	Premium Molded Cable, DB37 Male / Male, 2.5ft (0.75m)	38.75	36.42	34.10	31.78	29.45
CS2N37MM-5	Premium Molded Cable, DB37 Male / Male, 5.0ft (1.5m)	42.50	39.95	37.40	34.85	32.30
CS2N37MM-10	Premium Molded Cable, DB37 Male / Male, 10.0ft (3.0m)	50.00	47.00	44.00	41.00	38.00
CS2N37MM-25	Premium Molded Cable, DB37 Male / Male, 25.0ft (7.6m)	72.50	68.15	63.80	59.45	55.10
CS2N37MF-1	Premium Molded Cable, DB37 Male / Female, 1.0ft (0.3m)	36.50	34.31	32.12	29.93	27.74
CS2N37MF-2.5	Premium Molded Cable, DB37 Male / Female, 2.5ft (0.75m)	38.75	36.42	34.10	31.78	29.45
CS2N37MF-5	Premium Molded Cable, DB37 Male / Female, 5.0ft (1.5m)	42.50	39.95	37.40	34.85	32.30
CS2N37MF-10	Premium Molded Cable, DB37 Male / Female, 10.0ft (3.0m)	50.00	47.00	44.00	41.00	38.00
CS2N37MF-25	Premium Molded Cable, DB37 Male / Female, 25.0ft (7.6m)	72.50	68.15	63.80	59.45	55.10

RoHS Replacement 4-40 Screws for CS2N and CS2H Series Assemblies - Sold in 10/Packs

TS-CS21	Replacement Screws for CS2N9, CS2N15, CS2H15 Series Assemblies, Pkg/10	3.90	3.67	3.43	3.20	2.96
TS-CS2N25	Replacement Screws for CS2N25 Series Assemblies, Pkg/10	4.10	3.85	3.61	3.36	3.12
TS-CS2N37	Replacement Screws for CS2N37 Series Assemblies, Pkg/10	4.25	3.99	3.74	3.49	3.23



Distinguishing between male and female D-Sub connectors
See the free video tip and more at L-com.com/Videos/A14