



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

Deluxe Molded Black D-Sub Cables

These cables give the user the option to color match to black equipment and are constructed identically to our popular CSMN light gray cable series.

✓RoHS Deluxe 9 Pin D-Sub Molded Cables - Shielded and Fully Populated

CSMNB9MM-1	Deluxe Molded Cable, DB9 Male / Male, 1.0ft (0.3m)	6.75	6.21	5.67	5.13	4.59
CSMNB9MM-5	Deluxe Molded Cable, DB9 Male / Male, 5.0ft (1.5m)	8.75	8.05	7.35	6.65	5.95
CSMNB9MM-10	Deluxe Molded Cable, DB9 Male / Male, 10.0ft (3.0m)	11.25	10.35	9.45	8.55	7.65
CSMNB9MM-25	Deluxe Molded Cable, DB9 Male / Male, 25.0ft (7.6m)	18.75	17.25	15.75	14.25	12.75
CSMNB9MM-50	Deluxe Molded Cable, DB9 Male / Male, 50.0ft (15.2m)	31.25	28.75	26.25	23.75	21.25
CSMNB9MF-2.5	Deluxe Molded Cable, DB9 Male / Female, 2.5ft (0.8m)	7.50	6.90	6.30	5.70	5.10
CSMNB9MF-5	Deluxe Molded Cable, DB9 Male / Female, 5.0ft (1.5m)	8.75	8.05	7.35	6.65	5.95
CSMNB9MF-10	Deluxe Molded Cable, DB9 Male / Female, 10.0ft (3.0m)	11.25	10.35	9.45	8.55	7.65
CSMNB9MF-15	Deluxe Molded Cable, DB9 Male / Female, 15.0ft (4.6m)	13.75	12.65	11.55	10.45	9.35
CSMNB9MF-50	Deluxe Molded Cable, DB9 Male / Female, 50.0ft (15.2m)	31.25	28.75	26.25	23.75	21.25

✓RoHS Deluxe 15 Pin D-Sub Molded Cables - Shielded and Fully Populated

CSMNB15MM-1	Deluxe Molded Cable, DB15 Male / Male, 1.0ft (0.3m)	10.35	9.73	9.11	8.49	7.87
CSMNB15MM-5	Deluxe Molded Cable, DB15 Male / Male, 5.0ft (1.5m)	12.75	11.98	11.22	10.46	9.69
CSMNB15MM-10	Deluxe Molded Cable, DB15 Male / Male, 10.0ft (3.0m)	15.75	14.80	13.86	12.92	11.97
CSMNB15MM-25	Deluxe Molded Cable, DB15 Male / Male, 25.0ft (7.6m)	24.75	23.26	21.78	20.30	18.81
CSMNB15MM-50	Deluxe Molded Cable, DB15 Male / Male, 50.0ft (15.2m)	39.75	37.36	34.98	32.60	30.21
CSMNB15MF-1	Deluxe Molded Cable, DB15 Male / Female, 1.0ft (0.3m)	10.35	9.73	9.11	8.49	7.87
CSMNB15MF-2.5	Deluxe Molded Cable, DB15 Male / Female, 2.5ft (0.8m)	11.25	10.57	9.90	9.23	8.55
CSMNB15MF-5	Deluxe Molded Cable, DB15 Male / Female, 5.0ft (1.5m)	12.75	11.98	11.22	10.46	9.69
CSMNB15MF-10	Deluxe Molded Cable, DB15 Male / Female, 10.0ft (3.0m)	15.75	14.80	13.86	12.92	11.97
CSMNB15MF-15	Deluxe Molded Cable, DB15 Male / Female, 15.0ft (4.6m)	18.75	17.63	16.50	15.38	14.25
CSMNB15MF-25	Deluxe Molded Cable, DB15 Male / Female, 25.0ft (7.6m)	24.75	23.26	21.78	20.30	18.81
CSMNB15MF-50	Deluxe Molded Cable, DB15 Male / Female, 50.0ft (15.2m)	39.75	37.36	34.98	32.60	30.21

✓RoHS Deluxe 25 Pin D-Sub Molded Cables - Shielded and Fully Populated

CSMNB25MM-1	Deluxe Molded Cable, DB25 Male / Male, 1.0ft (0.3m)	9.15	8.42	7.69	6.95	6.22
CSMNB25MM-5	Deluxe Molded Cable, DB25 Male / Male, 5.0ft (1.5m)	10.75	9.89	9.03	8.17	7.31
CSMNB25MM-10	Deluxe Molded Cable, DB25 Male / Male, 10.0ft (3.0m)	12.75	11.73	10.71	9.69	8.67
CSMNB25MM-25	Deluxe Molded Cable, DB25 Male / Male, 25.0ft (7.6m)	18.75	17.25	15.75	14.25	12.75
CSMNB25MM-50	Deluxe Molded Cable, DB25 Male / Male, 50.0ft (15.2m)	28.75	26.45	24.15	21.85	19.55
CSMNB25MF-2.5	Deluxe Molded Cable, DB25 Male / Female, 2.5ft (0.8m)	9.75	8.97	8.19	7.41	6.63
CSMNB25MF-5	Deluxe Molded Cable, DB25 Male / Female, 5.0ft (1.5m)	10.75	9.89	9.03	8.17	7.31
CSMNB25MF-10	Deluxe Molded Cable, DB25 Male / Female, 10.0ft (3.0m)	12.75	11.73	10.71	9.69	8.67
CSMNB25MF-15	Deluxe Molded Cable, DB25 Male / Female, 15.0ft (4.6m)	14.75	13.57	12.39	11.21	10.03
CSMNB25MF-50	Deluxe Molded Cable, DB25 Male / Female, 50.0ft (15.2m)	28.75	26.45	24.15	21.85	19.55

Low Smoke Zero Halogen (LSZH) D-Sub Cable Assemblies, DB9, DB15 and DB25

LSZH D-Sub cable assemblies are available in DB9, DB15 and DB25 connector sizes with male to male and male to female configurations. Cable is 24AWG with a foil/braid shield. Color is black.

✓RoHS Low Smoke Zero Halogen 9 Pin D-Sub Cables - Fully Populated and Double Shielded

CSMUZ9MM-1	LSZH Cable, DB9 Male / Male, 1.0ft (0.3m)	27.75	26.64	25.53	24.42	23.31
CSMUZ9MM-5	LSZH Cable, DB9 Male / Male, 5.0ft (1.5m)	33.75	32.40	31.05	29.70	28.35
CSMUZ9MM-10	LSZH Cable, DB9 Male / Male, 10.0ft (3.0m)	41.25	39.60	37.95	36.30	34.65
CSMUZ9MM-25	LSZH Cable, DB9 Male / Male, 25.0ft (7.6m)	56.25	51.75	47.25	42.75	38.25
CSMUZ9MM-125	LSZH Cable, DB9 Male / Male, 125.0ft (38.1m)	206.25	198.00	189.75	181.50	173.25
CSMUZ9MF-1	LSZH Cable, DB9 Male / Female, 1.0ft (0.3m)	27.75	26.64	25.53	24.42	23.31
CSMUZ9MF-5	LSZH Cable, DB9 Male / Female, 5.0ft (1.5m)	33.75	32.40	31.05	29.70	28.35
CSMUZ9MF-10	LSZH Cable, DB9 Male / Female, 10.0ft (3.0m)	41.25	39.60	37.95	36.30	34.65
CSMUZ9MF-25	LSZH Cable, DB9 Male / Female, 25.0ft (7.6m)	56.25	54.00	51.75	49.50	47.25
CSMUZ9MF-125	LSZH Cable, DB9 Male / Female, 125.0ft (38.1m)	206.25	198.00	189.75	181.50	173.25

✓RoHS Low Smoke Zero Halogen 15 Pin D-Sub Cables - Fully Populated and Double Shielded

CSMUZ15MM-1	LSZH Cable, DB15 Male / Male, 1.0ft (0.3m)	29.50	28.32	27.14	25.96	24.78
CSMUZ15MM-2.5	LSZH Cable, DB15 Male / Male, 2.5ft (0.8m)	32.50	31.20	29.90	28.60	27.30
CSMUZ15MM-5	LSZH Cable, DB15 Male / Male, 5.0ft (1.5m)	37.50	36.00	34.50	33.00	31.50
CSMUZ15MM-10	LSZH Cable, DB15 Male / Male, 10.0ft (3.0m)	47.50	45.60	43.70	41.80	39.90
CSMUZ15MM-15	LSZH Cable, DB15 Male / Male, 15.0ft (4.6m)	57.50	55.20	52.90	50.60	48.30
CSMUZ15MM-25	LSZH Cable, DB15 Male / Male, 25.0ft (7.6m)	66.00	63.36	60.72	58.08	55.44
CSMUZ15MM-50	LSZH Cable, DB15 Male / Male, 50.0ft (15.2m)	116.00	111.36	106.72	102.08	97.44
CSMUZ15MM-125	LSZH Cable, DB15 Male / Male, 125.0ft (38.1m)	266.00	255.36	244.72	234.08	223.44
CSMUZ15MF-1	LSZH Cable, DB15 Male / Female, 1.0ft (0.3m)	29.50	28.32	27.14	25.96	24.78
CSMUZ15MF-2.5	LSZH Cable, DB15 Male / Female, 2.5ft (0.8m)	32.50	31.20	29.90	28.60	27.30
CSMUZ15MF-5	LSZH Cable, DB15 Male / Female, 5.0ft (1.5m)	37.50	36.00	34.50	33.00	31.50
CSMUZ15MF-10	LSZH Cable, DB15 Male / Female, 10.0ft (3.0m)	47.50	45.60	43.70	41.80	39.90
CSMUZ15MF-15	LSZH Cable, DB15 Male / Female, 15.0ft (4.6m)	57.50	55.20	52.90	50.60	48.30
CSMUZ15MF-25	LSZH Cable, DB15 Male / Female, 25.0ft (7.6m)	66.00	63.36	60.72	58.08	55.44
CSMUZ15MF-50	LSZH Cable, DB15 Male / Female, 50.0ft (15.2m)	116.00	111.36	106.72	102.08	97.44
CSMUZ15MF-125	LSZH Cable, DB15 Male / Female, 125.0ft (38.1m)	266.00	255.36	244.72	234.08	223.44

✓RoHS Low Smoke Zero Halogen 25 Pin D-Sub Cables - Fully Populated and Double Shielded

CSMUZ25MM-2.5	LSZH Cable, DB25 Male / Male, 2.5ft (0.8m)	37.50	36.00	34.50	33.00	31.50
CSMUZ25MM-5	LSZH Cable, DB25 Male / Male, 5.0ft (1.5m)	45.00	43.20	41.40	39.60	37.80
CSMUZ25MM-15	LSZH Cable, DB25 Male / Male, 15.0ft (4.6m)	75.00	72.00	69.00	66.00	63.00
CSMUZ25MM-50	LSZH Cable, DB25 Male / Male, 50.0ft (15.2m)	165.00	158.40	151.80	145.20	138.60
CSMUZ25MM-125	LSZH Cable, DB25 Male / Male, 125.0ft (38.1m)	390.00	374.40	358.80	343.20	327.60
CSMUZ25MF-2.5	LSZH Cable, DB25 Male / Female, 2.5ft (0.8m)	37.50	36.00	34.50	33.00	31.50
CSMUZ25MF-5	LSZH Cable, DB25 Male / Female, 5.0ft (1.5m)	45.00	43.20	41.40	39.60	37.80
CSMUZ25MF-15	LSZH Cable, DB25 Male / Female, 15.0ft (4.6m)	75.00	72.00	69.00	66.00	63.00
CSMUZ25MF-50	LSZH Cable, DB25 Male / Female, 50.0ft (15.2m)	165.00	158.40	151.80	145.20	138.60
CSMUZ25MF-125	LSZH Cable, DB25 Male / Female, 125.0ft (38.1m)	390.00	374.40	358.80	343.20	327.60

More lengths available. Go to L-com.com