


**Multiconductor**

CS4-100  
• 4 Conductors

CS9-100  
• 9 Conductors

CS25-100  
• 25 Conductors




**Bulk Twisted Pair**

CSTP5-100  
• 5 Pair

CSTP125-100  
• 12.5 Pair


CSTP19-100  
• 19 Pair



**Low Smoke Zero Halogen**

CSLSZH09-100  
• 9 Conductors

CSLSZH25-100  
• 25 Conductors




**New PVC Large Gauge**

CSCPMS09-100  
• 9 Conductors

CSCPMS15-100  
• 15 Conductors

CSCPMS25-100  
• 25 Conductors



**Plenum Hi-Temperature**

CSPL04-100  
• 4 Conductors

CSPL15-100  
• 15 Conductors

Item #	Description	List Price
<b>✓RoHS Bulk Multiconductor Data Cable - 24 AWG Stranded Conductors</b>		
This is one of the most popular choices for data cable applications. Conductors are 24 AWG 7/32 stranded conductors with PVC insulation. Jacket is also PVC, color is Chrome Gray. Foil shielding with tinned drain wire. Choose from 4, 9, 15 or 25 conductors and 100 foot coils or 500 and 1,000 foot spools. UL and CSA Listed.		
CS4-100	4 Conductor 24 AWG Bulk Cable, 100ft (30.5m) Coil	24.00
CS4-500	4 Conductor 24 AWG Bulk Cable, 500ft (152.4m) Spool	120.00
CS4-1000	4 Conductor 24 AWG Bulk Cable, 1000ft (304.8m) Spool	240.00
CS9-100	9 Conductor 24 AWG Bulk Cable, 100ft (30.5m) Coil	34.00
CS9-500	9 Conductor 24 AWG Bulk Cable, 500ft (152.4m) Spool	170.00
CS9-1000	9 Conductor 24 AWG Bulk Cable, 1000ft (304.8m) Spool	340.00
CS15-100	15 Conductor 24 AWG Bulk Cable, 100ft (30.5m) Coil	50.00
CS15-500	15 Conductor 24 AWG Bulk Cable, 500ft (152.4m) Spool	250.00
CS15-1000	15 Conductor 24 AWG Bulk Cable, 1000ft (304.8m) Spool	500.00
CS25-100	25 Conductor 24 AWG Bulk Cable, 100ft (30.5m) Coil	80.00
CS25-500	25 Conductor 24 AWG Bulk Cable, 500ft (152.4m) Spool	400.00
CS25-1000	25 Conductor 24 AWG Bulk Cable, 1000ft (304.8m) Spool	800.00

<b>✓RoHS Bulk Twisted Pair Data Cable - Double Shielded, 26 AWG Stranded Conductors</b>		
Twisted pair bulk cable features difficult to find 26 AWG conductors with foil, drain wire and braid shield as well as a flexible PVC jacket. Choose from 5, 12.5, 19, or 25 pairs in 100, 500 or 1,000 foot spools. Jacket color is Light Gray.		
CSTP5-100	5 Pair 26 AWG Bulk Cable, 100ft (30.5m) Spool	54.00
CSTP5-500	5 Pair 26 AWG Bulk Cable, 500ft (152.4m) Spool	270.00
CSTP5-1000	5 Pair 26 AWG Bulk Cable, 1000ft (304.8m) Spool	540.00
CSTP125-100	12.5 Pair 26 AWG Bulk Cable, 100ft (30.5m) Spool	130.00
CSTP125-500	12.5 Pair 26 AWG Bulk Cable, 500ft (152.4m) Spool	650.00
CSTP125-1000	12.5 Pair 26 AWG Bulk Cable, 1000ft (304.8m) Spool	1300.00
CSTP19-100	19 Pair 26 AWG Bulk Cable, 100ft (30.5m) Spool	160.00
CSTP19-500	19 Pair 26 AWG Bulk Cable, 500ft (152.4m) Spool	800.00
CSTP19-1000	19 Pair 26 AWG Bulk Cable, 1000ft (304.8m) Spool	1600.00
CSTP25-100	25 Pair 26 AWG Bulk Cable, 100ft (30.5m) Spool	270.00
CSTP25-500	25 Pair 26 AWG Bulk Cable, 500ft (152.4m) Spool	1350.00

<b>✓RoHS Low Smoke Zero Halogen Data Cable - Double Shielded, 24 AWG Stranded Conductors</b>		
Low smoke zero halogen cable reduces the amount of toxic and corrosive gasses emitted during combustion. Typically used in poorly ventilated areas, low smoke zero halogen is becoming very popular with military contractors. Cable construction features 24 AWG stranded tinned copper conductors with high density polyethylene insulation, overall aluminum polyester foil shield with tinned copper braid and a 24 AWG drain wire. Cable jacket color is Black. Choose from 9, 15, or 25 conductor cable and 100, 500, or 1,000 foot put ups. L-com will manufacture cable assemblies featuring low smoke zero halogen cable with modest minimum requirements.		
CSLSZH09-100	9 Conductor 24 AWG LSZH Bulk Cable, 100ft (30.5m) Coil	70.00
CSLSZH09-500	9 Conductor 24 AWG LSZH Bulk Cable, 500ft (152.4m) Spool	350.00
CSLSZH09-1000	9 Conductor 24 AWG LSZH Bulk Cable, 1000ft (304.8m) Spool	700.00
CSLSZH15-100	15 Conductor 24 AWG LSZH Bulk Cable, 100ft (30.5m) Coil	120.00
CSLSZH15-500	15 Conductor 24 AWG LSZH Bulk Cable, 500ft (152.4m) Spool	600.00
CSLSZH15-1000	15 Conductor 24 AWG LSZH Bulk Cable, 1000ft (304.8m) Spool	1200.00
CSLSZH25-100	25 Conductor 24 AWG LSZH Bulk Cable, 100ft (30.5m) Coil	150.00
CSLSZH25-500	25 Conductor 24 AWG LSZH Bulk Cable, 500ft (152.4m) Spool	750.00
CSLSZH25-1000	25 Conductor 24 AWG LSZH Bulk Cable, 1000ft (304.8m) Spool	1500.00

<b>✓RoHS Heavy Duty Double Shielded Multiconductor Data Cable - 20 AWG Conductors, Foil + Braid Shield</b>		
Large gauge cable is now available for applications requiring higher current than typical data systems use. Features a dark gray UL2464 listed PVC jacket, aluminum mylar foil shield, tinned copper braid and 20 AWG stranded conductors. Available in 100, 500 or 1,000 foot spools.		
CSCPMS09-100	9 Conductor 20 AWG Double Shielded Bulk Cable, 100ft (30.5m) Coil	195.00
CSCPMS09-500	9 Conductor 20 AWG Double Shielded Bulk Cable, 500ft (152.4m) Spool	925.00
CSCPMS09-1000	9 Conductor 20 AWG Double Shielded Bulk Cable, 1000ft (304.8m) Spool	1750.00
CSCPMS15-100	15 Conductor 20 AWG Double Shielded Bulk Cable, 100ft (30.5m) Coil	300.00
CSCPMS15-500	15 Conductor 20 AWG Double Shielded Bulk Cable, 500ft (152.4m) Spool	1450.00
CSCPMS15-1000	15 Conductor 20 AWG Double Shielded Bulk Cable, 1000ft (304.8m) Spool	2750.00
CSCPMS25-100	25 Conductor 20 AWG Double Shielded Bulk Cable, 100ft (30.5m) Coil	525.00
CSCPMS25-500	25 Conductor 20 AWG Double Shielded Bulk Cable, 500ft (152.4m) Spool	2500.00
CSCPMS25-1000	25 Conductor 20 AWG Double Shielded Bulk Cable, 1000ft (304.8m) Spool	4750.00

<b>✓RoHS Plenum, Hi-Temperature Data Cable - Shielded, 24 AWG Stranded Conductors, -40°C to 150°C</b>		
Some harsh environments require protection beyond the capabilities of PVC. Halar (thermoplastic fluoropolymer) insulated cable provides excellent thermal characteristics, electrical properties and chemical resistance. Cable construction features 24 AWG stranded tinned copper conductors, overall aluminum/mylar shield with 24 AWG drain wire and Halar insulated conductors and cable jacket. Cable jacket color is Clear. Choose from 4, 9, 15, or 25 conductor cable and 100, 500, or 1,000 foot put ups. L-com will manufacture cable assemblies featuring plenum cable with modest minimum requirements.		
CSPL04-100	4 Conductor 24 AWG Plenum Bulk Cable, 100ft (30.5m) Coil	60.00
CSPL04-500	4 Conductor 24 AWG Plenum Bulk Cable, 500ft (152.4m) Spool	300.00
CSPL04-1000	4 Conductor 24 AWG Plenum Bulk Cable, 1000ft (304.8m) Spool	600.00
CSPL09-100	9 Conductor 24 AWG Plenum Bulk Cable, 100ft (30.5m) Coil	110.00
CSPL09-500	9 Conductor 24 AWG Plenum Bulk Cable, 500ft (152.4m) Spool	550.00
CSPL09-1000	9 Conductor 24 AWG Plenum Bulk Cable, 1000ft (304.8m) Spool	1100.00
CSPL15-100	15 Conductor 24 AWG Plenum Bulk Cable, 100ft (30.5m) Coil	170.00
CSPL15-500	15 Conductor 24 AWG Plenum Bulk Cable, 500ft (152.4m) Spool	850.00
CSPL15-1000	15 Conductor 24 AWG Plenum Bulk Cable, 1000ft (304.8m) Spool	1700.00
CSPL25-100	25 Conductor 24 AWG Plenum Bulk Cable, 100ft (30.5m) Coil	240.00
CSPL25-500	25 Conductor 24 AWG Plenum Bulk Cable, 500ft (152.4m) Spool	1200.00
CSPL25-1000	25 Conductor 24 AWG Plenum Bulk Cable, 1000ft (304.8m) Spool	2400.00

