

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

### Heavy Duty Cable Cutter - Cuts Copper Multiconductor Cable Clean

This heavy duty cable cutter is ideal for performing clean cuts of multiconductor cable. It offers steel construction and high leverage-extra sharp shears. The HTC60 measures 9.5" (24.1cm) in length and can cut copper multiconductor cabling up to 3/4" (1.9cm) diameter. Comfortable to use plastic dipped handles.

HTC60	Cable Cutter - to 3/4 inch (1.9cm) diameter	19.95	19.55	19.15	18.75	18.35
-------	---	-------	-------	-------	-------	-------

### Wire Stripper and Shear - Up to 20 AWG Conductors

The HTC2030 is similar in design to the HTC1620 except it has 6 circular notches for stripping 20-30 AWG wires. The tool also has a small shearing surface for cutting wires. Spring loaded design returns blades to open after use, locking mechanism keeps blades closed when not in use. Steel construction, plastic coated handles.

HTC2030	Wire Stripper and Shear	10.95	10.73	10.51	10.29	10.07
---------	-------------------------	-------	-------	-------	-------	-------

### Rotary Cable Stripper - Cuts Cable Jackets

These tools offer an economical and consistent cable jacket strip every time. Featuring easy to adjust cutting depth, these tools strip both around the cable perimeter and lengthwise. RCS10 strips cable jackets ranging from 0.125" (0.3cm) to 1.0" (2.5cm). MKO2 strips cable jackets ranging from 0.18" (0.5cm) to 1.12" (2.8cm). Choose RCS10 for light duty use and MKO2 for heavier duty use.

MKO2	Round Cable Stripper	29.95	29.35	28.75	28.15	27.55
------	----------------------	-------	-------	-------	-------	-------

### RoHS Cable Ties - 4 Sizes in Packs of 100 Pieces

Cable ties come in handy to secure cable assemblies in different applications. Four different sizes, in packages of 100 pieces each. Color is Black.

CTB-05	6 inch (20.3cm) Cable Ties, Pkg/100	6.95	6.53	6.12	5.70	CALL
CTB-07	8 inch (15.2cm) Cable Ties, Pkg/100	7.95	7.47	7.00	6.52	CALL
CTB-09	8.5 inch (21.6cm) Cable Ties, Pkg/100	8.95	8.41	7.88	7.34	CALL
CTB-12	11.5 inch (29.2cm) Cable Ties, Pkg/100	9.95	9.35	8.76	8.16	CALL

### RoHS Cable Tie Mounts - 0.75" (1.9cm) and 1.50" (3.8cm) Sizes, Pkg/10

Cable tie mounts allow the user to secure wire and/or cable quickly and easily to a surface. Mounts can be secured with screws or adhesive. Material is UL94V-2 rated nylon, color is Black.

CTM-0.75	Black Calbe Tie Mount, 0.75" (1.9cm), Pkg/10	3.75	3.45	3.15	2.85	2.55
CTM-1.5	Black Calbe Tie Mount, 1.50" (3.8cm), Pkg/10	7.25	6.67	6.09	5.51	4.93

### RoHS Spiral Wrap Tubing - Pkg/100ft (30.5m), Polyethylene Material

Polyethylene spiral wrap tubing is ideal for wire harnessing and cable bundling. Spiral wrap secures itself tightly to wire and cable being bundled, is extremely flexible, abrasion resistant and allows for easy breakouts. Available in .125" (0.3cm), .25" (0.6cm) and .5" (1.3cm) diameters, color is Clear.

TUBSWT-0.125	Spiral Wrap Tubing, .125" (0.3cm) Diameter, 100ft (30.5m)	18.50	18.13	17.76	17.39	17.02
TUBSWT-0.25	Spiral Wrap Tubing, .25" (0.6cm) Diameter, 100ft (30.5m)	29.50	28.91	28.32	27.73	27.14
TUBSWT-0.5	Spiral Wrap Tubing, .5" (1.3cm) Diameter, 100ft (30.5m)	52.50	51.45	50.40	49.35	48.30

### RoHS Expandable Sleeveing - Pkg/100ft (30.5m), Polyester Material with VW-1 Flammability Rating

Polyester expandable flexible tubing is ideal for protecting wire and/or cable. The open weave design allows for flexible routing, high resistance to abrasion and broad range of expansion. Available in .125" (0.3cm), .25" (0.6cm) and .5" (1.3cm) diameters, color is Black with White tracer.

TUBEXP-0.125	Expandable Braid Sleeveing, .125" (0.3cm) Diameter, 100ft (30.5m)	19.50	17.94	16.38	14.82	13.26
TUBEXP-0.25	Expandable Braid Sleeveing, .25" (0.6cm) Diameter, 100ft (30.5m)	24.50	22.54	20.58	18.62	16.66
TUBEXP-0.5	Expandable Braid Sleeveing, .5" (1.3cm) Diameter, 100ft (30.5m)	33.50	30.82	28.14	25.46	22.78

### RoHS Cable Labels - Wraparound Style, 3 Sizes to Choose From

We've had multiple requests for wraparound style write on labels to use for cable identification. They are now available, packaged in 30 pieces per package for the occasional user versus 1000 piece packs found elsewhere. Just write or type on the white part of the label, then wrap the clear part over to prevent smudging. There are three sizes to choose from: CL0515 up to 0.275 inch (0.7cm) diameter, CL1150 up to 0.275 inch diameter and CL1375 up to 1.0 inch (2.5cm) diameter.

CL0515	0.5in (1.3cm) x 1.5in (3.8cm) Wraparound Cable Label, Pkg/30	5.95	5.83	5.71	5.59	5.47
CL1150	1.0in (2.5cm) x 1.5in (3.8cm) Wraparound Cable Label, Pkg/30	7.95	7.79	7.63	7.47	7.31
CL1375	1.0in (2.5cm) x 3.75in (9.5cm) Wraparound Cable Label, Pkg/30	5.95	5.83	5.71	5.59	5.47

### RoHS Split Loom Tubing - Pkg/100ft (30.5m), Nylon Material

Nylon split loom tubing is ideal for automotive and industrial wire harnesses as well as marine wire protection. Split tubing allows for easy breakouts and is resistant to abrasion, gasoline, oil and other chemicals. Available in .25" (0.6cm), .5" (1.3cm) and 1" (2.5cm) diameters, color is Black.

TUBSPLT-0.25	Split Loom Tubing, .25" (0.6cm) Diameter, 100ft (30.5m)	29.50	28.91	28.32	27.73	27.14
TUBSPLT-0.5	Split Loom Tubing, .5" (1.3cm) Diameter, 100ft (30.5m)	45.50	44.59	43.68	42.77	41.86
TUBSPLT-1.0	Split Loom Tubing, 1.0" (2.5cm) Diameter, 100ft (30.5m)	55.50	54.39	53.28	52.17	51.06

Item #	Description	List Price
--------	-------------	------------

### 3M Heat Shrink Tubing Kits


3M's popular kits are versatile assortments of flexible polyolefin heat shrink tubing used in a variety of electronic and electrical applications. Each kit is packaged in a plastic box. These kits allow the engineer, designer or technician a selection of popular sizes and colors for small projects and prototypes. The black kit contains 102 pieces of six inch long tubing in six sizes ranging from 3/16 (.05cm) to 1 inch (2.5cm) inside diameter. The color kit contains 133 pieces of six inch long tubing in six sizes ranging from 3/32 (0.2cm) to 1/2 inch (1.3cm) inside diameter and seven colors. Shrink ratio is 2:1.

SPVFP301-BLK	Heat Shrink Kit, Black Colors	57.95
SPVFP301-ASST	Heat Shrink Kit, Assorted Colors	57.95

### RoHS 3M Copper Foil Shielding Tape with Conductive Adhesive

Copper foil shielding tape provides an easy to apply, time saving, cost effective way to shield against EMI/RFI radiation. This tape is conductive through the adhesive and offers mechanical, electrical and thermal values to meet shielding effectiveness frequency requirements. Meets UL 510 flame retardancy requirements. 3/8" (1.0cm) width is ideal for securing cable shields to backshell grommets. See page 93 for complete backshell offering.

TAP1181-3/8	Copper Foil Shielding Tape, 2.6 MIL x 3/8 inch (1.0cm) W x 18 Yards (16.5m)	15.50
TAP1181-3/4	Copper Foil Shielding Tape, 2.6 MIL x 3/4 inch (1.9cm) W x 18 Yards (16.5m)	30.50



**Tips**  
Easy-to-understand tips to help with some of today's popular product applications. [L-com.com/Tips](http://L-com.com/Tips)