



Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
--------	-------------	-------	-----	-------	-------	---------	---------

✓RoHS USB 3.0 Cables - Type A - A Connectors

USB 3.0 cables are up to 10 times faster than USB 2.0 - 4.8 Gbps versus 480 Mbps. The increased bandwidth substantially reduces the time required for transferring large amounts of data or video. For example, an HD movie that would require 14 minutes to download with USB 2.0 devices and cables would take approximately 70 seconds using USB 3.0 equipment. The key change in the cables allowing for more speed is the addition of two data pairs bringing the number of conductors to eight.

CAU3AA-05M	USB 3.0 Type A - A Cable, 0.5m	Blue	10.75	9.89	9.03	8.17	7.31
CAU3AA-1M	USB 3.0 Type A - A Cable, 1.0m	Blue	11.50	10.58	9.66	8.74	7.82
CAU3AA-2M	USB 3.0 Type A - A Cable, 2.0m	Blue	13.00	11.96	10.92	9.88	8.84
CAU3AA-3M	USB 3.0 Type A - A Cable, 3.0m	Blue	14.50	13.34	12.18	11.02	9.86
CAU3AA-5M	USB 3.0 Type A - A Cable, 5.0m	Blue	17.50	16.10	14.70	13.30	11.90

✓RoHS USB 3.0 Cables - Type A - B Connectors

CAU3AB-05M	USB 3.0 Type A - B Cable, 0.5m	Blue	11.25	10.35	9.45	8.55	7.65
CAU3AB-1M	USB 3.0 Type A - B Cable, 1.0m	Blue	12.00	11.04	10.08	9.12	8.16
CAU3AB-2M	USB 3.0 Type A - B Cable, 2.0m	Blue	13.50	12.42	11.34	10.26	9.18
CAU3AB-3M	USB 3.0 Type A - B Cable, 3.0m	Blue	15.00	13.80	12.60	11.40	10.20
CAU3AB-5M	USB 3.0 Type A - B Cable, 5.0m	Blue	18.00	16.56	15.12	13.68	12.24

✓RoHS USB 3.0 Compliant Cables - Type A - Micro B Connectors

CAU3AMICB-05M	USB 3.0 Type A - Micro B Cable, 0.5m	Blue	12.50	11.50	10.50	9.50	8.50
CAU3AMICB-1M	USB 3.0 Type A - Micro B Cable, 1.0m	Blue	13.25	12.19	11.13	10.07	9.01
CAU3AMICB-2M	USB 3.0 Type A - Micro B Cable, 2.0m	Blue	14.75	13.57	12.39	11.21	10.03
CAU3AMICB-3M	USB 3.0 Type A - Micro B Cable, 3.0m	Blue	16.25	14.95	13.65	12.35	11.05
CAU3AMICB-5M	USB 3.0 Type A - Micro B Cable, 5.0m	Blue	19.25	17.71	16.17	14.63	13.09

✓RoHS USB 3.0 Compliant Extension Cables - Type A Male / Female Connectors

CAU3AX-05M	USB 3.0 Type A Male / Female Extension Cable, 0.5m	Blue	11.75	10.81	9.87	8.93	7.99
CAU3AX-1M	USB 3.0 Type A Male / Female Extension Cable, 1.0m	Blue	12.50	11.50	10.50	9.50	8.50
CAU3AX-2M	USB 3.0 Type A Male / Female Extension Cable, 2.0m	Blue	14.00	12.88	11.76	10.64	9.52
CAU3AX-3M	USB 3.0 Type A Male / Female Extension Cable, 3.0m	Blue	15.50	14.26	13.02	11.78	10.54

✓RoHS Premium USB 2.0 Cables - Type A - A Connectors, PVC Jacket, 30 Microinches Gold, 20 AWG Power Leads

Premium USB 2.0 cables contain 20 AWG power wires for maximum power transfer.

CSMUAA-05M	Premium USB Type A - A Cable, 0.5m	Lt. Gray	7.95	7.31	6.68	6.04	5.41
CSMUAA-1M	Premium USB Type A - A Cable, 1.0m	Lt. Gray	8.45	7.77	7.10	6.42	5.75
CSMUAA-2M	Premium USB Type A - A Cable, 2.0m	Lt. Gray	9.45	8.69	7.94	7.18	6.43
CSMUAA-3M	Premium USB Type A - A Cable, 3.0m	Lt. Gray	10.45	9.61	8.78	7.94	7.11
CSMUAA-4M	Premium USB Type A - A Cable, 4.0m	Lt. Gray	11.95	10.99	10.04	9.08	8.13
CSMUAA-5M	Premium USB Type A - A Cable, 5.0m	Lt. Gray	12.45	11.45	10.46	9.46	8.47

✓RoHS Premium USB 2.0 Cables - Type A - B Connectors, PVC Jacket, 30 Microinches Gold, 20 AWG Power Leads

CSMUAB-05M	Premium USB Type A - B Cable, 0.5m	Lt. Gray	6.95	6.39	5.84	5.28	4.73
CSMUAB-1M	Premium USB Type A - B Cable, 1.0m	Lt. Gray	7.45	6.85	6.26	5.66	5.07
CSMUAB-2M	Premium USB Type A - B Cable, 2.0m	Lt. Gray	8.45	7.77	7.10	6.42	5.75
CSMUAB-3M	Premium USB Type A - B Cable, 3.0m	Lt. Gray	9.45	8.69	7.94	7.18	6.43
CSMUAB-4M	Premium USB Type A - B Cable, 4.0m	Lt. Gray	10.45	9.61	8.78	7.94	7.11
CSMUAB-5M	Premium USB Type A - B Cable, 5.0m	Lt. Gray	11.45	10.53	9.62	8.70	7.79

✓RoHS Premium USB 2.0 Ext. Cables - Type A Connectors, PVC Jacket, 30 Microinches Gold, 20 AWG Power Leads

CSMUAX-1M	Premium USB Type A Male / Female Extension Cable, 1.0m	Lt. Gray	7.95	7.63	7.31	6.76	5.96
CSMUAX-2M	Premium USB Type A Male / Female Extension Cable, 2.0m	Lt. Gray	8.95	8.59	8.23	7.61	6.71
CSMUAX-3M	Premium USB Type A Male / Female Extension Cable, 3.0m	Lt. Gray	9.95	9.55	9.15	8.46	7.46

✓RoHS Deluxe USB 2.0 Cables - Type A - B Connectors, 30 Microinches Gold, 26 AWG Power Leads

L-com's standard USB cable offering, the ECUSB series, provides high performance at competitive prices. These quality constructed cables feature USB 2.0 Compliant 26 AWG power leads and are finished in an attractive medium gray color. Each cable is functionally tested to ensure the highest level of quality and performance. These cables allow for transfer rates up to 480 Mbps and can be used with simple Plug and Play connections for devices such as printers, keyboards/mice, digital cameras and other USB peripherals.

ECUSBAB-05M	Deluxe USB Type A - B Cable, 0.5m	Gray	4.35	3.91	3.48	3.04	2.61
ECUSBAB-1M	Deluxe USB Type A - B Cable, 1.0m	Gray	4.75	4.28	3.80	3.32	2.85
ECUSBAB-2M	Deluxe USB Type A - B Cable, 2.0m	Gray	5.55	5.00	4.44	3.88	3.33
ECUSBAB-3M	Deluxe USB Type A - B Cable, 3.0m	Gray	6.35	5.71	5.08	4.44	3.81
ECUSBAB-4M	Deluxe USB Type A - B Cable, 4.0m	Gray	7.15	6.44	5.72	5.00	4.29
ECUSBAB-5M	Deluxe USB Type A - B Cable, 5.0m	Gray	7.95	7.16	6.36	5.56	4.77

✓RoHS Premium USB 2.0 Cables - Type A-B Connectors, Black, 30 Microinches Gold, 24 AWG Power Leads

CAUBLKAB-05M	Premium USB Type A - B Cable, 0.5m	Black	5.20	4.68	4.16	3.64	3.12
CAUBLKAB-1M	Premium USB Type A - B Cable, 1.0m	Black	5.65	5.09	4.52	3.96	3.39
CAUBLKAB-2M	Premium USB Type A - B Cable, 2.0m	Black	6.55	5.89	5.24	4.59	3.93
CAUBLKAB-3M	Premium USB Type A - B Cable, 3.0m	Black	7.45	6.71	5.96	5.21	4.47
CAUBLKAB-4M	Premium USB Type A - B Cable, 4.0m	Black	8.35	7.51	6.68	5.84	5.01
CAUBLKAB-5M	Premium USB Type A - B Cable, 5.0m	Black	9.25	8.33	7.40	6.47	5.55



CAUBLKAB-M

"I've been doing business with you for over 5 years. You're always very professional; provide excellent products, lowest prices, and prompt service. You sell the largest line of wireless products that I've seen." - Ron Grigg, Dlux Information Systems