

COILUAB

Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
--------	-------------	-------	-----	-------	-------	---------	---------

**✓RoHS USB Coil Cord - Type A Latching Connector to Type B Connector, 10.5 Feet Extended**

This unique cable assembly features a polyurethane jacketed coil cord plus a latching Type A USB connector providing improved mating retention with any USB Type A jack. The latches lock into the channels on each side of a USB jack when fully mated. Retracted length is approximately 2.5 feet expanding to 10.5 feet. Fully shielded and USB 2.0 compliant, this cable contains two 28 AWG power conductors plus one 28 AWG twisted pair for data lines.

COILUAB	USB Coil Cord, Latching Type A Male / Type B Male	Black	16.95	16.27	15.59	14.41	12.71
---------	---	-------	-------	-------	-------	-------	-------

**✓RoHS Variable Length USB Coil Cable - Mini B 5 Position Male/Female**

This innovative USB coil cable from L-com features a retracted length 0.5 meters and an expanded length of two meters and can be used with GPS systems as well as cameras and other peripherals using the USB Mini B5 interface. All 5 mini B positions are connected to insure proper functionality in every application. The tough, durable polyurethane jacket enhances recoil memory and 30 microinch gold plated contacts provide reliable connections with repeated mating cycles. Order online today!

COILMB5EXT-2M	USB Coil Cable - Mini B 5 Position Male / Female, 0.5m to 2.0m	Black	11.50	10.58	9.66	8.74	7.82
---------------	--	-------	-------	-------	------	------	------

**✓RoHS Flex USB Cables - USB Connectors Bend, Rotate and Lock Into Place**

FlexUSB Cables are the first USB cables with a flexible, ratcheting connector and the smallest profile in the industry. FlexUSB Cables bend, rotate and lock into place, providing versatility in difficult to reach and confined spaces. USB 2.0 compliant!

CAFLEX AM-AF-6	USB Ext. Cable, Rotating USB Type A Male / Std. Type A Fem., 6.0ft (1.8m)	Black	12.99	12.21	11.43	10.65	9.87
CAFLEX AM-BM-6	USB Cable, Rotating USB Type A Male / Std. Type B Male, 6.0ft (1.8m)	Black	12.99	12.21	11.43	10.65	9.87
CAFLEX AM-MB5-6	USB Cable, Rotating USB Type A Male / Std. Mini B5 Male, 6.0ft (1.8m)	Black	12.99	12.21	11.43	10.65	9.87
CAFLEX MB5M-AM-3	USB Cable, Rotating USB Mini B5 Male / Std. Type A Male, 3.0ft (0.9m)	Black	11.99	11.27	10.55	9.83	9.11
CAFLEX MB5M-AM-6	USB Cable, Rotating USB Mini B5 Male / Std. Type A Male, 6.0ft (1.8m)	Black	12.99	12.21	11.43	10.65	9.87

**✓RoHS Flexible USB Adapter, Type A Male/Female**

L-com's UADFLEX-1 flexible USB adapter features vertical and horizontal hinges which allow the adapter to rotate in virtually any direction, making it perfect for hard to reach or tight fit applications. This flexible USB adapter is shielded to protect against data corrupting EMI/RFI and utilizes gold plating on all contacts to provide reliable connections with repeated mating cycles.

UADFLEX-1	USB Flexible Adapter, Type A Male / Type A Female	Black	9.99	9.19	8.39	7.59	6.79
-----------	---	-------	------	------	------	------	------

**✓RoHS USB 2.0 and 3.0 Adapters - Molded and Fully Shielded**

These adapters provide an economical way for users to solve gender and connector type mismatches among standard USB connectors.

UAD010MF	USB Adapter, Type A Male / Type B Female	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD011FM	USB Adapter, Type A Female / Type B Male	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD012FF	USB Adapter, Type B Female / Type B Female	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD013FF	USB Adapter, Type A Female / Type B Female	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD014MM	USB Adapter, Type A Male / Type A Male	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD015FF	USB Adapter, Type A Female / Type A Female	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD016MM	USB Adapter, Type B Male / Type B Male	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD017FM	USB Adapter, Type A Female / Mini DIN 6 Male	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD018MF	USB Adapter, Type A Male / Mini DIN 6 Female	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD019FM	USB Adapter, Type A Female / Mini-B5 Male	Black	4.25	4.17	3.99	3.74	3.19
UAD026MF	USB Adapter, Type A Male / Female	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD027MF	USB Adapter, Type B Male / Female	Lt. Gray	4.25	4.17	3.99	3.74	3.19

**✓RoHS USB 2.0 Micro B Adapters**

UAD030MF	USB Adapter, Micro B Male / Mini B5 Female	Black	4.25	4.17	3.99	3.74	3.19
UAD031MM	USB Adapter, Micro B Male / Standard A Male	Black	4.25	4.17	3.99	3.74	3.19
UAD032FM	USB Adapter, Micro B Male / Standard A Female	Lt. Gray	4.25	4.17	3.99	3.74	3.19
UAD033FM	USB Adapter, Micro B Male / Standard B Female	Lt. Gray	4.25	4.17	3.99	3.74	3.19

**✓RoHS USB 3.0 Adapters**

UAD035MF	USB 3.0 Socket Saver, Type A Male / Type A Female	Blue	8.75	8.57	8.22	7.70	6.56
UAD036FF	USB 3.0 Gender Changer, Type A Female / Type A Female	Blue	8.75	8.57	8.22	7.70	6.56
UAD037MM	USB 3.0 Gender Changer, Type A Male / Type A Male	Blue	8.75	8.57	8.22	7.70	6.56

**✓RoHS USB Type A Low Profile Right Angle Adapters**

L-com's UADAA90 series low profile right angle USB adapters are perfect for tight fit applications. Two exit options are available allowing cables to exit in opposite directions. These USB adapters are a much lower cost solution when compared to rotating USB adapters.

UADAA90-1	Right Angle USB Adapter, Type A Male / Female, Exit 1	Lt. Gray	4.95	4.55	4.16	3.76	3.37
UADAA90-2	Right Angle USB Adapter, Type A Male / Female, Exit 2	Lt. Gray	4.95	4.55	4.16	3.76	3.37

**✓RoHS USB Type B Low Profile Right Angle Adapters**

L-com's UADBB90 series low profile right angle USB adapters feature two exit options allowing cables to exit in opposite directions. Our UADBB90 series USB adapters are a much lower cost solution when compared to rotating USB adapters. Additionally, these robust 90° USB adapters feature 20 AWG power leads for maximum power transfer and 100% shielding throughout for protection against data corrupting EMI/RFI.

UADBB90-1	Right Angle USB Adapter, Type B Male / Female, Exit 1	Lt. Gray	4.95	4.55	4.16	3.76	3.37
UADBB90-2	Right Angle USB Adapter, Type B Male / Female, Exit 2	Lt. Gray	4.95	4.55	4.16	3.76	3.37



COILMB5EXT-2M




CAFLEX AM-AF



CAFLEX AM-MB5



UADFLEX-1



UAD013FF

UAD031MM

UAD035MF

UADAA90-1

UADBB90-1

UAD026MF

UAD032FM

UAD036FF

UADAA90-2

UADBB90-2

"Everything was much easier to find. The pictures on the web site do a good job of capturing the products. The check out was smooth. It appeared to be secure and it was pretty streamlined. All in all a "bang up job" on the site."

- Nathaniel B. Lyon, Owner, Northfield WiFi