



Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
--------	-------------	-------	-----	-------	-------	---------	---------

**RoHS USB Revision 2.0 Compliant Bulk Cable**

This cable will support the 480 Mbps transmission rate of a USB 2.0 network and is also backward compatible with older, slower USB networks. USB bulk cable features two 20 AWG power conductors plus one 28 AWG twisted pair for the data lines. A flexible PVC jacket covers the braid, foil and drain wire shield. Choose from 100, 500 or 1000 foot spools. Jacket color is Light Gray.

CSUSB-100	USB Revision 2.0 Compliant Bulk Cable, 100ft (30.5m) Spool	Lt. Gray	49.00	46.06	43.12	40.18	CALL
CSUSB-500	USB Revision 2.0 Compliant Bulk Cable, 500ft (152.4m) Spool	Lt. Gray	225.00	211.50	198.00	184.50	CALL
CSUSB-1000	USB Revision 2.0 Compliant Bulk Cable, 1000ft (304.8m) Spool	Lt. Gray	395.00	371.30	347.60	323.90	CALL

**RoHS USB Revision 2.0 Compliant Bulk Cable**

USB bulk cable features two 24 or 28 AWG power conductors plus one 28 AWG twisted pair for the data lines. A flexible PVC jacket covers the braid, foil, and drain wire shield. Choose from 100, 500 or 1000 foot put-ups. Jacket color is black. Compatible with L-com CNUUSB connector series.

CBL-USB2-2824-100	USB Revision 2.0 Compliant Bulk Cable, 100ft (30.5m) Spool	Black	36.00	33.84	31.68	29.52	CALL
CBL-USB2-2824-500	USB Revision 2.0 Compliant Bulk Cable, 500ft (152.4m) Spool	Black	165.00	155.10	145.20	135.30	CALL
CBL-USB2-2824-1000	USB Revision 2.0 Compliant Bulk Cable, 1000ft (304.8m) Spool	Black	295.00	277.30	259.60	241.90	CALL
CBL-USB2-2828-100	USB Revision 2.0 Compliant Bulk Cable, 100ft (30.5m) Spool	Black	25.00	23.50	22.00	20.50	CALL
CBL-USB2-2828-500	USB Revision 2.0 Compliant Bulk Cable, 500ft (152.4m) Spool	Black	108.00	101.52	95.04	88.56	CALL
CBL-USB2-2828-1000	USB Revision 2.0 Compliant Bulk Cable, 1000ft (304.8m) Spool	Black	195.00	183.30	171.60	159.90	CALL

**RoHS LSZH USB Revision 2.0 Compliant Bulk Cable**

Halogen free USB bulk cable features two 20 AWG power conductors plus one 28 AWG twisted pair for the data lines. A flexible LSZH jacket covers the braid, foil and drain wire shield. Low smoke zero halogen cable reduces the amount of toxic and corrosive gases emitted during combustion. Choose from 100, 500 or 1000 foot (30.5, 152.4 or 304.8m) put-ups. Jacket color is black.

CBL-USBZ-2820-100	LSZH USB Revision 2.0 Compliant Bulk Cable, 100ft (30.5m) Spool	Black	105.00	98.70	92.40	86.10	CALL
CBL-USBZ-2820-500	LSZH USB Revision 2.0 Compliant Bulk Cable, 500ft (152.4m) Spool	Black	495.00	465.30	435.60	405.90	CALL
CBL-USBZ-2820-1000	LSZH USB Revision 2.0 Compliant Bulk Cable, 1000ft (304.8m) Spool	Black	900.00	846.00	792.00	738.00	CALL

**RoHS USB Connectors and Hoods, Type A and B**

USB connectors and hoods are now available for custom lengths and applications. Connectors feature gold plated solder contacts, nickel-plated steel shells and a UL94V-0 rated housing.

CNUUSB-A	USB Type A Connector		1.39	1.36	1.31	1.22	1.04
CNUUSB-B	USB Type B Connector		1.39	1.36	1.31	1.22	1.04
HOODUSB-Z-A	LSZH USB Type A Hood	Black	0.89	0.87	0.84	0.78	0.67
HOODUSB-Z-B	LSZH USB Type B Hood	Black	0.89	0.87	0.84	0.78	0.67
HOODUSB-A	USB Type A Hood	Lt. Gray	0.64	0.63	0.60	0.56	0.48
HOODUSB-B	USB Type B Hood	Lt. Gray	0.64	0.63	0.60	0.56	0.48

**RoHS USB Type A and B Female Field Termination Connector**

The USB field termination female connectors provide an easy and convenient way to perform field termination for USB applications. USB 2.0 standard A and B connector styles are available. Separate connection points are provided for all 4 positions of the connector plus the ground. Terminal block design with set screws provides reliable electrical connections utilizing no special tools. The terminal block area is clearly marked making proper termination virtually foolproof. Panel mountable using 4-40 screws provided.

USBAFT	USB Field Termination Connector, Type A Female		6.25	5.88	5.50	5.13	4.75
USBFT	USB Field Termination Connector, Type B Female		6.25	5.88	5.50	5.13	4.75

**RoHS USB Type A, B, Mini B5 and Micro B Female Connector Covers - Protect Unused Ports, Pkg/10**

These covers are perfect for protecting unused female ports in our panel mount couplers or any expensive equipment from physical damage, dirt and dust. Made from soft ABS, these covers attach easily and stay in place with a snug friction fit.

CAPUSB-A	USB Protective Cover for Type A Jacks, Pkg/10	Black	6.50	5.98	5.46	4.94	4.42
CAPUSB-B	USB Protective Cover for Type B Jacks, Pkg/10	Black	6.50	5.98	5.46	4.94	4.42
CAPUSB-MB5	USB Protective Cover for Type Mini B5 Jacks, Pkg/10	Black	6.50	5.98	5.46	4.94	4.42
CAPUSB-MICB	USB Protective Cover for Type Micro B Jacks, Pkg/10	Black	6.50	5.98	5.46	4.94	4.42

**RoHS USB Cable Assembly Male Connector Dust Covers - Pkg/10**

These hard to find covers are perfect for protecting unused USB cable assembly connectors from physical damage, dirt and dust. Made from PVC, they attach easily and stay in place with a snug friction fit.

CVRUSB-A	USB Protective Cover for USB 2.0 & 3.0 Type A Plugs, Pkg/10	Black	5.50	5.06	4.62	4.18	3.74
CVRUSB-B	USB Protective Cover for USB 2.0 Type B Plugs, Pkg/10	Black	5.50	5.06	4.62	4.18	3.74
CVRUSB-MB4	USB Protective Cover for USB 2.0 Type Mini B4 Plugs, Pkg/10	Black	5.50	5.06	4.62	4.18	3.74
CVRUSB-MB5	USB Protective Cover for USB 2.0 Type Mini B5 Plugs, Pkg/10	Black	5.50	5.06	4.62	4.18	3.74
CVRUSB-MICB	USB Protective Cover for USB 2.0 Type Micro B Plugs, Pkg/10	Black	5.50	5.06	4.62	4.18	3.74
CVRUSB3.0-B	USB Protective Cover for USB 3.0 Type B Plugs, Pkg/10	Black	5.50	5.06	4.62	4.18	3.74
CVRUSB3.0-MICB	USB Protective Cover for USB 3.0 Type Micro B Plugs, Pkg/10	Black	5.50	5.06	4.62	4.18	3.74

**USB 2.0 Manual Switch Box - (1) Type B and (2) Type A Ports**

This handy switch box allows the user to share two USB devices with one computer. Equipped with one Type B I/O port and two type A ports. Lightweight design and all metal case provides easy set up and durability.

SWIT-USB2-BAA	USB Manual Switch Box		11.75	11.52	11.28	11.04	10.81
---------------	-----------------------	--	-------	-------	-------	-------	-------

