

| Item # | Description | 1-9 | 10-24 | 25-99 | 100-249 | 250-499 |
|--------|-------------|-----|-------|-------|---------|---------|
|--------|-------------|-----|-------|-------|---------|---------|

**✓RoHS External Serial ATA Cable Assemblies - Fully Shielded, Protect Against EMI/RFI**

L-com's CAESA series of external Serial ATA cables provide fast data transfer speeds for external storage devices. SATA is now available "outside the box". These fully shielded cables provide extra protection from EMI/RFI and support speeds up to three Gigabits per second.

|           |  |      |      |      |      |      |
|-----------|--|------|------|------|------|------|
| CAESA-05M | External Serial ATA Cable Assembly, 0.5m | 6.95 | 6.53 | 6.12 | 5.70 | 5.28 |
| CAESA-1M  | External Serial ATA Cable Assembly, 1.0m | 7.95 | 7.47 | 7.00 | 6.52 | 6.04 |
| CAESA-2M  | External Serial ATA Cable Assembly, 2.0m | 9.95 | 9.35 | 8.76 | 8.16 | 7.56 |

**✓RoHS External Serial ATA to Latching SATA II Cable Assemblies, Fully Shielded**

L-com's CAESA2 series of External SATA to SATA II latching cable assemblies connect eSATA external drives/enclosures to SATA II enabled systems. These robust assemblies feature fully shielded cables that provide extra protection from EMI/RFI and support speeds up to three Gigabits per second. The SATA II latching connector ensures a secure connection.

|            |  |      |      |      |      |      |
|------------|--|------|------|------|------|------|
| CAESA2-05M | eSATA to SATA II Latching Cable Assembly, 0.5m | 6.95 | 6.53 | 6.12 | 5.70 | 5.28 |
| CAESA2-1M  | eSATA to SATA II Latching Cable Assembly, 1.0m | 7.95 | 7.47 | 7.00 | 6.52 | 6.04 |
| CAESA2-2M  | eSATA to SATA II Latching Cable Assembly, 2.0m | 9.95 | 9.35 | 8.76 | 8.16 | 7.56 |

**✓RoHS SATA and eSATA Connector Covers for Male and Female Connectors, Pkg/10**

These hard to find covers are perfect for protecting unused connector ports in any equipment as well as cable assembly connectors. Four part numbers are available - CVR-ESATA and CVRSATA cover cable assembly connectors, CAP-ESATA and CAPSATA cover computer/equipment ports. These covers attach easily and stay in place with a snug friction fit. Color is black.

|           |   |      |      |      |      |      |
|-----------|---|------|------|------|------|------|
| CVRSATA   | Protective Cover for SATA Cable Assembly Connector, Pkg/10  | 5.50 | 5.06 | 4.62 | 4.18 | 3.74 |
| CVR-ESATA | Protective Cover for eSATA Cable Assembly Connector, Pkg/10 | 5.50 | 5.06 | 4.62 | 4.18 | 3.74 |
| CAPSATA   | Protective Cover for SATA Computer/Connector Ports, Pkg/10  | 6.50 | 5.98 | 5.46 | 4.94 | 4.42 |
| CAP-ESATA | Protective Cover for eSATA Computer/Connector Ports, Pkg/10 | 6.50 | 5.98 | 5.46 | 4.94 | 4.42 |

**✓RoHS Serial ATA (SATA) Cable Assemblies with Latching Connectors- Straight and Right Angle Connectors**

L-com's latching Serial ATA cable assemblies provide a secure connection every time. These SATA assemblies feature two shielded 26 AWG pairs in a PVC jacket, gold plated contacts and two straight polarized seven position connectors. Both straight to straight and straight to right angle versions are offered. Custom lengths are available with modest minimum requirements. Call us today with your custom SATA requirements.

|             |  |      |      |      |      |      |
|-------------|--|------|------|------|------|------|
| CASATAL-8   | Latching Serial ATA Cable, Straight / Straight, 8.0in (20.3cm)     | 3.75 | 3.45 | 3.15 | 2.85 | 2.55 |
| CASATAL-12  | Latching Serial ATA Cable, Straight / Straight, 12.0in (30.4cm)    | 3.95 | 3.63 | 3.32 | 3.00 | 2.69 |
| CASATAL-16  | Latching Serial ATA Cable, Straight / Straight, 16.0in (40.6cm)    | 4.15 | 3.82 | 3.49 | 3.15 | 2.82 |
| CASATAL-18  | Latching Serial ATA Cable, Straight / Straight, 18.0in (45.7cm)    | 4.25 | 3.91 | 3.57 | 3.23 | 2.89 |
| CASATAL-24  | Latching Serial ATA Cable, Straight / Straight, 24.0in (61.0cm)    | 4.60 | 4.23 | 3.86 | 3.50 | 3.13 |
| CASATAL-36  | Latching Serial ATA Cable, Straight / Straight, 36.0in (91.4cm)    | 5.25 | 4.83 | 4.41 | 3.99 | 3.57 |
| CASATARL-8  | Latching Serial ATA Cable, Straight / Right Angle, 8.0in (20.3cm)  | 4.25 | 3.91 | 3.57 | 3.23 | 2.89 |
| CASATARL-12 | Latching Serial ATA Cable, Straight / Right Angle, 12.0in (30.4cm) | 4.45 | 4.09 | 3.74 | 3.38 | 3.03 |
| CASATARL-16 | Latching Serial ATA Cable, Straight / Right Angle, 16.0in (40.6cm) | 4.65 | 4.28 | 3.91 | 3.53 | 3.16 |
| CASATARL-18 | Latching Serial ATA Cable, Straight / Right Angle, 18.0in (45.7cm) | 4.75 | 4.37 | 3.99 | 3.61 | 3.23 |
| CASATARL-24 | Latching Serial ATA Cable, Straight / Right Angle, 24.0in (61.0cm) | 5.10 | 4.69 | 4.28 | 3.88 | 3.47 |
| CASATARL-36 | Latching Serial ATA Cable, Straight / Right Angle, 36.0in (91.4cm) | 5.75 | 5.29 | 4.83 | 4.37 | 3.91 |

**✓RoHS Serial ATA Cable Assemblies - Straight to Straight and Straight to Right Angle Connectors**

Serial ATA cables are replacing wide Parallel ATA ribbon cables in many applications. The Serial ATA cable is smaller, more flexible and easier to route inside a chassis. With the trend toward miniaturization, these characteristics are beneficial in many product designs. The cables feature two shielded 26 AWG pairs in a PVC jacket, gold plated contacts and polarized seven position connectors. Available in straight to straight and straight to right angle connector orientations in lengths of 0.5 and 1 meter.

|             |  |      |      |      |      |      |
|-------------|--|------|------|------|------|------|
| CASATA-05M  | Serial ATA Cable, Straight / Straight, 0.5m    | 4.25 | 3.83 | 3.40 | 2.97 | 2.55 |
| CASATA-1M   | Serial ATA Cable, Straight / Straight, 1.0m    | 5.25 | 4.73 | 4.20 | 3.67 | 3.15 |
| CASATAR-05M | Serial ATA Cable, Straight / Right Angle, 0.5m | 4.75 | 4.28 | 3.80 | 3.32 | 2.85 |
| CASATAR-1M  | Serial ATA Cable, Straight / Right Angle, 1.0m | 5.75 | 5.17 | 4.60 | 4.02 | 3.45 |

**✓RoHS Serial ATA Extension Cable Assemblies (SATA) - Male to Female Connectors**

These handy cables can be used to extend SATA cables as well as create space in tightly packed areas where bulky disk-on-modules (DOMs) are difficult to connect. These cables feature a bright red PVC jacket, gold contacts and are fully shielded.

|              |  |      |      |      |      |      |
|--------------|--|------|------|------|------|------|
| CASATAEXT-12 | Serial ATA Extension Cable, 12" (30.4cm) | 4.25 | 3.91 | 3.57 | 3.23 | 2.89 |
| CASATAEXT-20 | Serial ATA Extension Cable, 20" (50.8cm) | 4.75 | 4.37 | 3.99 | 3.61 | 3.23 |

**✓RoHS Slim SATA Cables**



Slim SATA cables are now available for slimline SATA drives. A compact power and data connector plugs directly into the slimline data drive and splits into a standard latching SATA cable plus a 4 position power connector.

|          |                               |      |      |      |      |      |
|----------|-------------------------------|------|------|------|------|------|
| CASSA-8  | Slim SATA Cable, 8" (20.3cm)  | 7.50 | 6.90 | 6.30 | 5.70 | 5.10 |
| CASSA-18 | Slim SATA Cable, 18" (45.7cm) | 8.00 | 7.36 | 6.72 | 6.08 | 5.44 |

**✓RoHS Ultra ATA 133 Cables - 80 Cond. Round Shielded Cable with Three 40 Signal/40 Ground IDE Connectors**

Connectors are IDE 40 signal plus 40 ground, color coded and polarized for easy plug in. Also, these cables are compatible with ATA 100, 66, 33 drives and many CD-ROMS, zip drives and tape drives. See diagram below for connector spacing.

|              |   |      |      |      |      |      |
|--------------|---|------|------|------|------|------|
| CAATA133-324 | Ultra ATA133 Cable, 3 Connector, 24" (61.0cm) | 8.95 | 8.23 | 7.52 | 6.80 | 6.09 |
| CAATA133-336 | Ultra ATA133 Cable, 3 Connector, 36" (91.4cm) | 9.95 | 9.15 | 8.36 | 7.56 | 6.77 |



**Free technical support**  
 Call toll free at 1-800-343-1455  
 if you have questions about your application.

