



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

**DIN and Mini DIN Cables for Computer Keyboards, Mice and Other Uses**

These Premium DK Series are the finest DIN/Mini DIN cables on the market. As the illustration reveals, the painstaking attention to detail beneath the surface makes the difference. All DK cables listed are wired straight-thru, fully populated, double shielded (copper braid and aluminum mylar), 24 AWG and fully over molded. Color: Gray.



**RoHS Premium DIN 5 Cables - Fully Populated - Double Shielded**

DK225MM-3	Molded Cable, DIN 5 Male / Male, 3.0ft (0.9m)	6.75	6.34	5.94	5.54	5.13
DK225MM-6	Molded Cable, DIN 5 Male / Male, 6.0ft (1.8m)	9.75	9.16	8.58	8.00	7.41
DK225MM-10	Molded Cable, DIN 5 Male / Male, 10.0ft (3.0m)	13.75	12.92	12.10	11.28	10.45
DK225MM-20	Molded Cable, DIN 5 Male / Male, 20.0ft (6.0m)	23.75	22.32	20.90	19.48	18.05
DK225MM-25	Molded Cable, DIN 5 Male / Male, 25.0ft (7.6m)	28.75	27.02	25.30	23.58	21.85
DK225MF-3	Molded Extension Cable, DIN 5, Male / Female, 3.0ft (0.9m)	6.75	6.34	5.94	5.54	5.13
DK225MF-6	Molded Extension Cable, DIN 5, Male / Female, 6.0ft (1.8m)	9.75	9.16	8.58	8.00	7.41
DK225MF-10	Molded Extension Cable, DIN 5, Male / Female, 10.0ft (3.0m)	13.75	12.92	12.10	11.28	10.45
DK225MF-20	Molded Extension Cable, DIN 5, Male / Female, 20.0ft (6.0m)	23.75	22.32	20.90	19.48	18.05
DK225MF-25	Molded Extension Cable, DIN 5, Male / Female, 25.0ft (7.6m)	28.75	27.02	25.30	23.58	21.85

**RoHS Premium Mini DIN 6 Cables - Fully Populated - Double Shielded**

DK226MM-1	Molded Cable, Mini DIN 6 Male / Male, 1.0ft (0.3m)	6.95	6.53	6.12	5.70	5.28
DK226MM-2	Molded Cable, Mini DIN 6 Male / Male, 2.0ft (0.6m)	7.95	7.47	7.00	6.52	6.04
DK226MM-3	Molded Cable, Mini DIN 6 Male / Male, 3.0ft (0.9m)	8.95	8.41	7.88	7.34	6.80
DK226MM-6	Molded Cable, Mini DIN 6 Male / Male, 6.0ft (1.8m)	11.95	11.23	10.52	9.80	9.08
DK226MM-10	Molded Cable, Mini DIN 6 Male / Male, 10.0ft (3.0m)	15.95	14.99	14.04	13.08	12.12
DK226MM-15	Molded Cable, Mini DIN 6 Male / Male, 15.0ft (4.6m)	20.95	19.69	18.44	17.18	15.92
DK226MM-20	Molded Cable, Mini DIN 6 Male / Male, 20.0ft (6.0m)	25.95	24.39	22.84	21.28	19.72
DK226MM-25	Molded Cable, Mini DIN 6 Male / Male, 25.0ft (7.6m)	30.95	29.09	27.24	25.38	23.52
DK226MF-3	Molded Extension Cable, Mini DIN 6 Male / Female, 3.0ft (0.9m)	8.95	8.41	7.88	7.34	6.80
DK226MF-6	Molded Extension Cable, Mini DIN 6 Male / Female, 6.0ft (1.8m)	11.95	11.23	10.52	9.80	9.08
DK226MF-10	Molded Extension Cable, Mini DIN 6 Male / Female, 10.0ft (3.0m)	15.95	14.99	14.04	13.08	12.12
DK226MF-15	Molded Extension Cable, Mini DIN 6 Male / Female, 15.0ft (4.6m)	20.95	19.69	18.44	17.18	15.92
DK226MF-20	Molded Extension Cable, Mini DIN 6 Male / Female, 20.0ft (6.0m)	25.95	24.39	22.84	21.28	19.72
DK226MF-25	Molded Extension Cable, Mini DIN 6 Male / Female, 25.0ft (7.6m)	30.95	29.09	27.24	25.38	23.52

**RoHS Premium Mini DIN 8 Cables - Fully Populated - Double Shielded**

DK238MM-1	Molded Cable, Mini DIN 8 Male / Male, 1.0ft (0.3m)	8.70	8.18	7.66	7.13	6.61
DK238MM-2	Molded Cable, Mini DIN 8 Male / Male, 2.0ft (0.6m)	9.70	9.12	8.54	7.95	7.37
DK238MM-3	Molded Cable, Mini DIN 8 Male / Male, 3.0ft (0.9m)	10.70	10.06	9.42	8.77	8.13
DK238MM-6	Molded Cable, Mini DIN 8 Male / Male, 6.0ft (1.8m)	13.70	12.88	12.06	11.23	10.41
DK238MM-10	Molded Cable, Mini DIN 8 Male / Male, 10.0ft (3.0m)	17.70	16.64	15.58	14.51	13.45
DK238MM-15	Molded Cable, Mini DIN 8 Male / Male, 15.0ft (4.6m)	22.70	21.34	19.98	18.61	17.25
DK238MM-20	Molded Cable, Mini DIN 8 Male / Male, 20.0ft (6.0m)	27.70	26.04	24.38	22.71	21.05
DK238MM-25	Molded Cable, Mini DIN 8 Male / Male, 25.0ft (7.6m)	32.70	30.74	28.78	26.81	24.85
DK238MF-3	Molded Extension Cable, Mini DIN 8 Male / Female, 3.0ft (0.9m)	10.70	10.06	9.42	8.77	8.13
DK238MF-6	Molded Extension Cable, Mini DIN 8 Male / Female, 6.0ft (1.8m)	13.70	12.88	12.06	11.23	10.41
DK238MF-10	Molded Extension Cable, Mini DIN 8 Male / Female, 10.0ft (3.0m)	17.70	16.64	15.58	14.51	13.45
DK238MF-15	Molded Extension Cable, Mini DIN 8 Male / Female, 15.0ft (4.6m)	22.70	21.34	19.98	18.61	17.25
DK238MF-20	Molded Extension Cable, Mini DIN 8 Male / Female, 20.0ft (6.0m)	27.70	26.04	24.38	22.71	21.05
DK238MF-25	Molded Extension Cable, Mini DIN 8 Male / Female, 25.0ft (7.6m)	32.70	30.74	28.78	26.81	24.85

**Economy Mini DIN Cables - Shielded, Molded, Fully Populated**

These cables provide an economical choice suitable for many applications and are comparable with most cables on the market. Available with Mini DIN 6 or 8 position connectors. Construction features durable PVC mold, 28 AWG conductors and 360 degree foil shield. Color: Gray.

**RoHS Economy Mini DIN 6 Cables - Male to Male and Male to Female**

CSMD6MM-3	Economy Molded Cable, Mini DIN 6 Male / Male, 3.0ft (0.9m)	4.45	4.18	3.92	3.65	3.38
CSMD6MM-6	Economy Molded Cable, Mini DIN 6 Male / Male, 6.0ft (1.8m)	5.50	5.17	4.84	4.51	4.18
CSMD6MM-10	Economy Molded Cable, Mini DIN 6 Male / Male, 10.0ft (3.0m)	6.90	6.49	6.07	5.66	5.24
CSMD6MM-25	Economy Molded Cable, Mini DIN 6 Male / Male, 25.0ft (7.6m)	12.15	11.42	10.69	9.96	9.23
CSMD6MF-3	Economy Molded Cable, Mini DIN 6 Male / Female, 3.0ft (0.9m)	4.45	4.18	3.92	3.65	3.38
CSMD6MF-6	Economy Molded Cable, Mini DIN 6 Male / Female, 6.0ft (1.8m)	5.50	5.17	4.84	4.51	4.18
CSMD6MF-10	Economy Molded Cable, Mini DIN 6 Male / Female, 10.0ft (3.0m)	6.90	6.49	6.07	5.66	5.24
CSMD6MF-25	Economy Molded Cable, Mini DIN 6 Male / Female, 25.0ft (7.6m)	12.15	11.42	10.69	9.96	9.23

**RoHS Economy Mini DIN 8 Cables - Male to Male and Male to Female**

CSMD8MM-3	Economy Molded Cable, Mini DIN 8 Male / Male, 3.0ft (0.9m)	5.60	5.26	4.93	4.59	4.26
CSMD8MM-6	Economy Molded Cable, Mini DIN 8 Male / Male, 6.0ft (1.8m)	7.10	6.67	6.25	5.82	5.40
CSMD8MM-10	Economy Molded Cable, Mini DIN 8 Male / Male, 10.0ft (3.0m)	9.10	8.55	8.01	7.46	6.92
CSMD8MM-25	Economy Molded Cable, Mini DIN 8 Male / Male, 25.0ft (7.6m)	16.60	15.60	14.61	13.61	12.62
CSMD8MF-3	Economy Molded Cable, Mini DIN 8 Male / Female, 3.0ft (0.9m)	5.60	5.26	4.93	4.59	4.26
CSMD8MF-6	Economy Molded Cable, Mini DIN 8 Male / Female, 6.0ft (1.8m)	7.10	6.67	6.25	5.82	5.40
CSMD8MF-10	Economy Molded Cable, Mini DIN 8 Male / Female, 10.0ft (3.0m)	9.10	8.55	8.01	7.46	6.92
CSMD8MF-25	Economy Molded Cable, Mini DIN 8 Male / Female, 25.0ft (7.6m)	16.60	15.60	14.61	13.61	12.62

"Just wanted to comment on the excellent catalog. I find it very informative and helpful. It's good to see usage descriptions right there in the catalog." - Farren C.