



Codes for SCSI Connector Ends



NOTE: All cable lengths are in meters.
1m = 3.28 ft

| Item # | Description | # Prs | Code | 1-9 | 10-24 | 25-99 |
|--------|-------------|-------|------|-----|-------|-------|
|--------|-------------|-------|------|-----|-------|-------|

Small Computer System Interface (SCSI) Products

Developed as a general purpose data transfer system, the Small Computer System Interface or SCSI standard is most known for connecting data storage devices such as hard drives. L-com carries the four common connector styles for this system to allow easy interconnection of all your SCSI equipment. The above connector guide will help you select the correct connector for each application. Contact us today for all your SCSI cabling needs.

✓RoHS Ultra SCSI (SCSI-5) Cables with .8mm Pitch High-Density Connectors, Offset Backshells

Many SCSI devices now utilize the VHDCI (Very High Density Cable Interconnect) standard. The high performance standard and the mechanical precision of this connector system make workmanship absolutely critical. L-com has fulfilled this requirement with three popular connector combinations. All .8mm connectors utilize offset backshells for applications requiring two side-by-side ports. Special versions will be considered with modest minimums.

| | | | | | | |
|--------------|---|----|-----|-------|-------|-------|
| CA2000MM-05M | Ultra SCSI Cable, .8mm Male / Male, 0.5m | 34 | A-A | 67.95 | 66.59 | 63.87 |
| CA2000MM-1M | Ultra SCSI Cable, .8mm Male / Male, 1.0m | 34 | A-A | 71.95 | 70.51 | 67.63 |
| CA2000MM-2M | Ultra SCSI Cable, .8mm Male / Male, 2.0m | 34 | A-A | 79.95 | 78.35 | 75.15 |
| CA2000MM-3M | Ultra SCSI Cable, .8mm Male / Male, 3.0m | 34 | A-A | 87.95 | 86.19 | 82.67 |
| CA2051MM-05M | Ultra SCSI Cable, .8mm Male / HPDB50 Male, 0.5m | 25 | A-B | 54.95 | 53.85 | 51.65 |
| CA2051MM-1M | Ultra SCSI Cable, .8mm Male / HPDB50 Male, 1.0m | 25 | A-B | 58.95 | 57.77 | 55.41 |
| CA2051MM-2M | Ultra SCSI Cable, .8mm Male / HPDB50 Male, 2.0m | 25 | A-B | 66.95 | 65.61 | 62.93 |
| CA2051MM-3M | Ultra SCSI Cable, .8mm Male / HPDB50 Male, 3.0m | 25 | A-B | 74.95 | 73.45 | 70.45 |
| CA2060MM-05M | Ultra SCSI Cable, .8mm Male / HPDB68 Male, 0.5m | 34 | A-C | 59.95 | 58.75 | 56.35 |
| CA2060MM-1M | Ultra SCSI Cable, .8mm Male / HPDB68 Male, 1.0m | 34 | A-C | 63.95 | 62.67 | 60.11 |
| CA2060MM-2M | Ultra SCSI Cable, .8mm Male / HPDB68 Male, 2.0m | 34 | A-C | 71.95 | 70.51 | 67.63 |
| CA2060MM-3M | Ultra SCSI Cable, .8mm Male / HPDB68 Male, 3.0m | 34 | A-C | 79.95 | 78.35 | 75.15 |

✓RoHS Premium Grade SCSI-3 Cables with Ferrite Cores - Reduce Noise Problems

Frequent OEM requests have prompted us to add a premium SCSI-3 cable utilizing ferrite cores to the line. Molded ferrites reduce radiated emissions and undesirable currents within the shield. These cables can be helpful in passing today's tough emissions standards.

| | | | | | | |
|--------------|--|----|-----|-------|-------|-------|
| CAF900MM-05M | SCSI-3 Cable, HPDB68 Male / Male with Ferrites, 0.5m | 34 | C-C | 46.45 | 42.73 | 39.02 |
| CAF900MM-1M | SCSI-3 Cable, HPDB68 Male / Male with Ferrites, 1.0m | 34 | C-C | 50.95 | 46.87 | 42.80 |
| CAF900MM-2M | SCSI-3 Cable, HPDB68 Male / Male with Ferrites, 2.0m | 34 | C-C | 59.95 | 55.15 | 50.36 |
| CAF900MM-3M | SCSI-3 Cable, HPDB68 Male / Male with Ferrites, 3.0m | 34 | C-C | 68.95 | 63.43 | 57.92 |

✓RoHS Standard Grade SCSI-3 Cables - Fully Molded and Shielded

All SCSI-3 cables are fully populated with 34 twisted pairs. The high density DB68 connectors utilize 2-56 threaded screws for mounting.

| | | | | | | |
|-------------|--|----|-----|-------|-------|-------|
| CA900MM-05M | SCSI-3 Cable, HPDB68 Male / Male, 0.5m | 34 | C-C | 34.45 | 31.69 | 28.94 |
| CA900MM-1M | SCSI-3 Cable, HPDB68 Male / Male, 1.0m | 34 | C-C | 38.95 | 35.83 | 32.72 |
| CA900MM-2M | SCSI-3 Cable, HPDB68 Male / Male, 2.0m | 34 | C-C | 47.95 | 44.11 | 40.28 |

✓RoHS Low Smoke Zero Halogen SCSI-3 Cable Assemblies

These cables meet the requirements of SCSI-3 systems. The high density DB68 SCSI connectors use 2-56 threaded thumbscrews for mounting. Cable assembly construction features 30 microinch gold plated copper alloy contacts, die cast zinc alloy hoods, 28 AWG polypropylene insulated conductors, foil/braid shield and a LSZH outer jacket. Color is Black. L-com will manufacture custom cable assemblies with modest minimum requirements.

| | | | | | | |
|-------------|---|----|-----|--------|--------|-------|
| CAU900MM-1M | LSZH SCSI-3 Cable, HPDB68 Male / Male, 1.0m | 34 | C-C | 84.95 | 78.15 | 71.36 |
| CAU900MM-2M | LSZH SCSI-3 Cable, HPDB68 Male / Male, 2.0m | 34 | C-C | 99.95 | 91.95 | 83.96 |
| CAU900MM-3M | LSZH SCSI-3 Cable, HPDB68 Male / Male, 3.0m | 34 | C-C | 114.95 | 105.75 | 96.56 |

| Item # | Description | 1-9 | 10-24 | 25-99 | 100-249 | 250-499 |
|--------|-------------|-----|-------|-------|---------|---------|
|--------|-------------|-----|-------|-------|---------|---------|

✓RoHS 2-56 SCSI-3 Replacement Thumbscrews, Pkg/10

These thumbscrews are designed for all L-com's molded SCSI-3/HPDB68 cable assemblies - CAF900MM, CA900MM and CA2060MM. Material is steel with nickel finish.

| | | | | | | |
|----------|---|------|------|------|------|------|
| TS-SCSI3 | 2-56 SCSI-3 Replacement Thumbscrews, Pkg/10 | 4.10 | 3.85 | 3.61 | 3.36 | 3.12 |
|----------|---|------|------|------|------|------|

