


L-com vs. Our Competitors

Superior performance requires superior construction. The features beneath the surface are the reason many OEMs have chosen L-com as a key supplier of critical cabling. Superior connector termination utilizing an all steel box provides 360° shielding and reliable strain relief.


The bulk cable is double shielded and utilizes 3 mini true 75 Ohm coaxial lines for unmatched video performance. Available on L-com CTL premium and deluxe cable assemblies.

CTL3VGA / CGSVG A Cable Makeup



A cutaway view of one of L-com's premium and deluxe cables

L-com's Construction



CTLF3VGAMM (with ferrites) CTL3VGAMM-B

Best Seller

CTL3VGAMM

CGSVGAMM

Item #	Description	#Coax	1-9	10-24	25-99	100-249	250-499
RoHS Premium Grade Black SVGA Cables - HD15M to HD15M with Coaxial Inners and Ferrites							
Premium video assemblies utilize coaxial and twisted pair signal lines plus ferrite cores on either end for optimum video performance.							
CTLF3VGAMM-5	SVGA Cable, HD15 Male / Male with Ferrites, 5.0ft (1.5m)	3	32.00	30.72	29.44	28.16	26.88
CTLF3VGAMM-10	SVGA Cable, HD15 Male / Male with Ferrites, 10.0ft (3.0m)	3	42.00	40.32	38.64	36.96	35.28
CTLF3VGAMM-25	SVGA Cable, HD15 Male / Male with Ferrites, 25.0ft (7.6m)	3	72.00	69.12	66.24	63.36	60.48
CTLF3VGAMM-50	SVGA Cable, HD15 Male / Male with Ferrites, 50.0ft (15.2m)	3	122.00	117.12	112.24	107.36	102.48
CTLF3VGAMM-100	SVGA Cable, HD15 Male / Male with Ferrites, 100.0ft (30.5m)	3	222.00	213.12	204.24	195.36	186.48
CTLF3VGAMM-200	SVGA Cable, HD15 Male / Male with Ferrites, 200.0ft (61.0m)	3	422.00	405.12	388.24	371.36	354.48
RoHS Deluxe Grade Black SVGA Cables - HD15M to HD15M with Coaxial Inners							
Deluxe video assemblies utilize coaxial and twisted pair signal lines for low loss of signal.							
CTL3VGAMM-3B	SVGA Cable, HD15 Male / Male, 3.0ft (0.9m)	3	21.00	19.74	18.48	17.22	15.96
CTL3VGAMM-5B	SVGA Cable, HD15 Male / Male, 5.0ft (1.5m)	3	24.00	22.56	21.12	19.68	18.24
CTL3VGAMM-10B	SVGA Cable, HD15 Male / Male, 10.0ft (3.0m)	3	31.50	29.61	27.72	25.83	23.94
CTL3VGAMM-20B	SVGA Cable, HD15 Male / Male, 20.0ft (6.1m)	3	46.50	43.71	40.92	38.13	35.34
CTL3VGAMM-25B	SVGA Cable, HD15 Male / Male, 25.0ft (7.6m)	3	54.00	50.76	47.52	44.28	41.04
CTL3VGAMM-50B	SVGA Cable, HD15 Male / Male, 50.0ft (15.2m)	3	91.50	86.01	80.52	75.03	69.54
CTL3VGAMM-100B	SVGA Cable, HD15 Male / Male, 100.0ft (30.5m)	3	166.50	156.51	146.52	136.53	126.54
CTL3VGAMM-150B	SVGA Cable, HD15 Male / Male, 150.0ft (45.7m)	3	241.50	227.01	212.52	198.03	183.54
CTL3VGAMM-200B	SVGA Cable, HD15 Male / Male, 200.0ft (61.0m)	3	316.50	297.51	278.52	259.53	240.54
RoHS Deluxe Grade Black SVGA Extension Cables - HD15M to HD15F with Coaxial Inners							
CTL3VGAMF-5B	SVGA Extension Cable, HD15 Male / Female, 5.0ft (1.5m)	3	24.00	22.56	21.12	19.68	18.24
CTL3VGAMF-10B	SVGA Extension Cable, HD15 Male / Female, 10.0ft (3.0m)	3	31.50	29.61	27.72	25.83	23.94
CTL3VGAMF-20B	SVGA Extension Cable, HD15 Male / Female, 20.0ft (6.1m)	3	46.50	43.71	40.92	38.13	35.34
CTL3VGAMF-25B	SVGA Extension Cable, HD15 Male / Female, 25.0ft (7.6m)	3	54.00	50.76	47.52	44.28	41.04
CTL3VGAMF-50B	SVGA Extension Cable, HD15 Male / Female, 50.0ft (15.2m)	3	91.50	86.01	80.52	75.03	69.54
CTL3VGAMF-75B	SVGA Extension Cable, HD15 Male / Female, 75.0ft (22.9m)	3	129.00	121.26	113.52	105.78	98.04
CTL3VGAMF-100B	SVGA Extension Cable, HD15 Male / Female, 100.0ft (30.5m)	3	166.50	156.51	146.52	136.53	126.54
CTL3VGAMF-150B	SVGA Extension Cable, HD15 Male / Female, 150.0ft (45.7m)	3	241.50	227.01	212.52	198.03	183.54
RoHS Deluxe Grade Gray SVGA Cables - HD15M to HD15M or HD15M to HD15F with Coaxial Inners							
These deluxe cables mate with high resolution color monitors and workstations having HD15 D-Sub connectors. High efficiency coaxial wiring is featured to support critical color lines. All molded construction, fully shielded throughout. OEM quantity pricing and special lengths upon request. Color: Gray.							
CTL3VGAMM-3	SVGA Cable, HD15 Male / Male, 3.0ft (0.9m)	3	26.95	24.79	22.64	20.48	18.33
CTL3VGAMM-5	SVGA Cable, HD15 Male / Male, 5.0ft (1.5m)	3	28.95	26.63	24.32	22.00	19.69
CTL3VGAMM-10	SVGA Cable, HD15 Male / Male, 10.0ft (3.0m)	3	33.95	31.23	28.52	25.80	23.09
CTL3VGAMF-5	SVGA Extension Cable, HD15 Male / Female, 5.0ft (1.5m)	3	28.95	26.63	24.32	22.00	19.69
CTL3VGAMF-10	SVGA Extension Cable, HD15 Male / Female, 10.0ft (3.0m)	3	33.95	31.23	28.52	25.80	23.09
CTL3VGAMF-25	SVGA Extension Cable, HD15 Male / Female, 25.0ft (7.6m)	3	48.95	45.03	41.12	37.20	33.29
RoHS Standard Grade Black SVGA Cable Assemblies - HD15M to HD15M or HD15M to HD15F							
L-com's new competitively priced standard grade SVGA cables feature three 75 Ohm coaxial cables to assure high quality video signal transmission. Fully molded backshells provide durability and long life expectancy. These rugged RoHS compliant assemblies are available in standard off the shelf lengths from 3 to 50 feet.							
CGSVGAMM-3	SVGA Cable, HD15 Male / Male, 3.0ft (0.9m)	3	10.99	10.11	9.23	8.35	7.47
CGSVGAMM-5	SVGA Cable, HD15 Male / Male, 5.0ft (1.5m)	3	11.99	11.03	10.07	9.11	8.15
CGSVGAMM-10	SVGA Cable, HD15 Male / Male, 10.0ft (3.0m)	3	18.79	17.29	15.78	14.28	12.78
CGSVGAMM-20	SVGA Cable, HD15 Male / Male, 20.0ft (6.1m)	3	32.00	29.44	26.88	24.32	21.76
CGSVGAMM-25	SVGA Cable, HD15 Male / Male, 25.0ft (7.6m)	3	35.00	32.20	29.40	26.60	23.80
CGSVGAMM-50	SVGA Cable, HD15 Male / Male, 50.0ft (15.2m)	3	68.99	63.47	57.95	52.43	46.91
CGSVGAMF-3	SVGA Cable, HD15 Male / Female, 3.0ft (0.9m)	3	11.20	10.30	9.41	8.51	7.62
CGSVGAMF-5	SVGA Cable, HD15 Male / Female, 5.0ft (1.5m)	3	12.20	11.22	10.25	9.27	8.30
CGSVGAMF-10	SVGA Cable, HD15 Male / Female, 10.0ft (3.0m)	3	19.05	17.53	16.00	14.48	12.95
CGSVGAMF-20	SVGA Cable, HD15 Male / Female, 20.0ft (6.1m)	3	33.33	30.66	28.00	25.33	22.66
CGSVGAMF-25	SVGA Cable, HD15 Male / Female, 25.0ft (7.6m)	3	35.49	32.65	29.81	26.97	24.13
CGSVGAMF-50	SVGA Cable, HD15 Male / Female, 50.0ft (15.2m)	3	69.19	63.65	58.12	52.58	47.05