

**Best Seller**




CTLB3VGAMM-T  
CTLB3VGAMM-TP  
CTLB3VGAMM-TZ



CTLB3VGAMF-T


Fits through 3/4" conduit



.750"



CTL3KVM



CTL3KVMF



CTLVCCMM

Item #	Description	#Coax	1-9	10-24	25-99	100-249	250-499
<b>✓RoHS SVGA Cables with Low Profile Disconnect Feature - HD15 Male to HD15 Male or HD15 Female</b>							
Now there is a solution to your difficult installation problems. A fully populated DDC compliant assembly with HD15 male/male or male/female connectors utilizing our Super Thin cable, reversible hardware plus a low profile break connector. The low profile break connector's small size (.75" wide) allows routing through 3/4" (1.9cm) conduit and through tight spaces that would not accommodate the size of a HD15 connector. Color: Black.							
CTLB3VGAMM-15T	Super Thin SVGA Cable, HD15 Male / Male, 15.0ft (4.6m)	3	70.00	63.00	56.00	49.00	42.00
CTLB3VGAMM-20T	Super Thin SVGA Cable, HD15 Male / Male, 20.0ft (6.1m)	3	80.00	72.00	64.00	56.00	48.00
CTLB3VGAMM-25T	Super Thin SVGA Cable, HD15 Male / Male, 25.0ft (7.6m)	3	90.00	81.00	72.00	63.00	54.00
CTLB3VGAMM-50T	Super Thin SVGA Cable, HD15 Male / Male, 50.0ft (15.24m)	3	140.00	126.00	112.00	98.00	84.00
CTLB3VGAMM-75T	Super Thin SVGA Cable, HD15 Male / Male, 75.0ft (22.9m)	3	190.00	171.00	152.00	133.00	114.00
CTLB3VGAMF-15T	Super Thin SVGA Cable, HD15 Male / Female, 15.0ft (4.6m)	3	70.00	63.00	56.00	49.00	42.00
CTLB3VGAMF-20T	Super Thin SVGA Cable, HD15 Male / Female, 20.0ft (6.1m)	3	80.00	75.20	70.40	65.60	60.80
CTLB3VGAMF-25T	Super Thin SVGA Cable, HD15 Male / Female, 25.0ft (7.6m)	3	90.00	81.00	72.00	63.00	54.00
CTLB3VGAMF-50T	Super Thin SVGA Cable, HD15 Male / Female, 50.0ft (15.24m)	3	140.00	126.00	112.00	98.00	84.00
CTLB3VGAMF-75T	Super Thin SVGA Cable, HD15 Male / Female, 75.0ft (22.9m)	3	190.00	171.00	152.00	133.00	114.00

<b>✓RoHS Plenum Jacket SVGA Cables with Low Profile Disconnect Feature - HD15 Male to HD15 Male</b>							
This series is identical to our SVGA cables with one important exception, the outer jacket is made from CMP grade plenum material for applications where fire resistance and low smoke characteristics are critical. Color: Black.							
CTLB3VGAMM-15TP	Super Thin Plenum SVGA Cable, HD15 Male / Male, 15.0ft (4.6m)	3	225.00	220.50	216.00	211.50	207.00
CTLB3VGAMM-25TP	Super Thin Plenum SVGA Cable, HD15 Male / Male, 25.0ft (7.6m)	3	325.00	318.50	312.00	305.50	299.00
CTLB3VGAMM-50TP	Super Thin Plenum SVGA Cable, HD15 Male / Male, 50.0ft (15.24m)	3	575.00	563.50	552.00	540.50	529.00
CTLB3VGAMM-75TP	Super Thin Plenum SVGA Cable, HD15 Male / Male, 75.0ft (22.9m)	3	825.00	808.50	792.00	775.50	759.00

<b>✓RoHS LSZH Jacket SVGA Cables with Low Profile Disconnect Feature - HD15 Male to HD15 Male</b>							
This series features a fully populated DDC compliant assembly with (2) low profile HD15 male connectors and our low smoke zero halogen Super Thin cable. An additional feature is our unique user defined mounting hardware plus a low profile break connector which allows routing through 3/4" (1.9cm) conduit and other tight spaces. Offered in standard lengths with a 1 foot lead in length to the low profile connector.							
CTLB3VGAMM-15TZ	Super Thin LSZH SVGA Cable, HD15 Male / Male, 15.0ft (4.6m)	3	85.00	79.90	74.80	69.70	64.60
CTLB3VGAMM-20TZ	Super Thin LSZH SVGA Cable, HD15 Male / Male, 20.0ft (6.1m)	3	100.00	94.00	88.00	82.00	76.00
CTLB3VGAMM-25TZ	Super Thin LSZH SVGA Cable, HD15 Male / Male, 25.0ft (7.6m)	3	115.00	108.10	101.20	94.30	87.40
CTLB3VGAMM-50TZ	Super Thin LSZH SVGA Cable, HD15 Male / Male, 50.0ft (15.24m)	3	190.00	178.60	167.20	155.80	144.40
CTLB3VGAMM-75TZ	Super Thin LSZH SVGA Cable, HD15 Male / Male, 75.0ft (22.9m)	3	265.00	249.10	233.20	217.30	201.40

**Use the CTLB series cable for running through 3/4" (1.9cm) conduit**



**Online Video**

[L-com.com/videos/A04](http://L-com.com/videos/A04)



**STEP 1**  
Feed socket end through conduit (3/4" min. dia.) into destination outlet.



**STEP 2**  
Slip shrinkable tubing onto cable, mate the breakout connector matching alignment arrows and secure.



**STEP 3**  
Attach pre-terminated HD15 connector to faceplate and attach to outlet.

<b>✓RoHS KVM Cables - Integrate HD15 Video and 2 Mini DIN 6 Keyboard and Mouse Lines in One</b>							
The CTL3KVM series combines a HD15 (video) cable with two Mini DIN 6 (keyboard and mouse) lines into one assembly. Available in male-male genders for interconnection between a KVM switch and CPU or male-female for connecting between a CPU and the keyboard, monitor and mouse. Color: Black.							
CTL3KVM-3	KVM Cable, Male / Male, 3.0ft (0.9m)	47.70	45.79	43.88	41.98	40.07	
CTL3KVM-5	KVM Cable, Male / Male, 5.0ft (1.5m)	51.50	49.44	47.38	45.32	43.26	
CTL3KVM-7.5	KVM Cable, Male / Male, 7.5 ft (2.3cm)	56.25	54.00	51.75	49.50	47.25	
CTL3KVM-10	KVM Cable, Male / Male, 10.0ft (3.0m)	61.00	58.56	56.12	53.68	51.24	
CTL3KVM-20	KVM Cable, Male / Male, 20.0ft (6.1m)	80.00	76.80	73.60	70.40	67.20	
CTL3KVM-25	KVM Cable, Male / Male, 25.0ft (7.6m)	89.50	85.92	82.34	78.76	75.18	
CTL3KVM-50	KVM Cable, Male / Male, 50.0ft (15.24m)	137.00	131.52	126.04	120.56	115.08	
CTL3KVM-100	KVM Cable, Male / Male, 100.0ft (30.5m)	232.00	222.72	213.44	204.16	194.88	
CTL3KVMF-3	KVM Cable, Male / Female, 3.0ft (0.9m)	49.70	47.71	45.72	43.74	41.75	
CTL3KVMF-5	KVM Cable, Male / Female, 5.0ft (1.5m)	53.50	51.36	49.22	47.08	44.94	
CTL3KVMF-7.5	KVM Cable, Male / Female, 7.5 ft (2.3cm)	58.25	55.92	53.59	51.26	48.93	
CTL3KVMF-10	KVM Cable, Male / Female, 10.0ft (3.0m)	63.00	60.48	57.96	55.44	52.92	
CTL3KVMF-20	KVM Cable, Male / Female, 20.0ft (6.1m)	82.00	78.72	75.44	72.16	68.88	
CTL3KVMF-25	KVM Cable, Male / Female, 25.0ft (7.6m)	91.50	87.84	84.18	80.52	76.86	
CTL3KVMF-50	KVM Cable, Male / Female, 50.0ft (15.24m)	139.00	133.44	127.88	122.32	116.76	
CTL3KVMF-100	KVM Cable, Male / Female, 100.0ft (30.5m)	234.00	224.64	215.28	205.92	196.56	

**Enhanced Video Connector (EVC or P&D) Cable Assemblies**

The Video Electronics Standards Association (VESA) established a standard for advanced high bandwidth/high resolution monitors. It's called EVC, which stands for Enhanced Video Connector. Also known as P&D (Plug & Display), this standard was designed for higher bandwidth video transmission exceeding 2 GHz. It also utilizes connections for multimedia devices via Universal Serial Bus (USB), IEEE-1394 and Display Data Channel (DDC) pins inherent in the connector.

<b>✓RoHS EVC Male to EVC Male, Fully Populated, Molded Cable Assembly</b>							
CTLVCCMM-5	EVC Cable, Male / Male, 5.0ft (1.5m)	104.00	101.92	99.84	97.76	95.68	
CTLVCCMM-10	EVC Cable, Male / Male, 10.0ft (3.0m)	116.50	114.17	111.84	109.51	107.18	
CTLVCCMM-15	EVC Cable, Male / Male, 15.0ft (4.6m)	129.00	126.42	123.84	121.26	118.68	
CTLVCCMM-25	EVC Cable, Male / Male, 25.0ft (7.6m)	154.00	150.92	147.84	144.76	141.68	
CTLVCCMM-50	EVC Cable, Male / Male, 50.0ft (15.24m)	259.00	253.82	248.64	243.46	238.28	

**Running CTLB cable through 3/4" (1.9cm) conduit**  
See the free video tip and more at [L-com.com/Videos/A04](http://L-com.com/Videos/A04)

