





CTL3B-B



CTL4B-B




CTL5B-B



CTL8B-B



PR175B1675BLK



PR35B3275BLK

Item #	Description	#Coax	1-9	10-24	25-99	100-249	250-499
<b>Premium 3 Line Coaxial Cable with BNC Plugs</b>							
CTL3B-5B	Premium Multi-Coaxial Cable, 3 BNC Male / Male, 5.0ft (1.5m)	3	21.75	20.01	18.27	16.53	14.79
CTL3B-7.5B	Premium Multi-Coaxial Cable, 3 BNC Male / Male, 7.5ft (2.3m)	3	25.15	23.14	21.13	19.11	17.10
CTL3B-10B	Premium Multi-Coaxial Cable, 3 BNC Male / Male, 10.0ft (3.0m)	3	28.50	26.22	23.94	21.66	19.38
CTL3B-15B	Premium Multi-Coaxial Cable, 3 BNC Male / Male, 15.0ft (4.6m)	3	35.25	32.43	29.61	26.79	23.97
CTL3B-25B	Premium Multi-Coaxial Cable, 3 BNC Male / Male, 25.0ft (7.6m)	3	48.75	44.85	40.95	37.05	33.15
CTL3B-50B	Premium Multi-Coaxial Cable, 3 BNC Male / Male, 50.0ft (15.24m)	3	82.50	75.90	69.30	62.70	56.10

**Premium 4 Line Coaxial Cable with BNC Plugs**

These multiple line coaxial assemblies provide a neatly packaged bundle for use in such applications as video servers. They replace individual coaxial runs that can be difficult to handle in high density applications eliminating unsightly cable entanglements. Individual coaxial lines are color coded to assure proper connections are made. All coaxial lines are 75 Ohm impedance and feature full shield coverage comprised of copper braid and aluminum backed Mylar.

CTL4B-5B	Premium Multi-Coaxial Cable, 4 BNC Male / Male, 5.0ft (1.5m)	4	26.50	24.38	22.26	20.14	18.02
CTL4B-7.5B	Premium Multi-Coaxial Cable, 4 BNC Male / Male, 7.5ft (2.3m)	4	30.75	28.29	25.83	23.37	20.91
CTL4B-10B	Premium Multi-Coaxial Cable, 4 BNC Male / Male, 10.0ft (3.0m)	4	35.00	32.20	29.40	26.60	23.80
CTL4B-15B	Premium Multi-Coaxial Cable, 4 BNC Male / Male, 15.0ft (4.6m)	4	43.50	40.02	36.54	33.06	29.58
CTL4B-25B	Premium Multi-Coaxial Cable, 4 BNC Male / Male, 25.0ft (7.6m)	4	60.50	55.66	50.82	45.98	41.14
CTL4B-50B	Premium Multi-Coaxial Cable, 4 BNC Male / Male, 50.0ft (15.24m)	4	103.00	94.76	86.52	78.28	70.04

**Premium 5 Line Coaxial Cable with BNC Plugs**

L-com's Premium grade five line BNC coaxial cables are perfect for professional 75 Ohm analog video applications. Each coax line is color coded so identification of attached devices for troubleshooting and reference is a snap. These cables feature double shielding consisting of a copper braid as well as aluminum Mylar wrap.

CTL5B-5B	Premium Multi-Coaxial Cable, 5 BNC Male / Male, 5.0ft (1.5m)	5	31.50	28.98	26.46	23.94	21.42
CTL5B-7.5B	Premium Multi-Coaxial Cable, 5 BNC Male / Male, 7.5ft (2.3m)	5	36.75	33.81	30.87	27.93	24.99
CTL5B-10B	Premium Multi-Coaxial Cable, 5 BNC Male / Male, 10.0ft (3.0m)	5	42.00	38.64	35.28	31.92	28.56
CTL5B-15B	Premium Multi-Coaxial Cable, 5 BNC Male / Male, 15.0ft (4.6m)	5	52.50	48.30	44.10	39.90	35.70
CTL5B-25B	Premium Multi-Coaxial Cable, 5 BNC Male / Male, 25.0ft (7.6m)	5	73.50	67.62	61.74	55.86	49.98
CTL5B-50B	Premium Multi-Coaxial Cable, 5 BNC Male / Male, 50.0ft (15.24m)	5	126.00	115.92	105.84	95.76	85.68

**Premium 8 Line Coaxial Cable with BNC Plugs**

Perfect for high density video applications, these eight line coaxial cables replace individual coax cable runs that can be difficult to handle and route in dense connectivity applications. Double shielded and color coded, these robust cable assemblies provide quality 75 Ohm analog video output.

CTL8B-5B	Premium Multi-Coaxial Cable, 8 BNC Male / Male, 5.0ft (1.5m)	8	75.00	70.50	66.00	61.50	57.00
CTL8B-7.5B	Premium Multi-Coaxial Cable, 8 BNC Male / Male, 7.5ft (2.3m)	8	80.00	75.20	70.40	65.60	60.80
CTL8B-10B	Premium Multi-Coaxial Cable, 8 BNC Male / Male, 10.0ft (3.0m)	8	85.00	79.90	74.80	69.70	64.60
CTL8B-15B	Premium Multi-Coaxial Cable, 8 BNC Male / Male, 15.0ft (4.6m)	8	95.00	89.30	83.60	77.90	72.20
CTL8B-20B	Premium Multi-Coaxial Cable, 8 BNC Male / Male, 20.0ft (6.1m)	8	105.00	98.70	92.40	86.10	79.80
CTL8B-25B	Premium Multi-Coaxial Cable, 8 BNC Male / Male, 25.0ft (7.6m)	8	115.00	108.10	101.20	94.30	87.40

**L-com 75 Ohm BNC 1U/2U Patch Panels – 19" (48.3cm) Rack Style**

These robust BNC patch panels are made from 16 gauge cold rolled steel and finished with a durable black powder coat. These patch panels can be mounted in any 19" rack or cabinet.

PR175B1675BLK	1.75" (4.4cm) Panel, 16 - 75 Ohm BNC Adapters Insulated	109.95	101.15	92.36	83.56	CALL
PR35B3275BLK	3.50" (8.9cm) Panel, 32 - 75 Ohm BNC Adapters Insulated	209.95	193.15	176.36	159.56	CALL



**Distinguishing between 50 and 75 Ohm BNC connectors**

BNC connectors are one of the few coaxial connectors that are available in two impedance values of 50 and 75 Ohms. You can distinguish the two types by the absence of dielectric material at the interface of the 75 Ohm version as shown.

