



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

**RG59A/U - 75 Ohm Coaxial Cables with Inline Molded BNC and RCA Plugs**

L-com offers a wide variety of RG59A/U cable assemblies utilizing BNC and RCA connectors. RG59A/U cable is one of the most commonly used 75 Ohm cables. In addition to inline configurations L-com offers right angle and female bulkheads. All connectors feature a molded strain relief while the Type F connector features a captivated gold plated center pin for enhanced performance. The stranded center conductor of the RG59A/U cable provides maximum flexibility.

<p><b>75 Ohm Impedance</b></p>	<p><b>RG59A/U</b></p> <ul style="list-style-type: none"> <li>Center Conductor: 22 (7 x 30) AWG bare compacted copper</li> <li>Shielding: Bare copper braid (96% coverage)</li> <li>Insulation: Foam polyethylene</li> <li>Jacket: Black PVC</li> <li>Operating Temperature: -40°C - +80°C</li> </ul>	<p><b>NOMINAL ATTENUATION</b></p>		
		MHz	db/100ft	db/100m
		50	2.1	6.9
100	3.0	9.8		
200	4.5	14.8		
400	6.6	21.7		
1000	10.9	35.8		

**RoHS RG59A/U - 75 Ohm Coaxial Cables with Two Inline BNC Plugs**

CC59A-05	RG59A Cable, BNC Male / Male, 0.5ft (0.2m)	8.75	8.40	8.05	7.70	7.35
CC59A-1	RG59A Cable, BNC Male / Male, 1.0ft (0.3m)	9.00	8.64	8.28	7.92	7.56
CC59A-1.5	RG59A Cable, BNC Male / Male, 1.5ft (0.5m)	9.25	8.88	8.51	8.14	7.77
CC59A-2	RG59A Cable, BNC Male / Male, 2.0ft (0.6m)	9.50	9.12	8.74	8.36	7.98
CC59A-2.5	RG59A Cable, BNC Male / Male, 2.5ft (0.8m)	9.75	9.36	8.97	8.58	8.19
CC59A-3	RG59A Cable, BNC Male / Male, 3.0ft (0.9m)	10.00	9.60	9.20	8.80	8.40
CC59A-4	RG59A Cable, BNC Male / Male, 4.0ft (1.2m)	10.50	10.08	9.66	9.24	8.82
CC59A-5	RG59A Cable, BNC Male / Male, 5.0ft (1.5m)	11.00	10.56	10.12	9.68	9.24
CC59A-6	RG59A Cable, BNC Male / Male, 6.0ft (1.8m)	11.50	11.04	10.58	10.12	9.66
CC59A-7.5	RG59A Cable, BNC Male / Male, 7.5ft (2.3m)	12.25	11.76	11.27	10.78	10.29
CC59A-10	RG59A Cable, BNC Male / Male, 10.0ft (3.0m)	13.50	12.96	12.42	11.88	11.34
CC59A-12	RG59A Cable, BNC Male / Male, 12.0ft (3.6m)	14.50	13.92	13.34	12.76	12.18
CC59A-15	RG59A Cable, BNC Male / Male, 15.0ft (4.6m)	16.00	15.36	14.72	14.08	13.44
CC59A-25	RG59A Cable, BNC Male / Male, 25.0ft (7.6m)	21.00	20.16	19.32	18.48	17.64
CC59A-50	RG59A Cable, BNC Male / Male, 50.0ft (15.2m)	33.50	32.16	30.82	29.48	28.14
CC59A-75	RG59A Cable, BNC Male / Male, 75.0ft (22.9m)	46.00	44.16	42.32	40.48	38.64
CC59A-100	RG59A Cable, BNC Male / Male, 100.0ft (30.5m)	58.50	56.16	53.82	51.48	49.14
CC59A-150	RG59A Cable, BNC Male / Male, 150.0ft (45.7m)	83.50	80.16	76.82	73.48	70.14
CC59A-200	RG59A Cable, BNC Male / Male, 200.0ft (61m)	108.50	104.16	99.82	95.48	91.14

**RoHS RG59A/U - 75 Ohm Coaxial Cables with Inline BNC to Right Angle BNC Plugs**

CC59A-1HR	RG59A Cable, BNC Male / 90° Male, 1.0ft (0.3m)	11.25	10.80	10.35	9.90	9.45
CC59A-1.5HR	RG59A Cable, BNC Male / 90° Male, 1.5ft (0.5m)	11.50	11.04	10.58	10.12	9.66
CC59A-2HR	RG59A Cable, BNC Male / 90° Male, 2.0ft (0.6m)	11.75	11.28	10.81	10.34	9.87
CC59A-2.5HR	RG59A Cable, BNC Male / 90° Male, 2.5ft (0.8m)	12.00	11.52	11.04	10.56	10.08
CC59A-3HR	RG59A Cable, BNC Male / 90° Male, 3.0ft (0.9m)	12.25	11.76	11.27	10.78	10.29
CC59A-4HR	RG59A Cable, BNC Male / 90° Male, 4.0ft (1.2m)	12.75	12.24	11.73	11.22	10.71
CC59A-5HR	RG59A Cable, BNC Male / 90° Male, 5.0ft (1.5m)	13.25	12.72	12.19	11.66	11.13
CC59A-7.5HR	RG59A Cable, BNC Male / 90° Male, 7.5ft (2.3m)	14.50	13.92	13.34	12.76	12.18
CC59A-10HR	RG59A Cable, BNC Male / 90° Male, 10.0ft (3.0m)	15.75	15.12	14.49	13.86	13.23

**RoHS RG59A/U - 75 Ohm Coaxial Cables with Two Inline RCA Plugs**

CC59A-RR-1	RG59A Cable, RCA Male / Male, 1.0ft (0.3m)	4.50	4.32	4.14	3.96	3.78
CC59A-RR-3	RG59A Cable, RCA Male / Male, 3.0ft (0.9m)	5.50	5.28	5.06	4.84	4.62
CC59A-RR-6	RG59A Cable, RCA Male / Male, 6.0ft (1.8m)	7.00	6.72	6.44	6.16	5.88
CC59A-RR-9	RG59A Cable, RCA Male / Male, 9.0ft (2.7m)	8.50	8.16	7.82	7.48	7.14
CC59A-RR-12	RG59A Cable, RCA Male / Male, 12.0ft (3.6m)	10.00	9.60	9.20	8.80	8.40

**RoHS RG59A/U - 75 Ohm Coaxial Cables with Inline RCA to Inline BNC Plug**

CC59A-RB-1	RG59A Cable, RCA Male / BNC Male, 1.0ft (0.3m)	4.50	4.32	4.14	3.96	3.78
CC59A-RB-3	RG59A Cable, RCA Male / BNC Male, 3.0ft (0.9m)	5.50	5.28	5.06	4.84	4.62
CC59A-RB-6	RG59A Cable, RCA Male / BNC Male, 6.0ft (1.8m)	7.00	6.72	6.44	6.16	5.88
CC59A-RB-9	RG59A Cable, RCA Male / BNC Male, 9.0ft (2.7m)	8.50	8.16	7.82	7.48	7.14
CC59A-RB-12	RG59A Cable, RCA Male / BNC Male, 12.0ft (3.6m)	10.00	9.60	9.20	8.80	8.40

<p><b>75 Ohm Impedance</b></p>	<p><b>RG59B/U</b></p> <ul style="list-style-type: none"> <li>Center Conductor: 22 AWG solid bare copper covered steel</li> <li>Shielding: Bare copper braid (95% coverage)</li> <li>Insulation: Polyethylene</li> <li>Jacket: Black PVC</li> <li>Operating Temperature: -40°C - +80°C</li> </ul>	<p><b>NOMINAL ATTENUATION</b></p>		
		MHz	db/100ft	db/100m
		50	2.4	7.9
100	3.4	11.1		
200	4.9	16.1		
400	7.0	23.0		
1000	12.0	39.3		

**RoHS RG59B/U - 75 Ohm Coaxial Cables with Two Inline BNC Plugs**

CC59B-05	RG59B Cable, BNC Male / Male, 0.5ft (0.2m)	8.75	8.40	8.05	7.70	7.35
CC59B-1	RG59B Cable, BNC Male / Male, 1.0ft (0.3m)	9.00	8.64	8.28	7.92	7.56
CC59B-1.5	RG59B Cable, BNC Male / Male, 1.5ft (0.5m)	9.25	8.88	8.51	8.14	7.77
CC59B-2	RG59B Cable, BNC Male / Male, 2.0ft (0.6m)	9.50	9.12	8.74	8.36	7.98
CC59B-2.5	RG59B Cable, BNC Male / Male, 2.5ft (0.8m)	9.75	9.36	8.97	8.58	8.19
CC59B-3	RG59B Cable, BNC Male / Male, 3.0ft (0.9m)	10.00	9.60	9.20	8.80	8.40
CC59B-4	RG59B Cable, BNC Male / Male, 4.0ft (1.2m)	10.50	10.08	9.66	9.24	8.82
CC59B-5	RG59B Cable, BNC Male / Male, 5.0ft (1.5m)	11.00	10.56	10.12	9.68	9.24
CC59B-6	RG59B Cable, BNC Male / Male, 6.0ft (1.8m)	11.50	11.04	10.58	10.12	9.66
CC59B-7.5	RG59B Cable, BNC Male / Male, 7.5ft (2.3m)	12.25	11.76	11.27	10.78	10.29
CC59B-10	RG59B Cable, BNC Male / Male, 10.0ft (3.0m)	13.50	12.96	12.42	11.88	11.34
CC59B-12	RG59B Cable, BNC Male / Male, 12.0ft (3.6m)	14.50	13.92	13.34	12.76	12.18
CC59B-15	RG59B Cable, BNC Male / Male, 15.0ft (4.6m)	16.00	15.36	14.72	14.08	13.44
CC59B-25	RG59B Cable, BNC Male / Male, 25.0ft (7.6m)	21.00	20.16	19.32	18.48	17.64
CC59B-50	RG59B Cable, BNC Male / Male, 50.0ft (15.2m)	33.50	32.16	30.82	29.48	28.14
CC59B-75	RG59B Cable, BNC Male / Male, 75.0ft (22.9m)	46.00	44.16	42.32	40.48	38.64
CC59B-100	RG59B Cable, BNC Male / Male, 100.0ft (30.5m)	58.50	56.16	53.82	51.48	49.14
CC59B-150	RG59B Cable, BNC Male / Male, 150.0ft (45.7m)	83.50	80.16	76.82	73.48	70.14
CC59B-200	RG59B Cable, BNC Male / Male, 200.0ft (61.0m)	108.50	104.16	99.82	95.48	91.14

"I would like to say that your web site is the best I have ever seen. Well-designed and great photos of the products. It makes it so easy to select the right product. Also the same comments for your catalog. Thanks." - Terry Halbrooks, Deputy Sheriff, Rayville, LA