


### What is S-Video (S-VHS)?

The term S-Video is derived from the way the video signal is transmitted. In S-Video the signal is separated into two components hence the term Separate Video or S-Video. Two 75 Ohm coaxial cables and a Mini DIN 4 connector are utilized to transmit the two component signals. One of the coaxial cables carries the Luminance Signal (brightness or Y component) while the second 75 Ohm coaxial cable carries the Chrominance Signal (color or C component). By separating the video signal into two components a better quality picture is produced than composite video that utilizes one coaxial cable to transmit both signals. The term S-VHS is an acronym for Super-Video Home System.



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

#### ✓RoHS Molded S-Video Cable Assemblies, 75 Ohm Dual Coaxial in Single Jacket

CCD234MM-1	Molded Mini DIN 4 Male / Male, 1.0ft (0.3m)	5.50	5.17	4.84	4.51	4.18
CCD234MM-2	Molded Mini DIN 4 Male / Male, 2.0ft (0.6m)	6.20	5.83	5.46	5.08	4.71
CCD234MM-3	Molded Mini DIN 4 Male / Male, 3.0ft (0.9m)	6.90	6.49	6.07	5.66	5.24
CCD234MM-5	Molded Mini DIN 4 Male / Male, 5.0ft (1.5m)	8.30	7.80	7.30	6.81	6.31
CCD234MM-7.5	Molded Mini DIN 4 Male / Male, 7.5ft (2.3m)	10.05	9.45	8.84	8.24	7.64
CCD234MM-10	Molded Mini DIN 4 Male / Male, 10.0ft (3.0m)	11.80	11.09	10.38	9.68	8.97
CCD234MM-20	Molded Mini DIN 4 Male / Male, 20.0ft (6.1m)	18.80	17.67	16.54	15.42	14.29
CCD234MM-30	Molded Mini DIN 4 Male / Male, 30.0ft (9.1m)	25.80	24.25	22.70	21.16	19.61
CCD234MM-40	Molded Mini DIN 4 Male / Male, 40.0ft (12.2m)	32.80	30.83	28.86	26.90	24.93
CCD234MM-50	Molded Mini DIN 4 Male / Male, 50.0ft (15.2m)	39.80	37.41	35.02	32.64	30.25
CCD234MF-1	Molded Mini DIN 4 Male / Female, 1.0ft (0.3m)	5.50	5.17	4.84	4.51	4.18
CCD234MF-2	Molded Mini DIN 4 Male / Female, 2.0ft (0.6m)	6.20	5.83	5.46	5.08	4.71
CCD234MF-3	Molded Mini DIN 4 Male / Female, 3.0ft (0.9m)	6.90	6.49	6.07	5.66	5.24
CCD234MF-5	Molded Mini DIN 4 Male / Female, 5.0ft (1.5m)	8.30	7.80	7.30	6.81	6.31
CCD234MF-7.5	Molded Mini DIN 4 Male / Female, 7.5ft (2.3m)	10.05	9.45	8.84	8.24	7.64
CCD234MF-10	Molded Mini DIN 4 Male / Female, 10.0ft (3.0m)	11.80	11.09	10.38	9.68	8.97
CCD234MF-20	Molded Mini DIN 4 Male / Female, 20.0ft (6.1m)	18.80	17.67	16.54	15.42	14.29

#### ✓RoHS Assembled S-Video Cable Assemblies, 75 Ohm Dual Coaxial in Single Jacket

CCD244MM-1	Assembled Mini DIN 4 Male / Male, 1.0ft (0.3m)	13.50	12.69	11.88	11.07	10.26
CCD244MM-2	Assembled Mini DIN 4 Male / Male, 2.0ft (0.6m)	14.20	13.35	12.50	11.64	10.79
CCD244MM-3	Assembled Mini DIN 4 Male / Male, 3.0ft (0.9m)	14.90	14.01	13.11	12.22	11.32
CCD244MM-5	Assembled Mini DIN 4 Male / Male, 5.0ft (1.5m)	16.30	15.32	14.34	13.37	12.39
CCD244MM-7.5	Assembled Mini DIN 4 Male / Male, 7.5ft (2.3m)	18.05	16.97	15.88	14.80	13.72
CCD244MM-10	Assembled Mini DIN 4 Male / Male, 10.0ft (3.0m)	19.80	18.61	17.42	16.24	15.05
CCD244MM-20	Assembled Mini DIN 4 Male / Male, 20.0ft (6.1m)	26.80	25.19	23.58	21.98	20.37
CCD244MF-1	Assembled Mini DIN 4 Male / Female, 1.0ft (0.3m)	13.50	12.69	11.88	11.07	10.26
CCD244MF-2	Assembled Mini DIN 4 Male / Female, 2.0ft (0.6m)	14.20	13.35	12.50	11.64	10.79
CCD244MF-3	Assembled Mini DIN 4 Male / Female, 3.0ft (0.9m)	14.90	14.01	13.11	12.22	11.32
CCD244MF-5	Assembled Mini DIN 4 Male / Female, 5.0ft (1.5m)	16.30	15.32	14.34	13.37	12.39
CCD244MF-7.5	Assembled Mini DIN 4 Male / Female, 7.5ft (2.3m)	18.05	16.97	15.88	14.80	13.72
CCD244MF-10	Assembled Mini DIN 4 Male / Female, 10.0ft (3.0m)	19.80	18.61	17.42	16.24	15.05
CCD244MF-20	Assembled Mini DIN 4 Male / Female, 20.0ft (6.1m)	26.80	25.19	23.58	21.98	20.37

#### ✓RoHS Assembled S-Video Cable Assemblies - Molded Dual BNC-M, 75 Ohm Dual Coaxial Breakout Cable

CCD244MB-1	Assembled Mini DIN 4 Male / Dual BNC Male, 1.0ft (0.3m)	13.50	12.69	11.88	11.07	10.26
CCD244MB-2	Assembled Mini DIN 4 Male / Dual BNC Male, 2.0ft (0.6m)	14.20	13.35	12.50	11.64	10.79
CCD244MB-3	Assembled Mini DIN 4 Male / Dual BNC Male, 3.0ft (0.9m)	14.90	14.01	13.11	12.22	11.32
CCD244MB-5	Assembled Mini DIN 4 Male / Dual BNC Male, 5.0ft (1.5m)	16.30	15.32	14.34	13.37	12.39
CCD244MB-7.5	Assembled Mini DIN 4 Male / Dual BNC Male, 7.5ft (2.3m)	18.05	16.97	15.88	14.80	13.72
CCD244MB-10	Assembled Mini DIN 4 Male / Dual BNC Male, 10.0ft (3.0m)	19.80	18.61	17.42	16.24	15.05
CCD244MB-20	Assembled Mini DIN 4 Male / Dual BNC Male, 20.0ft (6.1m)	26.80	25.19	23.58	21.98	20.37

#### Assembled S-Video to Single Composite RCA Cable Assemblies

These cables combine the S-Video Mini DIN 4 connector found on SVHS with the single RCA connector used for composite video allowing the conversion from S-Video transmission to composite video.

CCD144MR-2	Assembled Mini DIN 4 Male / Single RCA Male, 2.0ft (0.6m)	11.00	10.34	9.68	9.02	8.36
CCD144MR-6	Assembled Mini DIN 4 Male / Single RCA Male, 6.0ft (1.8m)	13.00	12.22	11.44	10.66	9.88
CCD144MR-10	Assembled Mini DIN 4 Male / Single RCA Male, 10.0ft (3.0m)	15.00	14.10	13.20	12.30	11.40
CCD144MR-15	Assembled Mini DIN 4 Male / Single RCA Male, 15.0ft (4.6m)	17.50	16.45	15.40	14.35	13.30
CCD144MR-20	Assembled Mini DIN 4 Male / Single RCA Male, 20.0ft (6.1m)	20.00	18.80	17.60	16.40	15.20
CCD144MR-25	Assembled Mini DIN 4 Male / Single RCA Male, 25.0ft (7.6m)	22.50	21.15	19.80	18.45	17.10

"When I order from you I know I get quality products that really do what they are advertised to do. The ongoing research is ever-present. I dread placing online orders, but again not with L-com.com. It is easy, complete, and I am not left wondering if the order went through." - Rick Glatt, Electronic Specialist, CO