

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

✓RoHS Premium RCA Audio/Video Molded Cables - 3 RCAs Per End

Premium high flex Thinline 75 Ohm coaxials and fully molded strain reliefs with gold plated connectors provide rugged and reliable connections. Individual legs colored: Yellow, White and Red.

CCR3MM-2	3 Line RCA Cable, RCA Male / Male, 2.0ft (0.6m)	9.00	8.28	7.56	6.84	6.12
CCR3MM-3	3 Line RCA Cable, RCA Male / Male, 3.0ft (0.9m)	10.00	9.20	8.40	7.60	6.80
CCR3MM-6	3 Line RCA Cable, RCA Male / Male, 6.0ft (1.8m)	13.00	11.96	10.92	9.88	8.84
CCR3MM-9	3 Line RCA Cable, RCA Male / Male, 9.0ft (2.7m)	16.00	14.72	13.44	12.16	10.88
CCR3MM-12	3 Line RCA Cable, RCA Male / Male, 12.0ft (3.6m)	19.00	17.48	15.96	14.44	12.92
CCR3MM-25	3 Line RCA Cable, RCA Male / Male, 25.0ft (7.6m)	32.00	29.44	26.88	24.32	21.76

✓RoHS Premium Molded RCA Audio Cable Assembly - 2 RCAs Per End

These high quality dual line coaxial cables with gold plated RCA connectors provide the best in audio transmission. Color coded in Red and White to easily identify the left and right channel.

CCR2MM-2	2 Line Dual RCA Cable, RCA Male / Male, 2.0ft (0.6m)	6.25	5.88	5.50	5.13	4.75
CCR2MM-3	2 Line Dual RCA Cable, RCA Male / Male, 3.0ft (0.9m)	6.75	6.34	5.94	5.54	5.13
CCR2MM-6	2 Line Dual RCA Cable, RCA Male / Male, 6.0ft (1.8m)	8.25	7.75	7.26	6.77	6.27
CCR2MM-9	2 Line Dual RCA Cable, RCA Male / Male, 9.0ft (2.7m)	9.75	9.16	8.58	8.00	7.41
CCR2MM-12	2 Line Dual RCA Cable, RCA Male / Male, 12.0ft (3.6m)	11.25	10.57	9.90	9.23	8.55
CCR2MM-25	2 Line Dual RCA Cable, RCA Male / Male, 25.0ft (7.6m)	17.75	16.68	15.62	14.56	13.49

✓RoHS Component Video (YCbCr) 3 RCA Plugs in a Single Jacket - Molded Strain Relief

These assemblies utilize premium grade 75 Ohm coaxial cable and gold plated connectors to assure optimum transmission of the component video signal. Coaxial cable is color coded with Red, Green, Blue lines for ease of use. They are bundled in a single jacket with molded strain reliefs providing a rugged yet compact assembly.

CVR3MM-2	3 Line Component Video Cable, RCA Male / Male, 2.0ft (0.6m)	9.00	8.28	7.56	6.84	6.12
CVR3MM-3	3 Line Component Video Cable, RCA Male / Male, 3.0ft (0.9m)	10.00	9.20	8.40	7.60	6.80
CVR3MM-6	3 Line Component Video Cable, RCA Male / Male, 6.0ft (1.8m)	13.00	11.96	10.92	9.88	8.84
CVR3MM-9	3 Line Component Video Cable, RCA Male / Male, 9.0ft (2.7m)	16.00	14.72	13.44	12.16	10.88
CVR3MM-12	3 Line Component Video Cable, RCA Male / Male, 12.0ft (3.6m)	19.00	17.48	15.96	14.44	12.92
CVR3MM-25	3 Line Component Video Cable, RCA Male / Male, 25.0ft (7.6m)	32.00	29.44	26.88	24.32	21.76

✓RoHS RCA Universal Sub-Panels

This Series features a dual RCA coupler model and two triple RCA coupler versions. Our dual model RCA couplers are white and red to denote the traditional left/right audio set up. The triple port versions feature, green, blue and red for component video and yellow, white and red for composite video and left/right audio. Each panel is supplied with four 6-32 screws for quick installation into L-com's universal frame. Pick and choose the connections you need.

USP2RCAB	Universal Sub-Panel, Dual RCA Couplers- Red/White	12.98	12.46	11.94	11.42	10.90
USP3RCA-CB	Universal Sub-Panel, Three RCA Couplers- Green/Blue/Red	15.98	15.34	14.70	14.06	13.42
USP2RCAB	Universal Sub-Panel, Dual RCA Couplers- Red/White	12.98	12.46	11.94	11.42	10.90
USP1SVID2RCAB	Universal Sub-Panel, Single S-Video and Dual RCA Couplers	20.98	20.14	19.30	18.46	17.62
UPR35-6B	Universal Master Rack Panel with 6 Openings, Black	24.95	23.95	22.95	21.96	20.96

✓RoHS RCA 1U and 2U Rack Panels

This series of RCA feedthru rack panels is offered in both 1U high 16 port and 2U high 32 port configurations. Panels are made from 16 gauge cold rolled steel and are finished with a durable black powdercoat. These rugged panels are an excellent choice for professional AV applications.

PR175RCA16	1.75" (4.4cm) x 19" (48.3cm) Panel (Black), 16 RCA Couplers	89.95	88.15	86.35	84.55	82.75
PR35RCA32	3.5" (8.9cm) x 19" (48.3cm) Panel (Black), 32 RCA Couplers	149.95	146.95	143.95	140.95	137.95

✓RoHS RCA Female Feed-Thru Adapter - with Red, Green, Blue, Yellow or White Insulators


These RCA feed-thru adapters feature insulators color coded for both video and audio applications. This color coding assists in component hookup to avoid improper connections.

BA400R	Coaxial Adapter, RCA Bulkhead Female / Female, Red Insulator	3.65	3.43	3.21	2.99	2.77
BA400G	Coaxial Adapter, RCA Bulkhead Female / Female, Green Insulator	3.65	3.43	3.21	2.99	2.77
BA400B	Coaxial Adapter, RCA Bulkhead Female / Female, Blue Insulator	3.65	3.43	3.21	2.99	2.77
BA400Y	Coaxial Adapter, RCA Bulkhead Female / Female, Yellow Insulator	3.65	3.43	3.21	2.99	2.77
BA400	Coaxial Adapter, RCA Bulkhead Female / Female, White Insulator	3.65	3.43	3.21	2.99	2.77
BA400A	Coaxial Adapter, RCA Bulkhead Female / Female, 0.5" (1.3cm) Circular Hole	3.65	3.43	3.21	2.99	2.77



How to tame the RGB, Component, S-Video, Composite beast


Color video signal is transmitted across a wide variety of transmission medias. Below is an illustration of how they work with each other.



Red + Black and White
Green + Black and White
Blue + Black and White

Color and black and white information is combined and transmitted across multiple lines

A converter is needed to separate the color signals from the black and white signals so that it can be transmitted across any one of these medias.



Black and White
Color
Color

Black and White
Color

Color + Black and White

Once the RGB signal is separated into color and black and white elements, interconnection between Component, S-Video and Composite is possible without the use of a converter.

"Rapid response and delivery are a must to succeed in winning a bid or contract. L-com has always been reliable and quick to turn around pricing and product when called upon." - Natasha M.