

Item #	Description	List Price
<b>AdderLink X50 and X50-MS2 Series VGA/USB Extenders</b>		
The AdderLink X50 was designed for use in applications where computers need to have their USB peripherals including keyboards and mice, high quality video and audio control extended up to 50m (150 ft.) across CAT5 or higher UTP cable. The AdderLink X50-MultiScreen adds a second video and transparent, high speed RS-232 up to baud rates of 19200. The AdderLink X50 (MS2) series provides sharp, bright and ultra high-resolution video over a VGA interface(s) and ensures total USB compatibility regardless of the computer being controlled or the peripheral being extended.		
X50-US	AdderLink X50-US, USB / Video Extender	575.00
X50-MS2-US	AdderLink X50-MS2-US, USB / Multiscreen Video Extender	779.00

**AdderLink X Series X-200 Extenders**

Fully featured USB keyboard, video and mouse extender with 44.1kHz digital stereo audio support for two computers. AdderLink X200s have been designed for use in applications where up to two computers can have their keyboard, video, audio and mouse control extended up to 300m (1000 feet) across Category 5 or higher UTP cable. The AdderLink X200 provides absolute real time keyboard and mouse performance along with hi-definition, hi-resolution video over a VGA interface.

X200-USB-P-US	AdderLink 100m (330 feet) Extender Pair, USB CAM, No Audio, No De-skew	390.00
X200A-USB-P-US	AdderLink 100m (330 feet) Extender Pair, USB CAM, Audio, No De-skew	499.00
X200AS-USB-P-US	AdderLink 300m (1000 feet) Extender Pair, USB CAM, Audio and De-skew	579.00

**AdderLink X Series X-DVI PRO Extenders**

The AdderLink X-DVI PRO allows users to distribute control of any computer which uses DVI video and USB. The X-DVI PRO can deliver perfect 1080p digital video at distances over 50 meters and resolutions up to 165 MPixels per second (e.g. 1920x1200 @ 60Hz or 3840 x 2400 @ 17Hz).

X-DVI PRO-US	DVI and 4-Port USB Over a Single CATx Cable to 50 meters	725.95
X-DVI PRO-MS2-US	Dual Head DVI, Audio and 4-Port USB Over a Single CATx Cable to 50 meters	1495.00

**AdderLink X Series X-USB PRO Extenders**

Adder's next generation USB, video and audio extenders deliver sharp, bright and high resolution video images and high quality audio at distances up to 300m (1000ft) over a single CATx cable.

X-USBPRO-US	VGA, Audio and 4-Port USB Hub (Full Speed) Extender to 300 meters Over a Single CATx Cable	895.00
X-USBPRO-MS2-US	Dual Head VGA, Audio and 4-Port USB Hub (Full Speed) Extender to 300 meters Over Two CATx Cables	1495.00

**Adder Command and Control Switch**

The Adder Command & Control Switch (CCS4USB) is a professional grade control switch delivering USB True Emulation for use with modern or custom USB peripherals and audio with RS232 control. Includes Free Flow Technology - automated mouse switching designed to work with CCS4USB to automatically switch between target computers simply by moving the mouse pointer from screen to screen and can be configured for almost any combinations of screens.

CCS4USB	1x4 USB Keyboard and Mouse Switch with Audio and FreeFlow Mouse Switching	459.00
---------	---	--------



**AdderLink ipeps KVM Over IP**


For Enterprise KVM solutions the AdderLink ipeps (IP Engine per Server) provides a non-blocking global solution by providing each computer with a dedicated KVM-via-IP engine. This can be enhanced by using the ADDER.NET Enterprise Management Software that provides a centralized and secure user access management interface. Where a KVM switch exists without KVM-over-IP functionality, the AdderLink ipeps is ideal for adding global management capabilities. Increasing numbers of computers are being used in remote, stand alone applications such as ATMs and digital signage play out devices. The incredibly small size of the AdderLink ipeps makes it perfect for remote management and control of dispersed computers, meaning that many tasks that would have required an expensive site visit can now be done from anywhere.


AL-IPEPS	AdderLink ipeps KVM over IP	449.00
AL-IPEPS-DA	AdderLink ipeps KVM over IP (with Local Access)	699.00

**AdderLink IP KVM Over IP**

Manage your computers from anywhere in the world with the high-performance AdderLink IP. The AdderLink IP only requires a KVM (keyboard, video, mouse) connection to your computer or KVM switch and doesn't need any custom software to be loaded on your servers. The AdderLink IP is fully compatible with VNC (Virtual Network Computing) and Java based web browsers and doesn't require the purchase of extra software 'seat' licenses. Features video modes up to 1280 x 1024 x 75Hz, video captured at 24 bits per pixel, adaptive color depth to match link speed and security features including AES 128 encryption, RSA 2048 authentication, auto logout after selectable inactive period and IP address restriction. Ships with KVM cable, universal power supply and installation CD. Rack mounting kits sold separately. Covered by a 2-year manufacturer's warranty.

AL-IP	AdderLink IP Stand Alone KVM	895.50
AL-IP-GOLD	AdderLink IP Gold KVM via IP with DVI & USB	1379.00
RMK4S	AdderLink IP KVM Rack Mount Kit	79.00
RMK4D	AdderLink IP KVM Dual Rack Mount Kit	119.00



 To see our entire product offering go to... [L-com.com](http://L-com.com)