



Item #	Description	1-9	10-24	25-99	100-249	250-499			
RG58C/U		<p>50 Ohm Impedance</p>							
RG58C/U									
<ul style="list-style-type: none"> Center Conductor: 20 (19 x 33) AWG tinned copper Shielding: Tinned copper braid (95% coverage) Insulation: Polyethylene Jacket: Black PVC Operating Temperature: -40°C - +85°C 									
							NOMINAL ATTENUATION		
							MHz	db/100ft	db/100m
		50	3.3	10.8					
		100	4.9	16.1					
		200	7.3	23.9					
		400	11.0	36.1					
		1000	20.0	65.6					

✓RoHS RG58C/U - 50 Ohm Coaxial Cables with Inline BNC to Right Angle BNC Plugs

CC58C-1HR	RG58C Cable, BNC Male / 90° Male, 1.0ft (0.3m)	10.45	9.82	9.20	8.57	7.94
CC58C-1.5HR	RG58C Cable, BNC Male / 90° Male, 1.5ft (0.45m)	10.60	9.96	9.33	8.69	8.06
CC58C-2HR	RG58C Cable, BNC Male / 90° Male, 2.0ft (0.6m)	10.75	10.10	9.46	8.82	8.17
CC58C-2.5HR	RG58C Cable, BNC Male / 90° Male, 2.5ft (0.75m)	10.90	10.25	9.59	8.94	8.28
CC58C-3HR	RG58C Cable, BNC Male / 90° Male, 3.0ft (0.9m)	11.05	10.39	9.72	9.06	8.40
CC58C-4HR	RG58C Cable, BNC Male / 90° Male, 4.0ft (1.2m)	11.35	10.67	9.99	9.31	8.63
CC58C-5HR	RG58C Cable, BNC Male / 90° Male, 5.0ft (1.5m)	11.65	10.95	10.25	9.55	8.85
CC58C-7.5HR	RG58C Cable, BNC Male / 90° Male, 7.5ft (2.3m)	12.40	11.66	10.91	10.17	9.42
CC58C-10HR	RG58C Cable, BNC Male / 90° Male, 10.0ft (3.0m)	13.15	12.36	11.57	10.78	9.99

✓RoHS RG58C/U - 50 Ohm Coaxial Cables with Two Right Angle BNC Plugs

CC58C-1HR2	RG58C Cable, BNC 90° Male / 90° Male, 1.0ft (0.3m)	12.50	11.75	11.00	10.25	9.50
CC58C-1.5HR2	RG58C Cable, BNC 90° Male / 90° Male, 1.5ft (0.45m)	12.65	11.89	11.13	10.37	9.61
CC58C-2HR2	RG58C Cable, BNC 90° Male / 90° Male, 2.0ft (0.6m)	12.80	12.03	11.26	10.50	9.73
CC58C-2.5HR2	RG58C Cable, BNC 90° Male / 90° Male, 2.5ft (0.75m)	12.95	12.17	11.40	10.62	9.84
CC58C-3HR2	RG58C Cable, BNC 90° Male / 90° Male, 3.0ft (0.9m)	13.10	12.31	11.53	10.74	9.96
CC58C-4HR2	RG58C Cable, BNC 90° Male / 90° Male, 4.0ft (1.2m)	13.40	12.60	11.79	10.99	10.18
CC58C-4HR2	RG58C Cable, BNC 90° Male / 90° Male, 5.0ft (1.5m)	13.70	12.88	12.06	11.23	10.41
CC58C-7.5HR2	RG58C Cable, BNC 90° Male / 90° Male, 7.5ft (2.3m)	14.45	13.58	12.72	11.85	10.98
CC58C-10HR2	RG58C Cable, BNC 90° Male / 90° Male, 10.0ft (3.0m)	15.20	14.29	13.38	12.46	11.55
CC58C-15HR2	RG58C Cable, BNC 90° Male / 90° Male, 15.0ft (4.6m)	16.70	15.70	14.70	13.69	12.69
CC58C-20HR2	RG58C Cable, BNC 90° Male / 90° Male, 20.0ft (6.1m)	18.20	17.11	16.02	14.92	13.83

✓RoHS RG58C/U - 50 Ohm Coaxial Cables with Two Inline SMA Plugs

CCS58A-05	RG58C Cable, SMA Male / Male, 0.5ft (0.15m)	14.55	13.68	12.80	11.93	11.06
CCS58A-1	RG58C Cable, SMA Male / Male, 1.0ft (0.3m)	14.70	13.82	12.94	12.05	11.17
CCS58A-1.5	RG58C Cable, SMA Male / Male, 1.5ft (0.45m)	14.85	13.96	13.07	12.18	11.29
CCS58A-2	RG58C Cable, SMA Male / Male, 2.0ft (0.6m)	15.00	14.10	13.20	12.30	11.40
CCS58A-2.5	RG58C Cable, SMA Male / Male, 2.5ft (0.75m)	15.15	14.24	13.33	12.42	11.51
CCS58A-3	RG58C Cable, SMA Male / Male, 3.0ft (0.9m)	15.30	14.38	13.46	12.55	11.63
CCS58A-4	RG58C Cable, SMA Male / Male, 4.0ft (1.2m)	16.00	15.04	14.08	13.12	12.16
CCS58A-5	RG58C Cable, SMA Male / Male, 5.0ft (1.5m)	16.30	15.32	14.34	13.37	12.39
CCS58A-7.5	RG58C Cable, SMA Male / Male, 7.5ft (2.3m)	16.67	15.67	14.67	13.67	12.67
CCS58A-10	RG58C Cable, SMA Male / Male, 10.0ft (3.0m)	17.80	16.73	15.66	14.60	13.53

✓RoHS RG58C/U - 50 Ohm Coaxial Cables with Inline SMA to Inline BNC Plugs

CCS58AB-05	RG58C Cable, SMA Male / BNC Male, 0.5ft (0.15m)	12.25	11.51	10.78	10.04	9.31
CCS58AB-1	RG58C Cable, SMA Male / BNC Male, 1.0ft (0.3m)	12.40	11.66	10.91	10.17	9.42
CCS58AB-1.5	RG58C Cable, SMA Male / BNC Male, 1.5ft (0.45m)	12.55	11.80	11.04	10.29	9.54
CCS58AB-2.5	RG58C Cable, SMA Male / BNC Male, 2.5ft (0.75m)	12.85	12.08	11.31	10.54	9.77
CCS58AB-5	RG58C Cable, SMA Male / BNC Male, 5.0ft (1.5m)	13.60	12.78	11.97	11.15	10.34
CCS58AB-7.5	RG58C Cable, SMA Male / BNC Male, 7.5ft (2.3m)	14.35	13.49	12.63	11.77	10.91
CCS58AB-10	RG58C Cable, SMA Male / BNC Male, 10.0ft (3.0m)	15.10	14.19	13.29	12.38	11.48

✓RoHS RG58C/U - 50 Ohm Coaxial Cables with Inline SMA to Right Angle SMA Plugs

CCS58A-05HR	RG58C Cable, SMA Male / 90° Male, 0.5ft (0.15m)	14.60	13.72	12.85	11.97	11.10
CCS58A-1HR	RG58C Cable, SMA Male / 90° Male, 1.0ft (0.3m)	14.75	13.86	12.98	12.10	11.21
CCS58A-1.5HR	RG58C Cable, SMA Male / 90° Male, 1.5ft (0.45m)	14.90	14.01	13.11	12.22	11.32
CCS58A-2HR	RG58C Cable, SMA Male / 90° Male, 2.0ft (0.6m)	15.05	14.15	13.24	12.34	11.44
CCS58A-2.5HR	RG58C Cable, SMA Male / 90° Male, 2.5ft (0.75m)	15.20	14.29	13.38	12.46	11.55
CCS58A-3HR	RG58C Cable, SMA Male / 90° Male, 3.0ft (0.9m)	15.35	14.43	13.51	12.59	11.67
CCS58A-4HR	RG58C Cable, SMA Male / 90° Male, 4.0ft (1.2m)	15.65	14.71	13.77	12.83	11.89
CCS58A-5HR	RG58C Cable, SMA Male / 90° Male, 5.0ft (1.5m)	15.95	14.99	14.04	13.08	12.12
CCS58A-7.5HR	RG58C Cable, SMA Male / 90° Male, 7.5ft (2.3m)	16.70	15.70	14.70	13.69	12.69
CCS58A-10HR	RG58C Cable, SMA Male / 90° Male, 10.0ft (3.0m)	17.45	16.40	15.36	14.31	13.26

✓RoHS RG58C/U - 50 Ohm Coaxial Cables with Two Right Angle SMA Plugs

CCS58A-05HR2	RG58C Cable, SMA 90° Male / 90° Male, 0.5ft (0.15m)	17.70	16.64	15.58	14.51	13.45
CCS58A-1HR2	RG58C Cable, SMA 90° Male / 90° Male, 1.0ft (0.3m)	17.85	16.78	15.71	14.64	13.57
CCS58A-1.5HR2	RG58C Cable, SMA 90° Male / 90° Male, 1.5ft (0.45m)	18.00	16.92	15.84	14.76	13.68
CCS58A-2.5HR2	RG58C Cable, SMA 90° Male / 90° Male, 2.5ft (0.75m)	18.15	17.06	15.97	14.88	13.79
CCS58A-5HR2	RG58C Cable, SMA 90° Male / 90° Male, 5.0ft (1.5m)	19.05	17.91	16.76	15.62	14.48
CCS58A-10HR2	RG58C Cable, SMA 90° Male / 90° Male, 10.0ft (3.0m)	20.55	19.32	18.08	16.85	15.62

✓RoHS RG58C/U - 50 Ohm Extension Cables with Inline SMA Plug to SMA Jack

CCS58AX-1	RG58C Cable, SMA Male / Female, 1.0ft (0.3m)	16.55	15.56	14.56	13.57	12.58
CCS58AX-2.5	RG58C Cable, SMA Male / Female, 2.5ft (0.75m)	17.00	15.98	14.96	13.94	12.92
CCS58AX-5	RG58C Cable, SMA Male / Female, 5.0ft (1.5m)	17.75	16.68	15.62	14.56	13.49

✓RoHS RG58C/U - 50 Ohm Coaxial Cables with Two Inline TNC Plugs

CC58T-1	RG58C Cable, TNC Male / Male, 1.0ft (0.3m)	9.60	9.02	8.45	7.87	7.30
CC58T-3	RG58C Cable, TNC Male / Male, 3.0ft (0.9m)	10.20	9.59	8.98	8.36	7.75
CC58T-6	RG58C Cable, TNC Male / Male, 6.0ft (1.8m)	11.10	10.43	9.77	9.10	8.44
CC58T-10	RG58C Cable, TNC Male / Male, 10.0ft (3.0m)	12.30	11.56	10.82	10.09	9.35
CC58T-15	RG58C Cable, TNC Male / Male, 15.0ft (4.6m)	13.80	12.97	12.14	11.32	10.49
CC58T-25	RG58C Cable, TNC Male / Male, 25.0ft (7.6m)	16.80	15.79	14.78	13.78	12.77
CC58T-50	RG58C Cable, TNC Male / Male, 50.0ft (15.2m)	24.30	22.84	21.38	19.93	18.47