


Item #	Description	1-9	10-24	25-99	100-249	250-499
<b>RoHS 100-Series 50 Ohm Coaxial Pigtails</b>						
CA-SBSPBPRCN36	100-Series Pigtails, SMB Plug Right Angle / SMB Plug Right Angle, 36" (91.4cm)	16.50	15.18	13.86	12.54	11.22
CA-SBSPBPRCN48	100-Series Pigtails, SMB Plug Right Angle / SMB Plug Right Angle, 48" (121.9cm)	17.50	16.10	14.70	13.30	11.90
CA-SBSPBPRCN12	100-Series Pigtails, SMB Plug / SMB Plug Right Angle, 12" (30.5cm)	14.50	13.34	12.18	11.02	9.86
CA-SBSPBPRCN18	100-Series Pigtails, SMB Plug / SMB Plug Right Angle, 18" (45.7cm)	15.00	13.80	12.60	11.40	10.20
CA-SBSPBPRCN24	100-Series Pigtails, SMB Plug / SMB Plug Right Angle, 24" (61cm)	15.50	14.26	13.02	11.78	10.54
CA-SBSPBPRCN30	100-Series Pigtails, SMB Plug / SMB Plug Right Angle, 30" (76.2cm)	16.00	14.72	13.44	12.16	10.88
CA-SBSPBPRCN36	100-Series Pigtails, SMB Plug / SMB Plug Right Angle, 36" (91.4cm)	16.50	15.18	13.86	12.54	11.22
CA-SBSPBPRCN48	100-Series Pigtails, SMB Plug / SMB Plug Right Angle, 48" (121.9cm)	17.50	16.10	14.70	13.30	11.90
CA-SEPNCMN19	100-Series Pigtails, S/E Type 237 Plug / Type N Male, 19" (48.3cm)	14.99	13.49	11.99	10.49	8.99
CA-SEPRJCN19	100-Series Pigtails, S/E Type 237 Plug / Reverse Polarity SMA Jack, 19" (48.3cm)	14.99	13.49	11.99	10.49	8.99
CA-SEPSFCN19	100-Series Pigtails, S/E Type 237 Plug / SMA Female, 19" (48.3cm)	14.99	13.49	11.99	10.49	8.99
CA-SNPNCMN19	100-Series Pigtails, SMA Nano Plug / Type N Male, 19" (48.3cm)	14.99	13.49	11.99	10.49	CALL
CA-SNPTFCN19	100-Series Pigtails, SMA Nano Plug / TNC Female, 19" (48.3cm)	14.99	13.49	11.99	10.49	CALL
CA-SNPFCN19	100-Series Pigtails, SMA Nano Plug / SMA Female, 19" (48.3cm)	14.99	13.49	11.99	10.49	CALL

**RoHS 195-Series 50 Ohm Coaxial Pigtails**

195 Series	195R Series Low-Loss Cable	NOMINAL ATTENUATION		
		MHz	db/100ft	db/100m
	• Center Conductor: Solid bare copper	900	11.1	36.5
	• Shielding: Foil + tinned copper braid (90% coverage)	1800	16.0	52.5
	• Insulation: Physical foam polyethylene (PTFE for Plenum Rated)	2500	19.0	62.4
	• Jacket: Polyvinyl Chloride (CMP Grade for Plenum Rated)	5800	29.9	98.1
	• Operating Temperature: -20°C - +60°C			

CA-AM1RSPA002	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Rev. Polarity SMA Plug, 2.0ft (0.6m)	21.95	19.75	17.56	15.36	13.17
CA-AM1RSPA004	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Rev. Polarity SMA Plug, 4.0ft (1.2m)	22.90	20.61	18.32	16.03	13.74
CA-AM1RSPA010	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Rev. Polarity SMA Plug, 10.0ft (3.0m)	25.80	23.22	20.64	18.06	15.48
CA-AM1RSPA020	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Rev. Polarity SMA Plug, 20.0ft	30.60	27.54	24.48	21.42	18.36
CA-AM1RTPA002	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Rev. Polarity TNC Plug, 2.0ft (0.6m)	21.95	19.75	17.56	15.36	13.17
CA-AM1RTPA004	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Rev. Polarity TNC Plug, 4.0ft (1.2m)	22.90	20.61	18.32	16.03	13.74
CA-AM1RTPA010	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Rev. Polarity TNC Plug, 10.0ft (3.0m)	25.80	23.22	20.64	18.06	15.48
CA-AM1RTPA020	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Rev. Polarity TNC Plug, 20.0ft (6.1m)	30.60	27.54	24.48	21.42	18.36
CA-AM1NMA002	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Type N Male, 2.0ft (0.6m)	22.55	20.30	18.04	15.79	13.53
CA-AM1NMA004	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Type N Male, 4.0ft (1.2m)	23.50	21.15	18.80	16.45	14.10
CA-AM1NMA010	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Type N Male, 10.0ft (3.0m)	26.40	23.76	21.12	18.48	15.84
CA-AM1NMA020	195-Series Pigtails, 3/4" (1.9cm) NMO Mount / Type N Male, 20.0ft (6.1m)	31.20	28.08	24.96	21.84	18.72
CA-AMNMA002	195-Series Pigtails, AlProx Male / Type N Male, 2.0ft (0.6m)	21.00	19.32	17.64	15.96	14.28
CA-AMNMA004	195-Series Pigtails, AlProx Male / Type N Male, 4.0ft (1.2m)	21.50	19.78	18.06	16.34	14.62
CA-AMNMA010	195-Series Pigtails, AlProx Male / Type N Male, 10.0ft (3.0m)	24.50	22.54	20.58	18.62	16.66
CA-AMNMA020	195-Series Pigtails, AlProx Male / Type N Male, 20.0ft (6.1m)	29.50	27.14	24.78	22.42	20.06
CA-BMRBMA002	195-Series Pigtails, BNC Male Right Angle / BNC Male, 2.0ft (0.6m)	24.00	21.60	19.20	16.80	14.40
CA-BMRBMA004	195-Series Pigtails, BNC Male Right Angle / BNC Male, 4.0ft (1.2m)	25.20	22.68	20.16	17.64	15.12
CA-BMRBMA010	195-Series Pigtails, BNC Male Right Angle / BNC Male, 10.0ft (3.0m)	28.80	25.92	23.04	20.16	17.28
CA-BMRBMA020	195-Series Pigtails, BNC Male Right Angle / BNC Male, 20.0ft (6.1m)	34.80	31.32	27.84	24.36	20.88
CA-BMRBMA002	195-Series Pigtails, BNC Male Right Angle / BNC Male Right Angle, 2.0ft (0.6m)	26.40	23.76	21.12	18.48	15.84
CA-BMRBMA004	195-Series Pigtails, BNC Male Right Angle / BNC Male Right Angle, 4.0ft (1.2m)	27.60	24.84	22.08	19.32	16.56
CA-BMRBMA010	195-Series Pigtails, BNC Male Right Angle / BNC Male Right Angle, 10.0ft (3.0m)	31.20	28.08	24.96	21.84	18.72
CA-BMRBMA020	195-Series Pigtails, BNC Male Right Angle / BNC Male Right Angle, 20.0ft (6.1m)	37.20	33.48	29.76	26.04	22.32
CA-FMNMA002	195-Series Pigtails, Type F Male / Type N Male, 2.0ft (0.6m)	16.95	15.25	13.56	11.86	10.17
CA-FMNMA004	195-Series Pigtails, Type F Male / Type N Male, 4.0ft (1.2m)	17.80	16.02	14.24	12.46	10.68
CA-FMNMA010	195-Series Pigtails, Type F Male / Type N Male, 10.0ft (3.0m)	21.70	19.53	17.36	15.19	13.02
CA-FMNMA020	195-Series Pigtails, Type F Male / Type N Male, 20.0ft (6.1m)	29.30	26.37	23.44	20.51	17.58
CA-NMNNMA002	195-Series Pigtails, Type N Male / Type N Male, 2.0ft (0.6m)	14.70	13.23	11.76	10.29	8.82
CA-NMNNMA004	195-Series Pigtails, Type N Male / Type N Male, 4.0ft (1.2m)	15.70	14.13	12.56	10.99	9.42
CA-NMNNMA010	195-Series Pigtails, Type N Male / Type N Male, 10.0ft (3.0m)	18.70	16.83	14.96	13.09	11.22
CA-NMNNMA020	195-Series Pigtails, Type N Male / Type N Male, 20.0ft (6.1m)	23.70	21.33	18.96	16.59	14.22
CA-NMNRMA002	195-Series Pigtails, Type N Male Right Angle / Type N Male, 2.0ft (0.6m)	30.00	27.00	24.00	21.00	18.00
CA-NMNRMA004	195-Series Pigtails, Type N Male Right Angle / Type N Male, 4.0ft (1.2m)	31.00	27.90	24.80	21.70	18.60
CA-NMNRMA010	195-Series Pigtails, Type N Male Right Angle / Type N Male, 10.0ft (3.0m)	34.00	30.60	27.20	23.80	CALL
CA-NMNRMA020	195-Series Pigtails, Type N Male Right Angle / Type N Male, 20.0ft (6.1m)	39.00	35.10	31.20	27.30	CALL
CA-NMNFMA002	195-Series Pigtails, Type N Male / Type N Female, 2.0ft (0.6m)	14.70	13.23	11.76	10.29	8.82
CA-NMNFMA004	195-Series Pigtails, Type N Male / Type N Female, 4.0ft (1.2m)	15.70	14.13	12.56	10.99	9.42
CA-NMNFMA010	195-Series Pigtails, Type N Male / Type N Female, 10.0ft (3.0m)	18.70	16.83	14.96	13.09	11.22
CA-NMNFMA020	195-Series Pigtails, Type N Male / Type N Female, 20.0ft (6.1m)	23.70	21.33	18.96	16.59	14.22
CA-NMRRSPA002	195-Series Pigtails, Type N Male Right Angle / Rev. Polarity SMA Plug, 2.0ft (0.6m)	27.70	24.93	22.16	19.39	16.62
CA-NMRRSPA004	195-Series Pigtails, Type N Male Right Angle / Rev. Polarity SMA Plug, 4.0ft (1.2m)	28.95	26.05	23.16	20.26	17.37
CA-NMRRSPA010	195-Series Pigtails, Type N Male Right Angle / Rev. Polarity SMA Plug, 10.0ft (3.0m)	32.70	29.43	26.16	22.89	19.62
CA-NMRRSPA020	195-Series Pigtails, Type N Male Right Angle / Rev. Polarity SMA Plug, 20.0ft (6.1m)	38.95	35.06	31.16	27.27	23.37
CA-NMRRSJA002	195-Series Pigtails, Type N Male Right Angle / Rev. Polarity SMA Jack, 2.0ft (0.6m)	24.95	22.45	19.96	17.46	14.97
CA-NMRRSJA004	195-Series Pigtails, Type N Male Right Angle / Rev. Polarity SMA Jack, 4.0ft (1.2m)	26.15	23.54	20.92	18.30	15.69
CA-NMRRSJA010	195-Series Pigtails, Type N Male Right Angle / Rev. Polarity SMA Jack, 10.0ft (3.0m)	29.75	26.78	23.80	20.82	17.85
CA-NMRRSJA020	195-Series Pigtails, Type N Male Right Angle / Rev. Polarity SMA Jack, 20.0ft (6.1m)	35.75	32.18	28.60	25.02	21.45
CA-NMRSMA002	195-Series Pigtails, Type N Male Right Angle / SMA Male, 2.0ft (0.6m)	24.95	22.45	19.96	17.46	14.97
CA-NMRSMA004	195-Series Pigtails, Type N Male Right Angle / SMA Male, 4.0ft (1.2m)	26.15	23.54	20.92	18.30	15.69
CA-NMRSMA010	195-Series Pigtails, Type N Male Right Angle / SMA Male, 10.0ft (3.0m)	29.75	26.78	23.80	20.82	17.85
CA-NMRSMA020	195-Series Pigtails, Type N Male Right Angle / SMA Male, 20.0ft (6.1m)	35.75	32.18	28.60	25.02	21.45
CA-NMRTMA002	195-Series Pigtails, Type N Male Right Angle / TNC Male, 2.0ft (0.6m)	24.95	22.45	19.96	17.46	14.97
CA-NMRTMA004	195-Series Pigtails, Type N Male Right Angle / TNC Male, 4.0ft (1.2m)	26.15	23.54	20.92	18.30	15.69
CA-NMRTMA010	195-Series Pigtails, Type N Male Right Angle / TNC Male, 10.0ft (3.0m)	29.75	26.78	23.80	20.82	17.85
CA-NMRTMA020	195-Series Pigtails, Type N Male Right Angle / TNC Male, 20.0ft (6.1m)	35.75	32.18	28.60	25.02	21.45



**We want to help you!**

See a complete list of free tips, tutorials and videos at [L-com.com/Resources](http://L-com.com/Resources)