


Item #	Description	1-9	10-24	25-99	100-249	250-499
 CA-RSPRNPAA010	195-Series Pigtaills, Rev. Polarity SMA Plug / Rev. Polarity Type N Plug, 10.0ft (3.0m)	29.80	26.82	23.84	20.86	17.88
CA-RSPRNPAA020	195-Series Pigtaills, Rev. Polarity SMA Plug / Rev. Polarity Type N Plug, 20.0ft (6.1m)	36.80	33.12	29.44	25.76	22.08
CA-RSJRTPB002	195-Series White Pigtaills, Rev. Pol. SMA Jack / Rev. Polarity TNC Plug, 2.0ft (0.6m)	22.80	20.52	18.24	15.96	13.68
CA-RSJRTPB004	195-Series White Pigtaills, Rev. Pol. SMA Jack / Rev. Polarity TNC Plug, 4.0ft (1.2m)	24.00	21.60	19.20	16.80	14.40
CA-RSJRTPB010	195-Series White Pigtaills, Rev. Polarity SMA Jack / Rev. Pol. TNC Plug, 10.0ft (3.0m)	27.60	24.84	22.08	19.32	16.56
CA-RSJRTPB020	195-Series White Pigtaills, Rev. Polarity SMA Jack / Rev. Pol. TNC Plug, 20.0ft (6.1m)	33.60	30.24	26.88	23.52	20.16
CA-RSJRTPA002	195-Series Pigtaills, Rev. Polarity SMA Jack / Rev. Polarity TNC Plug, 2.0ft (0.6m)	22.20	19.98	17.76	15.54	13.32
CA-RSJRTPA004	195-Series Pigtaills, Rev. Polarity SMA Jack / Rev. Polarity TNC Plug, 4.0ft (1.2m)	23.40	21.06	18.72	16.38	14.04
CA-RSJRTPA010	195-Series Pigtaills, Rev. Polarity SMA Jack / Rev. Polarity TNC Plug, 10.0ft (3.0m)	27.00	24.30	21.60	18.90	16.20
CA-RSJRTPA020	195-Series Pigtaills, Rev. Polarity SMA Jack / Rev. Polarity TNC Plug, 20.0ft (6.1m)	33.00	29.70	26.40	23.10	19.80
CA-RTPNMA001	195-Series White Pigtaills, Reverse Polarity TNC Plug / Type N Male, 1.0ft	9.99	8.99	7.99	6.99	CALL
CA-RTPNMA002	195-Series Pigtaills, Reverse Polarity TNC Plug / Type N Male, 2.0ft (0.6m)	9.99	8.99	7.99	6.99	5.99
CA-RTPNMA004	195-Series Pigtaills, Reverse Polarity TNC Plug / Type N Male, 4.0ft (1.2m)	12.99	11.69	10.39	9.09	7.79
CA-RTPNMA010	195-Series Pigtaills, Reverse Polarity TNC Plug / Type N Male, 10.0ft (3.0m)	14.99	13.49	11.99	10.49	8.99
CA-RTPNMA020	195-Series Pigtaills, Reverse Polarity TNC Plug / Type N Male, 20.0ft (6.1m)	17.99	16.19	14.39	12.59	10.79
CA-RTPRNMA002	195-Series Pigtaills, Rev. Pol. TNC Plug Rt. Angle / Type N Male Rt. Angle, 2.0ft (0.6m)	14.99	13.79	12.59	11.39	10.19
CA-RTPRNMA004	195-Series Pigtaills, Rev. Polarity TNC Plug Right Angle / Type N Male, 2.0ft (0.6m)	14.99	13.79	12.59	11.39	10.19
CA-RTPRNMA010	195-Series Pigtaills, Rev. Polarity TNC Plug Right Angle / Type N Male, 4.0ft (1.2m)	22.00	19.80	17.60	15.40	13.20
CA-RTPRNMA020	195-Series Pigtaills, Rev. Polarity TNC Plug Right Angle / Type N Male, 10.0ft (3.0m)	25.00	22.50	20.00	17.50	15.00
CA-RTPNFA002	195-Series Pigtaills, Reverse Polarity TNC Plug / Type N Female, 2.0ft (0.6m)	15.00	13.50	12.00	10.50	9.00
CA-RTPNFA004	195-Series Pigtaills, Reverse Polarity TNC Plug / Type N Female, 4.0ft (1.2m)	16.00	14.40	12.80	11.20	9.60
CA-RTPNFA010	195-Series Pigtaills, Reverse Polarity TNC Plug / Type N Female, 10.0ft (3.0m)	19.00	18.24	17.48	16.15	14.25
CA-RTPNFA020	195-Series Pigtaills, Reverse Polarity TNC Plug / Type N Female, 20.0ft (6.1m)	24.00	21.60	19.20	16.80	14.40
CA-RTPNFBA002	195-Series Pigtaills, Rev. Polarity TNC Plug / Type N Female Bulkhead, 2.0ft (0.6m)	19.00	17.10	15.20	13.30	11.40
CA-RTPNFBA004	195-Series Pigtaills, Rev. Polarity TNC Plug / Type N Female Bulkhead, 4.0ft (1.2m)	20.00	18.00	16.00	14.00	12.00
CA-RTPNFBA010	195-Series Pigtaills, Rev. Polarity TNC Plug / Type N Female Bulkhead, 10.0ft (3.0m)	23.00	20.70	18.40	16.10	13.80
CA-RTPNFBA020	195-Series Pigtaills, Rev. Polarity TNC Plug / Type N Female Bulkhead, 20.0ft (6.1m)	28.00	25.20	22.40	19.60	16.80
CA-RTPRTJA002	195-Series Pigtaills, Reverse Polarity TNC Plug / Rev. Polarity TNC Jack, 2.0ft (0.6m)	13.00	11.70	10.40	9.10	7.80
CA-RTPRTJA004	195-Series Pigtaills, Reverse Polarity TNC Plug / Rev. Polarity TNC Jack, 4.0ft (1.2m)	22.00	19.80	17.60	15.40	13.20
CA-RTPRTJA010	195-Series Pigtaills, Rev. Polarity TNC Plug / Rev. Polarity TNC Jack, 10.0ft (3.0m)	17.00	15.30	13.60	11.90	10.20
CA-RTPRTJA020	195-Series Pigtaills, Reverse Polarity TNC Plug / Reverse Polarity TNC Jack, 20.0ft	22.00	19.80	17.60	15.40	13.20
CA-RTPRTPA002	195-Series Pigtaills, Reverse Polarity TNC Plug / Rev. Polarity TNC Plug, 2.0ft (0.6m)	9.99	8.99	7.99	6.99	5.99
CA-RTPRTPA004	195-Series Pigtaills, Reverse Polarity TNC Plug / Rev. Polarity TNC Plug, 4.0ft (1.2m)	12.99	11.69	10.39	9.09	7.79
CA-RTPRTPA010	195-Series Pigtaills, Rev. Polarity TNC Plug / Rev. Polarity TNC Plug, 10.0ft (3.0m)	14.99	13.49	11.99	10.49	8.99
CA-RTPRTPA020	195-Series Pigtaills, Rev. Polarity TNC Plug / Rev. Polarity TNC Plug, 20.0ft (6.1m)	17.99	16.19	14.39	12.59	10.79
CA-SMNMA002	195-Series Pigtaills, SMA Male / Type N Male, 2.0ft (0.6m)	15.00	13.50	12.00	10.50	9.00
CA-SMNMA004	195-Series Pigtaills, SMA Male / Type N Male, 4.0ft (1.2m)	16.00	14.40	12.80	11.20	9.60
CA-SMNMA010	195-Series Pigtaills, SMA Male / Type N Male, 10.0ft (3.0m)	19.00	17.10	15.20	13.30	11.40
CA-SMNMA020	195-Series Pigtaills, SMA Male / Type N Male, 20.0ft (6.1m)	24.00	21.60	19.20	16.80	14.40
CA-SMRNMA002	195-Series Pigtaills, SMA Male Right Angle / Type N Male, 2.0ft (0.6m)	17.99	16.19	14.39	12.59	10.79
CA-SMRNMA004	195-Series Pigtaills, SMA Male Right Angle / Type N Male, 4.0ft (1.2m)	19.70	17.73	15.76	13.79	11.82
CA-SMRNMA010	195-Series Pigtaills, SMA Male Right Angle / Type N Male, 10.0ft (3.0m)	24.80	22.32	19.84	17.36	14.88
CA-SMRNMA020	195-Series Pigtaills, SMA Male Right Angle / Type N Male, 20.0ft (6.1m)	33.30	29.97	26.64	23.31	19.98
CA-SMRNFBA002	195-Series Pigtaills, SMA Male Right Angle / Type N Female Bulkhead, 2.0ft (0.6m)	21.99	19.79	17.59	15.39	13.19
CA-SMRNFBA004	195-Series Pigtaills, SMA Male Right Angle / Type N Female Bulkhead, 4.0ft (1.2m)	23.99	21.59	19.19	16.79	14.39
CA-SMRNFBA010	195-Series Pigtaills, SMA Male Right Angle / Type N Female Bulkhead, 10.0ft (3.0m)	29.99	26.99	23.99	20.99	17.99
CA-SMRNFBA020	195-Series Pigtaills, SMA Male Right Angle / Type N Female Bulkhead, 20.0ft (6.1m)	39.99	35.99	31.99	27.99	23.99
CA-SMRNFA002	195-Series Pigtaills, SMA Male Right Angle / Type N Female, 2.0ft (0.6m)	17.99	16.19	14.39	12.59	10.79
CA-SMRNFA004	195-Series Pigtaills, SMA Male Right Angle / Type N Female, 4.0ft (1.2m)	25.60	23.04	20.48	17.92	15.36
CA-SMRNFA010	195-Series Pigtaills, SMA Male Right Angle / Type N Female, 10.0ft (3.0m)	29.20	26.86	24.53	22.19	19.86
CA-SMRNFA020	195-Series Pigtaills, SMA Male Right Angle / Type N Female, 20.0ft (6.1m)	35.20	32.38	29.57	26.75	23.94
CA-SMNFBA002	195-Series Pigtaills, SMA Male / Type N Female Bulkhead, 2.0ft (0.6m)	21.99	19.79	17.59	15.39	13.19
CA-SMNFBA004	195-Series Pigtaills, SMA Male / Type N Female Bulkhead, 4.0ft (1.2m)	26.80	24.12	21.44	18.76	16.08
CA-SMNFBA010	195-Series Pigtaills, SMA Male / Type N Female Bulkhead, 10.0ft (3.0m)	30.40	27.36	24.32	21.28	18.24
CA-SMNFBA020	195-Series Pigtaills, SMA Male / Type N Female Bulkhead, 20.0ft (6.1m)	36.40	32.76	29.12	25.48	21.84
CA-SMNFPA002	195-Series Pigtaills, SMA Male / Type N Female, 2.0ft (0.6m)	14.99	13.49	11.99	10.49	8.99
CA-SMNFPA004	195-Series Pigtaills, SMA Male / Type N Female, 4.0ft (1.2m)	15.99	14.39	12.79	11.19	9.59
CA-SMNFPA010	195-Series Pigtaills, SMA Male / Type N Female, 10.0ft (3.0m)	18.99	17.09	15.19	13.29	11.39
CA-SMNFPA020	195-Series Pigtaills, SMA Male / Type N Female, 20.0ft (6.1m)	23.99	21.59	19.19	16.79	14.39
CA-SSMNMA006	195-Series Pigtaills, Shrouded SMA Male / Type N Male, 6.0" (15 cm)	10.49	9.44	8.39	7.34	CALL
CA-SSMNMA002	195-Series Pigtaills, Shrouded SMA Male / Type N Male, 2.0ft (0.6m)	15.99	14.71	13.43	12.15	10.87
CA-SSMNFA006	195-Series Pigtaills, Shrouded SMA Male / Type N Female, 6.0" (15 cm)	10.49	9.44	8.39	7.34	CALL
CA-TMNMMA002	195-Series Pigtaills, TNC Male / Type N Male, 2.0ft (0.6m)	14.99	13.49	11.99	10.49	8.99
CA-TMNMMA004	195-Series Pigtaills, TNC Male / Type N Male, 4.0ft (1.2m)	15.99	14.39	12.79	11.19	9.59
CA-TMNMMA010	195-Series Pigtaills, TNC Male / Type N Male, 10.0ft (3.0m)	18.99	17.09	15.19	13.29	11.39
CA-TMNMMA020	195-Series Pigtaills, TNC Male / Type N Male, 20.0ft (6.1m)	23.99	21.59	19.19	16.79	14.39
CA-TMNFPA002	195-Series Pigtaills, TNC Male / Type N Female, 2.0ft (0.6m)	16.99	15.29	13.59	11.89	10.19
CA-TMNFPA004	195-Series Pigtaills, TNC Male / Type N Female, 4.0ft (1.2m)	17.80	16.02	14.24	12.46	10.68
CA-TMNFPA010	195-Series Pigtaills, TNC Male / Type N Female, 10.0ft (3.0m)	21.99	19.79	17.59	15.39	13.19
CA-TMNFPA020	195-Series Pigtaills, TNC Male / Type N Female, 20.0ft (6.1m)	29.99	26.99	23.99	20.99	17.99
CA-WMNMMA002	195-Series Pigtaills, WaveRider Male / Type N Male, 2.0ft (0.6m)	16.99	15.63	14.27	12.91	11.55
CA-WMNMMA004	195-Series Pigtaills, WaveRider Male / Type N Male, 4.0ft (1.2m)	17.89	16.46	15.03	13.60	12.17
CA-WMNMMA005	195-Series Pigtaills, WaveRider Male / Type N Male, 5.0ft (1.5m)	18.24	16.78	15.32	13.86	12.40
CA-WMNMMA010	195-Series Pigtaills, WaveRider Male / Type N Male, 10.0ft (3.0m)	20.59	18.94	17.30	15.65	14.00
CA-WMNMMA020	195-Series Pigtaills, WaveRider Male / Type N Male, 20.0ft (6.1m)	26.99	27.59	25.19	22.79	20.39
CA-WMNFPA002	195-Series Pigtaills, WaveRider Male / Type N Female, 2.0ft (0.6m)	19.99	15.63	14.27	12.91	11.55
CA-WMNFPA004	195-Series Pigtaills, WaveRider Male / Type N Female, 4.0ft (1.2m)	17.89	16.46	15.03	13.60	12.17
CA-WMNFPA010	195-Series Pigtaills, WaveRider Male / Type N Female, 10.0ft (3.0m)	20.59	18.94	17.30	15.65	14.00
CA-WMNFPA020	195-Series Pigtaills, WaveRider Male / Type N Female, 20.0ft (6.1m)	29.99	27.59	25.19	22.79	20.39



To see our entire product offering go to... L-com.com

