

**LOW-LOSS CABLES**

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

**RoHS 200-Series 50 Ohm Coaxial Pigtails**

200 Series	50 Ohm Impedance	200 Series Low-Loss Cable	NOMINAL ATTENUATION			
			MHz	db/100ft	db/100m	
CA-NMNM002	200-Series Cable, Type N Male / Type N Male, 2.0ft (0.6m)	25.00	22.50	20.00	17.50	15.00
CA-NMNM004	200-Series Cable, Type N Male / Type N Male, 4.0ft (1.2m)	26.00	23.40	20.80	18.20	15.60
CA-NMNM010	200-Series Cable, Type N Male / Type N Male, 10.0ft (3.0m)	29.00	26.10	23.20	20.30	17.40
CA-NMNM020	200-Series Cable, Type N Male / Type N Male, 20.0ft (6.1m)	34.00	30.60	27.20	23.80	20.40
CA-NMNM050	200-Series Cable, Type N Male / Type N Male, 50.0ft (15.2m)	48.00	43.20	38.40	33.60	28.80
CA-NMNF002	200-Series Cable, Type N Male / Type N Female, 2.0ft (0.6m)	25.00	22.50	20.00	17.50	15.00
CA-NMNF004	200-Series Cable, Type N Male / Type N Female, 4.0ft (1.2m)	26.00	23.40	20.80	18.20	15.60
CA-NMNF010	200-Series Cable, Type N Male / Type N Female, 10.0ft (3.0m)	29.00	26.10	23.20	20.30	17.40
CA-NMNF020	200-Series Cable, Type N Male / Type N Female, 20.0ft (6.1m)	34.00	30.60	27.20	23.80	20.40
CA-RSPNME002	200-Series Cable, Reverse Polarity SMA Plug / Type N Male, 2.0ft (0.6m)	25.00	22.50	20.00	17.50	15.00
CA-RSPNME004	200-Series Cable, Reverse Polarity SMA Plug / Type N Male, 4.0ft (1.2m)	26.00	23.40	20.80	18.20	15.60
CA-RSPNME010	200-Series Cable, Reverse Polarity SMA Plug / Type N Male, 10.0ft (3.0m)	29.00	26.10	23.20	20.30	17.40
CA-RSPNME020	200-Series Cable, Reverse Polarity SMA Plug / Type N Male, 20.0ft (6.1m)	34.00	30.60	27.20	23.80	20.40
CA-RTPNME002	200-Series Cable, Reverse Polarity TNC Plug / Type N Male, 2.0ft (0.6m)	25.00	22.50	20.00	17.50	15.00
CA-RTPNME004	200-Series Cable, Reverse Polarity TNC Plug / Type N Male, 4.0ft (1.2m)	26.00	23.40	20.80	18.20	15.60
CA-RTPNME010	200-Series Cable, Reverse Polarity TNC Plug / Type N Male, 10.0ft (3.0m)	29.00	26.10	23.20	20.30	17.40
CA-RTPNME020	200-Series Cable, Reverse Polarity TNC Plug / Type N Male, 20.0ft (6.1m)	34.00	30.60	27.20	23.80	20.40

**RoHS 240-Series 50 Ohm Coaxial Pigtails**

240 Series	50 Ohm Impedance	240 Series Low-Loss Cable	NOMINAL ATTENUATION			
			MHz	db/100ft	db/100m	
CA-NMNM002	240-Series Cable, Type N Male / Type N Male, 2.0ft (0.6m)	20.55	18.50	16.44	14.38	12.33
CA-NMNM004	240-Series Cable, Type N Male / Type N Male, 4.0ft (1.2m)	22.45	20.20	17.96	15.71	13.47
CA-NMNM010	240-Series Cable, Type N Male / Type N Male, 10.0ft (3.0m)	28.10	25.29	22.48	19.67	16.86
CA-NMNM020	240-Series Cable, Type N Male / Type N Male, 20.0ft (6.1m)	37.50	33.75	30.00	26.25	22.50
CA-NMNF002	240-Series Cable, Type N Male / Type N Female, 2.0ft (0.6m)	25.00	22.50	20.00	17.50	15.00
CA-NMNF004	240-Series Cable, Type N Male / Type N Female, 4.0ft (1.2m)	27.00	24.30	21.60	18.90	16.20
CA-NMNF010	240-Series Cable, Type N Male / Type N Female, 10.0ft (3.0m)	33.00	29.70	26.40	23.10	19.80
CA-NMNF020	240-Series Cable, Type N Male / Type N Female, 20.0ft (6.1m)	43.00	38.70	34.40	30.10	25.80
CA-RTPNMT002	240-Series Cable, Reverse Polarity TNC Plug / Type N Male, 2.0ft (0.6m)	25.00	22.50	20.00	17.50	CALL
CA-RTPNMT004	240-Series Cable, Reverse Polarity TNC Plug / Type N Male, 4.0ft (1.2m)	27.00	24.30	21.60	18.90	16.20
CA-RTPNMT010	240-Series Cable, Reverse Polarity TNC Plug / Type N Male, 10.0ft (3.0m)	33.00	29.70	26.40	23.10	19.80
CA-RTPNMT020	240-Series Cable, Reverse Polarity TNC Plug / Type N Male, 20.0ft (6.1m)	43.00	38.70	34.40	30.10	25.80
CA-RTPNFT002	240-Series Cable, Reverse Polarity TNC Plug / Type N Female, 2.0ft (0.6m)	25.00	22.50	20.00	17.50	15.00
CA-RTPNFT004	240-Series Cable, Reverse Polarity TNC Plug / Type N Female, 4.0ft (1.2m)	27.00	24.30	21.60	18.90	16.20
CA-RTPNFT010	240-Series Cable, Reverse Polarity TNC Plug / Type N Female, 10.0ft (3.0m)	33.00	29.70	26.40	23.10	19.80
CA-RTPNFT020	240-Series Cable, Reverse Polarity TNC Plug / Type N Female, 20.0ft (6.1m)	43.00	38.70	34.40	30.10	25.80
CA-SMNM002	240-Series Cable, SMA Male / Type N Male, 2.0ft (0.6m)	20.55	18.50	16.44	14.38	12.33
CA-SMNM004	240-Series Cable, SMA Male / Type N Male, 4.0ft (1.2m)	22.45	20.20	17.96	15.71	13.47
CA-SMNM010	240-Series Cable, SMA Male / Type N Male, 10.0ft (3.0m)	28.10	25.29	22.48	19.67	16.86
CA-SMNM020	240-Series Cable, SMA Male / Type N Male, 20.0ft (6.1m)	37.50	33.75	30.00	26.25	22.50

**RoHS 400-Series 50 Ohm Coaxial Assemblies**

400 Series	50 Ohm Impedance	400 Series Low-Loss Cable	NOMINAL ATTENUATION			
			MHz	db/100ft	db/100m	
CA4RNP002	400-Series Cable, Reverse Polarity Type N Plug / Type N Male, 10.0ft (3.0m)	22.99	21.15	19.31	17.47	15.63
CA4RNP005	400-Series Cable, Rev. Polarity Type N Plug / Rev. Polarity Type N Plug, 75.0ft (22.9m)	89.99	82.79	75.59	68.39	61.19
CA4NRSF002	400-Series Cable, Reverse Polarity SMA Plug / Type N Male, 2.0ft (0.6m)	21.99	19.79	17.59	15.39	13.19
CA4NRSF010	400-Series Cable, Reverse Polarity SMA Plug / Type N Male, 10.0ft (3.0m)	27.99	25.19	22.39	19.59	16.79
CA4NRSF020	400-Series Cable, Reverse Polarity SMA Plug / Type N Male, 20.0ft (6.1m)	34.99	31.49	27.99	24.49	20.99
CA4NRSF025	400-Series Cable, Reverse Polarity SMA Plug / Type N Male, 25.0ft (7.6m)	39.99	35.99	31.99	27.99	23.99
CA4NRSF030	400-Series Cable, Reverse Polarity SMA Plug / Type N Male, 30.0ft (9.0m)	44.99	40.49	35.99	31.49	26.99
CA4NRSF050	400-Series Cable, Reverse Polarity SMA Plug / Type N Male, 50.0ft (15.2m)	49.99	44.99	39.99	34.99	29.99
CA4NRSF075	400-Series Cable, Reverse Polarity SMA Plug / Type N Male, 75.0ft (22.9m)	87.99	79.19	70.39	61.59	52.79
CA4NRSF100	400-Series Cable, Reverse Polarity SMA Plug / Type N Male, 100.0ft (30.5m)	119.99	110.39	100.79	91.19	81.59
CA4RTMRF002	400-Series Cable, Reverse Polarity TNC Jack / Rev. Polarity TNC Plug, 2.0ft (0.6m)	21.99	19.79	17.59	15.39	13.19
CA4RTMRF010	400-Series Cable, Reverse Polarity TNC Jack / Rev. Polarity TNC Plug, 10.0ft (3.0m)	27.99	25.19	22.39	19.59	16.79
CA4RTMRF020	400-Series Cable, Reverse Polarity TNC Jack / Rev. Polarity TNC Plug, 20.0ft (6.1m)	44.99	40.49	35.99	31.49	26.99
CA4RTMRF025	400-Series Cable, Reverse Polarity TNC Jack / Rev. Polarity TNC Plug, 25.0ft (7.6m)	49.99	44.99	39.99	34.99	29.99
CA4RTMRF050	400-Series Cable, Reverse Polarity TNC Jack / Rev. Polarity TNC Plug, 50.0ft (15.2m)	69.99	62.99	55.99	48.99	41.99
CA4RTPRP002	400-Series Cable, Reverse Polarity TNC Plug / Rev. Polarity TNC Plug, 2.0ft (0.6m)	21.99	19.79	17.59	15.39	13.19
CA4RTPRP010	400-Series Cable, Reverse Polarity TNC Plug / Rev. Polarity TNC Plug, 10.0ft (3.0m)	22.99	20.69	18.39	16.09	13.79
CA4RTPRP050	400-Series Cable, Reverse Polarity TNC Plug / Rev. Polarity TNC Plug, 50.0ft (15.2m)	44.99	43.19	41.39	38.24	33.74
CA4NMRTF002	400-Series Cable, Reverse Polarity TNC Plug / Type N Male, 2.0ft (0.6m)	21.99	19.79	17.59	15.39	13.19
CA4NMRTF010	400-Series Cable, Reverse Polarity TNC Plug / Type N Male, 10.0ft (3.0m)	27.99	25.19	22.39	19.59	16.79
CA4NMRTF020	400-Series Cable, Reverse Polarity TNC Plug / Type N Male, 20.0ft (6.1m)	39.99	35.99	31.99	27.99	23.99

