

| Item # | Description | 1-9 | 10-24 | 25-99 | 100-249 | 250-499 |
|--------------|----------------------------------------------------------------------------------|--------|--------|--------|---------|---------|
| CA4NMRTF025 | 400-Series Cable, Type N Male / Reverse Polarity TNC Plug, 25.0ft (7.6m) | 39.99 | 35.99 | 31.99 | 27.99 | 23.99 |
| CA4NMRTF050 | 400-Series Cable, Type N Male / Reverse Polarity TNC Plug, 50.0ft (15.2m) | 49.99 | 44.99 | 39.99 | 34.99 | 29.99 |
| CA4NMRTF100 | 400-Series Cable, Type N Male / Reverse Polarity TNC Plug, 100.0ft (30.5m) | 119.99 | 110.39 | 100.79 | 91.19 | 81.59 |
| CA4NMRSP002 | 400-Series Cable, Type N Male Right Angle / Rev. Polarity SMA Plug, 2.0ft (0.6m) | 21.99 | 19.79 | 17.59 | 15.39 | 13.19 |
| CA4NMRTRP002 | 400-Series Cable, Type N Male Right Angle / Rev. Polarity TNC Plug, 2.0ft (0.6m) | 21.99 | 19.79 | 17.59 | 15.39 | 13.19 |
| CA4N002 | 400-Series Cable, Type N Male / Type N Female, 2.0ft (0.6m) | 20.99 | 18.89 | 16.79 | 14.69 | 12.59 |
| CA4N010 | 400-Series Cable, Type N Male / Type N Female, 10.0ft (3.0m) | 25.99 | 23.39 | 20.79 | 18.19 | 15.59 |
| CA4N020 | 400-Series Cable, Type N Male / Type N Female, 20.0ft (6.1m) | 30.99 | 27.89 | 24.79 | 21.69 | 18.59 |
| CA4N025 | 400-Series Cable, Type N Male / Type N Female, 25.0ft (7.6m) | 35.99 | 32.39 | 28.79 | 25.19 | 21.59 |
| CA4N050 | 400-Series Cable, Type N Male / Type N Female, 50.0ft (15.2m) | 61.99 | 55.79 | 49.59 | 43.39 | 37.19 |
| CA4N100 | 400-Series Cable, Type N Male / Type N Female, 100.0ft (30.5m) | 120.99 | 111.31 | 101.63 | 91.95 | 82.27 |
| CA3N002 | 400-Series Cable, Type N Male / Type N Male, 2.0ft (0.6m) | 19.99 | 17.99 | 15.99 | 13.99 | 11.99 |
| CA3N010 | 400-Series Cable, Type N Male / Type N Male, 10.0ft (3.0m) | 24.99 | 22.49 | 19.99 | 17.49 | 14.99 |
| CA3N020 | 400-Series Cable, Type N Male / Type N Male, 20.0ft (6.1m) | 29.99 | 26.99 | 23.99 | 20.99 | 17.99 |
| CA3N025 | 400-Series Cable, Type N Male / Type N Male, 25.0ft (7.6m) | 34.99 | 31.49 | 27.99 | 24.49 | 20.99 |
| CA3N030 | 400-Series Cable, Type N Male / Type N Male, 30.0ft (9.0m) | 40.45 | 36.41 | 32.36 | 28.32 | 24.27 |
| CA3N040 | 400-Series Cable, Type N Male / Type N Male, 40.0ft (12.0m) | 50.50 | 45.45 | 40.40 | 35.35 | 30.30 |
| CA3N050 | 400-Series Cable, Type N Male / Type N Male, 50.0ft (15.2m) | 60.99 | 54.89 | 48.79 | 42.69 | 36.59 |
| CA3N075 | 400-Series Cable, Type N Male / Type N Male, 75.0ft (22.9m) | 87.99 | 79.19 | 70.39 | 61.59 | 52.79 |
| CA3N100 | 400-Series Cable, Type N Male / Type N Male, 100.0ft (30.5m) | 119.99 | 107.99 | 95.99 | 83.99 | 71.99 |
| CA-NMRNMF002 | 400-Series Cable, Type N Male Right Angle / Type N Male, 2.0ft (0.6m) | 18.99 | 17.09 | 15.19 | 13.29 | CALL |
| CA-NMRNMF010 | 400-Series Cable, Type N Male Right Angle / Type N Male, 10.0ft (3.0m) | 22.99 | 20.69 | 18.39 | 16.09 | CALL |
| CA-NMRNMF025 | 400-Series Cable, Type N Male Right Angle / Type N Male, 25.0ft (7.6m) | 34.99 | 31.49 | 27.99 | 24.49 | CALL |
| CA-NMRNMF050 | 400-Series Cable, Type N Male Right Angle / Type N Male, 50.0ft (15.2m) | 44.99 | 40.49 | 35.99 | 31.49 | CALL |
| CA4NMSM002 | 400-Series Cable, SMA Male / Type N Male, 2.0ft (0.6m) | 24.99 | 22.49 | 19.99 | 17.49 | 14.99 |
| CA4NMSM010 | 400-Series Cable, SMA Male / Type N Male, 10.0ft (3.0m) | 29.99 | 26.99 | 23.99 | 20.99 | 17.99 |
| CA4NMSM025 | 400-Series Cable, SMA Male / Type N Male, 25.0ft (7.6m) | 49.99 | 44.99 | 39.99 | 34.99 | 29.99 |

RoHS 400-Series Ultra Flex 50 Ohm Coaxial Assemblies

L-com's 400-Series Ultra Flex coax cable assemblies are ideal for indoor or outdoor applications that require maximum flexibility due to curves, bends and twists.

| | | | | |
|-------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|----------|---------|
| <p>400 Series</p> <p>0.405 in. (10.3mm) Nominal</p> <p>50 Ohm Impedance</p> | <p>400 Series Ultra Flex Low-Loss Cable</p> <ul style="list-style-type: none"> Center Conductor: Copper clad aluminum Shielding: Foil + tinned copper braid Insulation: Physical foam polyethylene Jacket: Black Thermoplastic Elastomer Operating Temperature: -40°C - +85°C | NOMINAL ATTENUATION | | |
| | | MHz | db/100ft | db/100m |
| | 900 | 4.7 | 15.4 | |
| | 1800 | 6.8 | 22.3 | |
| | 2500 | 8.1 | 26.6 | |
| | 5800 | 13.0 | 42.6 | |

| | | | | | | |
|--------------|----------------------------------------------------------------------------|--------|--------|--------|--------|--------|
| CA-NMNMH005 | 400-Series Cable, Type N Male / Type N Male, 5.0ft (1.5m) | 22.25 | 20.91 | 19.58 | 18.25 | 16.91 |
| CA-NMNMH010 | 400-Series Cable, Type N Male / Type N Male, 10.0ft (3.0m) | 30.95 | 29.09 | 27.24 | 25.38 | 23.52 |
| CA-NMNMH015 | 400-Series Cable, Type N Male / Type N Male, 15.0ft (4.6m) | 39.80 | 37.41 | 35.02 | 32.64 | 30.25 |
| CA-NMNMH025 | 400-Series Cable, Type N Male / Type N Male, 25.0ft (7.6m) | 58.80 | 55.27 | 51.74 | 48.22 | 44.69 |
| CA-NMNMH050 | 400-Series Cable, Type N Male / Type N Male, 50.0ft (15.2m) | 102.90 | 96.73 | 90.55 | 84.38 | 78.20 |
| CA-NMNMH075 | 400-Series Cable, Type N Male / Type N Male, 75.0ft (22.9m) | 149.60 | 140.62 | 131.65 | 122.67 | 113.70 |
| CA-NMNMH100 | 400-Series Cable, Type N Male / Type N Male, 100.0ft (30.5m) | 193.70 | 182.08 | 170.46 | 158.83 | 147.21 |
| CA-NMNFH005 | 400-Series Cable, Type N Male / Type N Female, 5.0ft (1.5m) | 21.90 | 20.59 | 19.27 | 17.96 | 16.64 |
| CA-NMNFH010 | 400-Series Cable, Type N Male / Type N Female, 10.0ft (3.0m) | 30.60 | 28.76 | 26.93 | 25.09 | 23.26 |
| CA-NMNFH015 | 400-Series Cable, Type N Male / Type N Female, 15.0ft (4.6m) | 39.45 | 37.08 | 34.72 | 32.35 | 29.98 |
| CA-NMNFH025 | 400-Series Cable, Type N Male / Type N Female, 25.0ft (7.6m) | 58.50 | 54.99 | 51.48 | 47.97 | 44.46 |
| CA-NMNFH050 | 400-Series Cable, Type N Male / Type N Female, 50.0ft (15.2m) | 102.65 | 96.49 | 90.33 | 84.17 | 78.01 |
| CA-NMNFH075 | 400-Series Cable, Type N Male / Type N Female, 75.0ft (22.9m) | 149.25 | 140.29 | 131.34 | 122.39 | 113.43 |
| CA-NMNFH100 | 400-Series Cable, Type N Male / Type N Female, 100.0ft (30.5m) | 193.40 | 181.80 | 170.19 | 158.59 | 146.98 |
| CA-NMRTPH005 | 400-Series Cable, Type N Male / Reverse Polarity TNC Plug, 5.0ft (1.5m) | 21.50 | 20.21 | 18.92 | 17.63 | 16.34 |
| CA-NMRTPH010 | 400-Series Cable, Type N Male / Reverse Polarity TNC Plug, 10.0ft (3.0m) | 30.20 | 28.39 | 26.58 | 24.76 | 22.95 |
| CA-NMRTPH015 | 400-Series Cable, Type N Male / Reverse Polarity TNC Plug, 15.0ft (4.6m) | 39.00 | 36.66 | 34.32 | 31.98 | 29.64 |
| CA-NMRTPH025 | 400-Series Cable, Type N Male / Reverse Polarity TNC Plug, 25.0ft (7.6m) | 58.05 | 54.57 | 51.08 | 47.60 | 44.12 |
| CA-NMRTPH050 | 400-Series Cable, Type N Male / Reverse Polarity TNC Plug, 50.0ft (15.2m) | 102.20 | 96.07 | 89.94 | 83.80 | 77.67 |
| CA-NMRTPH075 | 400-Series Cable, Type N Male / Reverse Polarity TNC Plug, 75.0ft (22.9m) | 148.80 | 139.87 | 130.94 | 122.02 | 113.09 |
| CA-NMRTPH100 | 400-Series Cable, Type N Male / Reverse Polarity TNC Plug, 100.0ft (30.5m) | 192.95 | 181.37 | 169.80 | 158.22 | 146.64 |
| CA-NMRSPH005 | 400-Series Cable, Type N Male / Reverse Polarity SMA Plug, 5.0ft (1.5m) | 21.30 | 20.02 | 18.74 | 17.47 | 16.19 |
| CA-NMRSPH010 | 400-Series Cable, Type N Male / Reverse Polarity SMA Plug, 10.0ft (3.0m) | 30.00 | 28.20 | 26.40 | 24.60 | 22.80 |
| CA-NMRSPH015 | 400-Series Cable, Type N Male / Reverse Polarity SMA Plug, 15.0ft (4.6m) | 38.80 | 36.47 | 34.14 | 31.82 | 29.49 |
| CA-NMRSPH025 | 400-Series Cable, Type N Male / Reverse Polarity SMA Plug, 25.0ft (7.6m) | 57.80 | 54.33 | 50.86 | 47.40 | 43.93 |
| CA-NMRSPH050 | 400-Series Cable, Type N Male / Reverse Polarity SMA Plug, 50.0ft (15.2m) | 102.00 | 95.88 | 89.76 | 83.64 | 77.52 |
| CA-NMRSPH075 | 400-Series Cable, Type N Male / Reverse Polarity SMA Plug, 75.0ft (22.9m) | 148.60 | 139.68 | 130.77 | 121.85 | 112.94 |
| CA-NMRSPH100 | 400-Series Cable, Type N Male / Reverse Polarity SMA Plug, 100.0ft (30.5m) | 192.75 | 181.19 | 169.62 | 158.06 | 146.49 |

RoHS 600-Series 50 Ohm Coaxial Assemblies

| | | | | |
|-------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|----------|---------|
| <p>600 Series</p> <p>0.590 in. (15.0mm) Nominal</p> <p>50 Ohm Impedance</p> | <p>600 Series Low-Loss Cable</p> <ul style="list-style-type: none"> Center Conductor: Solid copper Shielding: Foil + tinned copper braid Insulation: Physical foam polyethylene Jacket: Polyethylene Operating Temperature: -40°C - +80°C | NOMINAL ATTENUATION | | |
| | | MHz | db/100ft | db/100m |
| | 900 | 2.5 | 8.2 | |
| | 1800 | 3.7 | 12.1 | |
| | 2500 | 4.4 | 14.5 | |
| | 5800 | 7.3 | 23.8 | |

| | | | | | | |
|-------------|--------------------------------------------------------------|--------|--------|--------|--------|--------|
| CA-6NMNM010 | 600-Series Cable, Type N Male / Type N Male, 10.0ft (3.0m) | 52.00 | 46.80 | 41.60 | 36.40 | 31.20 |
| CA-6NMNM025 | 600-Series Cable, Type N Male / Type N Male, 25.0ft (7.6m) | 70.00 | 63.00 | 56.00 | 49.00 | 42.00 |
| CA-6NMNM050 | 600-Series Cable, Type N Male / Type N Male, 50.0ft (15.2m) | 100.00 | 92.00 | 84.00 | 76.00 | 68.00 |
| CA-6NMNM075 | 600-Series Cable, Type N Male / Type N Male, 75.0ft (22.9m) | 130.00 | 119.60 | 109.20 | 98.80 | 88.40 |
| CA-6NMNM100 | 600-Series Cable, Type N Male / Type N Male, 100.0ft (30.5m) | 160.00 | 147.20 | 134.40 | 121.60 | 108.80 |
| CA-6NMNM125 | 600-Series Cable, Type N Male / Type N Male, 125.0ft (38.1m) | 242.50 | 218.25 | 194.00 | 169.75 | 145.50 |
| CA-6NMNM150 | 600-Series Cable, Type N Male / Type N Male, 150.0ft (45.7m) | 220.00 | 202.40 | 184.80 | 167.20 | 149.60 |



Free access to over 3,000 CAD models
 Download CAD models and 2D drawings for integrating into your projects. L-com.com/CadDemo