


Item #	Description	1-9	10-24	25-99	100-249	250-499																
RG59A/U	 <p>75 Ohm Impedance</p>	RG59A/U <ul style="list-style-type: none"> Center Conductor: 22 (7 x 30) AWG bare compacted copper Shielding: Bare copper braid (96% coverage) Insulation: Foam polyethylene Jacket: Black PVC Operating Temperature: -40°C - +80°C 																				
		NOMINAL ATTENUATION <table border="1"> <thead> <tr> <th>MHz</th> <th>db/100ft</th> <th>db/100m</th> </tr> </thead> <tbody> <tr> <td>50</td> <td>2.1</td> <td>6.9</td> </tr> <tr> <td>100</td> <td>3.0</td> <td>9.8</td> </tr> <tr> <td>200</td> <td>4.5</td> <td>14.8</td> </tr> <tr> <td>400</td> <td>6.6</td> <td>21.7</td> </tr> <tr> <td>1000</td> <td>10.9</td> <td>35.8</td> </tr> </tbody> </table>					MHz	db/100ft	db/100m	50	2.1	6.9	100	3.0	9.8	200	4.5	14.8	400	6.6	21.7	1000
MHz	db/100ft	db/100m																				
50	2.1	6.9																				
100	3.0	9.8																				
200	4.5	14.8																				
400	6.6	21.7																				
1000	10.9	35.8																				

✓RoHS RG59A/U - 75 Ohm Coaxial Cables with Inline BNC to Type F Plug

CC59A-BF-1	RG59A Cable, BNC Male / Type F Male, 1.0ft (0.3m)	6.00	5.76	5.52	5.28	5.04
CC59A-BF-3	RG59A Cable, BNC Male / Type F Male, 3.0ft (0.9m)	7.00	6.72	6.44	6.16	5.88
CC59A-BF-6	RG59A Cable, BNC Male / Type F Male, 6.0ft (1.8m)	8.50	8.16	7.82	7.48	7.14
CC59A-BF-9	RG59A Cable, BNC Male / Type F Male, 9.0ft (2.7m)	10.00	9.60	9.20	8.80	8.40
CC59A-BF-12	RG59A Cable, BNC Male / Type F Male, 12.0ft (3.7m)	11.50	11.04	10.58	10.12	9.66

✓RoHS RG59A/U - 75 Ohm Coaxial Cables with Two Type F Plugs

CCF59-1	RG59A Cable, Type F Male / Male, 1.0ft (0.3m)	4.50	4.32	4.14	3.96	3.78
CCF59-3	RG59A Cable, Type F Male / Male, 3.0ft (0.9m)	5.50	5.28	5.06	4.84	4.62
CCF59-6	RG59A Cable, Type F Male / Male, 6.0ft (1.8m)	7.00	6.72	6.44	6.16	5.88
CCF59-9	RG59A Cable, Type F Male / Male, 9.0ft (2.7m)	8.50	8.16	7.82	7.48	7.14
CCF59-12	RG59A Cable, Type F Male / Male, 12.0ft (3.7m)	10.00	9.60	9.20	8.80	8.40
CCF59-25	RG59A Cable, Type F Male / Male, 25.0ft (7.6m)	16.50	15.84	15.18	14.52	13.86
CCF59-50	RG59A Cable, Type F Male / Male, 50.0ft (15.2m)	29.00	27.84	26.68	25.52	24.36

✓RoHS RG59A/U - 75 Ohm Coaxial Cables with Two Inline RCA Plugs

CC59A-RR-1	RG59A Cable, RCA Male / Male, 1.0ft (0.3m)	4.50	4.32	4.14	3.96	3.78
CC59A-RR-3	RG59A Cable, RCA Male / Male, 3.0ft (0.9m)	5.50	5.28	5.06	4.84	4.62
CC59A-RR-6	RG59A Cable, RCA Male / Male, 6.0ft (1.8m)	7.00	6.72	6.44	6.16	5.88
CC59A-RR-9	RG59A Cable, RCA Male / Male, 9.0ft (2.7m)	8.50	8.16	7.82	7.48	7.14
CC59A-RR-12	RG59A Cable, RCA Male / Male, 12.0ft (3.7m)	10.00	9.60	9.20	8.80	8.40

✓RoHS RG59A/U - 75 Ohm Coaxial Cables with Inline RCA to Inline BNC Plug


CC59A-RB-1	RG59A Cable, RCA Male / BNC Male, 1.0ft (0.3m)	4.50	4.32	4.14	3.96	3.78
CC59A-RB-3	RG59A Cable, RCA Male / BNC Male, 3.0ft (0.9m)	5.50	5.28	5.06	4.84	4.62
CC59A-RB-6	RG59A Cable, RCA Male / BNC Male, 6.0ft (1.8m)	7.00	6.72	6.44	6.16	5.88
CC59A-RB-9	RG59A Cable, RCA Male / BNC Male, 9.0ft (2.7m)	8.50	8.16	7.82	7.48	7.14
CC59A-RB-12	RG59A Cable, RCA Male / BNC Male, 12.0ft (3.7m)	10.00	9.60	9.20	8.80	8.40

✓RoHS RG59A/U - 75 Ohm Coaxial Cables with Inline RCA to Type F Plug

CC59A-RF-1	RG59A Cable, RCA Male / Type F Male, 1.0ft (0.3m)	4.50	4.32	4.14	3.96	3.78
CC59A-RF-3	RG59A Cable, RCA Male / Type F Male, 3.0ft (0.9m)	5.50	5.28	5.06	4.84	4.62
CC59A-RF-6	RG59A Cable, RCA Male / Type F Male, 6.0ft (1.8m)	7.00	6.72	6.44	6.16	5.88
CC59A-RF-9	RG59A Cable, RCA Male / Type F Male, 9.0ft (2.7m)	8.50	8.16	7.82	7.48	7.14
CC59A-RF-12	RG59A Cable, RCA Male / Type F Male, 12.0ft (3.7m)	10.00	9.60	9.20	8.80	8.40

RG59B/U - 75 Ohm Coaxial Cables with Molded BNC and Type F Plugs

L-com offers a wide variety of RG59B/U cable assemblies utilizing BNC and Type F (next pg.) connectors. RG59B/U cable is one of the most commonly used 75 Ohm cables. In addition to inline configurations L-com offers right angle and female bulkheads. All connectors feature a molded strain relief while the Type F connector features a captivated gold plated center pin for enhanced performance. The solid center conductor of the RG59B/U cable provides optimum insertion loss performance.

RG59B/U	 <p>75 Ohm Impedance</p>	NOMINAL ATTENUATION																	
		MHz	db/100ft	db/100m															
RG59B/U <ul style="list-style-type: none"> Center Conductor: 22 AWG solid bare copper covered steel Shielding: Bare copper braid (95% coverage) Insulation: Polyethylene Jacket: Black PVC Operating Temperature: -40°C - +80°C 																			
<table border="1"> <tbody> <tr> <td>50</td> <td>2.4</td> <td>7.9</td> </tr> <tr> <td>100</td> <td>3.4</td> <td>11.1</td> </tr> <tr> <td>200</td> <td>4.9</td> <td>16.1</td> </tr> <tr> <td>400</td> <td>7.0</td> <td>23.0</td> </tr> <tr> <td>1000</td> <td>12.0</td> <td>39.3</td> </tr> </tbody> </table>					50	2.4	7.9	100	3.4	11.1	200	4.9	16.1	400	7.0	23.0	1000	12.0	39.3
50	2.4	7.9																	
100	3.4	11.1																	
200	4.9	16.1																	
400	7.0	23.0																	
1000	12.0	39.3																	

✓RoHS RG59B/U - 75 Ohm Coaxial Cables with Two Inline BNC Plugs

CC59B-05	RG59B Cable, BNC Male / Male, 0.5ft (0.15m)	8.75	8.40	8.05	7.70	7.35
CC59B-1	RG59B Cable, BNC Male / Male, 1.0ft (0.3m)	9.00	8.64	8.28	7.92	7.56
CC59B-1.5	RG59B Cable, BNC Male / Male, 1.5ft (0.45m)	9.25	8.88	8.51	8.14	7.77
CC59B-2	RG59B Cable, BNC Male / Male, 2.0ft (0.6m)	9.50	9.12	8.74	8.36	7.98
CC59B-2.5	RG59B Cable, BNC Male / Male, 2.5ft (0.75m)	9.75	9.36	8.97	8.58	8.19
CC59B-3	RG59B Cable, BNC Male / Male, 3.0ft (0.9m)	10.00	9.60	9.20	8.80	8.40
CC59B-4	RG59B Cable, BNC Male / Male, 4.0ft (1.2m)	10.50	10.08	9.66	9.24	8.82
CC59B-5	RG59B Cable, BNC Male / Male, 5.0ft (1.5m)	11.00	10.56	10.12	9.68	9.24
CC59B-6	RG59B Cable, BNC Male / Male, 6.0ft (1.8m)	11.50	11.04	10.58	10.12	9.66
CC59B-7.5	RG59B Cable, BNC Male / Male, 7.5ft (2.3m)	12.25	11.76	11.27	10.78	10.29
CC59B-10	RG59B Cable, BNC Male / Male, 10.0ft (3.0m)	13.50	12.96	12.42	11.88	11.34
CC59B-12	RG59B Cable, BNC Male / Male, 12.0ft (3.7m)	14.50	13.92	13.34	12.76	12.18
CC59B-15	RG59B Cable, BNC Male / Male, 15.0ft (4.6m)	16.00	15.36	14.72	14.08	13.44
CC59B-25	RG59B Cable, BNC Male / Male, 25.0ft (7.6m)	21.00	20.16	19.32	18.48	17.64
CC59B-50	RG59B Cable, BNC Male / Male, 50.0ft (15.2m)	33.50	32.16	30.82	29.48	28.14
CC59B-75	RG59B Cable, BNC Male / Male, 75.0ft (22.9m)	46.00	44.16	42.32	40.48	38.64
CC59B-100	RG59B Cable, BNC Male / Male, 100.0ft (30.5m)	58.50	56.16	53.82	51.48	49.14
CC59B-150	RG59B Cable, BNC Male / Male, 150.0ft (45.7m)	83.50	80.16	76.82	73.48	70.14
CC59B-200	RG59B Cable, BNC Male / Male, 200.0ft (60.1m)	108.50	104.16	99.82	95.48	91.14



Informative e-mail newsletters

Our newsletters are packed with tips, tutorials, product info and downloads! L-com.com/Newsletter

