



Item #	Description	1-9	10-24	25-99	100-249	250-499
<b>RG59B/U</b>  <b>75 Ohm Impedance</b>	<b>RG59B/U</b>	<ul style="list-style-type: none"> <li>Center Conductor: 22 AWG solid bare copper covered steel</li> <li>Shielding: Bare copper braid (95% coverage)</li> <li>Insulation: Polyethylene</li> <li>Jacket: Black PVC</li> <li>Operating Temperature: -40°C - +80°C</li> </ul>			<b>NOMINAL ATTENUATION</b>	
		MHz	db/100ft	db/100m		
		50	2.4	7.9		
		100	3.4	11.1		
		200	4.9	16.1		
	400	7.0	23.0			
	1000	12.0	39.3			

**RoHS RG59B/U - 75 Ohm Coaxial Cables with Inline BNC Plug to BNC Jack**

CC59B-MF-1	RG59B Cable, BNC Male / Female Bulkhead, 1.0ft (0.3m)	12.00	11.28	10.56	9.84	9.12
CC59B-MF-3	RG59B Cable, BNC Male / Female Bulkhead, 3.0ft (0.9m)	13.00	12.22	11.44	10.66	9.88
CC59B-MF-6	RG59B Cable, BNC Male / Female Bulkhead, 6.0ft (1.8m)	14.50	13.63	12.76	11.89	11.02
CC59B-MF-10	RG59B Cable, BNC Male / Female Bulkhead, 10.0ft (3.0m)	16.50	15.51	14.52	13.53	12.54
CC59B-MF-25	RG59B Cable, BNC Male / Female Bulkhead, 25.0ft (7.6m)	24.00	22.56	21.12	19.68	18.24
CC59B-MF-50	RG59B Cable, BNC Male / Female Bulkhead, 50.0ft (15.2m)	36.50	34.31	32.12	29.93	27.74

**RoHS RG59B/U - 75 Ohm Coaxial Cables with One Inline BNC to One Right Angle BNC Plug**

CC59B-1HR	RG59B Cable, BNC Male / 90° Male, 1.0ft (0.3m)	11.25	10.80	10.35	9.90	9.45
CC59B-1.5HR	RG59B Cable, BNC Male / 90° Male, 1.5ft (0.5m)	11.50	11.04	10.58	10.12	9.66
CC59B-2HR	RG59B Cable, BNC Male / 90° Male, 2.0ft (0.6m)	11.75	11.28	10.81	10.34	9.87
CC59B-3HR	RG59B Cable, BNC Male / 90° Male, 3.0ft (0.9m)	12.25	11.76	11.27	10.78	10.29
CC59B-4HR	RG59B Cable, BNC Male / 90° Male, 4.0ft (1.2m)	12.75	12.24	11.73	11.22	10.71
CC59B-5HR	RG59B Cable, BNC Male / 90° Male, 5.0ft (1.5m)	13.25	12.72	12.19	11.66	11.13
CC59B-7.5HR	RG59B Cable, BNC Male / 90° Male, 7.5ft (2.3m)	14.50	13.92	13.34	12.76	12.18
CC59B-10HR	RG59B Cable, BNC Male / 90° Male, 10.0ft (3.0m)	15.75	15.12	14.49	13.86	13.23

**RoHS RG59B/U - 75 Ohm Coaxial Cables with Two Right Angle BNC Plugs**

CC59B-1HR2	RG59B Cable, BNC 90° Male / 90° Male, 1.0ft (0.3m)	15.00	14.40	13.80	13.20	12.60
CC59B-2HR2	RG59B Cable, BNC 90° Male / 90° Male, 2.0ft (0.6m)	15.50	14.88	14.26	13.64	13.02
CC59B-2.5HR2	RG59B Cable, BNC 90° Male / 90° Male, 2.5ft (0.8m)	15.75	15.12	14.49	13.86	13.23
CC59B-3HR2	RG59B Cable, BNC 90° Male / 90° Male, 3.0ft (0.9m)	16.00	15.36	14.72	14.08	13.44
CC59B-7.5HR2	RG59B Cable, BNC 90° Male / 90° Male, 7.5ft (2.3m)	18.25	17.52	16.79	16.06	15.33

**RoHS RG59B/U - 75 Ohm Coaxial Cables with Two Inline Molded Type F Plugs**

CCF59B-1	RG59B Cable, Type F Male / Male, 1.0ft (0.3m)	4.50	4.32	4.14	3.96	3.78
CCF59B-3	RG59B Cable, Type F Male / Male, 3.0ft (0.9m)	5.50	5.28	5.06	4.84	4.62
CCF59B-6	RG59B Cable, Type F Male / Male, 6.0ft (1.8m)	7.00	6.72	6.44	6.16	5.88
CCF59B-9	RG59B Cable, Type F Male / Male, 9.0ft (2.7m)	8.50	8.16	7.82	7.48	7.14
CCF59B-12	RG59B Cable, Type F Male / Male, 12.0ft (3.7m)	10.00	9.60	9.20	8.80	8.40
CCF59B-25	RG59B Cable, Type F Male / Male, 25.0ft (7.6m)	16.50	15.84	15.18	14.52	13.86
CCF59B-50	RG59B Cable, Type F Male / Male, 50.0ft (15.2m)	29.00	27.84	26.68	25.52	24.36
CCF59B-100	RG59B Cable, Type F Male / Male, 100.0ft (30.5m)	54.00	51.84	49.68	47.52	45.36

**RoHS RG6/U - 75 Ohm Coaxial Cables with Two Inline Type F Plugs**

This series features low loss RG6 coaxial cable popular in transmission of television signal over cable. Features include: gold flash on connector surfaces, molded strain relief on the connector for superior protection and a captivated gold plated center conductor, not the cable's center conductor typically found in lower quality assemblies.

<b>RG6/U</b>  <b>75 Ohm Impedance</b>	<b>RG6/U</b>	<b>NOMINAL ATTENUATION</b>			
		MHz	db/100ft	db/100m	
		• Center Conductor: 18 AWG solid bare copper covered steel	50	1.5	4.9
		• Shielding: Inner foil (100% coverage); Outer, copper braid (60% coverage)	100	2.1	6.9
		• Insulation: Foam Polyethylene	200	3.1	10.2
• Jacket: Black PVC	400	4.5	14.8		
• Operating Temperature: -40°C - +80°C	1000	7.3	23.9		

CCF6-1	RG6 Cable, Type F Male / Male, 1.0ft (0.3m)	5.75	5.17	4.60	4.02	3.45
CCF6-3	RG6 Cable, Type F Male / Male, 3.0ft (0.9m)	6.75	6.08	5.40	4.72	4.05
CCF6-6	RG6 Cable, Type F Male / Male, 6.0ft (1.8m)	8.25	7.42	6.60	5.77	4.95
CCF6-9	RG6 Cable, Type F Male / Male, 9.0ft (2.7m)	9.75	8.78	7.80	6.82	5.85
CCF6-12	RG6 Cable, Type F Male / Male, 12.0ft (3.7m)	11.25	10.13	9.00	7.87	6.75
CCF6-25	RG6 Cable, Type F Male / Male, 25.0ft (7.6m)	17.75	15.97	14.20	12.42	10.65
CCF6-50	RG6 Cable, Type F Male / Male, 50.0ft (15.2m)	30.25	27.23	24.20	21.17	18.15
CCF6-100	RG6 Cable, Type F Male / Male, 100.0ft (30.5m)	55.25	49.73	44.20	38.67	33.15

