



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

RG179B/U - High Temperature Cable with Inline BNC and SMB Plugs

This 75 Ohm cable features a Brown tinted FEP outer jacket and an operating temperature of 200°C. Offered with both BNC and SMB plugs in eight convenient lengths. Other lengths and connector combinations available with modest minimums.

RG179B/U		RG179B/U • Center Conductor: 30 AWG (7 x 38) stranded silver plated copper covered steel • Shielding: Silver coated copper braid (95% coverage) • Insulation: TFE teflon • Jacket: Brown FEP • Operating Temperature: -70°C - +200°C	NOMINAL ATTENUATION		
			MHz	db/100ft	db/100m
			50	8.5	27.9
			100	10.0	32.8
			200	12.5	41.0
			400	16.0	52.5
			1000	24.0	78.7

RG179B/U - 75 Ohm High Temperature Cable with Two Inline BNC Plugs

CC179B-1	RG179 Cable, BNC Male / Male, 1.0ft (0.3m)	21.00	20.16	19.32	18.48	17.64
CC179B-1.5	RG179 Cable, BNC Male / Male, 1.5ft (0.45m)	21.75	20.88	20.01	19.14	18.27
CC179B-2	RG179 Cable, BNC Male / Male, 2.0ft (0.6m)	22.50	21.60	20.70	19.80	18.90
CC179B-2.5	RG179 Cable, BNC Male / Male, 2.5ft (0.75m)	23.25	22.32	21.39	20.46	19.53
CC179B-5	RG179 Cable, BNC Male / Male, 5.0ft (1.5m)	27.00	25.92	24.84	23.76	22.68
CC179B-7.5	RG179 Cable, BNC Male / Male, 7.5ft (2.3m)	30.75	29.52	28.29	27.06	25.83
CC179B-10	RG179 Cable, BNC Male / Male, 10.0ft (3.0m)	34.50	33.12	31.74	30.36	28.98
CC179B-15	RG179 Cable, BNC Male / Male, 15.0ft (4.6m)	42.00	40.32	38.64	36.96	35.28

RG179B/U - 75 Ohm High Temperature Cable with Two Inline SMB Plugs

CC179S-1	RG179 Cable, SMB Male / Male, 1.0ft (0.3m)	36.00	34.56	33.12	31.68	30.24
CC179S-1.5	RG179 Cable, SMB Male / Male, 1.5ft (0.45m)	36.75	35.28	33.81	32.34	30.87
CC179S-2	RG179 Cable, SMB Male / Male, 2.0ft (0.6m)	37.50	36.00	34.50	33.00	31.50
CC179S-2.5	RG179 Cable, SMB Male / Male, 2.5ft (0.75m)	38.25	36.72	35.19	33.66	32.13
CC179S-5	RG179 Cable, SMB Male / Male, 5.0ft (1.5m)	42.00	40.32	38.64	36.96	35.28
CC179S-7.5	RG179 Cable, SMB Male / Male, 7.5ft (2.3m)	45.75	43.92	42.09	40.26	38.43
CC179S-10	RG179 Cable, SMB Male / Male, 10.0ft (3.0m)	49.50	47.52	45.54	43.56	41.58

Thinline 75 Ohm (.11" Dia.) Coaxial Cable Assemblies

Substitute our smaller diameter, more flexible, lighter weight thinline cable assemblies for your traditional 75 Ohm cable assemblies. This coaxial cable features a spiral tinned copper shield and a proprietary air foamed dielectric. This 75 Ohm cable is less than half the size of RG59 and RG6 cable assemblies. Available in BNC, RCA and Type F connectors all with fully molded strain relief.

Thinline		Thinline • Center Conductor: 28 AWG (7 x 38) stranded tinned copper wire • Shielding: Tinned copper spiral shield (95% coverage) • Insulation: Foamed polyethylene • Jacket: Black PVC • Operating Temperature: -40°C - +80°C	NOMINAL ATTENUATION		
			MHz	db/100ft	db/100m
			5	1.4	4.6
			10	2.1	6.9
			30	3.8	12.5
			50	5.1	16.7
			100	7.6	24.9

Thinline - 75 Ohm Coaxial Cables with Two Inline BNC Plugs

CTL1B-1	Thinline Cable, BNC Male / Male, 1.0ft (0.3m)	7.00	6.72	6.44	6.16	5.88
CTL1B-2.5	Thinline Cable, BNC Male / Male, 2.5ft (0.75m)	7.75	7.44	7.13	6.82	6.51
CTL1B-5	Thinline Cable, BNC Male / Male, 5.0ft (1.5m)	9.00	8.64	8.28	7.92	7.56
CTL1B-7.5	Thinline Cable, BNC Male / Male, 7.5ft (2.3m)	10.25	9.84	9.43	9.02	8.61
CTL1B-10	Thinline Cable, BNC Male / Male, 10.0ft (3.0m)	11.50	11.04	10.58	10.12	9.66
CTL1B-15	Thinline Cable, BNC Male / Male, 15.0ft (4.6m)	14.00	13.44	12.88	12.32	11.76
CTL1B-25	Thinline Cable, BNC Male / Male, 25.0ft (7.6m)	19.00	18.24	17.48	16.72	15.96

Thinline - 75 Ohm Coaxial Cables with Two Inline RCA Plugs

CTL1R-1	Thinline Cable, RCA Male / Male, 1.0ft (0.3m)	5.50	5.28	5.06	4.84	4.62
CTL1R-5	Thinline Cable, RCA Male / Male, 5.0ft (1.5m)	7.50	7.20	6.90	6.60	6.30
CTL1R-10	Thinline Cable, RCA Male / Male, 10.0ft (3.0m)	10.00	9.60	9.20	8.80	8.40
CTL1R-15	Thinline Cable, RCA Male / Male, 15.0ft (4.6m)	12.50	12.00	11.50	11.00	10.50
CTL1R-25	Thinline Cable, RCA Male / Male, 25.0ft (7.6m)	17.50	16.80	16.10	15.40	14.70

Thinline - 75 Ohm Coaxial Cables with Two Inline Type F Plugs

CTL1F-1	Thinline Cable, Type F Male / Male, 1.0ft (0.3m)	5.50	5.28	5.06	4.84	4.62
CTL1F-5	Thinline Cable, Type F Male / Male, 5.0ft (1.5m)	7.50	7.20	6.90	6.60	6.30
CTL1F-10	Thinline Cable, Type F Male / Male, 10.0ft (3.0m)	10.00	9.60	9.20	8.80	8.40
CTL1F-15	Thinline Cable, Type F Male / Male, 15.0ft (4.6m)	12.50	12.00	11.50	11.00	10.50
CTL1F-25	Thinline Cable, Type F Male / Male, 25.0ft (7.6m)	17.50	16.80	16.10	15.40	14.70

Thinline - 75 Ohm Coaxial Cables with One Inline RCA to One Inline BNC Plug

CTL1RB-1	Thinline Cable, RCA Male / BNC Male, 1.0ft (0.3m)	5.50	5.28	5.06	4.84	4.62
CTL1RB-5	Thinline Cable, RCA Male / BNC Male, 5.0ft (1.5m)	7.50	7.20	6.90	6.60	6.30
CTL1RB-10	Thinline Cable, RCA Male / BNC Male, 10.0ft (3.0m)	10.00	9.60	9.20	8.80	8.40
CTL1RB-15	Thinline Cable, RCA Male / BNC Male, 15.0ft (4.6m)	12.50	12.00	11.50	11.00	10.50
CTL1RB-25	Thinline Cable, RCA Male / BNC Male, 25.0ft (7.6m)	17.50	16.80	16.10	15.40	14.70

Thinline - 75 Ohm Coaxial Cables with One Inline Type F to One Inline BNC Plug

CTL1FB-1	Thinline Cable, Type F Male / BNC Male, 1.0ft (0.3m)	6.50	6.24	5.98	5.72	5.46
CTL1FB-5	Thinline Cable, Type F Male / BNC Male, 5.0ft (1.5m)	8.50	8.16	7.82	7.48	7.14
CTL1FB-10	Thinline Cable, Type F Male / BNC Male, 10.0ft (3.0m)	11.00	10.56	10.12	9.68	9.24
CTL1FB-15	Thinline Cable, Type F Male / BNC Male, 15.0ft (4.6m)	13.50	12.96	12.42	11.88	11.34
CTL1FB-25	Thinline Cable, Type F Male / BNC Male, 25.0ft (7.6m)	18.50	17.76	17.02	16.28	15.54