

Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
✓RoHS RCA Female Feed-Thru Adapter - 75 Ohm - with Red, Green, Blue, Yellow or White Insulators							
These RCA feed-thru adapters feature color coded insulators for video and audio applications. This color coding helps avoid improper connections.							
BA400R	Coaxial Adapter, RCA Bulkhead Female / Female, Red Insulator		3.65	3.43	3.21	2.99	2.77
BA400G	Coaxial Adapter, RCA Bulkhead Female / Female, Green Insulator		3.65	3.43	3.21	2.99	2.77
BA400B	Coaxial Adapter, RCA Bulkhead Female / Female, Blue Insulator		3.65	3.43	3.21	2.99	2.77
BA400Y	Coaxial Adapter, RCA Bulkhead Female / Female, Yellow Insulator		3.65	3.43	3.21	2.99	2.77
BA400	Coaxial Adapter, RCA Bulkhead Female / Female, White Insulator		3.65	3.43	3.21	2.99	2.77
BA400A	Coaxial Adapter, RCA Bulkhead Female / Female, 0.5" (1.3cm) Circular Hole		3.65	3.43	3.21	2.99	2.77

✓RoHS Type N Within Series Adapters - 50 Ohm

AXA-NMNM	Coaxial Adapter, Type N Male / Male Barrel Adapter		3.99	3.83	3.67	3.39	2.99
AXA-NNFB	Coaxial Adapter, Type N Female / Female Bullet Adapter		3.99	3.83	3.67	3.39	2.99
AXA-NMNM90	Coaxial Adapter, Type N Male / Male Right Angle Adapter		5.99	5.75	5.51	5.09	4.49
AXA-NMNF90	Coaxial Adapter, Type N Male / Female Right Angle Adapter		5.99	5.75	5.51	5.09	4.49
AXA-NNFB2	Coaxial Adapter, Type N Female / Female 1/4" (0.6cm) (Bulkhead)		3.49	3.35	3.21	2.97	2.62
AXA-NNFB	Coaxial Adapter, Type N Female / Female 1/8" (0.3cm) (Bulkhead)		3.49	3.35	3.21	2.97	2.62
BN126	Coaxial T Adapter, Type N Female / Female / Male		5.75	5.40	5.06	4.72	4.37
BN133	Coaxial T Adapter, Type N Female / Female / Female		5.75	5.40	5.06	4.72	4.37

✓RoHS Mini-UHF Within Series Adapters - 50 Ohm

BA470	Coaxial Adapter, Mini-UHF Female / 90° Male		5.99	5.93	5.87	5.81	5.75
BA476	Coaxial Adapter, Mini-UHF Female / Female		3.95	3.91	3.87	3.83	3.79
BA478	Coaxial Adapter, Mini-UHF Male / Male		3.95	3.71	3.48	3.24	3.00

✓RoHS UHF Within Series Adapters - 50 Ohm

BA170	Coaxial Adapter, UHF Female / Female		2.95	2.77	2.60	2.42	2.24
BA280	Coaxial Adapter, UHF Male / Male		2.95	2.77	2.60	2.42	2.24
BA303	Coaxial T Adapter, UHF Female / Female / Female		5.95	5.59	5.24	4.88	4.52
BA404Z	Coaxial Adapter, UHF Male / 90° Female		5.95	5.59	5.24	4.88	4.52
BA406Z	Coaxial Adapter, UHF Feed-Thru Female / Female		5.95	5.59	5.24	4.88	4.52



✓RoHS TNC Within Series Adapters - 50 Ohm

BA2301	Coaxial Adapter, TNC Bulkhead, Female / Female, Grounded		4.95	4.65	4.36	4.06	3.76
BA1090	Coaxial Adapter, TNC Bulkhead, Female / Female, Insulated Ground		5.95	5.59	5.24	4.88	4.52
BA4000	Coaxial Adapter, TNC Male / Female		3.75	3.52	3.30	3.08	2.85
AXA-RTJRTJ	Coaxial Adapter, RP-TNC Jack to RP-TNC Jack Bullet Adapter		3.99	3.83	3.67	3.39	2.99
AXA-RTPRTP	Coaxial Adapter, RP-TNC Plug to RP-TNC Plug Barrel Adapter		3.49	3.35	3.21	2.97	2.62
AXA-RTPRJT90	Coaxial Adapter, RP-TNC Plug to RP-TNC Jack, Right Angle		5.75	5.52	5.29	4.89	4.31

✓RoHS Insulated Coaxial Connections - 50 Ohm - Needed to Prevent Ground Loops and Noise

Data signals are particularly susceptible to both ground loop and common mode interference. Reducing the number of ground points of a coaxial wiring system reduces the number of potential ground loops and multiple noise currents.

BIF-CB	Coaxial Coupler, BNC Female / Female		2.95	2.77	2.60	2.42	2.24
BIF-CN	Coaxial Coupler, Type N Female / Female		6.95	6.53	6.12	5.70	5.28
BIF-TB1	Coaxial T Adapter, BNC Female / Male / Female		5.65	5.31	4.97	4.63	4.29
BIF-TB2	Coaxial T Adapter, BNC Female / Male / Female		5.95	5.59	5.24	4.88	4.52

✓RoHS BNC Connector Identifiers/Insulators - Take on New Look with Color-Coded Insulated Covers

The conventional BNC crimp connector may now be modified to be fully insulated, helping eliminate ground loop problems. Our colorful slip-on insulated covers are quick to assemble and provide color coding. The hood cover is installed over the BNC movable collar; the plastic bend strain protector is slipped on over ferrule after the crimping operation. An important feature is the added support offered by the bend-protector; it helps prevent cable breakage.

BIF-H0	Coaxial Connector Cover for BNC, Pkg/10	Black	1.95	1.79	1.64	1.48	1.33
BIF-H2	Coaxial Connector Cover for BNC, Pkg/10	Red	1.95	1.79	1.64	1.48	1.33
BIF-H5	Coaxial Connector Cover for BNC, Pkg/10	Green	1.95	1.79	1.64	1.48	1.33
BIF-H6	Coaxial Connector Cover for BNC, Pkg/10	Blue	1.95	1.79	1.64	1.48	1.33
BIF-H9	Coaxial Connector Cover for BNC, Pkg/10	White	1.95	1.79	1.64	1.48	1.33
BIF-P0-58	Coaxial Plastic Bend Protector for RG58, Pkg/10	Black	1.75	1.61	1.47	1.33	1.19
BIF-P2-58	Coaxial Plastic Bend Protector for RG58, Pkg/10	Red	1.75	1.61	1.47	1.33	1.19
BIF-P5-58	Coaxial Plastic Bend Protector for RG58, Pkg/10	Green	1.75	1.61	1.47	1.33	1.19
BIF-P6-58	Coaxial Plastic Bend Protector for RG58, Pkg/10	Blue	1.75	1.61	1.47	1.33	1.19
BIF-P9-58	Coaxial Plastic Bend Protector for RG58, Pkg/10	White	1.75	1.61	1.47	1.33	1.19
BIF-P0-59/62	Coaxial Plastic Bend Protector for RG59/62, Pkg/10	Black	1.75	1.61	1.47	1.33	1.19
BIF-P2-59/62	Coaxial Plastic Bend Protector for RG59/62, Pkg/10	Red	1.75	1.61	1.47	1.33	1.19
BIF-P5-59/62	Coaxial Plastic Bend Protector for RG59/62, Pkg/10	Green	1.75	1.61	1.47	1.33	1.19
BIF-P6-59/62	Coaxial Plastic Bend Protector for RG59/62, Pkg/10	Blue	1.75	1.61	1.47	1.33	1.19
BIF-P9-59/62	Coaxial Plastic Bend Protector for RG59/62, Pkg/10	White	1.75	1.61	1.47	1.33	1.19



Some Connectors are sold in 10-Packs. See website for details. Adapters are sold individually.



Helpful videos

How-to videos help with some of today's popular product applications. L-com.com/Tips