



Item #	Description	Cable Type	Attachment	1-9	10-24	25-99	100-249	250-499
<b>Coaxial Connectors</b>								
In addition to the most popular styles, L-com also provides harder to find connectors for all your application needs. Configurations include crimp style, clamp style, bulkhead style and panel mount connectors. Each connector is precision manufactured using only the highest quality materials.								
<b>✓RoHS TNC Coaxial Connectors, 50 Ohm</b>								
BAC893-58	TNC Male	RG58	Crimp	2.50	2.35	2.20	2.05	1.90
BAC525	TNC Male, Right Angle	RG58	Crimp	4.75	4.46	4.18	3.90	3.61
BAC545	TNC Male	RG142 / RG223 / RG400	Crimp	5.00	4.70	4.40	4.10	CALL
BAC531	TNC Male	RG174 / RG188 / RG316	Crimp	5.50	5.17	4.84	4.51	4.18
BAC504	TNC Male	RG213	Crimp	2.50	2.35	2.20	2.05	1.90
ATM-1204	TNC Male	Low-Loss 200-Series	Crimp	3.15	3.02	2.90	2.68	2.36
ATM-1506	TNC Male	Low-Loss 240-Series	Crimp	3.69	3.54	3.39	3.14	2.77
ATM-1402	TNC Male	Low-Loss 400-Series	Crimp	3.69	3.54	3.39	3.14	2.77
ATML-1400	TNC Male Reverse Thread	Low-Loss 400-Series	Crimp	3.49	3.35	3.21	2.97	2.62
BAC513	TNC Female	RG58	Crimp	2.50	2.35	2.20	2.05	1.90
BAC514	TNC Female	RG174 / 188/316	Crimp	2.50	2.35	2.20	2.05	1.90
BAC528	TNC Female Bulkhead	RG174 / 188/316	Crimp	6.00	5.64	5.28	4.92	4.56
BAC553	TNC Female	RG142 / RG223 / RG400	Crimp	5.50	5.17	4.84	4.51	4.18
BAC554	TNC Female Bulkhead	RG142 / RG223 / RG400	Crimp	6.25	5.88	5.50	5.13	4.75
ATF-1700	TNC Female	Low-Loss 195-Series, RG58	Crimp	1.69	1.62	1.55	1.44	1.27
ATF-1506	TNC Female	Low-Loss 240-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ATF-1402	TNC Female	Low-Loss 400-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ATF-3700	TNC Female Bulkhead	Low-Loss 195-Series, RG58	Crimp	3.49	3.35	3.21	2.97	2.62
ARTP-1A10	Reverse Polarity TNC Plug	RG6	Crimp	3.15	3.02	2.90	2.68	2.36
BAC500	Reverse Polarity TNC Plug	RG58	Crimp	4.95	4.55	4.16	3.76	3.37
ARTP-1100	Reverse Polarity TNC Plug	RG316 / RG174 / RG188	Crimp	4.95	4.55	4.16	3.76	3.37
ARTP-1708	Reverse Polarity TNC Plug	Low-Loss 195-Series, RG58	Crimp	3.15	3.02	2.90	2.68	2.36
ARTP-1200	Reverse Polarity TNC Plug	Low-Loss 200-Series	Crimp	3.15	3.02	2.90	2.68	2.36
ARTP-1502	Reverse Polarity TNC Plug	Low-Loss 240-Series	Crimp	4.19	4.02	3.85	3.56	3.14
ARTP-1312	Reverse Polarity TNC Plug	Low-Loss 300-Series	Crimp	4.19	4.02	3.85	3.56	3.14
ARTP-1404	Reverse Polarity TNC Plug	Low-Loss 400-Series	Crimp	4.19	4.02	3.85	3.56	3.14
ARTP-1606	Reverse Polarity TNC Plug	Low-Loss 600-Series	Crimp	5.25	5.04	4.83	4.46	3.94
BAC501	Reverse Polarity TNC Jack	RG58	Crimp	4.95	4.55	4.16	3.76	3.37
ARTJ-3702	Reverse Polarity TNC Jack Bulkhead	Low-Loss 195-Series, RG58	Crimp	3.15	3.02	2.90	2.68	2.36
ARTJ-1708	Reverse Polarity TNC Jack	Low-Loss 195-Series, RG58	Crimp	3.15	3.02	2.90	2.68	2.36
ARTJ-3400	Reverse Polarity TNC Jack Bulkhead	Low-Loss 400-Series	Crimp	3.15	3.02	2.90	2.68	2.36
ARTJ-1404	Reverse Polarity TNC Jack	Low-Loss 400-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ARTJ-1606	Reverse Polarity TNC Jack	Low-Loss 600-Series	Crimp	3.49	3.35	3.21	2.97	2.62
<b>✓RoHS TNC Coaxial Connectors, 75 Ohm</b>								
BAC893-59	TNC Male	RG59	Crimp	2.50	2.35	2.20	2.05	1.90
BAC933-59	TNC Male	RG59	Twist On	3.25	3.05	2.86	2.67	2.47
BAC709	TNC Male, Right Angle	RG59	Crimp	4.75	4.46	4.18	3.90	3.61
BAC986	TNC Male, Right Angle	RG59	Twist On	4.75	4.46	4.18	3.90	3.61
BAC934-59	TNC Female	RG59	Crimp	4.75	4.46	4.18	3.90	3.61
BAC901-59	TNC Female	RG59	Twist On	4.75	4.46	4.18	3.90	3.61
<b>✓RoHS SMA Coaxial Connectors, 50 Ohm</b>								
BAC03-G	SMA Male, Gold	RG58	Crimp	4.25	3.99	3.74	3.49	3.23
BAC02-G	SMA Male, Right Angle Gold	RG58	Crimp	4.25	3.99	3.74	3.49	3.23
ASM-1710	SMA Male, Right Angle 195-Series	RG58	Crimp	3.49	3.35	3.21	2.97	2.62
ASM-1708	SMA Male, Straight 195-Series	RG58	Crimp	3.49	3.35	3.21	2.97	2.62
BAC02A	SMA Male, Right Angle Nickel	RG174 / 188 / 316	Crimp	4.25	3.99	3.74	3.49	3.23
BAC03A	SMA Male, Nickel	RG174 / 188 / 316	Crimp	4.25	3.99	3.74	3.49	3.23
BAC03A-G	SMA Male, Gold	RG174 / 188 / 316	Crimp	4.25	3.99	3.74	3.49	3.23
BAC02A	SMA Male, Right Angle Nickel	RG174 / 188 / 316	Crimp	4.25	3.99	3.74	3.49	3.23
BAC02A-G	SMA Male, Right Angle Gold	RG174 / 188 / 316	Crimp	3.95	3.63	3.32	3.00	2.69
ASM-1102	SMA Male	Low-Loss 100-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ASM-1504	SMA Male	Low-Loss 240-Series	Crimp	3.15	3.02	2.90	2.68	2.36
ASM-1406	SMA Male	Low-Loss 400-Series	Crimp	3.49	3.35	3.21	2.97	2.62
HPC401	SMA Male	Low-Loss 400-Series	Crimp	9.50	8.74	7.98	7.22	6.46
BAC06A	SMA Female, Bulkhead Gold	RG174 / 188 / 316	Crimp	5.25	4.93	4.62	4.31	3.99
BAC05A	SMA Female, Nickel	RG174 / 188 / 316	Crimp	5.25	4.93	4.62	4.31	3.99
ASF-3700	SMA Female, Bulkhead	Low-Loss 195-Series, RG58	Crimp	3.49	3.35	3.21	2.97	2.62
ASF-1708	SMA Female	Low-Loss 195-Series, RG58	Crimp	3.49	3.35	3.21	2.97	2.62
BAC503	Reverse Polarity SMA Jack, Bulkhead	RG174 / 188 / 316	Crimp	4.95	4.55	4.16	3.76	3.37
BAC512	Reverse Polarity SMA Jack	RG174 / 188 / 316	Crimp	5.50	5.17	4.84	4.51	4.18
ARSJ-3700	Reverse Polarity SMA Jack, Bulkhead	Low-Loss 195-Series, RG58	Crimp	4.19	4.02	3.85	3.56	3.14
ARSJ-1700	Reverse Polarity SMA Jack	Low-Loss 195-Series, RG58	Crimp	4.19	4.02	3.85	3.56	3.14
ARSJ-1404	Reverse Polarity SMA Jack	Low-Loss 400-Series	Crimp	4.19	4.02	3.85	3.56	3.14
BAC502	Reverse Polarity SMA Plug	RG174 / 188 / 316	Crimp	4.95	4.55	4.16	3.76	3.37
ARSP-1100	Reverse Polarity SMA Plug	Low-Loss 100-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ARSP-1700	Reverse Polarity SMA Plug	Low-Loss 195-Series, RG58	Crimp	4.30	4.13	3.96	3.65	3.22
ARSP-1702	Reverse Polarity SMA Plug, Right Angle	Low-Loss 195-Series, RG58	Crimp	4.19	4.02	3.85	3.56	3.14
ARSP-1202	Reverse Polarity SMA Plug	Low-Loss 200-Series	Crimp	3.49	3.35	3.21	2.97	2.62
HPC202	Reverse Polarity SMA Plug	Low-Loss 200-Series	Crimp	6.25	5.88	5.50	5.13	4.75
ARSP-1504	Reverse Polarity SMA Plug	Low-Loss 240-Series	Crimp	4.19	4.02	3.85	3.56	3.14
ARSP-1404	Reverse Polarity SMA Plug	Low-Loss 400-Series	Crimp	5.25	5.04	4.83	4.46	3.94
HPC402	Reverse Polarity SMA Plug	Low-Loss 400-Series	Crimp	10.50	9.66	8.82	7.98	7.14

