


Item #	Description	Cable Type	Attachment	1-9	10-24	25-99	100-249	250-499
<b>RoHS Type N Coaxial Connectors, 50 Ohm</b>								
ANM-1A18	Type N Male	RG6	Crimp	3.49	3.35	3.21	2.97	2.62
BAC536	Type N Male	RG142, RG400	Crimp	5.50	5.17	4.84	4.51	4.18
BAC523	Type N Male	RG174	Crimp	6.75	6.34	5.94	5.54	5.13
BAN111	Type N Male	RG213	Clamp	6.25	5.88	5.50	5.13	4.75
BAC506	Type N Male	RG213	Crimp	6.00	5.64	5.28	4.92	4.56
BAC533	Type N Male Right Angle	RG223	Crimp	6.75	6.34	5.94	5.54	5.13
ANM-1114	Type N Male	RG316, RG174, RG188	Crimp	3.49	3.35	3.21	2.97	2.62
ANM-1700	Type N Male	Low-Loss 195-Series, RG58	Crimp	3.49	3.35	3.21	2.97	2.62
ANM-1716	Type N Male Right Angle	Low-Loss 195-Series, RG58	Crimp	4.19	4.02	3.85	3.56	3.14
ANM-1202	Type N Male	Low-Loss 200-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ANM-1508	Type N Male	Low-Loss 240-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ANM-1516	Type N Male Right Angle	Low-Loss 240-Series	Crimp	6.29	6.04	5.79	5.35	4.72
ANM-1304	Type N Male	Low-Loss 300-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ANM-1416	Type N Male Right Angle	Low-Loss 400-Series	Crimp	4.19	4.02	3.85	3.56	3.14
ANM-1406	Type N Male	Low-Loss 400-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ANM-2400	Type N Male	Low-Loss 400-Series	Clamp	3.69	3.54	3.39	3.14	2.77
ANM-2402	Type N Male Right Angle	Low-Loss 400-Series	Clamp	7.85	7.54	7.22	6.67	5.89
ANM-2602	Type N Male	Low-Loss 600-Series	Clamp	5.25	5.04	4.83	4.46	3.94
ANM-1610	Type N Male	Low-Loss 600-Series	Crimp	6.29	6.04	5.79	5.35	4.72
ANM-1616	Type N Male Right Angle	Low-Loss 600-Series	Crimp	6.29	6.04	5.79	5.35	4.72
ANM-2904	Type N Male	Low-Loss 900-Series	Clamp	29.99	28.19	26.39	24.59	22.79
ANF-1A18	Type N Female	RG6	Crimp	3.49	3.35	3.21	2.97	2.62
BAC527	Type N Female	RG174	Crimp	7.25	6.81	6.38	5.95	5.51
BAC542	Type N Female Bulkhead	RG55 / RG141 / RG142 / RG233	Crimp	4.95	4.75	4.55	4.21	3.71
ANF-3700	Type N Female Bulkhead	Low-Loss 195-Series, RG58	Crimp	4.19	4.02	3.85	3.56	3.14
ANF-1700	Type N Female	Low-Loss 195-Series, RG58	Crimp	3.49	3.35	3.21	2.97	2.62
ANF-5700	Type N Female Panel Mount	Low-Loss 195-Series, RG58	Crimp	3.69	3.54	3.39	3.14	2.77
ANF-1202	Type N Female	Low-Loss 200-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ANF-1508	Type N Female	Low-Loss 240-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ANF-1304	Type N Female	Low-Loss 300-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ANF-1406	Type N Female	Low-Loss 400-Series	Crimp	3.49	3.35	3.21	2.97	2.62
ANF-2400	Type N Female	Low-Loss 400-Series	Clamp	3.69	3.54	3.39	3.14	2.77
ANF-2602	Type N Female	Low-Loss 600-Series	Clamp	4.99	4.79	4.59	4.24	3.74
ANF-1610	Type N Female	Low-Loss 600-Series	Crimp	6.29	6.04	5.79	5.35	4.72
ANF-2904	Type N Female	Low-Loss 900-Series	Clamp	49.99	47.99	45.99	42.49	37.49
ARNJ-1700	Reverse Polarity Type N Jack	Low-Loss 195-Series, RG58	Crimp	4.19	4.02	3.85	3.56	3.14
ARNJ-1404	Reverse Polarity Type N Jack	Low-Loss 400-Series	Crimp	4.19	4.02	3.85	3.56	3.14
ARNP-1700	Reverse Polarity Type N Plug	Low-Loss 195-Series, RG58	Crimp	4.19	4.02	3.85	3.56	3.14
ARNP-1404	Reverse Polarity Type N Plug	Low-Loss 400-Series	Crimp	4.19	4.02	3.85	3.56	3.14

**RoHS BNC Coaxial Connectors, 50 Ohm**

BAC836A-58	BNC Male	RG58	Crimp	2.75	2.59	2.42	2.26	2.09
BAC836A-58P	BNC Male	RG58 Plenum	Crimp	3.50	3.29	3.08	2.87	2.66
BAC838-58	BNC Male	RG58	Twist On	4.25	3.99	3.74	3.49	3.23
BIF-83	BNC Male, Insulated	RG58	Crimp	4.25	3.99	3.74	3.49	3.23
BAC10A	BNC Male	RG58	Clamp	4.25	3.99	3.74	3.49	3.23
BAC547	BNC Male	RG142 / 223 / 400	Crimp	2.50	2.35	2.20	2.05	1.90
BAC836B-74	BNC Male	RG174 / 188 / 316	Crimp	4.75	4.46	4.18	3.90	3.61
BAC546	BNC Male, Right Angle	RG174 / 188 / 316	Crimp	4.75	4.46	4.18	3.90	3.61
BAC515	BNC Female	RG58	Crimp	4.25	3.99	3.74	3.49	3.23
BAC522	BNC Female Bulkhead	RG58	Crimp	5.25	4.93	4.62	4.31	3.99
BAC548	BNC Female	RG142	Crimp	4.75	4.46	4.18	3.90	3.61
BAC517	BNC Female	RG174 / 188 / 316	Crimp	4.25	3.99	3.74	3.49	3.23
BAC540	BNC Female	RG174 / 188 / 316	Crimp	4.00	3.76	3.52	3.28	3.04
ARBJ-1700	Reverse Polarity BNC Jack	Low-Loss 195-Series, RG58	Crimp	3.15	3.02	2.90	2.68	2.36
ARBP-1700	Reverse Polarity BNC Plug	Low-Loss 195-Series, RG58	Crimp	3.49	3.35	3.21	2.97	2.62
ARBP-1402	Reverse Polarity BNC Plug	Low-Loss 400-Series	Crimp	3.49	3.35	3.21	2.97	2.62

**RoHS BNC Coaxial Connectors, 75 Ohm**

BAC026	BNC Male	RG6	Twist On	3.25	3.05	2.86	2.67	2.47
BAC032	BNC Male	RG6	Crimp (2 Pc)	3.25	3.05	2.86	2.67	2.47
BAC029	BNC Male	RG6	Crimp (3 Pc)	3.25	3.05	2.86	2.67	2.47
BAC042	BNC Male	RG6-Q	Crimp	2.25	2.11	1.98	1.85	1.71
BAC024	BNC Male	RG59	Twist On	3.25	3.05	2.86	2.67	2.47
BAC027	BNC Male	RG59 (23 AWG C.C.)	Crimp	3.25	3.05	2.86	2.67	2.47
BAC027A	BNC Male	RG59 (20 AWG C.C.)	Crimp	3.25	3.05	2.86	2.67	2.47
BAC028	BNC Male	RG59 Plenum	Crimp (3 Pc)	3.25	3.05	2.86	2.67	2.47
BAC030	BNC Male	RG59	Crimp (2 Pc)	3.25	3.05	2.86	2.67	2.47
BAC031	BNC Male	RG59 Plenum	Crimp (2 Pc)	3.25	3.05	2.86	2.67	2.47
BAC033	BNC Male	RG59	Solder	4.25	3.99	3.74	3.49	3.23
BAC543	BNC Male, Right Angle	RG59	Crimp	4.75	4.46	4.18	3.90	3.61
BAC706	BNC Male, Right Angle	RG59/6	Crimp	5.75	5.40	5.06	4.72	4.37
BAC985	BNC Male, Right Angle	RG59/6	Twist On	5.75	5.40	5.06	4.72	4.37
BAC836A-59	BNC Male	RG59/6	Crimp	2.75	2.59	2.42	2.26	2.09
BAC551	BNC Male, Right Angle	RG179, RG187	Crimp	5.25	4.93	4.62	4.31	3.99
BAC836B-87	BNC Male	RG187/CTL	Crimp	2.75	2.59	2.42	2.26	2.09
BAC516	BNC Female	RG6	Crimp	3.95	3.71	3.48	3.24	3.00
BAC014	BNC Female	RG59	Twist On	3.95	3.71	3.48	3.24	3.00
BAC908-59	BNC Female	RG59/6	Crimp	3.95	3.71	3.48	3.24	3.00
BAC552	BNC Female Bulkhead	RG59	Crimp	5.25	4.93	4.62	4.31	3.99
BAC550	BNC Female Bulkhead	RG179	Crimp	4.00	3.76	3.52	3.28	3.04



More coaxial connectors are available  
See a complete list at  
[L-com.com/CoaxialConnectors](http://L-com.com/CoaxialConnectors)

Some Connectors are sold in 10-Packs.  
See website for details.  
Adapters are sold individually.

