


**Bulk Fiber Optic Cabling - Sold by the Meter**


L-com offers the most popular types of Simplex, Duplex, Breakout and Distribution cable. All available from stock in 1 meter intervals with a 25 meter minimum unless otherwise noted. Other cabling types are available by request. Jacket color of bulk cable may vary. **Note:** Bulk cable custom lengths are non-returnable.

**NOTE:**  
Cable measurements in meters.  
1m = 3.28 ft. Custom lengths are non-returnable.


SIMPLEX CABLE	✓RoHS Item #	Description	Outer Jacket	Price/m
	<ul style="list-style-type: none"> <li>Number of Fibers: 1</li> <li>Jacket Type: OFNR rated</li> <li>Operating Temperature: -40°C - +85°C</li> <li>Indoor Use</li> </ul> <p>Simplex cable is commonly used for short point to point patching.</p>	FOBOS1S-M FOBOM1S-M FOBOM2S-M	SM, 9/125 bulk simplex cable OM1, 62.5/125 bulk simplex cable OM2, 50/125 bulk simplex cable	Yellow Orange Orange
		<b>OM4 100 Gig Rated Simplex Bulk Cable, 50 Meter Minimum</b>		
	FOBOM4S-M	OM4, 100 Gig Rated 50/125 bulk simplex cable	Aqua	1.88







DUPLEX ZIPCORD	✓RoHS Item #	Description	Outer Jacket	Price/m
	<ul style="list-style-type: none"> <li>Number of Fibers: 2</li> <li>Jacket Type: Riser - OFNR rated</li> <li>Operating Temperature: -40°C - +85°C</li> <li>Zipcord can easily be split apart to create 2 simplex cords</li> <li>Indoor Use</li> </ul> <p>Zipcord is the common choice for building short duplex fiber runs or patch cords. It is the most flexible choice.</p>	FOBOS1Z-M FOBOM1Z-M FOBOM2Z-M FOBOM3Z-M	SM, 9/125 bulk duplex cable OM1, 62.5/125 bulk duplex cable OM2, 50/125 bulk duplex cable OM3, 10 Gig rated 50/125 bulk duplex cable	Yellow Orange Orange Aqua
		<b>OM4 100 Gig Rated Duplex Bulk Cable, 50 Meter Minimum</b>		
	FOBOM4Z-M	OM4, 100 Gig rated 50/125 bulk duplex cable	Aqua	2.80



BREAKOUT CABLE	✓RoHS Item #	Description	Outer Jacket	Price/m
	<ul style="list-style-type: none"> <li>Number of Fibers: 2, 4, 6, 12. Other fiber counts available by custom request</li> <li>Jacket: Plenum - OFNP rated</li> <li>Operating Temperature: -40°C - +85°C</li> <li>Indoor or Outdoor Use</li> </ul> <p>Breakout cable is user friendly because each fiber has its own jacket and aramid strength elements. Due to this, each fiber is extremely strong and rugged. Breakout fiber is also very stiff compared to distribution or zipcord.</p>	FOBOS1IB2-M FOBOM1B4-M FOBOS1IB6-M FOBOS1IB12-M FOBOM1IB2-M FOBOM1IB4-M FOBOM1IB6-M FOBOM1IB12-M FOBOM2IB2-M FOBOM2IB4-M FOBOM2IB6-M FOBOM2IB12-M FOBOM3IB2-M FOBOM3IB4-M FOBOM3IB6-M FOBOM3IB12-M	2 count SM, 9/125 bulk breakout cable 4 count SM, 9/125 bulk breakout cable 6 count SM, 9/125 bulk breakout cable 12 count SM, 9/125 bulk breakout cable 2 count OM1, 62.5/125 bulk breakout cable 4 count OM1, 62.5/125 bulk breakout cable 6 count OM1, 62.5/125 bulk breakout cable 12 count OM1, 62.5/125 bulk breakout cable 2 count OM2, 50/125 bulk breakout cable 4 count OM2, 50/125 bulk breakout cable 6 count OM2, 50/125 bulk breakout cable 12 count OM2, 50/125 bulk breakout cable 2 count OM3, 10 Gig Rated 50/125 bulk breakout cable 4 count OM3, 10 Gig Rated 50/125 bulk breakout cable 6 count OM3, 10 Gig Rated 50/125 bulk breakout cable 12 count OM3, 10 Gig Rated 50/125 bulk breakout cable	Yellow Yellow Yellow Yellow Orange Orange Orange Orange Orange Orange Orange Orange Aqua Aqua Aqua Aqua
		<b>OM4 100 Gig Rated Breakout Bulk Cable, 155 Meter Minimum</b>		
	FOBOM4IB2-M	2 count OM4, 100 Gig Rated 50/125 bulk breakout cable	Aqua	7.40
	FOBOM4IB4-M	4 count OM4, 100 Gig Rated 50/125 bulk breakout cable	Aqua	9.58
	FOBOM4IB6-M	6 count OM4, 100 Gig Rated 50/125 bulk breakout cable	Aqua	15.03
	FOBOM4IB12-M	12 count OM4, 100 Gig Rated 50/125 bulk breakout cable	Aqua	22.00



DISTRIBUTION CABLE	✓RoHS Item #	Description	Outer Jacket	Price/m
	<ul style="list-style-type: none"> <li>Number of Fibers: 6, 12, 24. Other fiber counts available by custom request</li> <li>Jacket: Plenum - OFNP rated</li> <li>Operating Temperature: 0°C - +80°C</li> </ul> <p>Distribution cable is more compact and flexible than breakout since each fiber is only protected by the 900 micron buffer.</p>	FOBSNGID6-M FOBSNGID12-M FOBSNGD24-M FOBOM1ID6-M FOBOM1ID12-M FOB625D24-M FOBOM2ID6-M FOBOM2ID12-M FOBS00D24-M FOBOM3ID6-M FOBOM3ID12-M FOBS01D24-M	6 count SM, 9/125 indoor bulk distribution cable 12 count SM, 9/125 indoor bulk distribution cable 24 count SM, 9/125 indoor/outdoor bulk distribution cable 6 count OM1, 62.5/125 indoor bulk distribution cable 12 count OM1, 62.5/125 indoor bulk distribution cable 24 count OM1, 62.5/125 indoor/outdoor bulk distribution cable 6 count OM2, 50/125 indoor bulk distribution cable 12 count OM2, 50/125 indoor bulk distribution cable 24 count OM2, 50/125 indoor/outdoor bulk distribution cable 6 count OM3, 10 Gig Rated 50/125 indoor bulk distribution cable 12 count OM3, 10 Gig Rated 50/125 indoor bulk distribution cable 24 count OM3, 10 Gig Rated 50/125 indoor/outdoor bulk dist. cable	Yellow Yellow Yellow Orange Orange Orange Orange Orange Orange Orange Orange Aqua Aqua Aqua
		<b>OM4 100 Gig Rated Distribution Cable, 155 Meter Minimum</b>		
	FOBOM4ID6-M	6 count OM4, 100 Gig Rated 50/125 indoor bulk distribution cable	Aqua	10.45
	FOBOM4ID12-M	6 count OM4, 100 Gig Rated 50/125 indoor bulk distribution cable	Aqua	18.45



**Latest news**  
Get the latest company and product news.  
[L-com.com/PressReleases](http://L-com.com/PressReleases)

