



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

**9/125**  
 L-com's single mode fiber optic patch cords and adapter cords are offered in both simplex and duplex configuration with OFNR Riser Rated jackets. All cables are 100% optically tested and utilize a PC or APC polish. Custom lengths and other connector types are available as are UPC polished assemblies. All cable measurements are in meters. 1m = 3.28 ft.

Item #	Description	1-9	10-24	25-99	100-249	250-499
<b>✓RoHS ST to ST Simplex Patch Cord, Single mode Fiber with OFNR Jacket</b>						
SFOST-01	SM Fiber Cable, ST / ST, 1.0m	10.00	9.40	8.80	8.20	7.60
SFOST-02	SM Fiber Cable, ST / ST, 2.0m	10.50	9.87	9.24	8.61	7.98
SFOST-03	SM Fiber Cable, ST / ST, 3.0m	11.00	10.34	9.68	9.02	8.36
SFOST-04	SM Fiber Cable, ST / ST, 4.0m	11.50	10.81	10.12	9.43	8.74
SFOST-05	SM Fiber Cable, ST / ST, 5.0m	12.00	11.28	10.56	9.84	9.12
<b>✓RoHS SC to SC Simplex Patch Cord, Single mode Fiber with OFNR Jacket</b>						
SFOSC-01	SM Fiber Cable, SC / SC, 1.0m	10.00	9.40	8.80	8.20	7.60
SFOSC-02	SM Fiber Cable, SC / SC, 2.0m	10.50	9.87	9.24	8.61	7.98
SFOSC-03	SM Fiber Cable, SC / SC, 3.0m	11.00	10.34	9.68	9.02	8.36
SFOSC-04	SM Fiber Cable, SC / SC, 4.0m	11.50	10.81	10.12	9.43	8.74
SFOSC-05	SM Fiber Cable, SC / SC, 5.0m	12.00	11.28	10.56	9.84	9.12
<b>✓RoHS FC to FC Simplex Patch Cord, Single mode Fiber with OFNR Jacket</b>						
SFOFC-01	SM Fiber Cable, FC / FC, 1.0m	10.00	9.40	8.80	8.20	7.60
SFOFC-02	SM Fiber Cable, FC / FC, 2.0m	10.50	9.87	9.24	8.61	7.98
SFOFC-03	SM Fiber Cable, FC / FC, 3.0m	11.00	10.34	9.68	9.02	8.36
SFOFC-04	SM Fiber Cable, FC / FC, 4.0m	11.50	10.81	10.12	9.43	8.74
SFOFC-05	SM Fiber Cable, FC / FC, 5.0m	12.00	11.28	10.56	9.84	9.12
<b>✓RoHS LC to LC Simplex Patch Cord, Single mode Fiber with OFNR Jacket</b>						
SFOLC-01	SM Fiber Cable, LC / LC, 1.0m	21.00	19.74	18.48	17.22	15.96
SFOLC-02	SM Fiber Cable, LC / LC, 2.0m	21.50	20.21	18.92	17.63	16.34
SFOLC-03	SM Fiber Cable, LC / LC, 3.0m	22.00	20.68	19.36	18.04	16.72
SFOLC-04	SM Fiber Cable, LC / LC, 4.0m	22.50	21.15	19.80	18.45	17.10
SFOLC-05	SM Fiber Cable, LC / LC, 5.0m	23.00	21.62	20.24	18.86	17.48
<b>✓RoHS ST to SC Simplex Adapter Cord, Single mode Fiber with OFNR Jacket</b>						
SFOST-SC-01	SM Fiber Cable, ST / SC, 1.0m	10.00	9.40	8.80	8.20	7.60
SFOST-SC-02	SM Fiber Cable, ST / SC, 2.0m	10.50	9.87	9.24	8.61	7.98
SFOST-SC-03	SM Fiber Cable, ST / SC, 3.0m	11.00	10.34	9.68	9.02	8.36
SFOST-SC-04	SM Fiber Cable, ST / SC, 4.0m	11.50	10.81	10.12	9.43	8.74
SFOST-SC-05	SM Fiber Cable, ST / SC, 5.0m	12.00	11.28	10.56	9.84	9.12
<b>✓RoHS ST to FC Simplex Adapter Cord, Single mode Fiber with OFNR Jacket</b>						
SFOST-FC-01	SM Fiber Cable, ST / FC, 1.0m	10.00	9.40	8.80	8.20	7.60
SFOST-FC-02	SM Fiber Cable, ST / FC, 2.0m	10.50	9.87	9.24	8.61	7.98
SFOST-FC-03	SM Fiber Cable, ST / FC, 3.0m	11.00	10.34	9.68	9.02	8.36
SFOST-FC-04	SM Fiber Cable, ST / FC, 4.0m	11.50	10.81	10.12	9.43	8.74
SFOST-FC-05	SM Fiber Cable, ST / FC, 5.0m	12.00	11.28	10.56	9.84	9.12
<b>✓RoHS SC to LC Simplex Adapter Cord, Single mode Fiber with OFNR Jacket</b>						
SFOSC-LC-01	SM Fiber Cable, SC / LC, 1.0m	15.00	14.10	13.20	12.30	11.40
SFOSC-LC-02	SM Fiber Cable, SC / LC, 2.0m	15.50	14.57	13.64	12.71	11.78
SFOSC-LC-03	SM Fiber Cable, SC / LC, 3.0m	16.00	15.04	14.08	13.12	12.16
SFOSC-LC-04	SM Fiber Cable, SC / LC, 4.0m	16.50	15.51	14.52	13.53	12.54
SFOSC-LC-05	SM Fiber Cable, SC / LC, 5.0m	17.00	15.98	14.96	13.94	12.92
<b>✓RoHS SC to SC Simplex Patch Cord, APC Single mode Fiber with OFNR Jacket</b>						
SFOSCA-01	SM Fiber Cable, SC / SC, 1.0m	12.00	11.28	10.56	9.84	9.12
SFOSCA-02	SM Fiber Cable, SC / SC, 2.0m	12.50	11.75	11.00	10.25	9.50
SFOSCA-03	SM Fiber Cable, SC / SC, 3.0m	13.00	12.22	11.44	10.66	9.88
SFOSCA-04	SM Fiber Cable, SC / SC, 4.0m	13.50	12.69	11.88	11.07	10.26
SFOSCA-05	SM Fiber Cable, SC / SC, 5.0m	14.00	13.16	12.32	11.48	10.64
<b>✓RoHS FC to FC Simplex Patch Cord, APC Single mode Fiber with OFNR Jacket</b>						
SFOFCA-01	SM Fiber Cable, FC / FC, 1.0m	12.50	11.75	11.00	10.25	9.50
SFOFCA-02	SM Fiber Cable, FC / FC, 2.0m	13.00	12.22	11.44	10.66	9.88
SFOFCA-03	SM Fiber Cable, FC / FC, 3.0m	13.50	12.69	11.88	11.07	10.26
SFOFCA-04	SM Fiber Cable, FC / FC, 4.0m	14.00	13.16	12.32	11.48	10.64
SFOFCA-05	SM Fiber Cable, FC / FC, 5.0m	14.50	13.63	12.76	11.89	11.02
<b>✓RoHS Dual SC to Dual SC Duplex Patch Cord, Single mode Fiber with OFNR Jacket</b>						
SFODSC-01	SM Fiber Cable, Dual SC / Dual SC, 1.0m	18.50	17.39	16.28	15.17	14.06
SFODSC-02	SM Fiber Cable, Dual SC / Dual SC, 2.0m	19.50	18.33	17.16	15.99	14.82
SFODSC-03	SM Fiber Cable, Dual SC / Dual SC, 3.0m	20.50	19.27	18.04	16.81	15.58
SFODSC-04	SM Fiber Cable, Dual SC / Dual SC, 4.0m	21.50	20.21	18.92	17.63	16.34
SFODSC-05	SM Fiber Cable, Dual SC / Dual SC, 5.0m	22.50	21.15	19.80	18.45	17.10
<b>✓RoHS Dual LC to Dual LC Clipped Duplex Patch Cord, Single mode Fiber with OFNR Jacket</b>						
SFODLC-CL-01	SM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 1.0m	31.00	29.14	27.28	25.42	23.56
SFODLC-CL-02	SM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 2.0m	32.00	30.08	28.16	26.24	24.32
SFODLC-CL-03	SM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 3.0m	33.00	31.02	29.04	27.06	25.08
SFODLC-CL-04	SM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 4.0m	34.00	31.96	29.92	27.88	25.84
SFODLC-CL-05	SM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 5.0m	35.00	32.90	30.80	28.70	26.60
SFODLC-CL-10	SM Fiber Cable, Dual Clipped LC / Dual Clipped LC, 10.0m	40.00	37.60	35.20	32.80	30.40

You can have custom fiber cables in as little as 48 hours. CALL 1-800-343-1455 NOW!

For other lengths and/or connector combinations please use our Product Configurator on our website [L-com.com](http://L-com.com) or contact our Sales or Customer Team. No minimum order requirements!



**RoHS status information**  
 listed on every product saves you time. [L-com.com/RoHS](http://L-com.com/RoHS)