



Item #	Description	1-9	10-24	25-99	100-249	250-499
<b>✓RoHS IP66/67 Harsh Environment Multimode or Single mode Duplex LC Cable Assemblies</b>						
L-com's IP66/67 rated Duplex LC cable assemblies are perfect for Industrial networks and harsh environments where protection from moisture, chemicals, corrosive gases and liquids is essential. These rugged assemblies feature robust outdoor rated cable, which stands up to hostile environments. Each assembly is 100% functionally tested and is covered by a one year manufacturer warranty. Accessories sold separately include a bulkhead style adapter where one side is designed for standard LC fiber cable connection and the other will accept the industrial LC connector. Additionally, caps for both the connector and bulkhead adapter are available.						
FODLC-IND-01	MM IP67 Fiber Cable, Dual LC / Dual LC, 1.0m	139.50	136.71	133.92	131.13	128.34
FODLC-IND-03	MM IP67 Fiber Cable, Dual LC / Dual LC, 3.0m	146.50	143.57	140.64	137.71	134.78
FODLC-IND-05	MM IP67 Fiber Cable, Dual LC / Dual LC, 5.0m	153.50	150.43	147.36	144.29	141.22
FODLC-IND-10	MM IP67 Fiber Cable, Dual LC / Dual LC, 10.0m	171.00	167.58	164.16	160.74	157.32
SFODLC-IND-01	SM IP67 Fiber Cable, Dual LC / Dual LC, 1.0m	153.50	150.43	147.36	144.29	141.22
SFODLC-IND-03	SM IP67 Fiber Cable, Dual LC / Dual LC, 3.0m	159.95	156.75	153.55	150.35	147.15
SFODLC-IND-05	SM IP67 Fiber Cable, Dual LC / Dual LC, 5.0m	166.50	163.17	159.84	156.51	153.18
SFODLC-IND-10	SM IP67 Fiber Cable, Dual LC / Dual LC, 10.0m	181.50	177.87	174.24	170.61	166.98
XLC-MM	MM IP67 Duplex LC Bulkhead Adapter	39.00	37.83	36.66	35.49	34.32
XLC-SM	SM IP67 Duplex LC Bulkhead Adapter	49.95	48.45	46.95	45.45	43.96
X-CAP	IP67 Duplex LC Cap with Chain for Bulkhead Receptacle	9.95	9.65	9.35	9.05	8.76
XPM-CAP2	IP67 Duplex LC Cap with Chain for Industrial Plugs	12.95	12.56	12.17	11.78	11.40

**Military Grade 62.5/125 Fiber Optic Patch Cables**

L-com's Military Grade fiber optic patch cables are built with specialized Military Tactical fiber cable that features impact and crush resistance characteristics which comply with Military requirements. Additionally, these robust assemblies are rated for operating temperatures of -55° to +85° Celsius. Three versions are available including Duplex ST, SC and LC styles. Our ST assemblies feature rust resistant stainless steel bodies and extra high force springs to ensure tight mating even when exposed to shock and vibration often encountered in the field under combat conditions.

**ST to ST Duplex Military Grade Multimode Fiber Optic Cables, 62.5/125 with Polyurethane Jacket**

FODSTMIL-01	MM Military Grade Fiber Cable, Dual ST / Dual ST, 1.0m	62.00	59.52	57.04	54.56	CALL
FODSTMIL-02	MM Military Grade Fiber Cable, Dual ST / Dual ST, 2.0m	67.00	64.32	61.64	58.96	CALL
FODSTMIL-03	MM Military Grade Fiber Cable, Dual ST / Dual ST, 3.0m	72.00	69.12	66.24	63.36	CALL
FODSTMIL-05	MM Military Grade Fiber Cable, Dual ST / Dual ST, 5.0m	82.00	78.72	75.44	72.16	CALL
FODSTMIL-10	MM Military Grade Fiber Cable, Dual ST / Dual ST, 10.0m	107.00	102.72	98.44	94.16	CALL

**✓RoHS SC to SC Duplex Military Grade Multimode Fiber Optic Cables, 62.5/125 with Polyurethane Jacket**

FODSCMIL-01	MM Military Grade Fiber Cable, Dual SC / Dual SC, 1.0m	29.00	27.84	26.68	25.52	CALL
FODSCMIL-02	MM Military Grade Fiber Cable, Dual SC / Dual SC, 2.0m	34.00	32.64	31.28	29.92	CALL
FODSCMIL-03	MM Military Grade Fiber Cable, Dual SC / Dual SC, 3.0m	39.00	37.44	35.88	34.32	CALL
FODSCMIL-05	MM Military Grade Fiber Cable, Dual SC / Dual SC, 5.0m	49.00	47.04	45.08	43.12	CALL
FODSCMIL-10	MM Military Grade Fiber Cable, Dual SC / Dual SC, 10.0m	74.00	71.04	68.08	65.12	CALL

**✓RoHS LC to LC Duplex Military Grade Multimode Fiber Optic Cables, 62.5/125 with Polyurethane Jacket**

FODLCMIL-01	MM Military Grade Fiber Cable, Dual LC / Dual LC, 1.0m	39.00	37.44	35.88	34.32	CALL
FODLCMIL-02	MM Military Grade Fiber Cable, Dual LC / Dual LC, 2.0m	44.00	42.24	40.48	38.72	CALL
FODLCMIL-03	MM Military Grade Fiber Cable, Dual LC / Dual LC, 3.0m	49.00	47.04	45.08	43.12	CALL
FODLCMIL-05	MM Military Grade Fiber Cable, Dual LC / Dual LC, 5.0m	59.00	56.64	54.28	51.92	CALL
FODLCMIL-10	MM Military Grade Fiber Cable, Dual LC / Dual LC, 10.0m	84.00	80.64	77.28	73.92	CALL

**Corning UniCam™ No Epoxy, No Polish Connectors - Fast and Easy Termination**

The UniCam connector is the ideal solution for all your field-installation multimode or single mode fiber optic connector requirements. The zero polish quick installation reduces the total installed cost of connection, making the UniCam connector cost-effective for all fiber applications. UniCam connectors are available in common connector configurations. Installation kit includes everything necessary to get started terminating ST, SC, FC and MT-RJ UniCam connectors.

FOC-9500050	Fiber Connector, UniCam ST Male, 62.5/125 Multimode	18.75	18.38	18.00	17.63	17.25
FOC-9505051	Fiber Connector, UniCam ST Male, 50/125 Multimode	19.25	18.86	18.48	18.09	17.71
FOC-9500040	Fiber Connector, UniCam SC Male, 62.5/125 Multimode	18.75	18.38	18.00	17.63	17.25
FOC-9505041	Fiber Connector, UniCam SC Male, 50/125 Multimode	18.75	18.38	18.00	17.63	17.25
FOC-9500099	Fiber Connector, UniCam LC Male, 62.5/125 Multimode	25.00	24.50	24.00	23.50	23.00
FOC-9505099	Fiber Connector, UniCam LC Male, 50/125 Multimode	25.00	24.50	24.00	23.50	23.00
FOC-9520051	Fiber Connector, UniCam ST SPC Male, Single mode	25.00	24.50	24.00	23.50	23.00
FOC-9520042	Fiber Connector, UniCam SC UPC Male, Single mode	26.50	25.97	25.44	24.91	24.38
FOC-9520099	Fiber Connector, UniCam LC UPC Male, Single mode	30.00	29.40	28.80	28.20	27.60
TKT-UNICAM	UniCam Tooling Kit for ST, SC, FC, MT-RJ, LC	799.00	783.02	767.04	751.06	735.08

**Miller® Fiber Optic Scribes - Diamond and Carbide Tips**

Two scribes are available for preparing fiber optic cable. The DS-90W is a professional tool utilizing a diamond tipped 90° wedge and retractable (pen-like) barrel. The CS-30W is an economical carbide tipped scribe for the more occasional user.

DS-90W	Diamond Fiber Optic Scribe, 90° Wedge	95.00	93.10	91.20	89.30	87.40
CS-30W	Carbide Fiber Optic Scribe, 30° Wedge	32.00	31.36	30.72	30.08	29.44

**Safety Glasses - A Must When Cutting or Scribing Fiber**

FOT-SG1	Safety Glasses	9.95	9.75	9.55	9.35	9.15
---------	----------------	------	------	------	------	------

**Fiber Optic Safety Kit - A Necessity When Terminating Fiber**

The FS-9500 is a must for personal protection during fiber termination. Included in the kit is a black rollup work mat which holds polishing plate in place and helps identify fiber splinters and a pair of quality safety glasses. Also included are a fiber scrap trash can, 1 splinter removal tweezer and 10 bifurcated cleaning swipes.

FS-9500	Fiber Safety Kit with Glasses	39.95	39.15	38.35	37.55	36.75
---------	-------------------------------	-------	-------	-------	-------	-------

For other lengths and/or connector combinations please use our Product Configurator on our website [L-com.com](http://L-com.com) or contact our Sales or Customer Team. No minimum order requirements!



**Custom design and manufacturing capabilities**

Our product design process takes you from concept to production. [L-com.com/Custom](http://L-com.com/Custom)