

Fiber Optic Pigtails

L-com's fiber optic pigtails provide a fast way to make factory terminations in the field. Factory terminated pigtails can easily be fusion or mechanically spliced to an existing fiber line. The jackets are available in all the standard colors and are sold individually rather than limiting you to pre-packaged quantities. All connectors utilize PC polish and all jackets are OFNR rated. Standard connectors include LC, SC, FC and ST. Standard lengths are 1.0, 2.0 and 3.0 meters. Standard jacket sizes include 900um, 2mm and 3mm. Please refer to L-com.com for complete part listing. Order online today!

- Available individually instead of pre-packaged quantities
- Connector options include LC, SC, FC, ST
- Common jacket sizes including 900um, 2mm, 3mm
- Up to 12 colors available (see L-com.com for all options)
- Available in single mode or multimode

Explanation of FPT Series Part Numbers

FPT9OM2- - -1

Series


Cable Size
9=900um
2=2mm
3=3mm

Mode
SNG=9/125
OM1=62.5/125
OM2=50/125
OM3=50/125 10G


Length
1=1.0m
2=2.0m
3=3.0m

Connector Style

Cable Color




LC




ST

Listings on L-com.com




FC

Listings on L-com.com



SC

Listings on L-com.com



BLK
GRY
YLV
ORG
BLU
GRN
RED
VIO
BRN
AQU
ROS
WHT

Item #	Description	Color	1-9	10-24	25-99	100-249
--------	-------------	-------	-----	-------	-------	---------

Single mode, 9/125 Fiber Optic Pigtails with 900um OFNR Jacket

FPT9SNG-LC-__-1	9/125 Rated Single mode Fiber Optic Pigtail, 900um, 1.0m		4.29	3.95	3.60	3.26
FPT9SNG-LC-__-2	9/125 Rated Single mode Fiber Optic Pigtail, 900um, 2.0m		4.63	4.26	3.89	3.52
FPT9SNG-LC-__-3	9/125 Rated Single mode Fiber Optic Pigtail, 900um, 3.0m		4.97	4.57	4.17	3.78

OM1, 62.5/125 Fiber Optic Pigtails with 900um OFNR Jacket

FPT9OM1-LC-__-1	62.5/125 Rated, OM1 Fiber Optic Pigtail, 900um, 1.0m		4.11	3.78	3.45	3.12
FPT9OM1-LC-__-2	62.5/125 Rated, OM1 Fiber Optic Pigtail, 900um, 2.0m		4.53	4.17	3.81	3.44
FPT9OM1-LC-__-3	62.5/125 Rated, OM1 Fiber Optic Pigtail, 900um, 3.0m		4.95	4.55	4.16	3.76

OM2, 50/125 Fiber Optic Pigtails with 900um OFNR Jacket

FPT9OM2-LC-__-1	50/125 Rated, OM2 Fiber Optic Pigtail, 900um, 1.0m		4.11	3.78	3.45	3.12
FPT9OM2-LC-__-2	50/125 Rated, OM2 Fiber Optic Pigtail, 900um, 2.0m		4.53	4.17	3.81	3.44
FPT9OM2-LC-__-3	50/125 Rated, OM2 Fiber Optic Pigtail, 900um, 3.0m		4.95	4.55	4.16	3.76

OM3, 10 Gig rated 50/125 LC Fiber Optic Pigtails with 900um OFNR Jacket

FPT9OM3-LC-ORG-1	50/125 10 Gig Rated, OM3 Fiber Optic Pigtail, 900um, 1.0m	Orange	4.47	4.11	3.75	3.40
FPT9OM3-LC-ORG-2	50/125 10 Gig Rated, OM3 Fiber Optic Pigtail, 900um, 2.0m	Orange	5.26	4.84	4.42	4.00
FPT9OM3-LC-ORG-3	50/125 10 Gig Rated, OM3 Fiber Optic Pigtail, 900um, 3.0m	Orange	6.05	5.57	5.08	4.60

Single mode, 9/125 Fiber Optic Pigtails with 2mm OFNR Jacket

Only available in the following colors: BLU, GRN, BRN, WHT, RED & YLV.

FPT2SNG-LC-__-1	9/125 Rated, Single mode Fiber Optic Pigtail, 2mm, 1.0m		4.29	3.95	3.60	3.26
FPT2SNG-LC-__-2	9/125 Rated, Single mode Fiber Optic Pigtail, 2mm, 2.0m		4.63	4.26	3.89	3.52
FPT2SNG-LC-__-3	9/125 Rated, Single mode Fiber Optic Pigtail, 2mm, 3.0m		4.97	4.57	4.17	3.78

OM1, 62.5/125 Fiber Optic Pigtails with 2mm OFNR Jacket

FPT2OM1-LC-ORG-1	62.5/125 Rated, OM1 Fiber Optic Pigtail, 2mm, 1.0m	Orange	4.16	3.83	3.49	3.16
FPT2OM1-LC-ORG-2	62.5/125 Rated, OM1 Fiber Optic Pigtail, 2mm, 2.0m	Orange	4.63	4.26	3.89	3.52
FPT2OM1-LC-ORG-3	62.5/125 Rated, OM1 Fiber Optic Pigtail, 2mm, 3.0m	Orange	5.11	4.70	4.29	3.88

OM2, 50/125 Fiber Optic Pigtails with 2mm OFNR Jacket

FPT2OM2-LC-ORG-1	50/125 Rated, OM2 Fiber Optic Pigtail, 2mm, 1.0m	Orange	4.16	3.83	3.49	3.16
FPT2OM2-LC-ORG-2	50/125 Rated, OM2 Fiber Optic Pigtail, 2mm, 2.0m	Orange	4.63	4.26	3.89	3.52
FPT2OM2-LC-ORG-3	50/125 Rated, OM2 Fiber Optic Pigtail, 2mm, 3.0m	Orange	5.11	4.70	4.29	3.88

Single mode, 9/125 Fiber Optic Pigtails with 3mm OFNR Jacket

Only available in the following colors BLU, GRN, BRN, WHT, RED, & YLV.

FPT3SNG-LC-__-1	9/125 Rated, Single mode Fiber Optic Pigtail, 3mm, 1.0m		4.29	3.95	3.60	3.26
FPT3SNG-LC-__-2	9/125 Rated, Single mode Fiber Optic Pigtail, 3mm, 2.0m		4.63	4.26	3.89	3.52
FPT3SNG-LC-__-3	9/125 Rated, Single mode Fiber Optic Pigtail, 3mm, 3.0m		4.97	4.57	4.17	3.78

OM1, 62.5/125 Fiber Optic Pigtails with 3mm OFNR Jacket

Only available in the following colors: BLU, ORG, GRN, RED & YLV.

FPT3OM1-LC-__-1	62.5/125 Rated, OM1 Fiber Optic Pigtail, 3mm, 1.0m		4.16	3.83	3.49	3.16
FPT3OM1-LC-__-2	62.5/125 Rated, OM1 Fiber Optic Pigtail, 3mm, 2.0m		4.63	4.26	3.89	3.52
FPT3OM1-LC-__-3	62.5/125 Rated, OM1 Fiber Optic Pigtail, 3mm, 3.0m		5.11	4.70	4.29	3.88


OM2, 50/125 Fiber Optic Pigtails with 3mm OFNR Jacket

Only available in the colors of ORG & GRY.

FPT3OM2-LC-__-1	50/125 Rated, OM2 Fiber Optic Pigtail, 3mm, 1.0m		4.16	3.83	3.49	3.16
FPT3OM2-LC-__-2	50/125 Rated, OM2 Fiber Optic Pigtail, 3mm, 2.0m		4.63	4.26	3.89	3.52
FPT3OM2-LC-__-3	50/125 Rated, OM2 Fiber Optic Pigtail, 3mm, 3.0m		5.11	4.70	4.29	3.88

OM3, 50/125 10 Gig Fiber Optic Pigtails with 3mm OFNR Jacket

FPT3OM3-LC-AQU-1	50/125 10 Gig OM3 Fiber Optic Pigtail, 3mm, 1.0m	Aqua	4.55	4.19	3.82	3.46
FPT3OM3-LC-AQU-2	50/125 10 Gig OM3 Fiber Optic Pigtail, 3mm, 2.0m	Aqua	5.42	4.99	4.55	4.12
FPT3OM3-LC-AQU-3	50/125 10 Gig OM3 Fiber Optic Pigtail, 3mm, 3.0m	Aqua	6.29	5.79	5.28	4.78



To see our entire product offering go to...L-com.com

