



Item #	Description	List Price
--------	-------------	------------

MPO Multifiber Ribbon 62.5 Multimode Cable and Fanout Assemblies

These multifiber assemblies provide advantages in size offering 12 times the density when compared to the same size SC connector. Factory terminated and tested, this system provides significant installation time savings. A push-pull design is utilized for easy mating and removal. Fanout assemblies are ideal for making connections within rack mounted or wall mounted fiber enclosures that utilize single fiber connectors.

RoHS 6 or 12 MPO Female Fiber Ribbon 62.5 Multimode Cable with OFNR Jacket

MTPF06-25	6 Fiber Ribbon Cable, MPO Female / Female, 25.0m	129.00
MTPF06-50	6 Fiber Ribbon Cable, MPO Female / Female, 50.0m	199.00
MTPF06-100	6 Fiber Ribbon Cable, MPO Female / Female, 100.0m	349.00
MTPF12-25	12 Fiber Ribbon Cable, MPO Female / Female, 25.0m	159.00
MTPF12-50	12 Fiber Ribbon Cable, MPO Female / Female, 50.0m	249.00
MTPF12-100	12 Fiber Ribbon Cable, MPO Female / Female, 100.0m	429.00

RoHS 6 or 12 MPO Male ST Fiber Ribbon 62.5 Multimode Fanout Cable with OFNR Jacket

MTPM06-ST-05	6 Fiber Ribbon Fanout Cable, MPO Male / ST Male, 5.0m	75.00
MTPM06-ST-10	6 Fiber Ribbon Fanout Cable, MPO Male / ST Male, 10.0m	89.00
MTPM12-ST-05	12 Fiber Ribbon Fanout Cable, MPO Male / ST Male, 5.0m	110.00
MTPM12-ST-10	12 Fiber Ribbon Fanout Cable, MPO Male / ST Male, 10.0m	129.00

RoHS 6 or 12 MPO Male SC Fiber Ribbon 62.5 Multimode Fanout Cable with OFNR Jacket

MTPM06-SC-05	6 Fiber Ribbon Fanout Cable, MPO Male / SC Male, 5.0m	75.00
MTPM06-SC-10	6 Fiber Ribbon Fanout Cable, MPO Male / SC Male, 10.0m	89.00
MTPM12-SC-05	12 Fiber Ribbon Fanout Cable, MPO Male / SC Male, 5.0m	110.00
MTPM12-SC-10	12 Fiber Ribbon Fanout Cable, MPO Male / SC Male, 10.0m	129.00

RoHS 6 or 12 MPO Male LC Fiber Ribbon 62.5 Multimode Fanout Cable with OFNR Jacket

MTPM06-LC-01	6 Fiber Ribbon Fanout Cable, MPO Male / LC Male, 1.0m	75.00
MTPM06-LC-05	6 Fiber Ribbon Fanout Cable, MPO Male / LC Male, 5.0m	86.00
MTPM06-LC-10	6 Fiber Ribbon Fanout Cable, MPO Male / LC Male, 10.0m	100.00
MTPM12-LC-01	12 Fiber Ribbon Fanout Cable, MPO Male / LC Male, 1.0m	110.00
MTPM12-LC-05	12 Fiber Ribbon Fanout Cable, MPO Male / LC Male, 5.0m	125.00
MTPM12-LC-10	12 Fiber Ribbon Fanout Cable, MPO Male / LC Male, 10.0m	144.00

Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
--------	-------------	-------	-----	-------	-------	---------	---------

RoHS Coupler for MPO Connectors - Mates Two MPOs

Note: Use of this coupler requires one of the two mating connectors to have alignment pins.

FOA-012	Coupler for 4, 6, 8 or 12 Port Ferrule MPO Connectors		18.95	18.19	17.43	16.11	14.21
---------	---	--	-------	-------	-------	-------	-------

RoHS MPO Cassettes

FSP-MPO-SC12-OM1	MPO Cassette 1-MPO-M/ 12 SC OM1	Beige	274.98	263.98	252.98	241.98	230.98
FSP-MPO-SC12-OM2	MPO Cassette 1-MPO-M/ 12 SC OM2	Beige	274.98	263.98	252.98	241.98	230.98
FSP-MPO-SC12-OM3	MPO Cassette 1-MPO-M/ 12 SC OM3	Aqua	284.98	273.58	262.18	250.78	239.38
FSP-MPO-SC12-OS1	MPO Cassette 1-MPO-M/ 12 SC OS1	Blue	294.98	283.18	271.38	259.58	247.78
FSP-MPO-LC24-OM1	MPO Cassette 2-MPO-M/ 24 LC OM1	Beige	497.98	478.06	458.14	438.22	418.30
FSP-MPO-LC24-OM2	MPO Cassette 1-MPO-M/ 24 LC OM2	Beige	497.98	478.06	458.14	438.22	418.30
FSP-MPO-LC24-OM3	MPO Cassette 2-MPO-M/ 24 LC OM3	Aqua	514.98	494.38	473.78	453.18	432.58
FSP-MPO-LC24-OS1	MPO Cassette 2-MPO-M/ 24 LC OS1	Blue	529.98	508.78	487.58	466.38	445.18

Item #	Description	List Price
--------	-------------	------------

RoHS Multimode (62.5/125) Loopbacks - Utilizing SC, LC, FC and MT-RJ Connectors

These handy assemblies are useful in a number of test applications. A generous yet manageable fiber loop virtually eliminates bend loss. FC Loopbacks do not contain a clip. Custom configurations will be considered in modest minimums. Please contact our sales representatives for assistance.

FOL-SC	Fiber Loopback, SC, 62.5/125	12.95
FOL-LC	Fiber Loopback, LC, 62.5/125	14.95
FOL-FC	Fiber Loopback, FC, 62.5/125	12.95
FOL-MTRJ	Fiber Loopback, MT-RJ, 62.5/125	12.95
FOL-MTRJ-NP	Fiber Loopback, MT-RJ, 62.5/125, No Pins	11.95

RoHS Multimode (50/125) Loopbacks - Utilizing SC, LC, FC and MT-RJ Connectors

FOL50-SC	Fiber Loopback, SC, 50/125	12.95
FOL50-LC	Fiber Loopback, LC, 50/125	14.95
FOL50-FC	Fiber Loopback, FC, 50/125	12.95
FOL50-MTRJ	Fiber Loopback, MT-RJ, 50/125	12.95
FOL50-MTRJ-NP	Fiber Loopback, MT-RJ, 50/125, No Pins	11.95

RoHS Single mode (9/125) Loopbacks - Utilizing FC, MU, LC and MT-RJ Connectors

SFOL-FC	Fiber Loopback, FC, 9/125	13.95
SFOL-MU	Fiber Loopback, MU, 9/125	29.00
SFOL-LC	Fiber Loopback, LC, 9/125	18.95
SFOL-MTRJ	Fiber Loopback, MT-RJ, 9/125	13.95
SFOL-MTRJ-NP	Fiber Loopback, MT-RJ, 9/125, No Pins	12.95

"You guys really do a great job. Your inventory and prices are very complete and competitive. I have never come to your site and left because I could not find it or because the prices were bad." - Jason Paige, Information Technology, Integral Capital Partners