

| Item # | Description | List Price |
|---|--|------------|
| ✓RoHS 19 inch (48.3cm) Rack Mounted Fiber Enclosures - For Splice Trays and Fiber Patch Panels | | |
| FE-RM1U12PSP | Fiber Enclosure Rack Mount, 1U, with 3 FSP Series Sub-Panel Openings | 179.98 |
| FE-RM2U24PSP | Fiber Enclosure Rack Mount, 2U, with 4 FSP Series Sub-Panel Openings | 204.98 |
| FE-RM3U48PSP | Fiber Enclosure Rack Mount, 3U, with 8 FSP Series Sub-Panel Openings | 229.98 |
| FE-RM4U72PSP | Fiber Enclosure Rack Mount 4U, with 12 FSP Series Sub-Panel Openings | 244.98 |






| | | |
|---|--|-------|
| ✓RoHS Wall Mounted Fiber Enclosures - To Mount Splice Trays and Fiber Patch Panels | | |
| FE-WM12PP | Fiber Enclosure Wall Mount, with 2 FSP Series Sub-Panel Openings | 81.98 |
| FE-WM24PP | Fiber Enclosure Wall Mount, with 4 FSP Series Sub-Panel Openings | 82.98 |

| | | |
|---|--|-------|
| ✓RoHS Splice Trays for Fiber Splices - Terminations and Distribution in Fiber Enclosures | | |
| FE-ST7MC | Fiber Enclosure Splice Tray, 7 in (17.8 cm) with Metal Cover | 19.99 |
| FE-ST7PC | Fiber Enclosure Splice Tray, 7 in (17.8 cm) with Lexan® Cover | 15.99 |
| FE-ST875MC | Fiber Enclosure Splice Tray, 8.75 in (22.2 cm) with Metal Cover | 26.99 |
| FE-ST875PC | Fiber Enclosure Splice Tray, 8.75 in (22.2 cm) with Lexan® Cover | 22.99 |

| Item # | Description | 1-9 | 10-24 | 25-99 | 100-249 |
|--|--|--------|--------|--------|---------|
| ✓RoHS Sub-Panels used to Populate FSP Series Patch Panels, FE & FSP DIN Rail Mount Enclosures | | | | | |
| FSP-BNK | Blank Sub-Panel | 11.98 | 11.50 | 11.02 | 10.54 |
| FSP-SCMTLC-BNK | Blank Sub-Panel with 6 SC Simplex/MT-RJ/LC Duplex Openings | 11.98 | 11.50 | 11.02 | 10.54 |
| FSP-MTRJ | Fiber Sub-Panel, 6 MT-RJ Couplers | 35.98 | 33.10 | 30.22 | 27.34 |
| FSP-SC-APC | Fiber Sub-Panel, 6 APC SC Simplex Couplers, Ceramic Sleeve | 71.98 | 66.22 | 60.46 | 54.70 |
| FSP-LCD6-BR | Fiber Sub-Panel, 6 LC Duplex Couplers, Bronze Sleeve | 39.98 | 36.78 | 33.58 | 30.38 |
| FSP-LCD6-CR | Fiber Sub-Panel, 6 LC Duplex Couplers, Ceramic Sleeve | 51.98 | 47.82 | 43.66 | 39.50 |
| FSP-SC-BR | Fiber Sub-Panel, 6 SC Simplex Couplers, Bronze Sleeve | 35.98 | 33.10 | 30.22 | 27.34 |
| FSP-SC-CR | Fiber Sub-Panel, 6 SC Simplex Couplers, Ceramic Sleeve | 44.98 | 41.38 | 37.78 | 34.18 |
| FSP-STFC-BNK | Blank Sub-Panel with 6 ST/FC Simplex Openings | 11.98 | 11.50 | 11.02 | 10.54 |
| FSP-FC-APC | Fiber Sub-Panel, 6 APC FC Simplex Couplers, Ceramic Sleeve | 101.98 | 93.82 | 85.66 | 77.50 |
| FSP-FC-BR | Fiber Sub-Panel, 6 FC Couplers, Bronze Sleeve | 53.98 | 49.66 | 45.34 | 41.02 |
| FSP-FC-CR | Fiber Sub-Panel, 6 FC Couplers, Ceramic Sleeve | 68.98 | 63.46 | 57.94 | 52.42 |
| FSP-ST-BR | Fiber Sub-Panel, 6 ST Couplers, Bronze Sleeve | 32.98 | 30.34 | 27.70 | 25.06 |
| FSP-ST-CR | Fiber Sub-Panel, 6 ST Couplers, Ceramic Sleeve | 47.98 | 44.14 | 40.30 | 36.46 |
| FSP-SCDLCQ6-BNK | Blank Sub-Panel with 6 SC Duplex/LC Quad Openings | 14.98 | 14.38 | 13.78 | 13.18 |
| FSP-LCQ6-BR | Fiber Sub-Panel, 6 LC Duplex Couplers, Bronze Sleeve | 110.68 | 101.83 | 92.97 | 84.12 |
| FSP-LCQ6-CR | Fiber Sub-Panel, 6 LC Duplex Couplers, Ceramic Sleeve | 134.68 | 123.91 | 113.13 | 102.36 |
| FSP-SCD6-APC | Fiber Sub-Panel, 6 SC Duplex Couplers, Ceramic Sleeve | 125.98 | 115.90 | 105.82 | 95.74 |
| FSP-SCD6-BR | Fiber Sub-Panel, 6 SC Duplex Couplers, Bronze Sleeve | 47.98 | 44.14 | 40.30 | 36.46 |
| FSP-SCD6-CR | Fiber Sub-Panel, 6 SC Duplex Couplers, Ceramic Sleeve | 62.98 | 57.94 | 52.90 | 47.86 |

| | | | | | |
|---|--|-------|-------|-------|-------|
| ✓RoHS Fiber Sub-Panel with 6 LC Keyed Multimode Couplers | | | | | |
| FSP-LCK-MM-PNK | Fiber Panel, 6 LC Keyed Multimode, Pink | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-WHT | Fiber Panel, 6 LC Keyed Multimode, White | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-YLW | Fiber Panel, 6 LC Keyed Multimode, Yellow | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-RED | Fiber Panel, 6 LC Keyed Multimode, Red | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-ORG | Fiber Panel, 6 LC Keyed Multimode, Orange | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-VLT | Fiber Panel, 6 LC Keyed Multimode, Violet | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-GRY | Fiber Panel, 6 LC Keyed Multimode, Gray | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-CBT | Fiber Panel, 6 LC Keyed Multimode, Cobalt | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-BRN | Fiber Panel, 6 LC Keyed Multimode, Brown | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-TRQ | Fiber Panel, 6 LC Keyed Multimode, Turquoise | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-MAG | Fiber Panel, 6 LC Keyed Multimode, Magenta | 99.98 | 95.98 | 91.98 | 87.98 |
| FSP-LCK-MM-OLV | Fiber Panel, 6 LC Keyed Multimode, Olive | 99.98 | 95.98 | 91.98 | 87.98 |

| | | |
|---|---|-------|
| ✓RoHS Plunger and Grommet Kit for FSP Series Sub-Panels - Pkg/50 | | |
| FSP-FASTENERS | Plunger and Grommet Kit for FSP Series Sub-Panels, Pkg/50 | 24.98 |



Tip *Fiber enclosures secure sub-panels and cables*

STEP 1

Install snap-in sub-panel with couplers.

STEP 2

Prepare distribution cable for installation on rear of panel by sliding tray out of case, either from the front or rear.

STEP 3

Attach feed cables to couplers on rear of panel.

STEP 4

Route and attach patching jumpers to couplers on front of panel.

STEP 5

Slide tray back into case.

STEP 6

Close cover on unit.

To see our entire product offering go to... L-com.com