





Server Cabinet	Security Cabinet	Network Cabinet
 <ul style="list-style-type: none"> <li>Fully vented front and split rear doors</li> <li>Fully vented top</li> <li>Temperature sensor</li> <li>Cable management</li> <li>Power distribution</li> <li>Cage nut rackrail</li> <li>Hardware</li> <li>Other options available</li> </ul> <p><b>WMRK Series</b></p>	 <ul style="list-style-type: none"> <li>Fully welded construction, open sides</li> <li>2,500 lb (1136.4kg) weight capacity</li> <li>Seismic certified (1994 UBC for seismic zone 4) for protecting 1,000 lbs (454.5kg) of essential equipment when used in conjunction with the WRK-Z4 brackets</li> <li>Generous 24.25" (61.6cm) OD width provides room for cables</li> <li>2 extra-wide pairs of 10-32 threaded rackrail standard</li> <li>Grounding and bonding stud installed in base</li> </ul> <p><b>WRK Series</b></p>	 <ul style="list-style-type: none"> <li>30" (76.2cm) OD width, 31.5" (80cm), 36" (91.4cm) and 42" (106.7cm) OD depth</li> <li>Fully welded construction provides a 2,500 lb (1136.4kg) weight capacity</li> <li>Seismic certified (UBC 1997 &amp; CBC 1998 Zone 4; IBC 2000, IBC 2003, ASCE7-01, NFPA 5000 Seismic Use Group III) for protecting 750 lbs (340.9kg) of essential equipment when used in conjunction with the MRK-Z4 brackets</li> <li>Vented rear door standard</li> <li>.125" (0.3cm) thick structural steel internal braces include 100 rack screws</li> <li>Grounded and bonding stud installed in base</li> </ul> <p><b>DRK Series</b></p>

Item #	Racking Height	Overall Height	Shipping Weight	1-9	10-24	25-49	100-249
<b>✓RoHS 36-42" (91.4cm - 106.7cm) Outside Depth Server Cabinets</b>							
WMRK-2436SVR	42" (106.7cm) (24 Space)	48.63" (123.5cm)	270 lbs (122.7kg)	2447.54	2398.59	2300.69	CALL
WMRK-2436SVR-AB	42" (106.7cm) (24 Space)	48.63" (123.5cm)	205 lbs (93.2kg)	1950.07	1911.07	1833.07	CALL
WMRK-4236SVR	73.50" (186.7cm) (42 Space)	80.07" (203.4cm)	230 lbs (122.7kg)	2736.06	2681.34	2571.90	CALL
WMRK-4236SVR-AB	73.50" (186.7cm) (42 Space)	80.07" (203.4cm)	165 lbs (104.5kg)	2089.35	2047.56	1963.99	CALL
WMRK-4242SVR	73.50" (186.7cm) (42 Space)	80.07" (203.4cm)	245 lbs (111.4kg)	2915.15	2856.85	2740.24	CALL
WMRK-4242SVR-AB	73.50" (186.7cm) (42 Space)	80.07" (203.4cm)	180 lbs (81.8kg)	2193.82	2104.27	1678.94	CALL
<b>✓RoHS 27.5" (69.9cm) Outside Depth 25.75" (65.4cm) Stand Alone, Non-Gangable Network Enclosures with Side Panels</b>							
WRKSA-2427	42" (106.7cm) (24 Space)	48.13" (122.3cm)	146 lbs (66.4kg)	956.60	937.47	899.20	717.45
WRKSA-3727	64.75" (164.5cm) (37 Space)	70.88" (180.0cm)	202 lbs (91.8kg)	1089.80	1068.00	1024.41	817.35
WRKSA-4027	70" (177.8cm) (40 Space)	76.13" (193.4cm)	212 lbs (96.4kg)	1162.43	1139.18	1092.68	871.82
WRKSA-4427	77" (195.6cm) (44 Space)	83.13" (211.2cm)	226 lbs (102.7kg)	1198.79	1174.81	1126.86	899.09
WRKSA-4427LRD*	77" (195.6cm) (44 Space)	83.13" (211.2cm)	195 lbs (88.6kg)	1089.80	1068.00	1024.41	817.35
*Enclosure does not include rear door							
<b>✓RoHS 32.5" (82.6cm) Outside Depth 30.75" (78.1cm) Stand Alone, Non-Gangable Network Enclosures with Side Panels</b>							
WRKSA-2432	42" (106.7cm) (24 Space)	48.13" (122.3cm)	164 lbs (74.5kg)	1041.35	1020.52	978.87	781.01
WRKSA-3732	64.75" (164.5cm) (37 Space)	70.88" (180.0cm)	218 lbs (99.1kg)	1162.43	1139.18	1092.68	871.82
WRKSA-4032	70" (177.8cm) (40 Space)	76.13" (193.4cm)	234 lbs (106.4kg)	1186.68	1162.95	1115.48	890.01
WRKSA-4432	77" (195.6cm) (44 Space)	83.13" (211.2cm)	250 lbs (113.6kg)	1295.65	1269.74	1217.91	971.74
WRKSA-4432LRD*	77" (195.6cm) (44 Space)	83.13" (211.2cm)	212 lbs (96.4kg)	1186.68	1162.95	1115.48	890.01
*Enclosure does not include rear door							
<b>✓RoHS 27.5" (69.9cm) Outside Depth 25.75" (65.4cm) Gangable Security/Data Cabinet Enclosures without Side Panels</b>							
WRK-2427	42" (106.7cm) (24 Space)	48.13" (122.3cm)	124 lbs (56.4kg)	932.36	913.71	876.42	699.27
WRK-3727	64.75" (164.5cm) (37 Space)	70.88" (180.0cm)	160 lbs (72.7kg)	1053.46	1032.39	990.25	790.10
WRK-4027	70" (177.8cm) (40 Space)	76.13" (193.4cm)	168 lbs (76.4kg)	1126.15	1103.63	1058.58	844.61
WRK-4427	77" (195.6cm) (44 Space)	83.13" (211.2cm)	176 lbs (80.0kg)	1162.43	1139.18	1092.68	871.82
WRK-4427LRD*	77" (195.6cm) (44 Space)	83.13" (211.2cm)	152 lbs (69.1kg)	1053.46	1032.39	990.25	790.10
*Enclosure does not include rear door							
<b>✓RoHS 32.5" (82.6cm) Outside Depth 30.75" (78.1cm) Gangable Security/Data Cabinet Enclosures without Side Panels</b>							
WRK-2432	42" (106.7cm) (24 Space)	48.13" (122.3cm)	138 lbs (62.7kg)	992.96	973.10	933.38	744.72
WRK-3732	64.75" (164.5cm) (37 Space)	70.88" (180.0cm)	178 lbs (80.9kg)	1101.93	1079.89	1035.81	826.45
WRK-4032	70" (177.8cm) (40 Space)	76.13" (193.4cm)	184 lbs (83.6kg)	1150.34	1127.33	1081.32	862.75
WRK-4432	77" (195.6cm) (44 Space)	83.13" (211.2cm)	181 lbs (82.3kg)	1198.79	1174.81	1126.86	899.09
WRK-4432LRD*	77" (195.6cm) (44 Space)	83.13" (211.2cm)	161 lbs (73.2kg)	1089.80	1068.00	1024.41	817.35
*Enclosure does not include rear door							
<b>✓RoHS DRK Series 31.5" (80.0cm), 36" (91.4cm) and 42" (106.7cm) Networking Cabinet, Deep Enclosures with Vented Rear Door</b>							
DRK19-44-31	77" (195.6cm) (44 Space)	83.50" (212.1cm)	195 lbs (88.6kg)	1732.68	1698.03	1628.72	1299.51
DRK19-44-31PRO	77" (195.6cm) (44 Space)	83.50" (212.1cm)	195 lbs (88.6kg)	1811.45	1775.22	1702.76	1358.59
DRK19-44-36	77" (195.6cm) (44 Space)	83.50" (212.1cm)	220 lbs (100.0kg)	1919.13	1880.75	1803.98	1439.35
DRK19-44-36PRO	77" (195.6cm) (44 Space)	83.50" (212.1cm)	220 lbs (100.0kg)	1997.80	1957.84	1877.93	1498.35
DRK19-44-42	77" (195.6cm) (44 Space)	83.50" (212.1cm)	240 lbs (109.1kg)	2131.15	2088.53	2003.28	1598.36
DRK19-44-42PRO	77" (195.6cm) (44 Space)	83.50" (212.1cm)	240 lbs (109.1kg)	2209.23	2165.05	2076.68	1656.92
<b>✓RoHS R4CN Series 19" (48.3cm) Relay and 4 Post Universal Rack Enclosures with Cage Nut Rackrails</b>							
R4CN-4524B	78.75" (200.0cm) (45 Space)	84.22" (213.9cm)	72 lbs (32.7kg)	690.53	676.72	649.10	517.90
R4CN-4530B	78.75" (200.0cm) (45 Space)	84.22" (213.9cm)	85 lbs (38.6kg)	842.86	826.00	792.29	632.14
R4CN-4536B	78.75" (200.0cm) (45 Space)	84.22" (213.9cm)	78 lbs (35.5kg)	913.94	895.66	859.10	685.46
R4CN-5124B	91" (231.1cm) (52 Space)	96.47" (245.0cm)	76 lbs (34.5kg)	748.92	733.94	703.98	561.69
R4CN-5130B	91" (231.1cm) (52 Space)	96.47" (245.0cm)	79 lbs (35.9kg)	875.86	858.34	823.31	656.89
R4CN-5136B	91" (231.1cm) (52 Space)	96.47" (245.0cm)	82 lbs (37.3kg)	952.02	932.98	894.90	714.01

 **Same day shipping**  
 Orders placed before 4:00 EST ship the same day.

