



Item #	Code	Description	Shipping Weight	1-9	10-24	25-49	100-249
--------	------	-------------	-----------------	-----	-------	-------	---------

**RoHS Top Plate Options - For WRKSA, WRK and DRK Series Enclosures**

MW-10FT	A	10" (25.4cm) Fan Top (Excluding Fan)	11 lbs (5.0kg)	53.26	52.19	50.06	39.95
MW-10FT-FC	B	Integrated 10" (25.4cm) Fan Top, Includes 1 Fan and Proportional Speed Fan Control	15 lbs (6.9kg)	529.62	519.03	497.84	397.22
MW-10FT-550CFM	B	Integrated 10" (25.4cm) Fan Top, Includes 1 Fan, 550 CFM	16 lbs (7.3kg)	399.65	391.66	375.67	299.74
MW-4FT	C	4.5" (11.4cm) Fan Top (Excluding Fans)	13 lbs (5.9kg)	53.26	52.19	50.06	39.95
MW-4FT-380CFM	D	Integrated 4.5" (11.4cm) Fan Top, Includes 4 Fans	18 lbs (8.2kg)	368.91	361.53	346.78	276.68
MW-4QFTFC	D	Integrated 4.5" (11.4cm) Fan Top, Includes 4 Quiet Fans	16 lbs (7.3kg)	632.09	619.45	594.16	474.07
MW-6FT	N/A	6" (15.2cm) Fan Top (Excluding Fans)	13 lbs (5.9kg)	51.44	50.41	48.35	38.58
MW-6FT-660CFM	N/A	Integrated 6" (15.2cm) Fan Top, Includes 3 Fans	14 lbs (6.4kg)	465.34	456.03	437.42	349.00
MW-LVT	N/A	64% Open Area Top	10 lbs (4.5kg)	80.41	78.80	75.59	60.31
MW-VT	E	Vented Top Plate	12 lbs (5.5kg)	53.26	52.19	50.06	39.95
MW-ST	F	Solid Top Plate	12 lbs (5.5kg)	53.26	52.19	50.06	39.95

**RoHS Top Options Server Cabinet**

ERK-4FT	N/A	4.5" (11.4cm) Fan Top (Excluding Fans)	6 lbs (2.7kg)	42.89	42.03	40.32	32.17
ERK-4FT-285CFM	N/A	Integrated 4.5" (11.4cm) Fan Top, Includes 3 Fans	11 lbs (5.0kg)	290.21	284.41	272.80	217.66
ERK-4QFT-FC	N/A	Integrated 4.5" (11.4cm) Fan Top, Includes 3 Quiet Fans	11 lbs (5.0kg)	523.10	512.64	491.71	392.33
ERK-6FT	N/A	6" (15.2cm) Fan Top (Excluding Fans)	6 lbs (2.7kg)	41.45	40.62	38.96	31.09
ERK-6FT-440CFM	N/A	Integrated 6" (15.2cm) Fan Top, Includes 2 Fans	9 lbs (4.1kg)	333.67	327.00	313.65	250.25
ERK-ST	N/A	Solid Top for any WMRK, ERK or SCRK Series Rack	6 lbs (2.7kg)	42.89	42.03	40.32	32.17
ERK-VT	N/A	Vented Top for any WMRK, ERK or SCRK Series Rack	6 lbs (2.7kg)	42.89	42.03	40.32	32.17

**RoHS Solid Front Door Options - For WRKSA and WRK Series Enclosures**

FD-24	G	Solid Front Door for 42" (106.7cm) Enclosures	23 lbs (10.5kg)	189.19	185.41	177.84	141.89
FD-37	G	Solid Front Door for 64.75" (164.5cm) Enclosures	44 lbs (20.0kg)	237.11	232.37	222.88	177.83
FD-40	G	Solid Front Door for 70" (177.8cm) Enclosures	46 lbs (20.9kg)	244.70	239.81	230.02	183.52
FD-44	G	Solid Front Door for 77" (195.6cm) Enclosures	52 lbs (23.6kg)	252.27	247.22	237.13	189.20

**RoHS Plexi Front Door Options - For WRKSA and WRK Series Enclosures**

PFD-24	H	Plexi Front Door for 42" (106.7cm) Enclosures	19 lbs (8.6kg)	329.89	323.29	310.10	247.42
PFD-37	H	Plexi Front Door for 64.75" (164.5cm) Enclosures	50 lbs (22.7kg)	501.01	490.99	470.95	375.76
PFD-40	H	Plexi Front Door for 70" (177.8cm) Enclosures	52 lbs (23.6kg)	531.95	521.31	500.03	398.96
PFD-44	H	Plexi Front Door for 77" (195.6cm) Enclosures	58 lbs (26.4kg)	569.06	557.68	534.92	426.79

**RoHS Vented Front Door Options - For WRKSA and WRK Series Enclosures**

VFD-24	I	Vented Front Door for 42" (106.7cm) Enclosures	20 lbs (9.1kg)	264.89	259.59	249.00	198.67
VFD-37	I	Vented Front Door for 64.75" (164.5cm) Enclosures	38 lbs (17.3kg)	327.94	321.38	308.26	245.95
VFD-40	I	Vented Front Door for 70" (177.8cm) Enclosures	44 lbs (20.0kg)	348.14	341.18	327.25	261.11
VFD-44	I	Vented Front Door for 77" (195.6cm) Enclosures	48 lbs (21.8kg)	378.39	370.82	355.69	283.79

**RoHS Vented Plexi Front Door Options - For WRKSA and WRK Series Enclosures**

PVFD-44	J	Vented Plexi Front Door for 77" (195.6cm) Enclosures	50 lbs (22.7kg)	737.89	723.13	693.62	553.42
---------	---	------------------------------------------------------	-----------------	--------	--------	--------	--------

**RoHS Caster Base Options - For WRKSA and WRK Series Enclosures**

CBS-WRK-27	K	Caster Base for 27" (68.6cm) Depth Enclosures, 1300 lbs (590.9kg) Capacity	24 lbs (10.9kg)	161.91	158.67	152.20	121.43
CBS-WRK-32	K	Caster Base for 32" (81.3cm) Depth Enclosures, 1300 lbs (590.9kg) Capacity	27 lbs (12.3kg)	181.10	177.48	170.23	135.82

**RoHS Rack Rail Options - For WRKSA and WRK Series Enclosures**

WRK-RR24	L	Rail Kit, 10-32 Threads, 24U WRK Series Enclosures	12 lbs (5.5kg)	93.30	91.43	87.70	69.97
WRK-RR37	L	Rail Kit, 10-32 Threads, 37U WRK Series Enclosures	15 lbs (6.8kg)	103.45	101.38	97.24	77.59
WRK-RR40	L	Rail Kit, 10-32 Threads, 40U WRK Series Enclosures	17.25 lbs (7.9kg)	111.00	108.78	104.34	83.25
WRK-RR44	L	Rail Kit, 10-32 Threads, 44U WRK Series Enclosures	20 lbs (9.1kg)	118.54	116.17	111.43	88.91

