



Item #	Code	Description	Spaces	Height	Shipping Weight	1-9	10-24	25-99	100-249
✓RoHS 19" (48.3cm) Relay/Frame Racks – Rugged Telecom Equipment and Patch Panel Mounting									
For the highest quality rack system choose the Middle Atlantic 19" (48.3cm) Relay Rack. Constructed with 11-gauge 10-32 threaded steel side channels, this rack can handle up to 400 lbs (181.8kg) of equipment and cabling. Incorporating a self-squaring, self-leveling design greatly reduces assembly time. Unique gusseted base means no shimming on uneven floors.									
DCR38	A	19" (48.3cm) Relay Rack Kit	38	72.00" (182.9cm)	36 lbs (16.4kg)	257.49	252.34	242.04	193.12
DCR45	A	19" (48.3cm) Relay Rack Kit	45	84.00" (213.4cm)	38 lbs (16.4kg)	273.09	267.63	256.70	204.82

✓RoHS 2 Post Relay Rack									
RLA19-1245B	A	Aluminum Open Frame Rack	45	78.75" (200cm)	39 (17.7kg)	210.17	205.97	197.56	157.63
RLA-CC	A	Cable Management Duct For RLA Series Open Frame Racks	45	77.00" (195.6cm)	20 (9.1kg)	288.32	282.55	271.02	216.24

✓RoHS 19" (48.3cm) Wall Mount Pivoting Rack Cabinets with Security Door									
The DWR series wall mount pivoting rack cabinets allow users an ideal method for securing equipment in a compact, lockable wall cabinet. The Wall Mount Pivoting Rack Cabinets feature fully welded construction with heavy-duty hinges for supporting heavy electronics. With abundant cable lacing points, cable pathways and proper cable bend radius can be maintained throughout the cabinet. Cabinet is shipped fully assembled with a plexiglass front door.									
DWR-1017PD	B	19" (48.3cm) Wall Mount Pivoting Rack Cabinet	10	17.50" (44.5cm)	86 lbs (39.1kg)	630.64	618.03	592.80	472.98
DWR-1617PD	B	19" (48.3cm) Wall Mount Pivoting Rack Cabinet	16	28.00" (71.1cm)	110 lbs (50.0kg)	777.32	761.77	730.68	582.99
DWR-2417PD	B	19" (48.3cm) Wall Mount Pivoting Rack Cabinet	24	42.00" (106.7cm)	138 lbs (62.7kg)	988.34	968.57	929.04	741.25

✓RoHS 19" (48.3cm) Wall Mount Rack Cabinet									
The SBX series wall mount rack cabinet features standard 18-gauge all steel construction and a removable backpan for simpler wall mounting. The backpan and cabinet top/bottom have laser cut electrical knockouts for easier cable installation. A locking front door secures valuable equipment inside and swings a full 180 degrees on a heavy-duty hinge allowing easy access to equipment.									
SBX-10	C	19" (48.3cm) Wall Mount Rack Cabinet	10	17.50" (44.5cm)	50 lbs (22.7kg)	416.24	407.92	391.27	312.18

✓RoHS 19" (48.3cm) Low Profile Wall Mounted Rack Enclosures									
The low profile wall mounted rack enclosures offer a secure housing for rackmountable equipment up to 23" (58.4cm) in depth. The top cover is keyed separately from the hinged door providing user access to equipment controls while restricting access to rear connections within the enclosure. Enclosures are available in 4-8U rack heights and support up to 150lbs (68.2kg).									
WRS-4	D	19" (48.3cm) Low Profile Wall Mounted Rack Enclosure	4	7.00" (17.8cm)	50 lbs (22.7kg)	409.77	401.57	385.18	307.33
WRS-6	D	19" (48.3cm) Low Profile Wall Mounted Rack Enclosure	6	10.50" (26.7cm)	60 lbs (27.3kg)	425.04	416.54	399.54	318.78
WRS-8	D	19" (48.3cm) Low Profile Wall Mounted Rack Enclosure	8	14.00" (35.6cm)	65 lbs (29.5kg)	479.52	469.93	450.75	359.64

✓RoHS Wall Mountable 19" (48.3cm) Relay Racks - Great for Telecom Equipment									
These wall mountable relay racks are especially useful when a stand up 19" (48.3cm) rack can't be used due to floor space limitations. Units come in 12" (30.5cm) or 18" (45.7cm) depths and various rack heights. Rugged steel construction and black powder coat finish. Rack screws included.									
WM812	E	12" (30.5cm) Deep Wall Mount Rack	8	14.00" (35.6cm)	18 lbs (8.2kg)	162.97	159.71	153.19	122.23
WM1512	E	12" (30.5cm) Deep Wall Mount Rack	15	26.25" (66.7cm)	19 lbs (8.6kg)	167.75	164.40	157.69	125.81
WM3012	E	12" (30.5cm) Deep Wall Mount Rack	30	52.50" (133.4cm)	28 lbs (12.7kg)	196.54	192.61	184.75	147.41
WM818	E	18" (45.7cm) Deep Wall Mount Rack	8	14.00" (35.6cm)	23 lbs (10.5kg)	186.93	183.19	175.71	140.20
WM1518	E	18" (45.7cm) Deep Wall Mount Rack	15	26.25" (66.7cm)	23 lbs (10.5kg)	203.70	199.63	191.48	152.77
WM3018	E	18" (45.7cm) Deep Wall Mount Rack	30	52.50" (133.4cm)	28 lbs (12.7kg)	227.69	223.14	214.03	170.77

✓RoHS 19" (48.3cm) Swing Frame Wall Racks - Sturdy, Effective Wall or Corner Mounting Device									
These swing gate wall racks are available in two heights with 12" (30.5cm) and 18" (45.7cm) depths. Rails are 10-32 thread with standard EIA hole spacing. Nominal 150 lb (68.2kg) capacity. They have convenient tie points and velcro loops for maximum internal cable management. EIA, TIA, RETMA compliant.									
DSGR12-12	F	12" (30.5cm) Deep Swing Gate Rack	12	24.50" (62.2cm)	35 lbs (15.9kg)	308.64	302.47	290.12	231.48
DSGR20-12	F	12" (30.5cm) Deep Swing Gate Rack	20	38.50" (97.8cm)	42 lbs (19.1kg)	343.81	336.93	323.18	257.86
DSGR12-18	F	18" (45.7cm) Deep Swing Gate Rack	12	24.50" (62.2cm)	38 lbs (17.3kg)	330.32	323.71	310.50	247.74
DSGR20-18	F	18" (45.7cm) Deep Swing Gate Rack	20	38.50" (97.8cm)	44 lbs (20.0kg)	392.55	384.70	369.00	294.41
SFR-12-18	F	Swing Frame Rack, 18" (45.7cm) Deep	12	21.00" (53.3cm)	38 lbs (17.3kg)	223.28	218.81	209.88	167.46
SFR-20-18	F	Swing Frame Rack, 18" (45.7cm) Deep	20	35.00" (88.9cm)	46 lbs (20.9kg)	283.72	278.05	266.70	212.79
SFR-25-18	F	Swing Frame Rack, 18" (45.7cm) Deep	25	44.00" (111.8cm)	30 lbs (13.6kg)	321.45	315.02	302.16	241.09
SFR-12-24	F	Swing Frame Rack, 24" (61.0cm) Deep	12	21.00" (53.3cm)	44 lbs (20.0kg)	256.45	251.32	241.06	192.34
SFR-20-24	F	Swing Frame Rack, 24" (61.0cm) Deep	20	35.00" (88.9cm)	43 lbs (19.5kg)	332.30	325.65	312.36	249.23
SFR-25-24	F	Swing Frame Rack, 24" (61.0cm) Deep	25	44.00" (111.8cm)	51 lbs (23.2kg)	373.84	366.36	351.41	280.38

✓RoHS 19" (48.3cm) Pivoting Panel Mount Cabinets - Handy Wall Mounting Allows Rear Access									
Conserve valuable floor space with these pivoting panel mount cabinets. The pivoting feature allows punching down while fully open. Rails are tapped 10-32 with standard EIA hole spacing. Available in four basic heights and 6" (15.2cm) or 12" (30.5cm) depth. Other features include: numerous cable tie points and velcro cable loops. Made of .060" (0.2cm) steel and .125" (0.3cm) thick tapped rails.									
DPPM2	G	6" (15.2cm) Pivoting Panel Wall Mount Cabinet	2	3.50" (8.9cm)	8 lbs (3.6kg)	83.27	81.60	78.27	62.45
DPPM4	G	6" (15.2cm) Pivoting Panel Wall Mount Cabinet	4	7.00" (17.8cm)	10 lbs (4.5kg)	95.87	93.95	90.12	71.90
DPPM6	G	6" (15.2cm) Pivoting Panel Wall Mount Cabinet	6	10.50" (26.7cm)	12 lbs (5.5kg)	103.45	101.38	97.24	77.59
DPPM6-12	G	12" (30.5cm) Pivoting Panel Wall Mount Cabinet	6	10.50" (26.7cm)	19 lbs (8.6kg)	171.56	168.13	161.27	128.67
DPPM8-12	G	12" (30.5cm) Pivoting Panel Wall Mount Cabinet	8	14.00" (35.6cm)	21 lbs (9.5kg)	184.15	180.47	173.10	138.11

Custom design and manufacturing capabilities

Our product design process takes you from concept to production. L-com.com/Custom

